

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P601330

Luminaire Tested: **ML4DM06AWW9FS1E - TIR4D25AWW - TL45R6G_ TL46S6G_ 3000K**

Issue Date: 7/29/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P601330
 Test Lab: COOPER LIGHTING SOLUTIONS
 Issue Date: 7/29/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO
 Catalog Number: ML4DM06AWW9FS1E - TIR4D25AWW - TL45R6G_ TL46S6G_ 3000K
 Description: DIRECT MOUNT, 25D WW OPTIC, LINEAR SPREAD LENS TRIM
 Light Source: (1) SELECTABLE LUMEN LED 90CRI / 3000K CCT
 Ballast/Driver: -

Summary

Lumens per Lamp: N/A
 Luminaire Lumens: 611.5 lumens
 Efficiency: N/A
 Efficacy: 73.7 lumens/watt
 Spacing Criteria (0/90/45): 1.21 / 0.78 / 1
 Luminous Opening: Circular (Dia: 0.21' x H: 0')
 CIE Type: Direct


Input Watts (W): 8.3
 Input Voltage (V): NR
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT



Meas			
Instrument	Identificatio		Calibration Due Date
Photometer	GONIO 1 11111111	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P601330
CATALOG NUMBER: ML4DM06AWW9FS1E - TIR4D25AWW - TL45R6G_ TL46S6G_ 3000K

Luminous Intensity Polar Plot



TEST NUMBER: P601330
 CATALOG NUMBER: ML4DM06AWW9FS1E - TIR4D25AWW - TL45R6G_ TL46S6G_ 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.8	7.7
10°-20°	127.4	20.8
20°-30°	166.5	27.2
30°-40°	142.7	23.3
40°-50°	81.6	13.4
50°-60°	33.4	5.5
60°-70°	10.7	1.7
70°-80°	2.3	0.4
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	340.6	55.7
0°-40°	483.3	79.0
0°-60°	598.4	97.8
0°-90°	611.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	611.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	494	494	494	494	494	
5°	606	569	488	413	394	63
15°	850	670	387	233	193	240
25°	860	592	255	122	102	394
35°	589	389	137	64	63	363
45°	259	176	59	32	39	197
55°	74	60	21	15	21	70
65°	16	14	9	6	7	17
75°	2	2	2	1	0	3
85°	0	0	0	0	0	0
90°	0	0	0	0	0	

TEST NUMBER: P601330

CATALOG NUMBER: ML4DM06AWW9FS1E - TIR4D25AWW - TL45R6G_ TL46S6G_ 3000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	45°	67.5°	90°	112.5°	135°
0°	493.9	493.9	493.9	493.9	493.9	493.9	493.9	493.9	493.9	493.9	493.9
2.5°	542.0	553.1	549.4	555.5	554.3	543.2	532.1	514.9	497.6	487.8	465.6
5°	606.0	619.6	629.4	622.0	618.4	609.7	569.1	530.9	487.8	444.7	412.6
7.5°	689.8	686.1	697.2	675.0	676.2	672.5	613.4	539.5	473.0	410.2	364.6
10°	755.1	744.0	755.1	747.7	732.9	715.7	644.2	535.8	454.5	375.7	314.1
12.5°	803.1	817.9	817.9	800.7	785.9	766.2	667.6	533.4	422.5	333.8	271.0
15°	849.9	854.9	846.2	832.7	817.9	777.3	670.1	517.3	386.8	293.2	232.8
17.5°	880.7	882.0	878.3	865.9	845.0	820.4	654.1	502.6	353.5	261.1	195.9
20°	893.0	883.2	882.0	859.8	841.3	819.1	640.5	466.8	324.0	223.0	170.0
22.5°	912.7	889.3	889.3	867.2	829.0	825.3	633.1	426.2	283.3	190.9	145.3
25°	859.8	856.1	863.5	832.7	803.1	797.0	592.5	395.4	255.0	165.1	121.9
27.5°	824.1	814.2	804.3	784.6	756.3	741.5	559.2	356.0	221.7	138.0	103.5
30°	751.4	751.4	739.1	729.2	691.0	679.9	500.1	319.0	189.7	118.3	86.2
32.5°	671.3	660.2	661.5	650.4	627.0	618.4	444.7	278.4	163.8	96.1	75.1
35°	588.8	576.5	570.3	561.7	558.0	530.9	389.2	240.2	136.7	83.8	64.1
37.5°	507.5	495.2	490.2	476.7	457.0	450.8	328.9	199.5	114.6	69.0	53.0
40°	395.4	395.4	394.2	379.4	373.2	369.5	272.2	166.3	93.6	55.4	45.6
42.5°	315.3	319.0	316.6	310.4	296.9	294.4	226.6	135.5	76.4	46.8	38.2
45°	258.7	247.6	245.1	243.9	236.5	235.3	176.1	107.2	59.1	38.2	32.0
47.5°	189.7	188.5	190.9	184.8	176.1	183.5	139.2	81.3	46.8	30.8	27.1
50°	138.0	140.4	140.4	134.3	131.8	134.3	107.2	61.6	34.5	24.6	23.4
52.5°	103.5	102.2	101.0	102.2	101.0	101.0	80.1	45.6	27.1	19.7	18.5
55°	73.9	73.9	72.7	75.1	76.4	73.9	60.4	33.3	20.9	16.0	14.8
57.5°	51.7	51.7	49.3	51.7	51.7	54.2	43.1	24.6	17.2	12.3	12.3
60°	34.5	34.5	34.5	35.7	37.0	37.0	29.6	17.2	13.5	9.9	9.9
62.5°	23.4	23.4	23.4	24.6	24.6	27.1	20.9	13.5	11.1	8.6	7.4
65°	16.0	16.0	16.0	16.0	17.2	17.2	13.5	9.9	8.6	7.4	6.2
67.5°	9.9	11.1	9.9	11.1	11.1	11.1	8.6	7.4	6.2	4.9	3.7
70°	7.4	7.4	7.4	7.4	7.4	7.4	6.2	6.2	4.9	3.7	2.5
72.5°	4.9	4.9	4.9	4.9	4.9	4.9	3.7	3.7	3.7	2.5	2.5
75°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	1.2	1.2
77.5°	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	0.0
80°	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	0.0	0.0
82.5°	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P601330
 CATALOG NUMBER: ML4DM06AWW9FS1E - TIR4D25AWW - TL45R6G_ TL46S6G_ 3000K

CANDELA DISTRIBUTION (continued):

	157.5°	180°
0°	493.9	493.9
2.5°	453.3	444.7
5°	384.3	394.2
7.5°	335.0	322.7
10°	280.8	273.5
12.5°	243.9	240.2
15°	202.0	193.4
17.5°	173.7	165.1
20°	145.3	139.2
22.5°	124.4	120.7
25°	107.2	102.2
27.5°	92.4	89.9
30°	80.1	80.1
32.5°	69.0	71.4
35°	61.6	62.8
37.5°	53.0	55.4
40°	49.3	51.7
42.5°	41.9	46.8
45°	35.7	39.4
47.5°	30.8	34.5
50°	25.9	29.6
52.5°	23.4	25.9
55°	19.7	20.9
57.5°	16.0	17.2
60°	12.3	13.5
62.5°	9.9	11.1
65°	7.4	7.4
67.5°	4.9	6.2
70°	2.5	3.7
72.5°	1.2	1.2
75°	1.2	0.0
77.5°	0.0	0.0
80°	0.0	0.0
82.5°	0.0	0.0
85°	0.0	0.0
87.5°	0.0	0.0
90°	0.0	0.0

(END OF REPORT)