

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: HALO

Report Number: P601332

Luminaire Tested: **ML4DM06AWW9FS1E - TIR4D25AWW - TL45R6G\_ TL46S6G\_ 4000K**

Issue Date: 7/29/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

**Test Information**

Test Method: LM-79-08  
 Report Number: P601332  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Issue Date: 7/29/2022  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: HALO  
 Catalog Number: ML4DM06AWW9FS1E - TIR4D25AWW - TL45R6G\_ TL46S6G\_ 4000K  
 Description: DIRECT MOUNT, 25D WW OPTIC, LINEAR SPREAD LENS TRIM  
 Light Source: (1) SELECTABLE LUMEN LED 90CRI / 4000K CCT  
 Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
 Luminaire Lumens: 644.4 lumens  
 Efficiency: N/A  
 Efficacy: 77.6 lumens/watt  
 Spacing Criteria (0/90/45): 1.21 / 0.78 / 1  
 Luminous Opening: Circular (Dia: 0.21' x H: 0')  
 CIE Type: Direct


Input Watts (W): 8.3  
 Input Voltage (V): NR  
 Input Current (Ain): NR  
 Voltage Rise (V): NR  
 Power Factor: NR  
 Total Harmonic Distortion (THDi): NR  
 Frequency (hertz): 60  
 Stabilization Time: NR  
 Operation Time: NR  
 Ambient Temperature (°C): NR  
 Test Distance: 25 FT



Meas			
Instrument	Identificatio		Calibration Due Date
Photometer	GONIO 1 11111111	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P601332  
CATALOG NUMBER: ML4DM06AWW9FS1E - TIR4D25AWW - TL45R6G\_ TL46S6G\_ 4000K

### Luminous Intensity Polar Plot



TEST NUMBER: P601332

CATALOG NUMBER: ML4DM06AWW9FS1E - TIR4D25AWW - TL45R6G\_ TL46S6G\_ 4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76
4	94	85	79	74	92	84	78	73	82	76	72	79	75	72	78	74	71	69
5	88	78	72	67	86	77	71	67	76	70	66	74	69	65	72	68	65	63
6	83	73	66	61	81	72	65	61	70	65	60	69	64	60	67	63	59	58
7	78	68	61	56	77	67	60	56	65	60	55	64	59	55	63	58	55	53
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49
9	70	59	52	48	68	58	52	48	57	52	47	56	51	47	55	51	47	46
10	66	55	49	44	65	55	48	44	54	48	44	53	48	44	52	47	44	42

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	164356	164356	164356
5°	202418	162923	131670
10°	255130	153585	92407
15°	292775	133246	66623
20°	316205	114721	49296
25°	315658	93617	37524
30°	288702	72886	30773
35°	239151	55547	25519
40°	171765	40643	22465
45°	121732	27821	18532
50°	71427	17832	15327
55°	42885	12166	12166
60°	22925	9031	9031
65°	12627	6799	5828
70°	7201	4801	3601
75°	3172	3172	0
80°	2364	2364	0
85°	0	0	0

TEST NUMBER: P601332

CATALOG NUMBER: ML4DM06AWW9FS1E - TIR4D25AWW - TL45R6G\_ TL46S6G\_ 4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	49.3	7.7
10°-20°	134.2	20.8
20°-30°	175.4	27.2
30°-40°	150.4	23.3
40°-50°	86.0	13.3
50°-60°	35.2	5.5
60°-70°	11.3	1.7
70°-80°	2.4	0.4
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
<b>0°-30°</b>	<b>358.9</b>	<b>55.7</b>
<b>0°-40°</b>	<b>509.3</b>	<b>79.0</b>
<b>0°-60°</b>	<b>630.5</b>	<b>97.8</b>
<b>0°-90°</b>	<b>644.4</b>	<b>100.0</b>
90°-120°	0.0	0.0
90°-150°	0.0	0.0
<b>90°-180°</b>	<b>0.0</b>	<b>0.0</b>
<b>0°-180°</b>	<b>644.4</b>	<b>100.0</b>

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	520	520	520	520	520	
5°	639	600	514	435	415	66
15°	896	706	408	245	204	253
25°	906	624	269	128	108	415
35°	620	410	144	68	66	383
45°	273	186	62	34	42	207
55°	78	64	22	16	22	74
65°	17	14	9	6	8	18
75°	3	3	3	1	0	4
85°	0	0	0	0	0	1
90°	0	0	0	0	0	

TEST NUMBER: P601332

CATALOG NUMBER: ML4DM06AWW9FS1E - TIR4D25AWW - TL45R6G\_ TL46S6G\_ 4000K

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	45°	67.5°	90°	112.5°	135°
0°	520.5	520.5	520.5	520.5	520.5	520.5	520.5	520.5	520.5	520.5	520.5
2.5°	571.1	582.8	578.9	585.4	584.1	572.4	560.7	542.6	524.4	514.0	490.6
5°	638.6	652.9	663.3	655.5	651.6	642.5	599.7	559.4	514.0	468.6	434.8
7.5°	726.9	723.0	734.7	711.3	712.6	708.7	646.4	568.5	498.4	432.2	384.2
10°	795.7	784.0	795.7	787.9	772.3	754.1	678.8	564.6	479.0	395.9	331.0
12.5°	846.3	861.9	861.9	843.7	828.1	807.3	703.5	562.0	445.2	351.8	285.6
15°	895.6	900.8	891.7	877.4	861.9	819.0	706.1	545.2	407.6	308.9	245.3
17.5°	928.1	929.4	925.5	912.5	890.4	864.5	689.2	529.6	372.5	275.2	206.4
20°	941.0	930.7	929.4	906.0	886.5	863.2	675.0	491.9	341.4	234.9	179.1
22.5°	961.8	937.1	937.1	913.8	873.5	869.6	667.2	449.1	298.5	201.2	153.2
25°	906.0	902.1	909.9	877.4	846.3	839.8	624.3	416.7	268.7	173.9	128.5
27.5°	868.4	858.0	847.6	826.8	797.0	781.4	589.3	375.1	233.6	145.4	109.0
30°	791.8	791.8	778.8	768.4	728.2	716.5	527.0	336.2	199.9	124.6	90.9
32.5°	707.4	695.7	697.0	685.3	660.7	651.6	468.6	293.3	172.6	101.2	79.2
35°	620.4	607.5	601.0	591.9	588.0	559.4	410.2	253.1	144.1	88.3	67.5
37.5°	534.8	521.8	516.6	502.3	481.6	475.1	346.6	210.3	120.7	72.7	55.8
40°	416.7	416.7	415.4	399.8	393.3	389.4	286.9	175.2	98.6	58.4	48.0
42.5°	332.3	336.2	333.6	327.1	312.8	310.2	238.8	142.8	80.5	49.3	40.2
45°	272.6	260.9	258.3	257.0	249.2	247.9	185.6	112.9	62.3	40.2	33.7
47.5°	199.9	198.6	201.2	194.7	185.6	193.4	146.7	85.7	49.3	32.4	28.6
50°	145.4	148.0	148.0	141.5	138.9	141.5	112.9	64.9	36.3	26.0	24.7
52.5°	109.0	107.7	106.4	107.7	106.4	106.4	84.4	48.0	28.6	20.8	19.5
55°	77.9	77.9	76.6	79.2	80.5	77.9	63.6	35.0	22.1	16.9	15.6
57.5°	54.5	54.5	51.9	54.5	54.5	57.1	45.4	26.0	18.2	13.0	13.0
60°	36.3	36.3	36.3	37.6	38.9	38.9	31.2	18.2	14.3	10.4	10.4
62.5°	24.7	24.7	24.7	26.0	26.0	28.6	22.1	14.3	11.7	9.1	7.8
65°	16.9	16.9	16.9	16.9	18.2	18.2	14.3	10.4	9.1	7.8	6.5
67.5°	10.4	11.7	10.4	11.7	11.7	11.7	9.1	7.8	6.5	5.2	3.9
70°	7.8	7.8	7.8	7.8	7.8	7.8	6.5	6.5	5.2	3.9	2.6
72.5°	5.2	5.2	5.2	5.2	5.2	5.2	3.9	3.9	3.9	2.6	2.6
75°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	1.3	1.3
77.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	0.0
80°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	0.0	0.0
82.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P601332  
 CATALOG NUMBER: ML4DM06AWW9FS1E - TIR4D25AWW - TL45R6G\_ TL46S6G\_ 4000K

**CANDELA DISTRIBUTION (continued):**

	157.5°	180°
0°	520.5	520.5
2.5°	477.7	468.6
5°	405.0	415.4
7.5°	353.1	340.1
10°	295.9	288.2
12.5°	257.0	253.1
15°	212.9	203.8
17.5°	183.0	173.9
20°	153.2	146.7
22.5°	131.1	127.2
25°	112.9	107.7
27.5°	97.3	94.8
30°	84.4	84.4
32.5°	72.7	75.3
35°	64.9	66.2
37.5°	55.8	58.4
40°	51.9	54.5
42.5°	44.1	49.3
45°	37.6	41.5
47.5°	32.4	36.3
50°	27.3	31.2
52.5°	24.7	27.3
55°	20.8	22.1
57.5°	16.9	18.2
60°	13.0	14.3
62.5°	10.4	11.7
65°	7.8	7.8
67.5°	5.2	6.5
70°	2.6	3.9
72.5°	1.3	1.3
75°	1.3	0.0
77.5°	0.0	0.0
80°	0.0	0.0
82.5°	0.0	0.0
85°	0.0	0.0
87.5°	0.0	0.0
90°	0.0	0.0

(END OF REPORT)