

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P601434

Luminaire Tested: **ML4DM10LSAWW9FS1E - TIR4D25AWW - TL43R2G_ TL44S2G_ 3500K**

Issue Date: 7/29/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P601434
 Test Lab: COOPER LIGHTING SOLUTIONS
 Issue Date: 7/29/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO
 Catalog Number: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL43R2G_ TL44S2G_ 3500K
 Description: DIRECT MOUNT, 25D WW OPTIC, DIFFUSE CLEAR LENS TRIM
 Light Source: (1) SELECTABLE LUMEN LED 90CRI / 3500K CCT
 Ballast/Driver: -

Summary

Lumens per Lamp: N/A
 Luminaire Lumens: 842.5 lumens
 Efficiency: N/A
 Efficacy: 70.2 lumens/watt
 Spacing Criteria (0/90/45): 1.33 / 0.62 / 0.83
 Luminous Opening: Circular (Dia: 0.21' x H: 0')
 CIE Type: Direct


Input Watts (W): 12
 Input Voltage (V): NR
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT



Meas			
Instrument	Identificatio		Calibration Due Date
Photometer	GONIO 1 11111111	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P601434
CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL43R2G_ TL44S2G_ 3500K

Luminous Intensity Polar Plot



TEST NUMBER: P601434

CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL43R2G_ TL44S2G_ 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85
3	101	94	88	84	99	92	87	83	89	85	82	87	83	80	85	82	79	78
4	95	87	81	76	93	85	80	75	83	78	75	81	77	74	79	76	73	71
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65
6	84	75	68	64	83	74	68	63	72	67	63	71	66	62	70	65	62	60
7	80	70	63	59	78	69	63	58	68	62	58	66	62	58	65	61	57	56
8	76	65	59	54	74	65	58	54	64	58	54	62	57	54	61	57	53	52
9	72	61	55	51	70	61	55	50	60	54	50	59	54	50	58	53	50	48
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	256717	256717	256717
5°	332027	247998	191641
10°	431192	219572	132198
15°	513436	173848	94312
20°	593362	132194	63644
25°	605569	99505	52296
30°	566282	72230	40910
35°	464463	48879	36505
40°	346538	31822	31822
45°	233551	21480	27955
50°	136713	15769	24317
55°	72173	11231	19268
60°	34987	6442	14715
65°	14121	4334	9788
70°	6740	2677	5355
75°	3538	1830	0
80°	2728	2728	0
85°	0	0	0

TEST NUMBER: P601434
 CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL43R2G_ TL44S2G_ 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.5	9.0
10°-20°	195.4	23.2
20°-30°	239.3	28.4
30°-40°	187.6	22.3
40°-50°	96.7	11.5
50°-60°	36.7	4.4
60°-70°	9.4	1.1
70°-80°	1.9	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	510.3	60.6
0°-40°	697.8	82.8
0°-60°	831.2	98.6
0°-90°	842.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	842.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	813	813	813	813	813	
5°	1048	948	782	663	605	109
15°	1571	1000	532	319	288	449
25°	1738	714	286	149	150	789
35°	1205	379	127	70	95	748
45°	523	131	48	38	63	407
55°	131	41	20	18	35	127
65°	19	7	6	6	13	23
75°	3	2	2	2	0	3
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0

TEST NUMBER: P601434

CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL43R2G_ TL44S2G_ 3500K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	45°	67.5°	90°	112.5°	135°
0°	813.0	813.0	813.0	813.0	813.0	813.0	813.0	813.0	813.0	813.0	813.0
2.5°	916.4	912.0	935.4	901.8	880.0	909.1	882.9	852.3	820.3	766.4	738.7
5°	1047.5	1050.5	1054.8	1044.6	1040.3	1037.3	948.5	865.4	782.4	700.8	662.9
7.5°	1197.6	1169.9	1187.4	1148.1	1155.4	1135.0	1009.7	852.3	744.5	639.6	550.7
10°	1344.8	1314.2	1328.7	1292.3	1283.6	1266.1	1044.6	817.3	684.8	543.4	467.7
12.5°	1470.1	1456.9	1442.4	1392.8	1375.4	1327.3	1044.6	770.7	600.3	469.1	381.7
15°	1570.6	1557.5	1541.4	1477.3	1423.4	1381.2	999.5	705.2	531.8	402.1	319.1
17.5°	1653.6	1602.6	1604.1	1512.3	1465.7	1410.3	955.8	638.1	460.4	336.6	271.0
20°	1765.8	1672.6	1656.5	1558.9	1471.5	1410.3	878.5	565.3	393.4	284.1	222.9
22.5°	1748.3	1665.3	1684.2	1540.0	1446.7	1422.0	792.6	488.1	338.0	238.9	179.2
25°	1738.1	1678.4	1646.3	1491.9	1379.7	1301.0	713.9	426.9	285.6	196.7	148.6
27.5°	1694.4	1604.1	1556.0	1400.1	1276.3	1212.2	620.7	361.3	238.9	155.9	125.3
30°	1553.1	1487.5	1436.5	1273.4	1142.2	1081.0	537.6	300.1	198.1	128.2	99.1
32.5°	1400.1	1343.3	1264.6	1130.6	980.5	920.8	445.8	256.4	161.7	102.0	83.0
35°	1204.9	1158.3	1084.0	948.5	804.2	778.0	378.8	205.4	126.8	81.6	69.9
37.5°	1015.5	974.7	898.9	776.5	664.4	626.5	306.0	164.6	102.0	67.0	59.7
40°	840.7	792.6	743.0	623.6	531.8	491.0	234.6	128.2	77.2	53.9	51.0
42.5°	668.7	639.6	585.7	498.3	407.9	381.7	174.8	96.2	61.2	45.2	43.7
45°	523.0	492.4	441.5	383.2	307.4	287.0	131.1	74.3	48.1	36.4	37.9
47.5°	381.7	367.1	333.6	284.1	234.6	211.3	99.1	58.3	37.9	30.6	32.1
50°	278.3	263.7	247.7	202.5	163.2	157.3	74.3	45.2	32.1	24.8	26.2
52.5°	192.3	190.9	173.4	144.2	119.5	109.3	56.8	35.0	26.2	20.4	21.9
55°	131.1	129.7	118.0	100.5	84.5	77.2	40.8	26.2	20.4	16.0	17.5
57.5°	84.5	86.0	78.7	68.5	55.4	51.0	27.7	18.9	14.6	11.7	13.1
60°	55.4	55.4	48.1	43.7	35.0	32.1	18.9	13.1	10.2	8.7	10.2
62.5°	33.5	35.0	30.6	24.8	21.9	18.9	11.7	8.7	7.3	5.8	7.3
65°	18.9	20.4	17.5	14.6	13.1	11.7	7.3	5.8	5.8	4.4	5.8
67.5°	11.7	11.7	10.2	8.7	7.3	7.3	4.4	4.4	4.4	4.4	4.4
70°	7.3	7.3	5.8	5.8	4.4	4.4	2.9	4.4	2.9	2.9	2.9
72.5°	4.4	4.4	2.9	2.9	2.9	2.9	2.9	2.9	2.9	1.5	1.5
75°	2.9	2.9	2.9	2.9	1.5	1.5	1.5	1.5	1.5	1.5	1.5
77.5°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	0.0
80°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P601434
 CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL43R2G_ TL44S2G_ 3500K

CANDELA DISTRIBUTION (continued):

	157.5°	180°
0°	813.0	813.0
2.5°	721.2	724.1
5°	622.1	604.6
7.5°	517.2	489.5
10°	418.1	412.3
12.5°	352.6	345.3
15°	295.8	288.5
17.5°	247.7	234.6
20°	206.9	189.4
22.5°	171.9	173.4
25°	147.2	150.1
27.5°	126.8	129.7
30°	106.4	112.2
32.5°	96.2	104.9
35°	83.0	94.7
37.5°	74.3	86.0
40°	65.6	77.2
42.5°	58.3	69.9
45°	51.0	62.6
47.5°	45.2	56.8
50°	37.9	49.5
52.5°	32.1	42.3
55°	26.2	35.0
57.5°	21.9	29.1
60°	17.5	23.3
62.5°	13.1	17.5
65°	8.7	13.1
67.5°	5.8	8.7
70°	4.4	5.8
72.5°	1.5	2.9
75°	0.0	0.0
77.5°	0.0	0.0
80°	0.0	0.0
82.5°	0.0	0.0
85°	0.0	0.0
87.5°	0.0	0.0
90°	0.0	0.0

(END OF REPORT)