

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P885657

Luminaire Tested: ML104LSFL95FS1E-TIR1D25NFL-TL1SDMBB-340LM-5000K

Issue Date: 6/19/2024

Test Information

Test Method: LM-79-2019
Report Number: P885657
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2402-314-141)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 6/19/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML104LSFL95FS1E-TIR1D25NFL-TL1SDMBB-340LM-5000K
Description: 1IN SQUARE ML FLEX, SELECTABLE CCT, WITH 25D TIR, MATTE BLACK BAFFLED TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 95CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 318.7 lumens
Efficiency: N/A
Efficacy: 52.2 lumens/watt
Spacing Criteria (0/90/45): 0.46 / 0.47 / 0.55
Luminous Opening: Rectangular (W 0.08' x L: 0.08' x H: 0')
CIE Type: Direct

Input Watts (W): 6.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P885657
CATALOG NUMBER: ML104LSFL95FS1E-TIR1D25NFL-TL1SDMBB-340LM-5000K

Luminous Intensity Polar Plot





TEST NUMBER: P885657

CATALOG NUMBER: ML104LSFL95FS1E-TIR1D25NFL-TL1SDMBB-340LM-5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100														
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95					95														
2	110	106	102	100	108	104	101	98	101	99	96	98	96	94	95	94	92	91					91														
3	106	100	96	93	104	99	95	92	96	93	91	94	92	89	92	90	88	87					87														
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	89	86	84	83					83														
5	98	91	86	83	96	90	86	82	88	84	81	87	83	81	85	82	80	79					79														
6	94	87	82	78	93	86	81	78	85	81	78	83	80	77	82	79	77	75					75														
7	91	83	78	75	89	82	78	75	81	77	74	80	77	74	79	76	73	72					72														
8	87	80	75	71	86	79	75	71	78	74	71	77	73	71	76	73	70	69					69														
9	84	77	72	68	83	76	72	68	75	71	68	74	71	68	74	70	68	67					67														
10	82	74	69	66	81	73	69	66	73	68	66	72	68	65	71	68	65	64					64														

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1477785	1477785	1477785
5°	1315856	1321302	1312122
10°	1013924	1021322	1024942
15°	691623	725483	717940
20°	454105	539054	469446
25°	240462	370612	244395
30°	111147	201174	108999
35°	59794	73229	59794
40°	40266	49776	42694
45°	25647	38580	25647
50°	5546	28213	5546
55°	3243	3243	3243
60°	3720	0	3720
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 38580 cd/sqm



TEST NUMBER: P885657

CATALOG NUMBER: ML104LSFL95FS1E-TIR1D25NFL-TL1SDMBB-340LM-5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.7	23.5
10°-20°	124.8	39.2
20°-30°	80.8	25.3
30°-40°	26.2	8.2
40°-50°	10.3	3.2
50°-60°	1.7	0.5
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	280.3	88.0
0°-40°	306.5	96.2
0°-60°	318.5	100.0
0°-90°	318.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	318.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	953	953	953	953	953	
5°	846	849	849	843	843	75
15°	431	443	452	450	447	121
25°	141	169	217	170	143	68
35°	32	40	39	39	32	21
45°	12	13	18	14	12	8
55°	1	1	1	1	1	1
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P885657

CATALOG NUMBER: ML104LSFL95FS1E-TIR1D25NFL-TL1SDMBB-340LM-5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	953.4	953.4	953.4	953.4	953.4
2.5°	933.5	931.2	933.5	930.0	930.0
5°	845.7	849.2	849.2	843.3	843.3
7.5°	760.2	757.8	755.5	750.8	754.3
10°	644.2	641.9	648.9	652.4	651.2
12.5°	535.3	535.3	540.0	550.5	541.1
15°	431.0	442.7	452.1	449.8	447.4
17.5°	352.6	364.3	385.4	373.6	359.6
20°	275.3	296.3	326.8	301.0	284.6
22.5°	207.3	231.9	272.9	235.4	210.8
25°	140.6	168.7	216.7	169.8	142.9
27.5°	92.5	111.3	165.2	114.8	94.9
30°	62.1	77.3	112.4	76.1	60.9
32.5°	41.0	56.2	65.6	55.1	42.2
35°	31.6	39.8	38.7	38.7	31.6
37.5°	24.6	29.3	29.3	28.1	25.8
40°	19.9	21.1	24.6	21.1	21.1
42.5°	15.2	17.6	21.1	17.6	16.4
45°	11.7	12.9	17.6	14.1	11.7
47.5°	3.5	8.2	15.2	8.2	3.5
50°	2.3	2.3	11.7	2.3	2.3
52.5°	2.3	1.2	5.9	1.2	2.3
55°	1.2	1.2	1.2	1.2	1.2
57.5°	1.2	1.2	1.2	1.2	1.2
60°	1.2	0.0	0.0	1.2	1.2
62.5°	1.2	0.0	0.0	0.0	1.2
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)