

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P601437

Luminaire Tested: **ML4DM10LSAWW9FS1E - TIR4D25AWW - TL45R6G_ TL46S6G_ 2700K**

Issue Date: 7/29/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P601437
 Test Lab: COOPER LIGHTING SOLUTIONS
 Issue Date: 7/29/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO
 Catalog Number: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL45R6G_ TL46S6G_ 2700K
 Description: DIRECT MOUNT, 25D WW OPTIC, LINEAR SPREAD LENS TRIM
 Light Source: (1) SELECTABLE LUMEN LED 90CRI / 2700K CCT
 Ballast/Driver: -

Summary

Lumens per Lamp: N/A
 Luminaire Lumens: 836.3 lumens
 Efficiency: N/A
 Efficacy: 69.7 lumens/watt
 Spacing Criteria (0/90/45): 1.21 / 0.78 / 1
 Luminous Opening: Circular (Dia: 0.21' x H: 0')
 CIE Type: Direct


Input Watts (W): 12
 Input Voltage (V): NR
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT



Meas		Calibration Due Date	
Instrument	Identificatio		
Photometer	GONIO 1 11111111	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P601437
CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL45R6G_ TL46S6G_ 2700K

Luminous Intensity Polar Plot



TEST NUMBER: P601437

CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL45R6G_ TL46S6G_ 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76
4	94	85	79	74	92	84	78	73	82	76	72	79	75	72	78	74	71	69
5	88	78	72	67	86	77	71	67	76	70	66	74	69	65	72	68	65	63
6	83	73	66	61	81	72	65	61	70	65	60	69	64	60	67	63	59	58
7	78	68	61	56	77	67	60	56	65	60	55	64	59	55	63	58	55	53
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49
9	70	59	52	48	68	58	52	48	57	52	47	56	51	47	55	51	47	46
10	66	55	49	44	65	55	48	44	54	48	44	53	48	44	52	47	44	42

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	213299	213299	213299
5°	262706	211420	170848
10°	331089	199308	119886
15°	379961	172900	86466
20°	410360	148861	63947
25°	409624	121490	48707
30°	374641	94581	39925
35°	310387	72084	33113
40°	222878	52762	29143
45°	157948	36127	24070
50°	92698	23187	19846
55°	55658	15745	15745
60°	29808	11683	11683
65°	16363	8817	7546
70°	9325	6186	4709
75°	4148	4148	0
80°	3091	3091	0
85°	0	0	0

TEST NUMBER: P601437

CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL45R6G_ TL46S6G_ 2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.0	7.7
10°-20°	174.2	20.8
20°-30°	227.6	27.2
30°-40°	195.2	23.3
40°-50°	111.6	13.4
50°-60°	45.6	5.5
60°-70°	14.6	1.7
70°-80°	3.1	0.4
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	465.8	55.7
0°-40°	661.0	79.0
0°-60°	818.2	97.8
0°-90°	836.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	836.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	676	676	676	676	676	
5°	829	778	667	564	539	86
15°	1162	916	529	318	264	328
25°	1176	810	349	167	140	538
35°	805	532	187	88	86	497
45°	354	241	81	44	54	269
55°	101	82	29	20	29	96
65°	22	18	12	8	10	24
75°	3	3	3	2	0	5
85°	0	0	0	0	0	1
90°	0	0	0	0	0	

TEST NUMBER: P601437

CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL45R6G_ TL46S6G_ 2700K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	45°	67.5°	90°	112.5°	135°
0°	675.5	675.5	675.5	675.5	675.5	675.5	675.5	675.5	675.5	675.5	675.5
2.5°	741.2	756.3	751.3	759.7	758.0	742.8	727.7	704.1	680.5	667.0	636.7
5°	828.8	847.3	860.8	850.6	845.6	833.8	778.2	726.0	667.0	608.1	564.3
7.5°	943.3	938.2	953.4	923.1	924.8	919.7	838.9	737.8	646.8	560.9	498.6
10°	1032.6	1017.4	1032.6	1022.5	1002.2	978.7	881.0	732.7	621.6	513.8	429.5
12.5°	1098.3	1118.5	1118.5	1094.9	1074.7	1047.7	913.0	729.4	577.8	456.5	370.6
15°	1162.3	1169.0	1157.2	1138.7	1118.5	1062.9	916.3	707.5	528.9	400.9	318.4
17.5°	1204.4	1206.1	1201.0	1184.2	1155.5	1121.8	894.4	687.3	483.4	357.1	267.8
20°	1221.2	1207.8	1206.1	1175.7	1150.5	1120.2	875.9	638.4	443.0	304.9	232.5
22.5°	1248.2	1216.2	1216.2	1185.9	1133.6	1128.6	865.8	582.8	387.4	261.1	198.8
25°	1175.7	1170.7	1180.8	1138.7	1098.3	1089.8	810.2	540.7	348.7	225.7	166.8
27.5°	1126.9	1113.4	1099.9	1073.0	1034.3	1014.0	764.7	486.8	303.2	188.7	141.5
30°	1027.5	1027.5	1010.7	997.2	945.0	929.8	683.9	436.3	259.4	161.7	117.9
32.5°	918.0	902.9	904.6	889.4	857.4	845.6	608.1	380.7	224.0	131.4	102.8
35°	805.2	788.3	779.9	768.1	763.1	726.0	532.3	328.5	187.0	114.5	87.6
37.5°	694.0	677.2	670.4	651.9	624.9	616.5	449.7	272.9	156.7	94.3	72.4
40°	540.7	540.7	539.0	518.8	510.4	505.3	372.3	227.4	128.0	75.8	62.3
42.5°	431.2	436.3	432.9	424.5	406.0	402.6	309.9	185.3	104.4	64.0	52.2
45°	353.7	338.6	335.2	333.5	323.4	321.7	240.9	146.5	80.9	52.2	43.8
47.5°	259.4	257.7	261.1	252.7	240.9	251.0	190.3	111.2	64.0	42.1	37.1
50°	188.7	192.0	192.0	183.6	180.2	183.6	146.5	84.2	47.2	33.7	32.0
52.5°	141.5	139.8	138.1	139.8	138.1	138.1	109.5	62.3	37.1	27.0	25.3
55°	101.1	101.1	99.4	102.8	104.4	101.1	82.5	45.5	28.6	21.9	20.2
57.5°	70.7	70.7	67.4	70.7	70.7	74.1	59.0	33.7	23.6	16.8	16.8
60°	47.2	47.2	47.2	48.8	50.5	50.5	40.4	23.6	18.5	13.5	13.5
62.5°	32.0	32.0	32.0	33.7	33.7	37.1	28.6	18.5	15.2	11.8	10.1
65°	21.9	21.9	21.9	21.9	23.6	23.6	18.5	13.5	11.8	10.1	8.4
67.5°	13.5	15.2	13.5	15.2	15.2	15.2	11.8	10.1	8.4	6.7	5.1
70°	10.1	10.1	10.1	10.1	10.1	10.1	8.4	8.4	6.7	5.1	3.4
72.5°	6.7	6.7	6.7	6.7	6.7	6.7	5.1	5.1	5.1	3.4	3.4
75°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	1.7	1.7
77.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	0.0
80°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	0.0	0.0
82.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P601437
 CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL45R6G_ TL46S6G_ 2700K

CANDELA DISTRIBUTION (continued):

	157.5°	180°
0°	675.5	675.5
2.5°	619.9	608.1
5°	525.5	539.0
7.5°	458.2	441.3
10°	384.1	373.9
12.5°	333.5	328.5
15°	276.3	264.5
17.5°	237.5	225.7
20°	198.8	190.3
22.5°	170.1	165.1
25°	146.5	139.8
27.5°	126.3	123.0
30°	109.5	109.5
32.5°	94.3	97.7
35°	84.2	85.9
37.5°	72.4	75.8
40°	67.4	70.7
42.5°	57.3	64.0
45°	48.8	53.9
47.5°	42.1	47.2
50°	35.4	40.4
52.5°	32.0	35.4
55°	27.0	28.6
57.5°	21.9	23.6
60°	16.8	18.5
62.5°	13.5	15.2
65°	10.1	10.1
67.5°	6.7	8.4
70°	3.4	5.1
72.5°	1.7	1.7
75°	1.7	0.0
77.5°	0.0	0.0
80°	0.0	0.0
82.5°	0.0	0.0
85°	0.0	0.0
87.5°	0.0	0.0
90°	0.0	0.0

(END OF REPORT)