

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: io LED

Report Number: A1921935A001

Luminaire Tested:

Test Date: 2019-12-20

Test Information

Test Method: LM-79-08
Report Number: A1921935A001
Test Lab: LEEDARSON
Test Date: 2019-12-20
Issue Date: 2019-12-20 15:05:52
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number:
Description: LCR2089FS1EMW
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 801.6 lumens
Efficiency: N/A
Efficacy: 81.8 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.21 / 1.29
Luminous Opening: Circular (Dia: 0.21' x H: 0')
CIE Type: Direct


Input Watts (W): 9.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: A1921935A001

CATALOG NUMBER:

Luminous Intensity Polar Plot



0% Up
100% Dn

— 0°-180° - - 45°-225° - - - 90°-270° - · - 135°-315°



TEST NUMBER: A1921935A001

CATALOG NUMBER:

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89				87	
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77				75	
3	94	84	77	71	91	83	76	70	80	74	69	77	72	68	75	70	67				65	
4	86	75	67	61	84	74	67	61	72	65	60	69	64	59	67	62	58				56	
5	80	68	60	53	78	67	59	53	65	58	53	63	57	52	61	56	51				50	
6	74	61	53	47	72	60	53	47	59	52	46	57	51	46	56	50	46				44	
7	69	56	48	42	67	55	47	42	54	47	41	52	46	41	51	45	41				39	
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37				35	
9	60	47	39	34	59	47	39	34	45	39	34	44	38	34	43	38	33				32	
10	56	44	36	31	55	43	36	31	42	35	31	41	35	31	40	35	31				29	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	111284	111284	111284	111284
5°	111009	111136	111391	111041
10°	110395	110717	111103	110427
15°	109405	109962	110520	109733
20°	108211	109020	109627	108616
25°	106500	107479	108458	106955
30°	103882	104906	106406	104321
35°	100120	101203	103252	100313
40°	95234	96599	99163	95358
45°	89195	90897	93899	89240
50°	81512	83927	87081	81758
55°	72128	75387	78866	73012
60°	60441	65003	68170	62278
65°	46323	52469	54943	49096
70°	29823	36677	38715	32973
75°	18726	22153	23622	21174
80°	16236	18972	19702	18242
85°	11631	14902	17446	13812



TEST NUMBER: A1921935A001

CATALOG NUMBER:

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.2	4.1
10°-20°	94.5	11.8
20°-30°	141.3	17.6
30°-40°	163.4	20.4
40°-50°	155.9	19.4
50°-60°	120.8	15.1
60°-70°	67.0	8.4
70°-80°	20.8	2.6
80°-90°	4.6	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	269.0	33.6
0°-40°	432.4	53.9
0°-60°	709.1	88.5
0°-90°	801.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	801.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	351	351	351	351	351	
5°	349	350	350	349	349	33
15°	334	335	337	335	334	94
25°	305	308	310	306	305	140
35°	259	262	267	259	259	162
45°	199	203	210	199	199	153
55°	131	136	143	132	131	117
65°	62	70	73	66	62	62
75°	15	18	19	17	15	18
85°	3	4	5	4	3	4
90°	0	0	0	0	0	0
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0



TEST NUMBER: A1921935A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	351.3	351.3	351.3	351.3	351.3	351.3	351.3	351.3	351.3	351.3	351.3
0.5°	351.3	351.1	351.2	351.4	351.2	351.2	351.2	351.1	351.4	351.6	351.4
1°	351.4	351.0	351.2	351.1	351.2	351.4	351.2	350.8	351.5	351.7	351.2
1.5°	351.0	351.0	351.0	351.0	350.9	351.1	351.0	351.0	351.4	351.8	351.3
2°	351.0	350.9	350.8	350.8	350.8	351.1	351.2	350.9	351.3	351.7	351.2
2.5°	350.6	350.7	350.4	350.8	351.0	350.8	351.1	350.6	351.2	351.5	350.9
3°	350.5	350.6	350.4	350.6	350.7	350.8	351.0	350.5	351.0	351.4	350.8
3.5°	350.0	350.4	350.1	350.4	350.5	350.6	350.7	350.5	350.9	351.2	350.8
4°	349.9	350.1	350.0	350.2	350.4	350.2	350.6	350.2	350.6	351.0	350.5
4.5°	349.5	349.8	349.6	350.0	350.0	349.8	350.3	350.1	350.4	350.4	349.9
5°	349.1	349.3	349.2	349.3	349.5	349.8	349.9	349.8	350.3	350.0	349.4
5.5°	348.7	348.8	348.9	349.0	349.1	349.4	349.4	349.3	349.9	349.6	349.1
6°	348.4	348.3	348.4	348.5	348.6	349.3	349.2	349.0	349.6	349.2	348.9
6.5°	347.7	347.8	348.1	348.0	348.4	348.5	348.7	348.6	349.1	348.8	348.5
7°	347.6	347.5	347.7	347.5	347.8	347.9	348.3	348.4	348.6	348.4	348.3
7.5°	346.7	346.8	347.0	347.0	347.6	347.3	347.8	347.9	348.0	347.9	347.6
8°	346.1	345.8	346.4	346.5	346.7	347.1	347.4	347.4	347.6	347.6	347.1
8.5°	345.4	345.4	345.8	346.0	346.4	346.4	346.7	346.8	347.0	347.0	346.8
9°	344.7	344.8	344.9	345.4	345.4	346.0	346.3	346.4	346.6	346.4	346.0
9.5°	344.0	344.4	344.3	344.9	345.2	345.4	345.5	345.9	346.0	345.8	345.1
10°	343.2	343.5	343.6	344.0	344.2	344.8	345.1	345.2	345.4	345.3	344.7
10.5°	342.6	342.7	342.9	343.1	343.5	344.0	344.3	344.5	344.6	344.5	343.9
11°	341.6	341.9	342.0	342.3	342.7	343.2	343.6	343.7	343.9	343.7	343.1
11.5°	340.8	341.2	341.4	341.5	341.9	342.4	342.8	343.0	343.4	342.9	342.4
12°	339.6	340.1	340.4	340.5	341.0	341.6	342.0	342.2	342.5	342.1	341.5
12.5°	338.9	339.4	339.6	339.7	340.4	340.9	341.2	341.6	341.6	341.2	340.8
13°	338.1	338.4	338.5	338.8	339.3	339.9	340.3	340.4	340.8	340.2	340.0
13.5°	337.0	337.4	337.6	337.7	338.4	338.8	339.3	339.4	340.0	339.3	339.1
14°	336.0	336.3	336.3	336.8	337.3	337.9	338.6	338.5	339.0	338.6	338.4
14.5°	334.8	335.2	335.4	335.8	336.6	336.9	337.5	337.8	338.0	337.4	337.3
15°	333.6	334.1	334.3	334.9	335.3	335.7	336.5	336.6	337.0	336.5	336.3
15.5°	332.4	332.9	333.5	333.7	334.2	334.7	335.5	335.7	336.0	335.4	335.3
16°	331.6	331.9	332.4	332.3	333.0	333.7	334.6	334.8	334.8	334.2	334.1
16.5°	330.5	330.6	331.1	331.3	332.2	332.6	333.4	333.6	333.8	333.3	332.9
17°	329.0	329.6	330.2	330.2	330.8	331.6	332.1	332.3	332.7	332.2	331.6
17.5°	327.8	328.1	328.8	328.7	329.8	330.2	330.8	331.4	331.4	330.9	330.8
18°	326.8	326.9	327.6	327.6	328.4	329.1	329.7	330.1	330.4	329.9	329.5
18.5°	325.4	325.6	326.3	326.4	327.0	327.7	328.6	329.0	329.1	328.6	328.1
19°	323.8	324.3	324.9	325.2	326.0	326.5	327.3	327.7	327.8	327.2	326.9
19.5°	322.6	322.8	323.3	323.8	324.7	325.5	325.9	326.6	326.7	326.0	325.5
20°	321.0	321.2	321.9	322.6	323.4	323.8	324.7	325.1	325.2	324.7	324.1
20.5°	319.6	319.8	320.5	320.9	321.9	322.4	323.3	323.8	324.0	323.3	322.9
21°	318.1	318.4	319.3	319.7	320.5	321.1	322.0	322.3	322.5	321.9	321.4
21.5°	316.6	316.8	317.5	318.2	319.0	319.7	320.6	321.0	321.1	320.7	319.9
22°	314.9	315.2	316.0	316.5	317.4	318.5	319.1	319.4	319.6	319.3	318.4



TEST NUMBER: A1921935A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
22.5°	313.2	313.6	314.2	315.1	316.0	316.8	317.6	318.1	318.2	317.8	316.7
23°	311.8	311.7	313.0	313.3	314.2	315.2	316.1	316.4	316.8	316.4	315.3
23.5°	310.1	310.1	311.1	311.7	312.7	313.6	314.4	314.8	315.2	314.7	313.7
24°	308.4	308.4	309.5	310.0	311.0	312.0	313.0	313.2	313.5	313.1	312.2
24.5°	306.7	306.6	307.6	308.4	309.3	310.2	311.2	311.6	312.0	311.5	310.4
25°	304.7	304.7	305.8	306.5	307.5	308.6	309.8	310.0	310.3	309.8	308.6
25.5°	303.0	302.6	303.9	304.5	306.0	306.6	307.8	308.4	308.5	308.2	307.0
26°	301.1	300.9	302.1	302.7	303.8	304.8	306.0	306.4	306.7	306.3	305.1
26.5°	299.0	298.8	299.8	300.7	301.8	302.9	303.9	304.7	304.8	304.4	303.1
27°	296.8	296.7	297.7	298.7	299.7	301.0	302.1	302.6	303.0	302.6	301.1
27.5°	294.6	294.8	295.5	296.3	297.6	298.6	300.1	300.8	300.9	300.5	299.4
28°	292.5	292.8	293.4	294.3	295.6	296.6	298.1	298.6	299.0	298.5	297.3
28.5°	290.6	291.0	291.1	292.2	293.4	294.5	296.2	296.7	297.0	296.4	295.2
29°	288.4	288.8	289.0	290.0	291.2	292.5	294.1	294.4	295.1	294.2	293.0
29.5°	286.2	286.2	286.5	287.7	289.0	290.4	291.8	292.7	292.9	292.3	290.8
30°	284.0	284.0	284.5	285.4	286.8	288.2	289.7	290.5	290.9	290.2	288.6
30.5°	281.7	281.6	281.8	282.8	284.6	285.8	287.4	288.5	288.8	288.2	286.6
31°	279.3	279.5	279.5	280.4	282.1	283.7	285.1	286.2	286.6	285.9	284.3
31.5°	276.9	276.9	276.9	277.7	279.8	280.9	282.8	284.0	284.2	283.6	282.2
32°	274.2	274.4	274.5	275.3	277.2	278.6	280.6	281.6	282.1	281.1	279.5
32.5°	271.8	271.9	271.7	272.7	274.8	276.0	278.1	279.3	279.6	278.9	277.2
33°	269.3	269.5	269.1	270.1	272.0	273.6	275.7	276.7	277.0	276.5	274.7
33.5°	266.7	266.9	266.5	267.4	269.6	270.9	273.4	274.3	274.8	273.9	272.2
34°	264.2	264.0	264.1	264.8	267.1	268.4	270.8	271.8	272.3	271.5	269.7
34.5°	261.5	261.4	261.2	262.2	264.4	265.8	268.0	269.3	269.8	268.8	266.9
35°	258.9	258.9	258.9	259.7	261.7	263.3	265.2	266.7	267.0	266.1	264.1
35.5°	256.2	256.1	256.3	256.8	258.9	260.7	263.0	264.2	264.5	263.5	261.5
36°	253.5	253.2	254.0	254.2	256.2	258.0	260.3	261.6	261.9	260.9	258.8
36.5°	250.7	250.5	250.9	251.4	253.5	255.3	257.6	258.8	259.3	258.4	256.3
37°	247.9	247.7	248.0	248.4	250.5	252.6	254.8	256.4	256.8	255.7	253.3
37.5°	245.0	244.7	245.3	245.6	247.8	249.6	252.4	253.4	254.0	252.7	250.2
38°	242.2	242.1	242.7	242.8	245.1	247.0	249.5	251.0	251.3	249.8	247.5
38.5°	239.3	239.2	239.5	240.0	242.2	244.2	246.6	248.0	248.3	247.1	244.6
39°	236.5	236.6	236.7	237.0	239.4	241.3	243.7	245.3	245.6	244.2	241.5
39.5°	233.4	233.6	233.5	234.1	236.6	238.2	241.0	242.6	242.6	241.5	238.6
40°	230.3	230.4	230.9	231.2	233.6	235.6	238.0	239.6	239.8	238.3	235.5
40.5°	227.3	227.6	227.6	228.1	230.5	232.5	235.2	236.6	236.8	235.6	232.6
41°	224.6	224.6	224.9	225.4	227.4	229.8	232.2	233.8	233.8	232.4	229.6
41.5°	221.6	221.3	222.0	222.2	224.6	226.6	229.3	230.7	230.8	229.5	226.7
42°	218.3	218.3	219.2	219.4	221.5	223.6	226.4	227.9	227.9	226.5	223.6
42.5°	215.0	215.4	215.9	216.3	218.3	220.8	223.5	224.9	224.8	223.5	220.6
43°	212.0	212.4	212.6	213.2	215.4	217.6	220.5	222.0	222.0	220.4	217.4
43.5°	209.0	209.5	209.5	209.9	212.4	214.3	217.4	218.9	218.8	217.4	214.3
44°	205.6	206.3	206.4	206.8	209.3	211.4	214.2	215.6	215.8	214.0	211.0
44.5°	202.6	202.9	203.3	203.8	206.1	208.4	211.1	212.7	212.7	211.1	207.8



TEST NUMBER: A1921935A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
45°	199.1	199.6	200.0	200.9	202.9	205.0	207.8	209.6	209.6	207.7	204.6
45.5°	195.9	196.3	197.0	197.5	199.5	202.1	204.6	206.3	206.3	204.5	201.4
46°	192.6	193.0	193.5	194.3	196.3	198.7	201.4	203.0	203.1	201.2	198.2
46.5°	189.5	190.0	190.6	191.2	193.3	195.5	198.1	199.9	199.9	198.1	195.0
47°	185.9	186.6	187.4	188.0	190.0	192.2	195.0	196.8	196.6	194.8	191.7
47.5°	182.5	183.2	184.1	184.7	186.8	189.1	191.7	193.2	193.2	191.4	188.5
48°	179.2	180.0	180.7	181.4	183.8	185.8	188.5	190.1	190.0	188.3	185.3
48.5°	175.8	176.6	177.4	178.3	180.2	182.6	185.2	186.8	186.6	185.0	181.8
49°	172.4	173.3	174.2	174.8	177.0	179.3	182.0	183.5	183.3	181.6	178.4
49.5°	169.0	169.8	171.0	171.5	173.6	175.9	178.6	180.0	180.0	178.3	175.1
50°	165.4	166.4	167.4	168.2	170.3	172.6	175.3	176.8	176.7	174.9	171.8
50.5°	162.0	163.0	163.8	164.8	166.9	169.0	171.9	173.3	173.3	171.6	168.5
51°	158.6	159.6	160.3	161.5	163.4	165.8	168.6	170.0	170.0	168.3	165.2
51.5°	155.1	156.1	157.1	158.0	160.0	162.5	165.0	166.5	166.6	165.0	161.6
52°	151.7	152.7	153.6	154.8	156.7	159.1	161.7	163.1	163.1	161.4	158.4
52.5°	148.2	149.2	150.2	151.4	153.6	155.6	158.2	159.7	159.8	158.0	155.1
53°	144.8	145.7	146.8	147.9	150.0	152.2	155.0	156.4	156.4	154.8	151.7
53.5°	141.1	142.3	143.1	144.6	146.6	148.9	151.6	153.1	153.1	151.2	148.3
54°	137.8	138.7	139.8	141.0	143.3	145.4	148.1	149.5	149.6	147.9	144.9
54.5°	134.1	135.2	136.3	137.6	139.9	142.0	144.7	146.0	146.1	144.4	141.4
55°	130.6	131.5	132.8	134.2	136.5	138.5	141.2	142.7	142.8	141.0	138.0
55.5°	126.9	128.0	129.4	130.7	133.1	135.2	137.7	139.1	139.4	137.5	134.6
56°	123.6	124.5	125.8	127.2	129.6	131.8	134.2	135.6	135.8	134.0	131.1
56.5°	120.1	121.1	122.4	123.8	126.4	128.4	130.7	132.0	132.1	130.6	127.8
57°	116.6	117.5	118.9	120.5	122.8	124.9	127.4	128.6	128.6	127.0	124.4
57.5°	113.0	114.0	115.4	117.0	119.6	121.6	123.7	125.2	125.1	123.6	121.0
58°	109.5	110.5	111.9	113.5	116.1	118.3	120.4	121.7	121.7	120.2	117.5
58.5°	106.1	106.8	108.5	110.0	112.7	114.9	116.9	118.2	118.1	116.8	114.0
59°	102.5	103.4	104.9	106.5	109.3	111.3	113.4	114.7	114.6	113.0	110.6
59.5°	99.0	99.9	101.4	103.1	105.8	107.9	110.0	111.2	111.0	109.6	107.0
60°	95.4	96.3	97.9	99.6	102.6	104.5	106.6	107.6	107.6	106.1	103.6
60.5°	92.0	92.9	94.4	96.3	99.2	101.2	103.1	104.1	104.1	102.7	100.2
61°	88.7	89.4	91.0	92.9	96.0	97.7	99.6	100.6	100.5	99.1	96.8
61.5°	85.4	86.1	87.7	89.6	92.6	94.4	96.1	97.0	97.0	95.7	93.4
62°	81.9	82.7	84.3	86.3	89.5	91.1	92.8	93.6	93.7	92.3	90.1
62.5°	78.6	79.3	81.0	82.8	86.1	87.7	89.3	90.2	90.2	89.0	86.7
63°	75.2	76.0	77.6	79.6	82.8	84.5	86.0	86.8	86.8	85.6	83.3
63.5°	71.8	72.7	74.3	76.4	79.6	81.2	82.7	83.4	83.4	82.1	80.1
64°	68.4	69.2	71.0	72.8	76.3	77.9	79.4	80.0	79.9	78.8	76.7
64.5°	65.1	66.0	67.7	69.7	73.2	74.6	76.1	76.7	76.5	75.4	73.4
65°	61.8	62.7	64.5	66.5	70.0	71.3	72.6	73.3	73.3	72.0	70.2
65.5°	58.4	59.4	61.2	63.1	66.7	68.0	69.3	70.0	70.0	68.9	67.0
66°	55.3	56.1	57.8	59.8	63.5	64.8	66.1	66.7	66.6	65.5	63.7
66.5°	52.1	53.1	54.8	56.7	60.3	61.6	62.8	63.4	63.3	62.3	60.7
67°	49.0	50.0	51.8	53.6	57.2	58.6	59.7	60.2	60.1	59.1	57.4



TEST NUMBER: A1921935A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
67.5°	46.0	46.9	48.6	50.5	54.3	55.5	56.4	57.0	56.9	56.0	54.5
68°	43.1	44.0	45.6	47.5	51.1	52.5	53.4	53.8	53.9	53.0	51.5
68.5°	40.2	41.2	42.7	44.6	48.2	49.5	50.3	50.8	50.8	49.9	48.5
69°	37.5	38.4	39.9	41.8	45.4	46.4	47.3	47.8	47.7	46.9	45.6
69.5°	34.8	35.7	37.2	38.8	42.4	43.5	44.4	44.8	44.7	44.0	42.8
70°	32.2	33.2	34.6	36.1	39.6	40.7	41.5	41.9	41.8	41.2	39.9
70.5°	29.8	30.7	32.2	33.6	36.8	37.9	38.7	39.1	39.1	38.4	37.3
71°	27.6	28.4	29.6	31.2	34.2	35.2	36.0	36.4	36.2	35.7	34.7
71.5°	25.4	26.1	27.4	28.8	31.6	32.7	33.3	33.7	33.6	33.2	32.1
72°	23.4	24.0	25.2	26.5	29.1	30.2	30.9	31.2	31.2	30.8	29.6
72.5°	21.7	22.2	23.3	24.4	26.8	27.8	28.6	28.9	28.8	28.4	27.4
73°	20.0	20.7	21.6	22.5	24.6	25.6	26.3	26.5	26.5	26.2	25.2
73.5°	18.6	19.1	20.0	21.0	22.6	23.5	24.2	24.5	24.4	24.1	23.2
74°	17.3	17.7	18.6	19.6	21.1	21.7	22.3	22.6	22.5	22.3	21.5
74.5°	16.2	16.6	17.5	18.3	19.5	20.2	20.7	20.9	20.8	20.6	19.9
75°	15.3	15.6	16.4	17.3	18.1	18.8	19.2	19.3	19.3	19.0	18.4
75.5°	14.6	14.9	15.6	16.4	17.0	17.6	17.9	17.8	17.8	17.8	17.2
76°	14.0	14.3	14.8	15.7	16.1	16.6	16.6	16.7	16.7	16.5	16.1
76.5°	13.3	13.7	14.2	14.9	15.3	15.6	15.8	15.6	15.6	15.6	15.3
77°	12.7	12.9	13.6	14.3	14.5	14.8	14.9	14.7	14.6	14.6	14.6
77.5°	12.1	12.4	12.8	13.5	13.8	14.2	14.4	14.1	13.9	13.9	13.9
78°	11.4	11.8	12.2	12.9	13.2	13.5	13.6	13.5	13.4	13.5	13.3
78.5°	10.9	11.1	11.6	12.1	12.4	12.7	12.8	12.8	12.6	12.6	12.5
79°	10.2	10.3	11.0	11.5	11.7	12.0	12.2	12.1	12.1	12.0	11.8
79.5°	9.6	9.9	10.3	10.8	11.1	11.3	11.5	11.5	11.4	11.4	11.3
80°	8.9	9.3	9.6	10.2	10.4	10.7	10.8	10.8	10.8	10.7	10.6
80.5°	8.4	8.6	9.0	9.4	9.7	10.2	10.5	10.3	10.4	10.3	10.1
81°	7.5	8.0	8.2	8.9	9.2	9.5	9.6	9.6	9.5	9.5	9.4
81.5°	7.2	7.4	7.8	8.2	8.5	8.7	9.0	9.1	9.0	9.0	8.7
82°	6.6	6.7	7.2	7.5	8.3	8.2	8.3	8.3	8.3	8.2	8.3
82.5°	6.0	6.2	6.6	6.9	7.2	7.5	7.7	7.8	7.7	7.7	7.4
83°	5.4	5.6	5.9	6.4	6.5	7.0	7.3	7.2	7.1	7.2	6.9
83.5°	4.8	5.0	5.3	5.8	6.2	6.2	6.4	6.5	6.4	6.4	6.1
84°	4.3	4.6	4.7	5.2	5.3	5.6	6.1	6.1	6.1	6.0	5.5
84.5°	3.7	4.0	4.2	4.6	4.9	5.1	5.2	5.3	5.3	5.2	5.0
85°	3.2	3.4	3.6	4.0	4.1	4.4	4.8	4.8	4.8	4.7	4.4
85.5°	2.6	2.8	3.0	3.4	3.8	4.2	4.2	4.2	4.1	4.2	4.1
86°	2.1	2.3	2.6	2.8	2.9	3.3	3.5	3.8	3.6	3.3	3.2
86.5°	1.5	1.7	2.0	2.3	2.4	2.8	3.0	3.0	3.0	3.0	2.7
87°	1.1	1.2	1.5	1.8	1.8	2.0	2.2	2.4	2.4	2.2	2.0
87.5°	0.6	0.7	0.9	1.2	1.2	1.8	2.0	2.0	1.9	1.8	1.6
88°	0.1	0.3	0.4	0.7	0.8	1.0	1.3	1.2	1.2	1.2	1.0
88.5°	0.0	0.0	0.0	0.2	0.2	0.6	0.8	0.8	0.8	0.8	0.5
89°	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.2	0.2	0.1	0.0
89.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1921935A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
91°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
91.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
93°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
93.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
94°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
94.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
96°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
96.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
101°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
101.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
103°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
103.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
104°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
104.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
106°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
106.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
108°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
108.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
109°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
109.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
111°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
111.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
112°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1921935A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
113°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
113.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
114°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
114.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
116°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
116.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
118°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
118.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
119°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
119.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
121°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
121.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
123°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
123.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
124°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
124.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
126°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
126.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
128°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
128.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
129°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
129.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
131°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
131.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
133°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
133.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
134°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
134.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1921935A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
136°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
136.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
138°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
138.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
139°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
139.5°	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140.5°	0.1	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
141°	0.2	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
141.5°	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142°	0.1	0.1	0.2	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.1	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
143°	0.1	0.2	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
143.5°	0.1	0.2	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
144°	0.1	0.2	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
144.5°	0.1	0.2	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.1	0.2	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145.5°	0.1	0.2	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
146°	0.1	0.3	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
146.5°	0.1	0.2	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
147°	0.1	0.2	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.1	0.2	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
148°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
148.5°	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
149°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
149.5°	0.1	0.1	0.1	0.1	0.2	0.0	0.0	0.0	0.1	0.0	0.0
150°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
150.5°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
151°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
151.5°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
152°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.1	0.1	0.1	0.1	0.2	0.1	0.0	0.0	0.1	0.0	0.1
153°	0.1	0.1	0.1	0.1	0.3	0.1	0.0	0.0	0.1	0.0	0.1
153.5°	0.1	0.1	0.1	0.1	0.3	0.1	0.0	0.1	0.1	0.0	0.0
154°	0.1	0.1	0.1	0.1	0.2	0.1	0.0	0.1	0.1	0.0	0.0
154.5°	0.1	0.1	0.1	0.1	0.2	0.1	0.0	0.1	0.1	0.0	0.0
155°	0.1	0.1	0.1	0.1	0.2	0.1	0.0	0.1	0.1	0.0	0.0
155.5°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.1	0.0	0.1
156°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.1	0.1	0.1
156.5°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.1	0.1	0.1
157°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.1	0.1	0.1



TEST NUMBER: A1921935A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
157.5°	0.1	0.1	0.1	0.1	0.2	0.1	0.3	0.1	0.1	0.2	0.1
158°	0.1	0.1	0.1	0.1	0.2	0.1	0.2	0.1	0.1	0.1	0.2
158.5°	0.1	0.1	0.1	0.1	0.2	0.1	0.2	0.1	0.1	0.1	0.2
159°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.1	0.1	0.2
159.5°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.1	0.1	0.2
160°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.1	0.1	0.2
160.5°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.1	0.1	0.2
161°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.1	0.1	0.2
161.5°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.0	0.1	0.2
162°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.0	0.1	0.2
162.5°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.0	0.2	0.3
163°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.0	0.2	0.2
163.5°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.0	0.1	0.2
164°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.0	0.1	0.2
164.5°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.0	0.1	0.2
165°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.0	0.1	0.2
165.5°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.0	0.1	0.1
166°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.0	0.1	0.1
166.5°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.0	0.1	0.1
167°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.0	0.1	0.1
167.5°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.0	0.1	0.1
168°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.0	0.1	0.1
168.5°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.0	0.1	0.1
169°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.0	0.1	0.1
169.5°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.0	0.1	0.1
170°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.0	0.1	0.1
170.5°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.0	0.1	0.1
171°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.0	0.1	0.1
171.5°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.0	0.1	0.1
172°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.0	0.1	0.1
172.5°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.0	0.1	0.1
173°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.0	0.1	0.1
173.5°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.0	0.1	0.1
174°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.0	0.1	0.1
174.5°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.0	0.1	0.1
175°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.0	0.1	0.1
175.5°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.0	0.1	0.1
176°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.0	0.1	0.1
176.5°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.0	0.1	0.1
177°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.0	0.1	0.1
177.5°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.0	0.1	0.1
178°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.0	0.1	0.1
178.5°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.0	0.1	0.1
179°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.0	0.1	0.1
179.5°	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.0	0.1	0.1



TEST NUMBER: A1921935A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
180°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1



TEST NUMBER: A1921935A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	351.3	351.3	351.3	351.3	351.3	351.3
0.5°	351.4	351.3	351.2	351.0	351.0	351.3
1°	351.2	351.2	351.1	351.0	350.6	351.4
1.5°	351.2	350.9	351.0	350.8	350.7	351.0
2°	351.0	350.9	350.7	350.7	350.4	351.0
2.5°	350.8	350.7	350.4	350.2	350.3	350.6
3°	350.7	350.4	350.2	350.4	349.8	350.5
3.5°	350.6	350.1	350.0	350.1	349.8	350.0
4°	350.2	349.8	349.6	349.8	349.5	349.9
4.5°	349.7	349.5	349.5	349.5	349.4	349.5
5°	349.4	349.2	349.2	348.8	348.8	349.1
5.5°	349.1	348.8	348.6	348.5	348.5	348.7
6°	348.7	348.2	348.2	348.2	348.0	348.4
6.5°	348.3	347.8	347.7	347.7	347.5	347.7
7°	347.9	347.5	347.2	347.1	347.1	347.6
7.5°	347.4	347.0	346.7	346.6	346.8	346.7
8°	346.8	346.2	346.1	346.0	346.0	346.1
8.5°	346.1	345.5	345.3	345.3	345.3	345.4
9°	345.5	344.9	344.5	344.8	344.5	344.7
9.5°	344.9	344.0	343.9	344.1	343.7	344.0
10°	344.2	343.3	343.2	343.2	342.9	343.2
10.5°	343.5	342.7	342.5	342.2	342.2	342.6
11°	342.5	342.0	341.5	341.3	341.6	341.6
11.5°	341.4	341.1	340.7	340.3	340.5	340.8
12°	340.6	340.0	339.7	339.5	339.8	339.6
12.5°	339.8	339.2	338.8	338.7	339.1	338.9
13°	339.1	338.4	338.0	337.7	338.1	338.1
13.5°	338.5	337.8	336.9	336.8	337.0	337.0
14°	337.3	336.6	336.0	335.8	335.6	336.0
14.5°	336.3	335.7	334.9	334.7	334.8	334.8
15°	335.1	334.6	333.7	333.4	333.6	333.6
15.5°	334.2	333.4	332.4	332.2	332.5	332.4
16°	333.0	332.0	331.5	331.1	331.3	331.6
16.5°	331.9	331.1	330.3	330.3	330.3	330.5
17°	330.9	330.1	329.1	329.3	328.8	329.0
17.5°	329.6	328.9	327.6	327.9	327.6	327.8
18°	328.4	327.5	326.6	326.7	326.2	326.8
18.5°	327.4	326.2	325.3	325.5	325.0	325.4
19°	326.2	325.0	324.1	324.2	323.5	323.8
19.5°	324.8	323.6	322.8	322.8	322.6	322.6
20°	323.4	322.2	321.2	321.2	321.1	321.0
20.5°	322.0	320.8	319.9	319.7	319.7	319.6
21°	320.6	319.2	318.3	318.2	318.2	318.1
21.5°	319.0	317.8	316.8	316.8	316.8	316.6
22°	317.6	316.2	315.2	315.2	315.0	314.9



TEST NUMBER: A1921935A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
22.5°	316.0	314.8	313.6	313.8	313.3	313.2
23°	314.4	313.0	312.1	312.1	311.8	311.8
23.5°	312.8	311.3	310.6	310.5	309.8	310.1
24°	311.2	309.6	308.9	308.9	308.2	308.4
24.5°	309.3	307.8	307.2	306.9	306.5	306.7
25°	307.6	306.0	305.2	305.0	304.4	304.7
25.5°	305.9	304.1	303.1	303.2	302.6	303.0
26°	303.9	302.2	301.1	301.1	300.7	301.1
26.5°	302.0	300.1	299.1	299.1	298.6	299.0
27°	299.9	298.0	297.3	297.2	296.9	296.8
27.5°	297.9	296.1	295.3	295.2	294.5	294.6
28°	295.8	294.0	293.0	292.9	292.5	292.5
28.5°	293.6	292.0	291.1	290.9	290.7	290.6
29°	291.6	290.0	288.9	288.7	288.5	288.4
29.5°	289.5	287.8	286.7	286.6	286.1	286.2
30°	287.0	285.2	284.3	284.1	283.9	284.0
30.5°	285.0	282.7	281.8	281.6	281.4	281.7
31°	282.4	280.4	279.4	279.4	279.2	279.3
31.5°	280.1	277.9	276.8	276.9	276.6	276.9
32°	277.4	275.4	274.3	274.2	273.9	274.2
32.5°	274.9	272.9	271.9	271.6	271.3	271.8
33°	272.2	270.4	269.2	268.9	268.9	269.3
33.5°	269.6	267.8	266.6	266.2	266.2	266.7
34°	267.0	265.1	263.8	263.5	263.9	264.2
34.5°	264.4	262.4	261.1	260.7	261.0	261.5
35°	261.6	259.4	258.4	258.3	258.5	258.9
35.5°	259.0	256.8	255.7	255.6	255.7	256.2
36°	256.2	254.1	253.0	252.6	253.1	253.5
36.5°	253.4	251.1	250.1	249.8	250.3	250.7
37°	250.6	248.3	247.2	247.0	247.4	247.9
37.5°	247.6	245.5	244.3	244.1	244.6	245.0
38°	244.6	242.6	241.4	241.2	241.6	242.2
38.5°	241.6	239.7	238.4	238.3	238.9	239.3
39°	238.6	236.5	235.4	235.3	236.0	236.5
39.5°	235.6	233.7	232.5	232.4	232.9	233.4
40°	232.4	230.6	229.4	229.1	229.9	230.3
40.5°	229.4	227.6	226.4	226.3	226.6	227.3
41°	226.2	224.7	223.5	223.3	223.7	224.6
41.5°	223.3	221.6	220.3	220.3	220.7	221.6
42°	220.1	218.6	217.2	217.2	217.7	218.3
42.5°	217.1	215.4	214.1	214.2	214.4	215.0
43°	213.8	212.3	211.1	210.9	211.2	212.0
43.5°	210.7	209.0	207.8	207.7	208.1	209.0
44°	207.4	205.8	204.5	204.4	204.7	205.6
44.5°	204.2	202.6	201.3	201.2	201.5	202.6



TEST NUMBER: A1921935A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
45°	201.0	199.2	197.9	197.8	198.1	199.1
45.5°	197.8	196.0	194.7	194.5	194.9	195.9
46°	194.5	192.7	191.3	191.2	191.7	192.6
46.5°	191.4	189.4	188.1	188.0	188.4	189.5
47°	188.2	186.1	184.8	184.6	184.8	185.9
47.5°	184.9	182.7	181.5	181.2	181.5	182.5
48°	181.6	179.4	178.2	177.8	178.1	179.2
48.5°	178.5	176.0	174.7	174.4	174.8	175.8
49°	175.0	172.7	171.3	171.0	171.4	172.4
49.5°	171.9	169.3	168.0	167.6	167.9	169.0
50°	168.3	165.9	164.5	164.2	164.5	165.4
50.5°	165.0	162.4	161.2	160.8	161.0	162.0
51°	161.5	159.1	157.8	157.4	157.7	158.6
51.5°	158.2	155.8	154.5	154.2	154.3	155.1
52°	154.8	152.6	151.0	150.7	150.8	151.7
52.5°	151.6	149.2	147.5	147.1	147.3	148.2
53°	148.1	145.8	144.3	143.7	143.9	144.8
53.5°	144.8	142.3	140.7	140.3	140.4	141.1
54°	141.5	139.0	137.2	136.8	136.8	137.8
54.5°	138.2	135.6	133.9	133.3	133.2	134.1
55°	134.7	132.2	130.6	129.9	129.7	130.6
55.5°	131.3	128.8	127.1	126.4	126.3	126.9
56°	127.9	125.5	123.8	123.0	122.9	123.6
56.5°	124.5	122.1	120.4	119.5	119.4	120.1
57°	121.2	118.7	117.0	116.0	115.8	116.6
57.5°	117.8	115.2	113.5	112.6	112.4	113.0
58°	114.5	111.7	110.1	109.0	108.9	109.5
58.5°	111.3	108.4	106.7	105.6	105.4	106.1
59°	107.7	105.0	103.4	102.1	101.8	102.5
59.5°	104.2	101.6	99.9	98.7	98.3	99.0
60°	101.0	98.3	96.4	95.2	94.9	95.4
60.5°	97.7	95.0	93.0	91.8	91.4	92.0
61°	94.4	91.7	89.7	88.6	88.1	88.7
61.5°	91.1	88.4	86.5	85.1	84.8	85.4
62°	87.8	85.0	83.2	81.7	81.4	81.9
62.5°	84.6	81.8	80.0	78.4	78.0	78.6
63°	81.3	78.5	76.7	75.0	74.6	75.2
63.5°	78.0	75.3	73.3	71.8	71.4	71.8
64°	74.7	72.0	70.1	68.5	68.0	68.4
64.5°	71.6	68.8	66.9	65.2	64.8	65.1
65°	68.2	65.5	63.6	62.0	61.5	61.8
65.5°	65.2	62.4	60.3	58.7	58.2	58.4
66°	61.9	59.2	57.1	55.6	54.9	55.3
66.5°	58.8	56.0	54.2	52.6	51.8	52.1
67°	55.8	53.0	51.1	49.5	48.9	49.0



TEST NUMBER: A1921935A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
67.5°	52.9	50.0	48.0	46.4	45.8	46.0
68°	49.9	46.9	45.2	43.6	42.9	43.1
68.5°	47.0	44.0	42.2	40.8	40.1	40.2
69°	44.0	41.1	39.6	38.2	37.3	37.5
69.5°	41.3	38.3	36.8	35.4	34.7	34.8
70°	38.5	35.6	34.2	32.9	32.1	32.2
70.5°	35.8	33.0	31.6	30.5	29.7	29.8
71°	33.3	30.6	29.2	28.2	27.4	27.6
71.5°	30.8	28.2	27.0	26.0	25.4	25.4
72°	28.4	26.0	25.0	24.0	23.3	23.4
72.5°	26.1	24.0	23.0	22.2	21.8	21.7
73°	24.1	22.2	21.4	20.6	20.0	20.0
73.5°	22.1	20.8	19.8	19.2	18.6	18.6
74°	20.5	19.4	18.6	17.9	17.4	17.3
74.5°	19.1	18.3	17.5	16.7	16.3	16.2
75°	17.8	17.3	16.6	15.9	15.3	15.3
75.5°	16.7	16.4	15.8	15.2	14.7	14.6
76°	15.9	15.5	15.0	14.4	14.1	14.0
76.5°	15.1	14.8	14.3	13.8	13.4	13.3
77°	14.6	14.1	13.6	13.1	12.7	12.7
77.5°	13.8	13.4	12.9	12.4	12.1	12.1
78°	13.0	12.7	12.2	11.8	11.5	11.4
78.5°	12.2	12.0	11.5	11.1	10.9	10.9
79°	11.6	11.3	10.9	10.5	10.2	10.2
79.5°	11.0	10.6	10.2	9.8	9.6	9.6
80°	10.3	10.0	9.6	9.2	9.0	8.9
80.5°	9.7	9.3	8.9	8.4	8.2	8.4
81°	9.1	8.9	8.3	8.0	7.8	7.5
81.5°	8.3	7.9	7.7	7.4	7.2	7.2
82°	7.7	7.4	7.0	6.8	6.6	6.6
82.5°	7.1	6.8	6.4	6.2	6.0	6.0
83°	6.4	6.2	5.8	5.5	5.5	5.4
83.5°	6.0	5.6	5.2	4.9	4.8	4.8
84°	5.2	5.0	4.6	4.5	4.4	4.3
84.5°	4.6	4.6	4.1	3.8	3.7	3.7
85°	4.1	3.8	3.6	3.3	3.2	3.2
85.5°	3.4	3.3	2.9	2.7	2.6	2.6
86°	2.8	2.7	2.4	2.2	2.1	2.1
86.5°	2.2	2.1	1.9	1.7	1.6	1.5
87°	1.9	1.7	1.4	1.1	1.1	1.1
87.5°	1.1	1.1	0.8	0.7	0.6	0.6
88°	0.8	0.6	0.4	0.1	0.1	0.1
88.5°	0.1	0.1	0.0	0.0	0.0	0.0
89°	0.0	0.0	0.0	0.0	0.0	0.0
89.5°	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1921935A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
90°	0.0	0.0	0.0	0.0	0.0	0.0
90.5°	0.0	0.0	0.0	0.0	0.0	0.0
91°	0.0	0.0	0.0	0.0	0.0	0.0
91.5°	0.0	0.0	0.0	0.0	0.0	0.0
92°	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0
93°	0.0	0.0	0.0	0.0	0.0	0.0
93.5°	0.0	0.0	0.0	0.0	0.0	0.0
94°	0.0	0.0	0.0	0.0	0.0	0.0
94.5°	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0
95.5°	0.0	0.0	0.0	0.0	0.0	0.0
96°	0.0	0.0	0.0	0.0	0.0	0.0
96.5°	0.0	0.0	0.0	0.0	0.0	0.0
97°	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0
98°	0.0	0.0	0.0	0.0	0.0	0.0
98.5°	0.0	0.0	0.0	0.0	0.0	0.0
99°	0.0	0.0	0.0	0.0	0.0	0.0
99.5°	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0
100.5°	0.0	0.0	0.0	0.0	0.0	0.0
101°	0.0	0.0	0.0	0.0	0.0	0.0
101.5°	0.0	0.0	0.0	0.0	0.0	0.0
102°	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0
103°	0.0	0.0	0.0	0.0	0.0	0.0
103.5°	0.0	0.0	0.0	0.0	0.0	0.0
104°	0.0	0.0	0.0	0.0	0.0	0.0
104.5°	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0
105.5°	0.0	0.0	0.0	0.0	0.0	0.0
106°	0.0	0.0	0.0	0.0	0.0	0.0
106.5°	0.0	0.0	0.0	0.0	0.0	0.0
107°	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0
108°	0.0	0.0	0.0	0.0	0.0	0.0
108.5°	0.0	0.0	0.0	0.0	0.0	0.0
109°	0.0	0.0	0.0	0.0	0.0	0.0
109.5°	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0
110.5°	0.0	0.0	0.0	0.0	0.0	0.0
111°	0.0	0.0	0.0	0.0	0.0	0.0
111.5°	0.0	0.0	0.0	0.0	0.0	0.0
112°	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1921935A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0
113°	0.0	0.0	0.0	0.0	0.0	0.0
113.5°	0.0	0.0	0.0	0.0	0.0	0.0
114°	0.0	0.0	0.0	0.0	0.0	0.0
114.5°	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0
115.5°	0.0	0.0	0.0	0.0	0.0	0.0
116°	0.0	0.0	0.0	0.0	0.0	0.0
116.5°	0.0	0.0	0.0	0.0	0.0	0.0
117°	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0
118°	0.0	0.0	0.0	0.0	0.0	0.0
118.5°	0.0	0.0	0.0	0.0	0.0	0.0
119°	0.0	0.0	0.0	0.0	0.0	0.0
119.5°	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0
120.5°	0.0	0.0	0.0	0.0	0.0	0.0
121°	0.0	0.0	0.0	0.0	0.0	0.0
121.5°	0.0	0.0	0.0	0.0	0.0	0.0
122°	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0
123°	0.0	0.0	0.0	0.0	0.0	0.0
123.5°	0.0	0.0	0.0	0.0	0.0	0.0
124°	0.0	0.0	0.0	0.0	0.0	0.0
124.5°	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0
125.5°	0.0	0.0	0.0	0.0	0.0	0.0
126°	0.0	0.0	0.0	0.0	0.0	0.0
126.5°	0.0	0.0	0.0	0.0	0.0	0.0
127°	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0
128°	0.0	0.0	0.0	0.0	0.0	0.0
128.5°	0.0	0.0	0.0	0.0	0.0	0.0
129°	0.0	0.0	0.0	0.0	0.0	0.0
129.5°	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0
130.5°	0.0	0.0	0.0	0.0	0.0	0.0
131°	0.0	0.0	0.0	0.0	0.0	0.0
131.5°	0.0	0.0	0.0	0.0	0.0	0.0
132°	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0
133°	0.0	0.0	0.0	0.0	0.0	0.0
133.5°	0.0	0.0	0.0	0.0	0.0	0.0
134°	0.0	0.0	0.0	0.0	0.0	0.0
134.5°	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1921935A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
135°	0.0	0.0	0.0	0.0	0.0	0.0
135.5°	0.0	0.0	0.0	0.0	0.0	0.0
136°	0.0	0.0	0.0	0.0	0.0	0.0
136.5°	0.0	0.0	0.0	0.0	0.0	0.0
137°	0.0	0.0	0.0	0.1	0.0	0.0
137.5°	0.0	0.0	0.0	0.1	0.0	0.0
138°	0.0	0.0	0.0	0.0	0.1	0.0
138.5°	0.0	0.0	0.0	0.0	0.1	0.0
139°	0.0	0.0	0.1	0.0	0.0	0.0
139.5°	0.0	0.0	0.1	0.0	0.0	0.0
140°	0.0	0.0	0.1	0.0	0.0	0.0
140.5°	0.0	0.0	0.1	0.0	0.0	0.1
141°	0.0	0.1	0.1	0.1	0.0	0.2
141.5°	0.0	0.1	0.1	0.1	0.0	0.1
142°	0.0	0.1	0.3	0.1	0.0	0.1
142.5°	0.0	0.1	0.2	0.1	0.0	0.1
143°	0.0	0.1	0.2	0.1	0.0	0.1
143.5°	0.0	0.1	0.2	0.1	0.0	0.1
144°	0.0	0.1	0.1	0.1	0.0	0.1
144.5°	0.0	0.1	0.2	0.1	0.0	0.1
145°	0.0	0.1	0.2	0.1	0.0	0.1
145.5°	0.0	0.1	0.1	0.1	0.0	0.1
146°	0.0	0.1	0.1	0.1	0.0	0.1
146.5°	0.0	0.1	0.1	0.1	0.0	0.1
147°	0.0	0.1	0.1	0.1	0.0	0.1
147.5°	0.0	0.1	0.1	0.1	0.0	0.1
148°	0.0	0.1	0.1	0.1	0.0	0.1
148.5°	0.0	0.1	0.1	0.1	0.0	0.1
149°	0.0	0.1	0.1	0.1	0.0	0.1
149.5°	0.0	0.1	0.1	0.1	0.0	0.1
150°	0.0	0.1	0.1	0.1	0.0	0.1
150.5°	0.0	0.1	0.2	0.1	0.0	0.1
151°	0.1	0.1	0.2	0.1	0.0	0.1
151.5°	0.1	0.1	0.1	0.1	0.0	0.1
152°	0.0	0.1	0.1	0.1	0.0	0.1
152.5°	0.0	0.1	0.1	0.1	0.0	0.1
153°	0.1	0.1	0.1	0.1	0.0	0.1
153.5°	0.1	0.1	0.1	0.1	0.0	0.1
154°	0.1	0.1	0.1	0.1	0.0	0.1
154.5°	0.1	0.1	0.1	0.1	0.0	0.1
155°	0.1	0.1	0.1	0.1	0.0	0.1
155.5°	0.1	0.1	0.1	0.1	0.0	0.1
156°	0.1	0.1	0.1	0.1	0.0	0.1
156.5°	0.2	0.1	0.1	0.1	0.0	0.1
157°	0.1	0.1	0.1	0.1	0.0	0.1



TEST NUMBER: A1921935A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
157.5°	0.1	0.1	0.1	0.1	0.0	0.1
158°	0.1	0.1	0.1	0.1	0.0	0.1
158.5°	0.1	0.1	0.1	0.1	0.0	0.1
159°	0.1	0.1	0.1	0.1	0.0	0.1
159.5°	0.1	0.1	0.1	0.1	0.0	0.1
160°	0.1	0.1	0.1	0.1	0.0	0.1
160.5°	0.1	0.1	0.1	0.1	0.0	0.1
161°	0.1	0.1	0.1	0.1	0.0	0.1
161.5°	0.1	0.1	0.1	0.1	0.0	0.1
162°	0.1	0.1	0.1	0.1	0.0	0.1
162.5°	0.1	0.1	0.1	0.1	0.0	0.1
163°	0.1	0.1	0.1	0.1	0.0	0.1
163.5°	0.1	0.1	0.1	0.1	0.0	0.1
164°	0.1	0.1	0.1	0.1	0.0	0.1
164.5°	0.1	0.1	0.1	0.1	0.0	0.1
165°	0.1	0.1	0.1	0.1	0.0	0.1
165.5°	0.1	0.1	0.1	0.1	0.0	0.1
166°	0.1	0.1	0.1	0.1	0.0	0.1
166.5°	0.1	0.1	0.1	0.1	0.0	0.1
167°	0.1	0.1	0.1	0.1	0.0	0.1
167.5°	0.1	0.1	0.1	0.1	0.0	0.1
168°	0.1	0.1	0.1	0.1	0.0	0.1
168.5°	0.1	0.1	0.1	0.1	0.0	0.1
169°	0.1	0.1	0.1	0.1	0.0	0.1
169.5°	0.1	0.1	0.1	0.1	0.0	0.1
170°	0.1	0.1	0.1	0.1	0.0	0.1
170.5°	0.1	0.1	0.1	0.1	0.0	0.1
171°	0.1	0.1	0.1	0.1	0.0	0.1
171.5°	0.1	0.1	0.1	0.1	0.0	0.1
172°	0.1	0.1	0.1	0.1	0.0	0.1
172.5°	0.1	0.1	0.1	0.1	0.0	0.1
173°	0.1	0.1	0.1	0.1	0.0	0.1
173.5°	0.1	0.1	0.1	0.1	0.0	0.1
174°	0.1	0.1	0.1	0.1	0.0	0.1
174.5°	0.1	0.1	0.1	0.1	0.0	0.1
175°	0.1	0.1	0.1	0.1	0.0	0.1
175.5°	0.1	0.1	0.1	0.1	0.0	0.1
176°	0.1	0.1	0.1	0.1	0.0	0.1
176.5°	0.1	0.1	0.1	0.1	0.0	0.1
177°	0.1	0.1	0.1	0.1	0.0	0.1
177.5°	0.1	0.1	0.1	0.1	0.0	0.1
178°	0.1	0.1	0.1	0.1	0.0	0.1
178.5°	0.1	0.1	0.1	0.1	0.0	0.1
179°	0.1	0.1	0.1	0.1	0.0	0.1
179.5°	0.1	0.1	0.1	0.1	0.0	0.1



TEST NUMBER: A1921935A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
180°	0.1	0.1	0.1	0.1	0.1	0.1

(END OF REPORT)