

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P601440

Luminaire Tested: **ML4DM10LSAWW9FS1E - TIR4D25AWW - TL45R6G_ TL46S6G_ 4000K**

Issue Date: 7/29/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P601440
 Test Lab: COOPER LIGHTING SOLUTIONS
 Issue Date: 7/29/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO
 Catalog Number: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL45R6G_ TL46S6G_ 4000K
 Description: DIRECT MOUNT, 25D WW OPTIC, LINEAR SPREAD LENS TRIM
 Light Source: (1) SELECTABLE LUMEN LED 90CRI / 4000K CCT
 Ballast/Driver: -

Summary

Lumens per Lamp: N/A
 Luminaire Lumens: 883.4 lumens
 Efficiency: N/A
 Efficacy: 73.6 lumens/watt
 Spacing Criteria (0/90/45): 1.21 / 0.78 / 1
 Luminous Opening: Circular (Dia: 0.21' x H: 0')
 CIE Type: Direct


Input Watts (W): 12
 Input Voltage (V): NR
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT



Meas		Calibration Due Date	
Instrument	Identificatio		
Photometer	GONIO 1 11111111	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P601440
CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL45R6G_ TL46S6G_ 4000K

Luminous Intensity Polar Plot



TEST NUMBER: P601440

CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL45R6G_ TL46S6G_ 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76
4	94	85	79	74	92	84	78	73	82	76	72	79	75	72	78	74	71	69
5	88	78	72	67	86	77	71	67	76	70	66	74	69	65	72	68	65	63
6	83	73	66	61	81	72	65	61	70	65	60	69	64	60	67	63	59	58
7	78	68	61	56	77	67	60	56	65	60	55	64	59	55	63	58	55	53
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49
9	70	59	52	48	68	58	52	48	57	52	47	56	51	47	55	51	47	46
10	66	55	49	44	65	55	48	44	54	48	44	53	48	44	52	47	44	42

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	225330	225330	225330
5°	277508	223370	180483
10°	349750	210530	126651
15°	401373	182641	91337
20°	433513	157262	67576
25°	432758	128319	51460
30°	395789	99904	42186
35°	327888	76132	35001
40°	235450	55730	30792
45°	166879	38136	25409
50°	97905	24464	20976
55°	58796	16681	16681
60°	31450	12378	12378
65°	17259	9340	7995
70°	9879	6555	4893
75°	4392	4392	0
80°	3273	3273	0
85°	0	0	0

TEST NUMBER: P601440
 CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL45R6G_ TL46S6G_ 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.6	7.7
10°-20°	184.0	20.8
20°-30°	240.5	27.2
30°-40°	206.2	23.3
40°-50°	117.9	13.4
50°-60°	48.2	5.5
60°-70°	15.4	1.7
70°-80°	3.3	0.4
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	492.0	55.7
0°-40°	698.2	79.0
0°-60°	864.4	97.8
0°-90°	883.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	883.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	714	714	714	714	714	
5°	876	822	705	596	569	91
15°	1228	968	559	336	279	347
25°	1242	856	368	176	148	568
35°	851	562	198	92	91	525
45°	374	254	85	46	57	284
55°	107	87	30	21	30	101
65°	23	20	12	9	11	25
75°	4	4	4	2	0	5
85°	0	0	0	0	0	1
90°	0	0	0	0	0	

TEST NUMBER: P601440

CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL45R6G_ TL46S6G_ 4000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	45°	67.5°	90°	112.5°	135°
0°	713.6	713.6	713.6	713.6	713.6	713.6	713.6	713.6	713.6	713.6	713.6
2.5°	783.0	799.0	793.6	802.5	800.7	784.7	768.7	743.8	718.9	704.7	672.6
5°	875.5	895.1	909.3	898.6	893.3	880.8	822.1	766.9	704.7	642.4	596.1
7.5°	996.5	991.1	1007.2	975.1	976.9	971.6	886.2	779.4	683.3	592.6	526.7
10°	1090.8	1074.8	1090.8	1080.1	1058.8	1033.9	930.6	774.1	656.6	542.7	453.8
12.5°	1160.2	1181.5	1181.5	1156.6	1135.3	1106.8	964.5	770.5	610.3	482.2	391.5
15°	1227.8	1234.9	1222.5	1202.9	1181.5	1122.8	968.0	747.4	558.7	423.5	336.3
17.5°	1272.3	1274.1	1268.7	1250.9	1220.7	1185.1	944.9	726.0	510.7	377.2	282.9
20°	1290.1	1275.9	1274.1	1242.1	1215.4	1183.3	925.3	674.4	468.0	322.1	245.6
22.5°	1318.6	1284.8	1284.8	1252.7	1197.6	1192.2	914.6	615.7	409.3	275.8	210.0
25°	1242.1	1236.7	1247.4	1202.9	1160.2	1151.3	855.9	571.2	368.3	238.4	176.2
27.5°	1190.4	1176.2	1162.0	1133.5	1092.6	1071.2	807.9	514.3	320.3	199.3	149.5
30°	1085.5	1085.5	1067.7	1053.4	998.3	982.3	722.5	460.9	274.0	170.8	124.6
32.5°	969.8	953.8	955.6	939.5	905.7	893.3	642.4	402.2	236.7	138.8	108.5
35°	850.6	832.8	823.9	811.4	806.1	766.9	562.3	347.0	197.5	121.0	92.5
37.5°	733.1	715.3	708.2	688.6	660.2	651.3	475.1	288.3	165.5	99.6	76.5
40°	571.2	571.2	569.4	548.1	539.2	533.8	393.3	240.2	135.2	80.1	65.8
42.5°	455.5	460.9	457.3	448.4	428.8	425.3	327.4	195.7	110.3	67.6	55.2
45°	373.7	357.7	354.1	352.3	341.7	339.9	254.5	154.8	85.4	55.2	46.3
47.5°	274.0	272.3	275.8	266.9	254.5	265.1	201.1	117.4	67.6	44.5	39.1
50°	199.3	202.9	202.9	194.0	190.4	194.0	154.8	89.0	49.8	35.6	33.8
52.5°	149.5	147.7	145.9	147.7	145.9	145.9	115.7	65.8	39.1	28.5	26.7
55°	106.8	106.8	105.0	108.5	110.3	106.8	87.2	48.0	30.3	23.1	21.4
57.5°	74.7	74.7	71.2	74.7	74.7	78.3	62.3	35.6	24.9	17.8	17.8
60°	49.8	49.8	49.8	51.6	53.4	53.4	42.7	24.9	19.6	14.2	14.2
62.5°	33.8	33.8	33.8	35.6	35.6	39.1	30.3	19.6	16.0	12.5	10.7
65°	23.1	23.1	23.1	23.1	24.9	24.9	19.6	14.2	12.5	10.7	8.9
67.5°	14.2	16.0	14.2	16.0	16.0	16.0	12.5	10.7	8.9	7.1	5.3
70°	10.7	10.7	10.7	10.7	10.7	10.7	8.9	8.9	7.1	5.3	3.6
72.5°	7.1	7.1	7.1	7.1	7.1	7.1	5.3	5.3	5.3	3.6	3.6
75°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	1.8	1.8
77.5°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	0.0
80°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	0.0	0.0
82.5°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P601440
 CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL45R6G_ TL46S6G_ 4000K

CANDELA DISTRIBUTION (continued):

	157.5°	180°
0°	713.6	713.6
2.5°	654.8	642.4
5°	555.2	569.4
7.5°	484.0	466.2
10°	405.7	395.0
12.5°	352.3	347.0
15°	291.8	279.4
17.5°	250.9	238.4
20°	210.0	201.1
22.5°	179.7	174.4
25°	154.8	147.7
27.5°	133.5	129.9
30°	115.7	115.7
32.5°	99.6	103.2
35°	89.0	90.8
37.5°	76.5	80.1
40°	71.2	74.7
42.5°	60.5	67.6
45°	51.6	56.9
47.5°	44.5	49.8
50°	37.4	42.7
52.5°	33.8	37.4
55°	28.5	30.3
57.5°	23.1	24.9
60°	17.8	19.6
62.5°	14.2	16.0
65°	10.7	10.7
67.5°	7.1	8.9
70°	3.6	5.3
72.5°	1.8	1.8
75°	1.8	0.0
77.5°	0.0	0.0
80°	0.0	0.0
82.5°	0.0	0.0
85°	0.0	0.0
87.5°	0.0	0.0
90°	0.0	0.0

(END OF REPORT)