

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: io LED

Report Number: A1912412A001

Luminaire Tested:

Test Date: 2019-08-01

**Test Information**

Test Method: LM-79-08  
Report Number: A1912412A001  
Test Lab: EVERFINE  
Test Date: 2019-08-01  
Issue Date: 2019-08-03 16:02:49  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number:  
Description: LCR2089FSE010MW\*  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 755.4 lumens  
Efficiency: N/A  
Efficacy: 84.9 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.21 / 1.3  
Luminous Opening: Point Source (0m x 0m x 0m)  
CIE Type: Direct


Input Watts (W): 8.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: A1912412A001

CATALOG NUMBER:

### Luminous Intensity Polar Plot





TEST NUMBER: A1912412A001

CATALOG NUMBER:

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	80	77	75
3	93	84	76	70	91	82	75	70	79	73	69	77	72	67	74	70	66	64
4	86	75	67	61	84	74	66	60	71	65	59	69	63	59	67	62	58	56
5	79	67	59	53	77	66	58	52	64	57	52	62	56	51	60	55	51	49
6	73	61	52	46	72	60	52	46	58	51	46	57	50	45	55	49	45	43
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	38
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	34
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31
10	56	43	36	30	55	43	35	30	42	35	30	41	35	30	40	34	30	28

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	Luminaire represents a point source (luminous area is zero).			
5°	No luminance values can be calculated.			
10°				
15°				
20°				
25°				
30°				
35°				
40°				
45°				
50°				
55°				
60°				
65°				
70°				
75°				
80°				
85°				



TEST NUMBER: A1912412A001

CATALOG NUMBER:

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	30.6	4.0
10°-20°	87.1	11.5
20°-30°	130.3	17.2
30°-40°	151.4	20.0
40°-50°	146.3	19.4
50°-60°	116.2	15.4
60°-70°	68.0	9.0
70°-80°	21.4	2.8
80°-90°	4.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	248.0	32.8
0°-40°	399.4	52.9
0°-60°	661.8	87.6
0°-90°	755.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	755.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	324	324	324	324	324	
5°	324	320	325	320	324	31
15°	310	306	311	307	310	87
25°	283	281	286	284	283	131
35°	243	240	245	242	243	152
45°	190	187	193	191	190	147
55°	130	128	132	132	130	116
65°	67	67	70	71	67	66
75°	17	18	19	19	17	20
85°	3	4	4	3	3	4
90°	0	0	0	0	0	0
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0



TEST NUMBER: A1912412A001

CATALOG NUMBER:

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	324.4	324.4	324.4	324.4	324.4	324.4	324.4	324.4	324.4	324.4	324.4
0.5°	328.0	324.2	324.0	321.4	321.9	321.8	326.1	324.7	326.6	323.2	321.5
1°	326.6	324.6	321.6	322.6	322.6	322.3	326.4	325.2	328.1	325.5	320.3
1.5°	326.8	323.3	322.4	321.9	323.1	321.0	327.5	324.7	327.9	323.4	320.6
2°	325.8	323.9	322.4	322.6	322.2	322.8	327.4	325.0	326.3	322.9	320.4
2.5°	323.3	323.0	322.0	322.0	322.0	322.6	327.0	324.5	325.4	321.5	321.2
3°	325.2	323.9	320.7	321.3	320.8	324.6	326.5	323.3	326.2	322.5	321.4
3.5°	324.1	322.6	320.6	321.4	320.0	324.1	326.1	323.8	326.4	323.2	322.8
4°	325.0	322.0	321.1	322.2	320.6	324.3	326.3	323.8	325.2	322.0	322.3
4.5°	324.7	321.1	320.4	319.7	320.3	320.5	325.2	323.4	324.7	322.5	320.4
5°	323.8	321.8	320.8	316.8	319.9	320.0	324.6	323.5	324.8	323.5	320.7
5.5°	325.4	321.4	320.8	319.8	319.6	319.6	325.1	321.4	323.8	321.2	322.2
6°	323.8	320.2	320.4	319.2	319.3	321.1	326.3	321.8	324.0	322.1	321.5
6.5°	323.4	318.1	319.0	318.8	318.1	321.2	323.5	322.7	323.0	322.3	321.4
7°	323.1	321.0	317.8	317.9	317.5	319.2	324.1	321.6	322.0	320.6	321.9
7.5°	321.8	319.1	317.6	318.7	317.3	319.3	324.2	318.6	321.5	320.3	320.4
8°	320.6	318.7	318.4	316.3	317.6	319.1	321.2	320.3	320.8	318.5	318.6
8.5°	320.2	319.9	317.9	315.5	316.8	319.0	322.2	319.5	321.1	319.0	319.2
9°	321.4	320.4	315.8	315.4	315.7	317.5	321.0	319.4	321.9	317.2	317.1
9.5°	320.0	316.7	315.9	315.6	314.9	315.5	320.1	319.5	321.1	317.6	317.6
10°	318.7	313.5	315.6	314.8	314.1	316.3	318.3	318.4	319.1	317.4	316.7
10.5°	317.8	313.3	315.4	314.0	314.0	315.8	319.2	317.9	317.0	316.1	316.4
11°	316.4	313.0	313.0	311.4	313.0	315.1	319.5	317.4	317.4	315.4	315.7
11.5°	315.5	313.1	312.8	311.4	312.2	313.0	317.9	315.4	317.4	313.6	315.2
12°	315.0	311.9	311.2	310.2	310.8	312.6	318.2	315.4	315.7	313.2	314.3
12.5°	314.0	312.3	311.8	309.1	310.0	312.0	316.0	314.2	314.4	312.3	313.8
13°	312.9	310.6	310.6	309.5	310.1	313.3	315.7	314.7	314.2	312.7	313.2
13.5°	313.5	310.2	308.9	306.6	309.1	311.4	314.9	312.5	314.9	311.2	312.2
14°	312.6	309.4	308.6	307.0	308.3	309.0	315.1	311.4	314.9	314.6	312.3
14.5°	312.7	308.7	307.7	305.0	307.4	308.1	311.8	310.2	312.7	309.8	309.6
15°	309.7	308.2	305.8	305.0	306.2	308.3	311.1	310.2	310.9	310.2	308.4
15.5°	310.4	307.4	305.7	303.9	304.1	306.8	308.3	309.3	309.4	308.0	307.1
16°	309.6	304.2	304.5	302.9	303.7	306.2	309.5	308.4	310.2	306.5	307.7
16.5°	308.6	303.3	302.5	303.2	302.9	305.8	308.0	308.1	308.3	307.2	305.6
17°	306.8	303.3	302.6	300.1	302.6	303.6	306.5	306.2	307.2	304.8	305.2
17.5°	303.7	301.4	301.4	300.0	301.4	301.1	307.8	304.4	306.6	303.6	302.4
18°	302.4	300.4	300.5	298.4	300.1	300.8	307.9	302.5	304.8	303.1	302.8
18.5°	302.1	300.0	299.3	299.0	299.2	299.2	302.0	302.5	304.0	300.5	300.2
19°	301.0	298.6	298.2	297.8	297.8	298.4	303.7	301.0	303.5	300.3	300.5
19.5°	300.0	296.6	296.4	295.8	296.8	296.7	301.6	299.3	301.5	298.9	298.4
20°	298.9	295.4	295.3	293.6	295.3	296.3	299.9	297.7	300.8	297.8	297.8
20.5°	298.5	294.5	294.0	292.1	294.3	294.7	299.5	297.9	299.5	296.8	296.4
21°	296.7	293.1	292.2	291.3	293.3	294.5	297.6	296.0	298.3	294.9	294.5
21.5°	296.1	292.3	291.6	290.2	291.5	291.3	297.0	294.3	297.0	294.6	293.7
22°	294.2	289.3	290.1	288.2	289.3	290.0	295.4	293.2	295.2	293.6	291.9



TEST NUMBER: A1912412A001

CATALOG NUMBER:

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
22.5°	292.8	289.2	288.5	285.7	288.8	288.5	294.2	292.0	294.2	291.9	291.7
23°	293.5	286.9	287.9	285.8	286.5	287.9	292.9	290.6	292.5	290.5	290.0
23.5°	290.3	286.4	285.6	284.2	284.8	286.9	289.8	289.4	290.5	289.2	288.5
24°	288.6	284.7	283.2	282.2	284.1	285.0	288.9	288.0	289.0	287.5	286.8
24.5°	285.7	284.4	281.2	280.8	281.6	283.9	287.6	286.8	288.6	286.0	285.7
25°	283.4	280.7	280.0	277.7	281.0	281.9	286.5	284.6	286.5	284.7	284.1
25.5°	283.0	279.5	278.6	277.6	279.1	280.5	283.8	283.1	285.3	282.0	281.4
26°	281.0	277.6	277.4	275.8	277.4	278.4	281.8	281.9	283.4	281.8	280.2
26.5°	279.5	276.9	274.7	273.9	275.5	276.5	280.5	280.0	281.5	279.6	279.1
27°	277.5	274.9	273.2	272.5	273.6	275.7	279.0	277.7	279.9	278.1	277.3
27.5°	274.9	273.5	270.6	270.4	271.7	272.7	277.9	276.9	277.7	275.8	275.6
28°	274.5	270.9	268.9	267.5	270.7	270.3	274.9	273.7	275.2	274.0	273.0
28.5°	272.5	268.8	267.0	265.7	268.1	268.3	273.6	272.1	273.8	272.4	271.1
29°	270.6	266.7	264.9	262.6	265.7	267.2	271.6	269.7	272.0	270.7	269.7
29.5°	267.5	264.5	262.5	262.1	263.2	264.5	269.0	266.9	269.8	268.8	268.2
30°	266.4	262.3	261.4	260.0	261.5	263.0	267.7	265.3	268.6	267.7	266.0
30.5°	262.6	259.6	259.0	258.2	260.2	261.2	265.5	263.6	266.5	263.1	263.8
31°	260.6	257.5	257.2	256.2	257.4	259.5	262.6	261.1	264.6	261.9	261.7
31.5°	259.9	256.0	255.2	255.7	255.0	255.6	260.4	259.6	261.5	261.2	259.4
32°	258.6	254.4	252.7	252.1	252.7	254.2	259.5	257.6	260.9	258.6	257.5
32.5°	255.0	251.7	250.6	250.0	250.2	252.2	256.6	254.8	257.4	256.0	256.0
33°	253.0	249.0	248.6	246.4	249.2	249.6	254.1	253.0	255.6	253.7	252.9
33.5°	249.2	246.5	246.7	243.2	246.7	247.6	251.4	251.0	252.8	251.6	249.8
34°	246.6	244.4	244.3	242.0	244.0	245.7	249.0	248.0	251.1	250.4	248.2
34.5°	244.7	242.3	242.1	241.6	241.8	243.4	247.0	246.3	248.4	248.2	246.3
35°	242.6	240.4	240.3	239.6	239.6	241.0	244.9	243.3	244.9	244.0	244.4
35.5°	240.2	237.6	238.1	236.7	236.9	238.2	242.0	241.1	244.0	242.2	242.4
36°	237.7	235.5	235.4	233.5	234.0	235.6	240.0	238.8	241.5	239.4	239.6
36.5°	235.3	233.5	233.1	232.2	232.0	233.0	237.1	236.2	238.5	237.0	236.8
37°	232.4	231.1	229.8	229.2	229.5	230.0	235.1	233.7	235.8	234.9	234.8
37.5°	230.4	228.5	227.7	226.3	227.5	227.6	232.7	230.9	233.6	232.2	232.1
38°	228.4	226.0	225.3	223.6	225.1	224.8	229.6	228.5	230.8	229.6	229.2
38.5°	225.3	223.4	222.8	221.6	221.9	222.6	226.6	226.1	228.4	227.7	226.9
39°	221.8	221.0	220.0	219.1	219.6	220.4	223.7	223.6	226.1	225.0	224.5
39.5°	219.8	218.4	217.2	216.5	216.9	217.6	221.8	220.6	223.5	222.3	222.3
40°	217.5	215.8	214.6	213.8	213.7	215.0	219.7	218.4	220.5	219.4	220.1
40.5°	215.4	213.6	212.2	210.8	211.0	212.3	216.8	215.2	217.7	217.1	217.1
41°	212.8	211.0	209.7	208.8	208.0	210.3	213.9	212.4	215.4	214.1	214.3
41.5°	210.2	208.1	207.0	206.2	205.3	207.9	211.1	209.6	212.2	211.6	211.8
42°	207.4	205.4	204.6	203.6	203.1	203.3	208.7	207.1	210.0	208.7	208.9
42.5°	204.7	203.0	201.6	201.0	200.6	201.5	204.9	204.6	206.3	205.8	206.1
43°	201.6	200.0	199.3	198.5	197.7	198.9	201.8	201.7	203.9	203.2	203.2
43.5°	198.5	197.2	196.9	195.8	194.6	195.7	199.2	199.0	201.4	200.3	200.3
44°	195.8	194.5	193.5	193.2	192.5	193.1	196.5	196.1	198.0	197.4	197.0
44.5°	192.9	191.4	190.9	190.4	189.8	190.5	193.6	193.4	195.6	194.7	194.2



TEST NUMBER: A1912412A001

CATALOG NUMBER:

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
45°	190.4	188.2	188.2	187.3	187.0	187.4	191.2	190.3	192.7	191.6	191.8
45.5°	187.8	185.5	185.2	184.1	183.8	184.6	188.1	186.8	189.7	188.8	189.1
46°	185.0	182.7	182.5	181.4	181.1	181.7	184.9	184.2	186.7	186.2	186.5
46.5°	182.1	180.1	179.4	178.7	178.4	178.8	182.2	181.5	183.7	183.6	183.9
47°	179.1	176.9	176.2	175.8	175.5	175.8	179.2	178.6	180.6	180.3	180.8
47.5°	176.1	174.4	173.0	172.6	172.5	173.0	176.1	175.7	177.7	177.2	177.6
48°	172.8	171.0	170.6	169.7	169.4	170.1	173.2	172.6	175.1	174.4	174.2
48.5°	170.2	168.4	167.7	167.4	167.0	167.0	170.4	169.6	172.3	171.9	171.6
49°	167.4	165.3	164.6	164.1	163.7	163.8	167.2	166.6	168.7	168.7	168.6
49.5°	164.3	162.5	161.6	161.0	160.2	161.0	164.2	163.7	165.8	165.4	165.0
50°	161.2	159.5	158.9	157.8	157.4	158.5	161.2	160.6	162.7	162.4	162.2
50.5°	158.2	156.4	155.7	154.9	154.2	155.9	158.1	157.4	159.8	159.7	159.3
51°	155.2	153.3	152.8	152.2	151.3	152.9	155.1	154.4	156.8	156.3	156.2
51.5°	151.9	150.3	149.5	149.1	148.4	149.9	152.3	151.7	154.0	153.5	153.6
52°	148.6	147.0	146.9	145.9	145.2	146.5	149.2	148.7	150.8	150.4	150.8
52.5°	145.4	143.9	143.9	142.8	142.1	143.2	146.2	146.0	147.9	147.3	147.7
53°	142.3	140.6	140.5	140.0	139.4	140.1	143.1	143.0	144.8	144.4	144.5
53.5°	139.2	137.6	137.6	136.7	136.5	137.3	139.8	140.1	141.8	141.1	141.4
54°	136.0	134.3	134.2	133.8	133.5	134.2	136.5	137.0	138.8	138.0	138.3
54.5°	132.7	131.1	130.9	130.5	130.5	130.9	133.5	133.8	135.5	135.0	135.0
55°	129.9	128.1	128.2	127.4	127.5	127.9	130.5	130.4	132.4	131.9	132.0
55.5°	126.6	125.2	125.0	124.6	124.4	125.2	127.2	127.3	129.1	128.9	128.7
56°	123.3	122.1	121.8	121.7	121.6	122.2	124.3	124.4	126.1	125.5	126.0
56.5°	120.2	118.9	118.6	118.5	118.6	119.2	121.3	121.5	122.8	122.8	122.8
57°	117.1	115.7	115.6	115.4	115.6	116.0	118.3	118.4	119.8	119.7	119.8
57.5°	113.9	112.6	112.6	112.1	112.6	112.8	115.0	115.3	116.6	116.6	116.6
58°	110.7	109.4	109.2	109.0	109.6	109.7	112.3	112.2	113.4	113.5	113.5
58.5°	107.6	106.4	106.1	105.8	106.6	106.9	109.3	109.2	110.4	110.2	110.4
59°	104.2	103.0	103.0	102.9	103.5	103.9	106.1	105.9	107.2	107.1	107.2
59.5°	101.2	99.8	99.8	99.9	100.4	101.1	102.9	102.8	104.0	104.0	104.1
60°	97.9	96.7	96.5	96.8	97.3	98.1	99.8	99.6	100.8	100.8	101.0
60.5°	94.8	93.5	93.4	93.6	94.2	95.1	96.8	96.5	97.8	97.7	97.8
61°	91.5	90.4	90.5	90.5	91.2	91.9	93.7	93.3	94.6	94.6	94.7
61.5°	88.4	87.4	87.7	87.7	88.1	88.8	90.6	90.4	91.6	91.2	91.6
62°	85.3	84.3	84.3	84.6	85.0	85.9	87.8	87.3	88.5	88.4	88.6
62.5°	82.4	81.2	81.1	81.5	82.0	82.8	84.7	84.3	85.4	85.3	85.5
63°	79.2	78.1	78.0	78.5	79.2	79.6	81.8	81.4	82.4	82.2	82.4
63.5°	76.0	74.9	75.0	75.4	76.3	76.6	78.7	78.4	79.2	79.2	79.2
64°	72.8	71.8	72.0	72.3	73.2	73.8	75.7	75.3	76.0	76.0	76.4
64.5°	69.6	68.8	68.8	69.3	70.1	71.0	72.8	72.3	72.9	72.9	73.2
65°	66.8	65.7	65.9	66.4	67.3	68.2	69.9	69.4	69.9	69.8	70.1
65.5°	63.8	62.6	62.9	63.3	64.4	65.4	67.0	66.4	67.0	66.7	66.9
66°	60.7	59.6	60.0	60.3	61.7	62.4	63.9	63.3	64.0	63.9	63.8
66.5°	57.7	56.7	56.8	57.5	58.8	59.5	61.0	60.3	61.0	61.0	60.9
67°	54.9	53.8	53.9	54.6	55.9	56.8	58.1	57.5	58.0	57.8	58.2





TEST NUMBER: A1912412A001

CATALOG NUMBER:

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
67.5°	51.9	50.9	51.1	51.7	53.2	54.2	55.4	54.7	55.2	55.0	55.4
68°	49.0	47.9	48.2	48.9	50.4	51.2	52.4	51.8	52.2	52.2	52.5
68.5°	46.1	45.2	45.3	46.2	47.5	48.6	49.7	49.0	49.3	49.3	49.6
69°	43.3	42.5	42.7	43.4	44.9	45.9	47.0	46.3	46.5	46.5	46.9
69.5°	40.6	39.6	39.9	40.7	42.2	43.2	44.2	43.5	43.7	43.8	44.2
70°	38.1	37.1	37.3	38.2	39.6	40.7	41.5	40.9	41.1	41.1	41.4
70.5°	35.4	34.4	34.7	35.5	37.1	38.2	39.1	38.3	38.4	38.6	38.8
71°	33.0	31.9	32.2	32.9	34.6	35.7	36.4	35.8	35.8	35.9	36.1
71.5°	30.4	29.6	29.7	30.6	32.3	33.1	33.8	33.4	33.4	33.4	33.7
72°	28.0	27.2	27.4	28.2	29.9	30.6	31.2	31.0	31.0	31.0	31.2
72.5°	25.9	25.0	25.2	26.0	27.7	28.2	28.8	28.7	28.7	28.6	28.9
73°	23.6	22.9	23.1	23.9	25.5	25.8	26.3	26.5	26.4	26.4	26.7
73.5°	21.7	20.9	21.3	22.0	23.4	23.5	24.0	24.5	24.4	24.2	24.6
74°	19.9	19.3	19.5	20.3	21.6	21.6	22.0	22.5	22.4	22.3	22.6
74.5°	18.1	17.6	17.8	18.5	20.0	19.7	20.2	20.7	20.7	20.5	20.9
75°	16.6	16.2	16.4	17.0	18.3	18.0	18.3	19.0	19.1	18.8	19.1
75.5°	15.2	14.9	15.2	15.6	16.8	16.4	16.8	17.4	17.3	17.2	17.4
76°	14.0	13.7	14.1	14.4	15.5	15.2	15.5	16.0	15.9	15.9	16.0
76.5°	13.2	13.0	13.1	13.4	14.2	14.0	14.5	14.8	14.8	14.6	14.7
77°	12.5	12.4	12.5	12.7	13.2	13.2	13.6	13.7	13.7	13.5	13.6
77.5°	11.8	11.8	11.9	12.1	12.4	12.4	12.7	12.9	12.9	12.7	12.6
78°	11.3	11.2	11.3	11.5	11.6	11.7	12.0	12.3	12.3	12.0	11.8
78.5°	10.6	10.6	10.7	11.0	11.2	11.1	11.5	11.7	11.6	11.6	11.2
79°	10.0	10.0	10.1	10.3	10.4	10.5	10.8	11.0	11.2	10.8	10.5
79.5°	9.4	9.4	9.5	9.7	9.8	9.9	10.3	10.4	10.5	10.5	10.1
80°	8.9	8.8	8.8	9.1	9.2	9.3	9.6	9.7	9.9	9.7	9.5
80.5°	8.3	8.2	8.4	8.7	8.6	8.7	9.0	9.1	9.4	9.2	8.8
81°	7.7	7.6	7.8	8.0	8.4	8.3	8.4	8.5	8.7	8.5	8.3
81.5°	7.1	7.1	7.2	7.4	7.3	7.5	7.7	8.1	8.3	8.1	7.9
82°	6.6	6.6	6.7	6.8	6.7	6.9	7.2	7.2	7.5	7.4	7.2
82.5°	6.0	6.0	5.9	6.3	6.2	6.2	6.5	6.7	7.0	6.8	6.6
83°	5.4	5.5	5.5	5.8	5.7	5.7	6.2	6.2	6.4	6.2	6.1
83.5°	4.8	4.9	4.9	5.1	5.1	5.1	5.4	5.4	6.0	5.5	5.4
84°	4.3	4.0	4.4	4.6	4.4	4.4	4.8	5.1	5.2	5.2	5.0
84.5°	3.8	3.8	3.9	4.1	4.2	4.0	4.4	4.4	4.6	4.5	4.3
85°	3.2	3.2	3.3	3.5	3.5	3.3	3.7	4.1	4.2	4.2	4.0
85.5°	2.8	2.8	2.8	2.9	3.0	3.0	3.1	3.2	3.7	3.4	3.2
86°	2.2	2.2	2.4	2.5	2.4	2.2	2.4	2.9	3.0	2.8	2.8
86.5°	1.7	1.7	1.8	2.0	1.9	2.0	2.0	2.2	2.5	2.4	2.2
87°	1.2	1.3	1.3	1.5	1.4	1.2	1.3	1.9	1.9	2.1	1.9
87.5°	0.8	0.7	0.8	1.0	0.8	0.9	1.1	1.2	1.4	1.3	1.2
88°	0.2	0.3	0.5	0.6	0.3	0.3	0.7	0.7	0.8	0.9	0.8
88.5°	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.1	0.3	0.3	0.1
89°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
89.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1912412A001

CATALOG NUMBER:

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
91°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
91.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
93°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
93.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
94°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
94.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
96°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
96.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
101°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
101.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
103°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
103.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
104°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
104.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
106°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
106.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
108°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
108.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
109°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
109.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
111°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
111.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
112°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1912412A001

CATALOG NUMBER:

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
113°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
113.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
114°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
114.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
116°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
116.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
118°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
118.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
119°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
119.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
121°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
121.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
123°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
123.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
124°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
124.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
126°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
126.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
128°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
128.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
129°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
129.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
131°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
131.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
133°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
133.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
134°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
134.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1912412A001

CATALOG NUMBER:

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
136°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
136.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
138°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
138.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
139°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
139.5°	0.0	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140.5°	0.0	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
141°	0.0	0.2	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
141.5°	0.0	0.2	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142°	0.0	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
143°	0.0	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
143.5°	0.0	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
144°	0.0	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
144.5°	0.0	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145.5°	0.0	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
146°	0.0	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
146.5°	0.0	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147°	0.0	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
148°	0.0	0.1	0.1	0.1	0.1	0.0	0.0	0.1	0.0	0.0	0.0
148.5°	0.0	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
149°	0.0	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
149.5°	0.0	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
150.5°	0.0	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
151°	0.0	0.1	0.1	0.1	0.1	0.0	0.0	0.1	0.0	0.0	0.0
151.5°	0.0	0.1	0.1	0.1	0.1	0.0	0.0	0.1	0.0	0.0	0.0
152°	0.0	0.1	0.1	0.1	0.1	0.0	0.0	0.1	0.1	0.0	0.0
152.5°	0.0	0.1	0.1	0.1	0.1	0.0	0.0	0.1	0.1	0.0	0.0
153°	0.0	0.1	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.0	0.0
153.5°	0.0	0.1	0.1	0.1	0.2	0.1	0.0	0.1	0.1	0.0	0.0
154°	0.0	0.1	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1	0.1
154.5°	0.0	0.1	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1	0.1
155°	0.0	0.1	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.0	0.0
155.5°	0.0	0.1	0.1	0.1	0.1	0.1	0.0	0.2	0.1	0.0	0.0
156°	0.0	0.1	0.1	0.1	0.1	0.1	0.0	0.2	0.2	0.0	0.1
156.5°	0.0	0.1	0.1	0.1	0.1	0.1	0.0	0.1	0.2	0.0	0.0
157°	0.0	0.1	0.1	0.1	0.1	0.1	0.0	0.1	0.2	0.1	0.1



TEST NUMBER: A1912412A001

CATALOG NUMBER:

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
157.5°	0.0	0.1	0.1	0.1	0.2	0.1	0.1	0.1	0.3	0.1	0.1
158°	0.0	0.1	0.1	0.1	0.1	0.1	0.2	0.1	0.2	0.2	0.1
158.5°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2
159°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.1
159.5°	0.0	0.1	0.1	0.1	0.1	0.1	0.2	0.1	0.2	0.1	0.1
160°	0.0	0.1	0.1	0.1	0.1	0.1	0.2	0.1	0.2	0.1	0.1
160.5°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.0	0.1
161°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.0	0.1
161.5°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.0	0.1
162°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.0	0.1
162.5°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.0	0.1
163°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.0	0.1
163.5°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.0	0.1
164°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.0	0.1
164.5°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.0	0.1
165°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.0	0.1
165.5°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.0	0.1
166°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.0	0.1
166.5°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.0	0.1
167°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.0	0.1
167.5°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.0	0.1
168°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.0	0.1
168.5°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.0	0.1
169°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.0	0.1
169.5°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.0	0.1
170°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.0	0.1
170.5°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.0	0.1
171°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.0	0.1
171.5°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.0	0.1
172°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.0	0.1
172.5°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.0	0.1
173°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.0	0.1
173.5°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.0	0.1
174°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.0	0.1
174.5°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.0	0.1
175°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.0	0.1
175.5°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.0	0.1
176°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.0	0.1
176.5°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.0	0.1
177°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.0	0.1
177.5°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.0	0.1
178°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.0	0.1
178.5°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.0	0.1
179°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.0	0.1
179.5°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.0	0.1



TEST NUMBER: A1912412A001

CATALOG NUMBER:

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1912412A001

CATALOG NUMBER:

**CANDELA DISTRIBUTION (continued):**

	247.5°	270°	292.5°	315°	337.5°	360°
0°	324.4	324.4	324.4	324.4	324.4	324.4
0.5°	319.7	322.6	322.5	325.9	323.7	328.0
1°	319.7	323.2	322.9	326.8	325.5	326.6
1.5°	320.7	321.0	323.2	325.9	323.8	326.8
2°	321.6	319.9	323.6	326.3	323.4	325.8
2.5°	319.9	319.2	322.1	325.7	323.7	323.3
3°	319.8	322.2	321.8	326.3	325.4	325.2
3.5°	320.8	323.1	323.4	326.4	324.4	324.1
4°	320.6	320.7	322.7	325.6	322.7	325.0
4.5°	319.5	320.2	322.3	324.1	322.9	324.7
5°	319.2	320.1	321.0	326.4	321.7	323.8
5.5°	318.2	321.4	320.2	325.2	321.1	325.4
6°	318.8	320.0	320.9	325.8	322.3	323.8
6.5°	319.0	320.1	321.4	323.4	321.7	323.4
7°	320.6	319.0	320.7	325.1	320.5	323.1
7.5°	318.1	318.8	319.8	324.2	319.2	321.8
8°	317.6	318.3	319.7	320.5	318.7	320.6
8.5°	317.2	317.8	318.2	322.2	320.0	320.2
9°	319.0	316.0	317.9	321.1	316.6	321.4
9.5°	316.2	315.4	317.6	320.5	317.9	320.0
10°	314.7	314.4	316.6	321.0	317.3	318.7
10.5°	313.0	314.9	314.8	318.7	315.0	317.8
11°	312.7	313.8	314.1	318.0	316.9	316.4
11.5°	312.2	315.8	315.2	317.4	314.5	315.5
12°	313.2	314.0	313.9	316.6	313.3	315.0
12.5°	311.2	313.0	312.2	317.8	314.0	314.0
13°	311.3	313.3	312.6	316.2	315.6	312.9
13.5°	309.9	312.1	311.4	315.1	316.8	313.5
14°	308.1	309.8	309.6	314.6	313.5	312.6
14.5°	307.4	308.6	309.6	314.2	310.6	312.7
15°	307.8	307.4	308.2	314.2	310.2	309.7
15.5°	307.2	307.7	307.0	313.4	307.6	310.4
16°	304.9	307.5	306.5	310.9	306.4	309.6
16.5°	304.2	305.3	305.5	309.4	306.8	308.6
17°	303.5	303.5	305.4	309.1	306.9	306.8
17.5°	302.1	302.4	302.5	308.8	303.9	303.7
18°	301.5	300.0	301.9	306.4	303.8	302.4
18.5°	299.7	300.5	300.9	304.4	300.6	302.1
19°	297.8	299.0	299.9	304.3	300.8	301.0
19.5°	297.4	298.5	299.5	302.1	298.4	300.0
20°	297.4	297.4	298.8	303.0	297.3	298.9
20.5°	295.2	296.1	296.3	302.8	296.6	298.5
21°	294.4	294.2	295.7	300.6	295.8	296.7
21.5°	292.6	293.8	293.9	298.8	293.9	296.1
22°	291.7	293.6	293.7	296.1	292.6	294.2



TEST NUMBER: A1912412A001

CATALOG NUMBER:

**CANDELA DISTRIBUTION (continued):**

	247.5°	270°	292.5°	315°	337.5°	360°
22.5°	290.1	290.6	290.9	294.9	290.6	292.8
23°	288.6	289.0	289.0	293.1	291.7	293.5
23.5°	287.8	287.6	288.4	292.7	289.5	290.3
24°	285.9	288.3	285.0	290.3	286.4	288.6
24.5°	284.5	287.5	284.5	287.3	285.8	285.7
25°	281.8	284.0	284.4	287.3	284.2	283.4
25.5°	280.4	279.2	280.0	285.7	281.2	283.0
26°	278.9	280.0	278.0	282.8	281.1	281.0
26.5°	276.4	277.2	277.2	281.2	279.3	279.5
27°	275.8	276.6	276.6	279.5	276.5	277.5
27.5°	273.4	274.4	274.6	278.1	275.9	274.9
28°	272.6	272.9	272.9	276.5	273.1	274.5
28.5°	270.0	269.0	269.8	274.1	269.4	272.5
29°	268.3	268.2	267.8	272.1	268.5	270.6
29.5°	265.7	266.8	266.4	270.4	267.4	267.5
30°	264.5	264.3	265.5	267.4	265.0	266.4
30.5°	262.4	262.6	263.9	265.3	262.9	262.6
31°	260.9	260.1	260.8	263.3	260.2	260.6
31.5°	258.4	257.4	258.5	260.9	257.5	259.9
32°	256.7	256.5	256.7	258.7	255.6	258.6
32.5°	254.5	253.8	253.9	256.1	252.5	255.0
33°	252.5	251.6	249.9	253.6	250.1	253.0
33.5°	250.3	248.9	247.3	251.9	249.2	249.2
34°	247.8	247.5	246.7	249.3	246.7	246.6
34.5°	245.4	245.2	244.6	247.1	243.8	244.7
35°	243.4	241.8	242.1	244.9	241.3	242.6
35.5°	241.1	240.3	239.6	242.6	238.5	240.2
36°	238.4	238.7	237.2	241.2	236.7	237.7
36.5°	236.1	237.6	235.0	238.2	234.5	235.3
37°	233.2	232.2	232.5	236.1	232.4	232.4
37.5°	230.7	230.6	230.3	233.3	229.8	230.4
38°	228.6	227.3	227.8	230.2	226.8	228.4
38.5°	225.9	226.0	225.5	227.5	225.3	225.3
39°	223.2	223.5	223.3	225.3	223.2	221.8
39.5°	221.0	220.9	220.2	222.6	220.3	219.8
40°	218.4	218.4	218.0	219.2	217.0	217.5
40.5°	215.8	214.8	215.2	217.4	214.3	215.4
41°	213.3	212.4	212.4	214.5	211.4	212.8
41.5°	210.2	211.0	209.8	211.9	208.7	210.2
42°	207.5	208.1	207.1	208.4	206.5	207.4
42.5°	204.5	204.9	204.4	205.7	203.5	204.7
43°	201.5	202.2	201.8	203.4	200.8	201.6
43.5°	198.9	200.5	199.1	200.6	198.2	198.5
44°	196.2	196.7	196.6	197.9	195.3	195.8
44.5°	192.6	193.8	193.6	195.2	192.9	192.9





TEST NUMBER: A1912412A001

CATALOG NUMBER:

**CANDELA DISTRIBUTION (continued):**

	247.5°	270°	292.5°	315°	337.5°	360°
45°	190.4	191.1	190.7	192.1	189.7	190.4
45.5°	187.3	188.6	187.9	189.6	186.9	187.8
46°	184.5	185.6	185.2	186.8	184.3	185.0
46.5°	181.8	182.7	182.6	183.8	181.4	182.1
47°	179.0	180.0	179.6	180.8	178.9	179.1
47.5°	175.9	176.8	176.6	177.6	175.9	176.1
48°	173.1	174.3	173.8	174.4	173.0	172.8
48.5°	170.2	171.5	170.6	171.2	169.6	170.2
49°	167.3	168.2	167.6	168.4	167.2	167.4
49.5°	164.4	165.2	164.6	165.6	163.5	164.3
50°	161.2	162.5	161.5	162.6	160.8	161.2
50.5°	158.2	159.5	158.9	159.7	157.8	158.2
51°	155.5	156.6	155.9	156.7	154.4	155.2
51.5°	152.2	153.5	153.0	153.6	151.6	151.9
52°	149.4	150.4	149.7	150.6	148.9	148.6
52.5°	146.6	147.4	146.8	147.6	145.5	145.4
53°	143.6	144.6	144.0	144.5	142.1	142.3
53.5°	140.6	141.6	140.7	141.4	139.1	139.2
54°	137.4	138.3	137.6	138.2	135.9	136.0
54.5°	134.4	135.2	134.6	135.2	132.9	132.7
55°	131.1	132.2	131.3	132.1	129.7	129.9
55.5°	128.2	128.8	128.3	129.0	126.6	126.6
56°	125.2	125.7	125.4	125.9	123.3	123.3
56.5°	122.3	122.4	122.2	122.7	120.3	120.2
57°	119.2	119.6	119.0	119.3	117.5	117.1
57.5°	116.2	116.3	115.8	116.4	114.2	113.9
58°	112.9	113.2	112.7	113.3	110.8	110.7
58.5°	109.7	110.1	109.7	110.0	107.8	107.6
59°	106.7	107.0	106.5	106.8	104.5	104.2
59.5°	103.5	103.8	103.4	103.9	101.3	101.2
60°	100.5	100.7	100.3	100.7	98.2	97.9
60.5°	97.4	97.7	97.2	97.5	95.3	94.8
61°	94.2	94.7	94.3	94.5	92.2	91.5
61.5°	91.3	91.6	91.4	91.5	89.1	88.4
62°	88.3	88.7	88.5	88.5	86.0	85.3
62.5°	85.2	85.7	85.2	85.5	82.7	82.4
63°	82.0	82.8	82.3	82.4	79.7	79.2
63.5°	79.1	79.9	79.4	79.1	76.6	76.0
64°	76.1	76.8	76.5	76.0	73.7	72.8
64.5°	73.0	73.8	73.5	73.2	70.8	69.6
65°	70.0	70.7	70.5	70.3	67.8	66.8
65.5°	67.2	67.7	67.6	67.1	64.7	63.8
66°	64.1	64.7	64.6	64.1	61.8	60.7
66.5°	61.1	61.8	61.8	61.1	59.0	57.7
67°	58.1	58.9	58.8	57.9	56.0	54.9



TEST NUMBER: A1912412A001

CATALOG NUMBER:

**CANDELA DISTRIBUTION (continued):**

	247.5°	270°	292.5°	315°	337.5°	360°
67.5°	55.3	56.1	56.1	55.0	53.1	51.9
68°	52.6	53.2	52.9	51.9	50.3	49.0
68.5°	49.9	50.5	50.0	48.8	47.5	46.1
69°	47.1	47.7	47.0	45.8	44.7	43.3
69.5°	44.3	45.0	44.0	42.8	41.9	40.6
70°	41.7	42.4	41.1	39.9	39.3	38.1
70.5°	39.1	39.7	38.3	37.0	36.5	35.4
71°	36.5	37.1	35.5	34.1	34.0	33.0
71.5°	34.0	34.5	32.6	31.3	31.4	30.4
72°	31.7	32.1	29.9	28.7	29.0	28.0
72.5°	29.4	29.6	27.4	26.3	26.6	25.9
73°	27.1	27.2	25.1	24.1	24.5	23.6
73.5°	25.0	25.0	22.9	22.0	22.4	21.7
74°	23.0	22.9	21.1	20.2	20.5	19.9
74.5°	21.2	21.0	19.4	18.5	18.6	18.1
75°	19.4	19.2	17.6	17.1	16.9	16.6
75.5°	17.8	17.4	16.4	15.8	15.4	15.2
76°	16.2	15.7	14.9	14.5	14.1	14.0
76.5°	14.8	14.4	13.7	13.3	13.0	13.2
77°	13.6	13.2	12.6	12.3	12.2	12.5
77.5°	12.6	12.1	11.6	11.6	11.4	11.8
78°	11.6	11.3	11.0	11.0	10.9	11.3
78.5°	11.0	10.7	10.4	10.3	10.2	10.6
79°	10.3	10.1	9.8	9.7	9.6	10.0
79.5°	9.7	9.5	9.1	9.1	9.0	9.4
80°	9.2	9.0	8.5	8.4	8.4	8.9
80.5°	8.6	8.4	7.9	7.8	7.9	8.3
81°	8.2	7.8	7.2	7.2	7.2	7.7
81.5°	7.6	7.1	6.7	6.6	6.8	7.1
82°	7.0	6.7	6.0	5.9	6.1	6.6
82.5°	6.4	6.1	5.5	5.3	5.4	6.0
83°	6.2	5.5	4.9	4.8	4.8	5.4
83.5°	5.3	5.0	4.3	4.1	4.4	4.8
84°	4.8	4.6	3.8	3.4	3.8	4.3
84.5°	4.1	3.9	3.2	3.0	3.4	3.8
85°	4.0	3.4	2.7	2.6	2.9	3.2
85.5°	3.1	2.9	2.4	2.2	2.4	2.8
86°	2.6	2.5	1.9	1.7	1.8	2.2
86.5°	2.1	1.7	1.4	1.2	1.5	1.7
87°	1.9	1.5	1.0	0.8	1.0	1.2
87.5°	1.0	1.0	0.4	0.4	0.6	0.8
88°	0.6	0.5	0.1	0.0	0.2	0.2
88.5°	0.0	0.1	0.0	0.0	0.0	0.0
89°	0.0	0.0	0.0	0.0	0.0	0.0
89.5°	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1912412A001

CATALOG NUMBER:

**CANDELA DISTRIBUTION (continued):**

	247.5°	270°	292.5°	315°	337.5°	360°
90°	0.0	0.0	0.0	0.0	0.0	0.0
90.5°	0.0	0.0	0.0	0.0	0.0	0.0
91°	0.0	0.0	0.0	0.0	0.0	0.0
91.5°	0.0	0.0	0.0	0.0	0.0	0.0
92°	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0
93°	0.0	0.0	0.0	0.0	0.0	0.0
93.5°	0.0	0.0	0.0	0.0	0.0	0.0
94°	0.0	0.0	0.0	0.0	0.0	0.0
94.5°	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0
95.5°	0.0	0.0	0.0	0.0	0.0	0.0
96°	0.0	0.0	0.0	0.0	0.0	0.0
96.5°	0.0	0.0	0.0	0.0	0.0	0.0
97°	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0
98°	0.0	0.0	0.0	0.0	0.0	0.0
98.5°	0.0	0.0	0.0	0.0	0.0	0.0
99°	0.0	0.0	0.0	0.0	0.0	0.0
99.5°	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0
100.5°	0.0	0.0	0.0	0.0	0.0	0.0
101°	0.0	0.0	0.0	0.0	0.0	0.0
101.5°	0.0	0.0	0.0	0.0	0.0	0.0
102°	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0
103°	0.0	0.0	0.0	0.0	0.0	0.0
103.5°	0.0	0.0	0.0	0.0	0.0	0.0
104°	0.0	0.0	0.0	0.0	0.0	0.0
104.5°	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0
105.5°	0.0	0.0	0.0	0.0	0.0	0.0
106°	0.0	0.0	0.0	0.0	0.0	0.0
106.5°	0.0	0.0	0.0	0.0	0.0	0.0
107°	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0
108°	0.0	0.0	0.0	0.0	0.0	0.0
108.5°	0.0	0.0	0.0	0.0	0.0	0.0
109°	0.0	0.0	0.0	0.0	0.0	0.0
109.5°	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0
110.5°	0.0	0.0	0.0	0.0	0.0	0.0
111°	0.0	0.0	0.0	0.0	0.0	0.0
111.5°	0.0	0.0	0.0	0.0	0.0	0.0
112°	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1912412A001

CATALOG NUMBER:

**CANDELA DISTRIBUTION (continued):**

	247.5°	270°	292.5°	315°	337.5°	360°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0
113°	0.0	0.0	0.0	0.0	0.0	0.0
113.5°	0.0	0.0	0.0	0.0	0.0	0.0
114°	0.0	0.0	0.0	0.0	0.0	0.0
114.5°	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0
115.5°	0.0	0.0	0.0	0.0	0.0	0.0
116°	0.0	0.0	0.0	0.0	0.0	0.0
116.5°	0.0	0.0	0.0	0.0	0.0	0.0
117°	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0
118°	0.0	0.0	0.0	0.0	0.0	0.0
118.5°	0.0	0.0	0.0	0.0	0.0	0.0
119°	0.0	0.0	0.0	0.0	0.0	0.0
119.5°	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0
120.5°	0.0	0.0	0.0	0.0	0.0	0.0
121°	0.0	0.0	0.0	0.0	0.0	0.0
121.5°	0.0	0.0	0.0	0.0	0.0	0.0
122°	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0
123°	0.0	0.0	0.0	0.0	0.0	0.0
123.5°	0.0	0.0	0.0	0.0	0.0	0.0
124°	0.0	0.0	0.0	0.0	0.0	0.0
124.5°	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0
125.5°	0.0	0.0	0.0	0.0	0.0	0.0
126°	0.0	0.0	0.0	0.0	0.0	0.0
126.5°	0.0	0.0	0.0	0.0	0.0	0.0
127°	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0
128°	0.0	0.0	0.0	0.0	0.0	0.0
128.5°	0.0	0.0	0.0	0.0	0.0	0.0
129°	0.0	0.0	0.0	0.0	0.0	0.0
129.5°	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0
130.5°	0.0	0.0	0.0	0.0	0.0	0.0
131°	0.0	0.0	0.0	0.0	0.0	0.0
131.5°	0.0	0.0	0.0	0.0	0.0	0.0
132°	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0
133°	0.0	0.0	0.0	0.0	0.0	0.0
133.5°	0.0	0.0	0.0	0.0	0.0	0.0
134°	0.0	0.0	0.0	0.0	0.0	0.0
134.5°	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1912412A001

CATALOG NUMBER:

**CANDELA DISTRIBUTION (continued):**

	247.5°	270°	292.5°	315°	337.5°	360°
135°	0.0	0.0	0.0	0.0	0.0	0.0
135.5°	0.0	0.0	0.0	0.0	0.0	0.0
136°	0.0	0.0	0.0	0.0	0.0	0.0
136.5°	0.0	0.0	0.0	0.0	0.1	0.0
137°	0.0	0.0	0.0	0.0	0.1	0.0
137.5°	0.0	0.1	0.0	0.0	0.1	0.0
138°	0.0	0.1	0.0	0.0	0.1	0.0
138.5°	0.0	0.1	0.0	0.0	0.2	0.0
139°	0.0	0.1	0.0	0.1	0.1	0.0
139.5°	0.0	0.1	0.0	0.1	0.1	0.0
140°	0.0	0.2	0.0	0.1	0.1	0.0
140.5°	0.0	0.2	0.1	0.1	0.1	0.0
141°	0.0	0.1	0.1	0.1	0.1	0.0
141.5°	0.0	0.1	0.1	0.1	0.2	0.0
142°	0.0	0.1	0.1	0.2	0.2	0.0
142.5°	0.0	0.1	0.1	0.1	0.2	0.0
143°	0.0	0.1	0.1	0.1	0.2	0.0
143.5°	0.0	0.1	0.2	0.1	0.2	0.0
144°	0.0	0.1	0.2	0.1	0.2	0.0
144.5°	0.0	0.1	0.1	0.1	0.2	0.0
145°	0.0	0.1	0.1	0.1	0.2	0.0
145.5°	0.0	0.1	0.1	0.1	0.2	0.0
146°	0.0	0.1	0.1	0.1	0.2	0.0
146.5°	0.0	0.1	0.1	0.1	0.2	0.0
147°	0.0	0.1	0.1	0.1	0.2	0.0
147.5°	0.0	0.1	0.1	0.1	0.2	0.0
148°	0.0	0.1	0.1	0.1	0.2	0.0
148.5°	0.0	0.1	0.1	0.1	0.2	0.0
149°	0.0	0.1	0.1	0.1	0.2	0.0
149.5°	0.0	0.1	0.1	0.1	0.2	0.0
150°	0.0	0.1	0.1	0.1	0.2	0.0
150.5°	0.0	0.1	0.1	0.1	0.2	0.0
151°	0.0	0.1	0.1	0.1	0.2	0.0
151.5°	0.0	0.1	0.1	0.1	0.2	0.0
152°	0.0	0.1	0.1	0.1	0.2	0.0
152.5°	0.1	0.1	0.1	0.1	0.2	0.0
153°	0.0	0.1	0.1	0.1	0.2	0.0
153.5°	0.0	0.1	0.1	0.1	0.2	0.0
154°	0.0	0.1	0.1	0.1	0.2	0.0
154.5°	0.1	0.1	0.1	0.1	0.2	0.0
155°	0.0	0.1	0.1	0.1	0.2	0.0
155.5°	0.0	0.1	0.1	0.1	0.2	0.0
156°	0.1	0.1	0.1	0.1	0.2	0.0
156.5°	0.1	0.1	0.1	0.1	0.2	0.0
157°	0.1	0.1	0.1	0.1	0.2	0.0



TEST NUMBER: A1912412A001

CATALOG NUMBER:

**CANDELA DISTRIBUTION (continued):**

	247.5°	270°	292.5°	315°	337.5°	360°
157.5°	0.1	0.1	0.1	0.1	0.2	0.0
158°	0.2	0.1	0.1	0.1	0.2	0.0
158.5°	0.1	0.1	0.1	0.1	0.2	0.0
159°	0.1	0.1	0.1	0.1	0.2	0.0
159.5°	0.1	0.1	0.1	0.1	0.2	0.0
160°	0.1	0.1	0.1	0.1	0.2	0.0
160.5°	0.1	0.1	0.1	0.1	0.2	0.0
161°	0.1	0.1	0.1	0.1	0.2	0.0
161.5°	0.1	0.1	0.1	0.1	0.2	0.0
162°	0.1	0.1	0.1	0.1	0.2	0.0
162.5°	0.1	0.1	0.1	0.1	0.2	0.0
163°	0.1	0.1	0.1	0.1	0.2	0.0
163.5°	0.1	0.1	0.1	0.1	0.2	0.0
164°	0.1	0.1	0.1	0.1	0.2	0.0
164.5°	0.1	0.1	0.1	0.1	0.2	0.0
165°	0.1	0.1	0.1	0.1	0.2	0.0
165.5°	0.1	0.1	0.1	0.1	0.2	0.0
166°	0.1	0.1	0.1	0.1	0.2	0.0
166.5°	0.1	0.1	0.1	0.1	0.2	0.0
167°	0.1	0.1	0.1	0.1	0.2	0.0
167.5°	0.1	0.1	0.1	0.1	0.2	0.0
168°	0.1	0.1	0.1	0.1	0.2	0.0
168.5°	0.1	0.1	0.1	0.1	0.2	0.0
169°	0.1	0.1	0.1	0.1	0.2	0.0
169.5°	0.1	0.1	0.1	0.1	0.2	0.0
170°	0.1	0.1	0.1	0.1	0.2	0.0
170.5°	0.1	0.1	0.1	0.1	0.2	0.0
171°	0.1	0.1	0.1	0.1	0.2	0.0
171.5°	0.1	0.1	0.1	0.1	0.2	0.0
172°	0.1	0.1	0.1	0.1	0.2	0.0
172.5°	0.1	0.1	0.1	0.1	0.2	0.0
173°	0.1	0.1	0.1	0.1	0.2	0.0
173.5°	0.1	0.1	0.1	0.1	0.2	0.0
174°	0.1	0.1	0.1	0.1	0.2	0.0
174.5°	0.1	0.1	0.1	0.1	0.2	0.0
175°	0.1	0.1	0.1	0.1	0.2	0.0
175.5°	0.1	0.1	0.1	0.1	0.2	0.0
176°	0.1	0.1	0.1	0.1	0.2	0.0
176.5°	0.1	0.1	0.1	0.1	0.2	0.0
177°	0.1	0.1	0.1	0.1	0.2	0.0
177.5°	0.1	0.1	0.1	0.1	0.2	0.0
178°	0.1	0.1	0.1	0.1	0.2	0.0
178.5°	0.1	0.1	0.1	0.1	0.2	0.0
179°	0.1	0.1	0.1	0.1	0.2	0.0
179.5°	0.1	0.1	0.1	0.1	0.2	0.0



TEST NUMBER: A1912412A001

CATALOG NUMBER:

**CANDELA DISTRIBUTION (continued):**

	247.5°	270°	292.5°	315°	337.5°	360°
180°	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)