

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P601441

Luminaire Tested: **ML4DM10LSAWW9FS1E - TIR4D25AWW - TL45R6G_ TL46S6G_ 5000K**

Issue Date: 7/29/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P601441
 Test Lab: COOPER LIGHTING SOLUTIONS
 Issue Date: 7/29/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO
 Catalog Number: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL45R6G_ TL46S6G_ 5000K
 Description: DIRECT MOUNT, 25D WW OPTIC, LINEAR SPREAD LENS TRIM
 Light Source: (1) SELECTABLE LUMEN LED 90CRI / 5000K CCT
 Ballast/Driver: -

Summary

Lumens per Lamp: N/A
 Luminaire Lumens: 923.3 lumens
 Efficiency: N/A
 Efficacy: 76.9 lumens/watt
 Spacing Criteria (0/90/45): 1.21 / 0.78 / 1
 Luminous Opening: Circular (Dia: 0.21' x H: 0')
 CIE Type: Direct


Input Watts (W): 12
 Input Voltage (V): NR
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT



Meas			
Instrument	Identificatio		Calibration Due Date
Photometer	GONIO 1 11111111	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P601441
CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL45R6G_ TL46S6G_ 5000K

Luminous Intensity Polar Plot



TEST NUMBER: P601441

CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL45R6G_ TL46S6G_ 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76
4	94	85	79	74	92	84	78	73	82	76	72	79	75	72	78	74	71	69
5	88	78	72	67	86	77	71	67	76	70	66	74	69	65	72	68	65	63
6	83	73	66	61	81	72	65	61	70	65	60	69	64	60	67	63	59	58
7	78	68	61	56	77	67	60	56	65	60	55	64	59	55	63	58	55	53
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49
9	70	59	52	48	68	58	52	48	57	52	47	56	51	47	55	51	47	46
10	66	55	49	44	65	55	48	44	54	48	44	53	48	44	52	47	44	42

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	235466	235466	235466
5°	289997	233418	188630
10°	365525	220021	132359
15°	419483	190879	95456
20°	453036	164352	70600
25°	452234	134102	53794
30°	413618	104426	44082
35°	342651	79563	36543
40°	246043	58244	32193
45°	174381	39878	26570
50°	102326	25594	21909
55°	61438	17396	17396
60°	32903	12946	12946
65°	18081	9713	8368
70°	10340	6832	5170
75°	4514	4514	0
80°	3455	3455	0
85°	0	0	0

TEST NUMBER: P601441
 CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL45R6G_ TL46S6G_ 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.6	7.7
10°-20°	192.3	20.8
20°-30°	251.3	27.2
30°-40°	215.5	23.3
40°-50°	123.3	13.4
50°-60°	50.4	5.5
60°-70°	16.1	1.7
70°-80°	3.4	0.4
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	514.2	55.7
0°-40°	729.7	79.0
0°-60°	903.4	97.8
0°-90°	923.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	923.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	746	746	746	746	746	
5°	915	859	736	623	595	95
15°	1283	1012	584	352	292	362
25°	1298	894	385	184	154	594
35°	889	588	206	97	95	549
45°	390	266	89	48	60	297
55°	112	91	32	22	32	105
65°	24	20	13	9	11	26
75°	4	4	4	2	0	5
85°	0	0	0	0	0	1
90°	0	0	0	0	0	

TEST NUMBER: P601441

CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL45R6G_ TL46S6G_ 5000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	45°	67.5°	90°	112.5°	135°
0°	745.7	745.7	745.7	745.7	745.7	745.7	745.7	745.7	745.7	745.7	745.7
2.5°	818.2	835.0	829.4	838.7	836.8	820.1	803.4	777.3	751.3	736.4	702.9
5°	914.9	935.4	950.3	939.1	933.5	920.5	859.2	801.5	736.4	671.3	623.0
7.5°	1041.4	1035.8	1052.6	1019.1	1020.9	1015.4	926.1	814.5	714.1	619.3	550.5
10°	1140.0	1123.2	1140.0	1128.8	1106.5	1080.5	972.6	808.9	686.2	567.2	474.2
12.5°	1212.5	1234.8	1234.8	1208.8	1186.5	1156.7	1007.9	805.2	637.9	504.0	409.1
15°	1283.2	1290.6	1277.6	1257.1	1234.8	1173.4	1011.7	781.1	583.9	442.6	351.5
17.5°	1329.7	1331.5	1325.9	1307.3	1275.7	1238.5	987.5	758.7	533.7	394.2	295.7
20°	1348.2	1333.4	1331.5	1298.0	1270.1	1236.7	967.0	704.8	489.1	336.6	256.6
22.5°	1378.0	1342.7	1342.7	1309.2	1251.5	1246.0	955.9	643.4	427.7	288.2	219.4
25°	1298.0	1292.5	1303.6	1257.1	1212.5	1203.2	894.5	596.9	384.9	249.2	184.1
27.5°	1244.1	1229.2	1214.4	1184.6	1141.8	1119.5	844.3	537.4	334.7	208.3	156.2
30°	1134.4	1134.4	1115.8	1100.9	1043.3	1026.5	755.0	481.7	286.4	178.5	130.2
32.5°	1013.5	996.8	998.6	981.9	946.6	933.5	671.3	420.3	247.3	145.1	113.4
35°	888.9	870.3	861.0	848.0	842.4	801.5	587.7	362.6	206.4	126.5	96.7
37.5°	766.2	747.6	740.1	719.7	689.9	680.6	496.5	301.3	172.9	104.1	80.0
40°	596.9	596.9	595.1	572.8	563.5	557.9	411.0	251.1	141.3	83.7	68.8
42.5°	476.1	481.7	477.9	468.6	448.2	444.5	342.2	204.6	115.3	70.7	57.6
45°	390.5	373.8	370.1	368.2	357.1	355.2	265.9	161.8	89.3	57.6	48.4
47.5°	286.4	284.5	288.2	278.9	265.9	277.1	210.1	122.7	70.7	46.5	40.9
50°	208.3	212.0	212.0	202.7	199.0	202.7	161.8	93.0	52.1	37.2	35.3
52.5°	156.2	154.4	152.5	154.4	152.5	152.5	120.9	68.8	40.9	29.8	27.9
55°	111.6	111.6	109.7	113.4	115.3	111.6	91.1	50.2	31.6	24.2	22.3
57.5°	78.1	78.1	74.4	78.1	78.1	81.8	65.1	37.2	26.0	18.6	18.6
60°	52.1	52.1	52.1	53.9	55.8	55.8	44.6	26.0	20.5	14.9	14.9
62.5°	35.3	35.3	35.3	37.2	37.2	40.9	31.6	20.5	16.7	13.0	11.2
65°	24.2	24.2	24.2	24.2	26.0	26.0	20.5	14.9	13.0	11.2	9.3
67.5°	14.9	16.7	14.9	16.7	16.7	16.7	13.0	11.2	9.3	7.4	5.6
70°	11.2	11.2	11.2	11.2	11.2	11.2	9.3	9.3	7.4	5.6	3.7
72.5°	7.4	7.4	7.4	7.4	7.4	7.4	5.6	5.6	5.6	3.7	3.7
75°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	1.9	1.9
77.5°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	0.0
80°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	0.0	0.0
82.5°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P601441
 CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL45R6G_ TL46S6G_ 5000K

CANDELA DISTRIBUTION (continued):

	157.5°	180°
0°	745.7	745.7
2.5°	684.4	671.3
5°	580.2	595.1
7.5°	505.8	487.2
10°	424.0	412.8
12.5°	368.2	362.6
15°	305.0	292.0
17.5°	262.2	249.2
20°	219.4	210.1
22.5°	187.8	182.2
25°	161.8	154.4
27.5°	139.5	135.8
30°	120.9	120.9
32.5°	104.1	107.9
35°	93.0	94.8
37.5°	80.0	83.7
40°	74.4	78.1
42.5°	63.2	70.7
45°	53.9	59.5
47.5°	46.5	52.1
50°	39.1	44.6
52.5°	35.3	39.1
55°	29.8	31.6
57.5°	24.2	26.0
60°	18.6	20.5
62.5°	14.9	16.7
65°	11.2	11.2
67.5°	7.4	9.3
70°	3.7	5.6
72.5°	1.9	1.9
75°	1.9	0.0
77.5°	0.0	0.0
80°	0.0	0.0
82.5°	0.0	0.0
85°	0.0	0.0
87.5°	0.0	0.0
90°	0.0	0.0

(END OF REPORT)