

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P886072

Luminaire Tested: ML204LSFL95FS1E-TIR1D25NFL-TL2RDDB-468LM-3500K

Issue Date: 7/18/2024


Test Information

Test Method: LM-79-2019
Report Number: P886072
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2402-314-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/18/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML204LSFL95FS1E-TIR1D25NFL-TL2RDMB-468LM-3500K
Description: 2IN ROUND ML FLEX, SELECTABLE CCT, WITH 25D TIR, MATTE BLACK TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 95CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 358.1 lumens
Efficiency: N/A
Efficacy: 44.8 lumens/watt
Spacing Criteria (0/90/45): 0.45 / 0.45 / 0.52
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P886072

CATALOG NUMBER: ML204LSFL95FS1E-TIR1D25NFL-TL2RDDB-468LM-3500K

Luminous Intensity Polar Plot





TEST NUMBER: P886072

CATALOG NUMBER: ML204LSFL95FS1E-TIR1D25NFL-TL2RDMB-468LM-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	115	112	110	108	112	110	108	107	106	105	103	102	101	100	99	98	97	96	95	94	93	92	91	90	89	88	87	86	85	84																
2	110	106	103	100	108	105	102	99	101	99	97	99	97	95	96	94	93	91	90	89	88	87	86	85	84	83	82	81	80																	
3	106	101	97	94	104	100	96	93	97	94	92	95	92	90	93	91	89	87	86	85	84	83	82	81	80	79	78	77	76																	
4	102	96	92	88	101	95	91	88	93	90	87	91	88	86	89	87	85	84	83	82	81	80	79	78	77	76	75	74	73																	
5	98	92	87	84	97	91	87	83	89	86	83	88	85	82	86	84	81	80	79	78	77	76	75	74	73	72	71	70	69																	
6	95	88	83	80	94	87	83	79	86	82	79	84	81	78	83	80	78	77	76	75	74	73	72	71	70	69	68	67	66																	
7	92	84	80	76	90	84	79	76	83	79	76	81	78	75	80	77	75	74	73	72	71	70	69	68	67	66	65	64	63																	
8	88	81	76	73	87	80	76	73	79	75	73	79	75	72	78	74	72	71	70	69	68	67	66	65	64	63	62	61	60																	
9	86	78	73	70	85	77	73	70	77	73	70	76	72	70	75	72	69	68	67	66	65	64	63	62	61	60	59	58	57																	
10	83	75	70	67	82	75	70	67	74	70	67	73	70	67	73	69	67	66	65	64	63	62	61	60	59	58	57	56	55																	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	562157
5°	493778
10°	376044
15°	262185
20°	186233
25°	114103
30°	45406
35°	20478
40°	13268
45°	6908
50°	691
55°	774
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6908 cd/sqm



TEST NUMBER: P886072

CATALOG NUMBER: ML204LSFL95FS1E-TIR1D25NFL-TL2RDMB-468LM-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.6	24.5
10°-20°	144.2	40.3
20°-30°	94.2	26.3
30°-40°	24.4	6.8
40°-50°	7.2	2.0
50°-60°	0.5	0.1
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	326.0	91.0
0°-40°	350.4	97.8
0°-60°	358.1	100.0
0°-90°	358.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	358.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1139	
5°	997	88
15°	513	144
25°	210	94
35°	34	24
45°	10	7
55°	1	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P886072

CATALOG NUMBER: ML204LSFL95FS1E-TIR1D25NFL-TL2RDMB-468LM-3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1139.4
2.5°	1109.8
5°	997.0
7.5°	880.5
10°	750.6
12.5°	624.3
15°	513.3
17.5°	425.5
20°	354.7
22.5°	284.0
25°	209.6
27.5°	136.2
30°	79.7
32.5°	48.4
35°	34.0
37.5°	26.9
40°	20.6
42.5°	16.1
45°	9.9
47.5°	1.8
50°	0.9
52.5°	0.9
55°	0.9
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)