

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P886204

Luminaire Tested: ML204LSFL95FS1E-TIR1D55WFL-TL2RDMW-468LM-5000K

Issue Date: 6/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P886204
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2402-314-83)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 6/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML204LSFL95FS1E-TIR1D55WFL-TL2RDMW-468LM-5000K
Description: 2IN ROUND ML FLEX, SELECTABLE CCT, WITH 55D TIR, MATTE WHITE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 95CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 558.7 lumens
Efficiency: N/A
Efficacy: 69.8 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.82
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P886204
CATALOG NUMBER: ML204LSFL95FS1E-TIR1D55WFL-TL2RDMW-468LM-5000K

Luminous Intensity Polar Plot





TEST NUMBER: P886204
 CATALOG NUMBER: ML204LSFL95FS1E-TIR1D55WFL-TL2RDMW-468LM-5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87																			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81																			
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76																			
5	93	85	79	75	91	84	78	74	82	77	74	80	76	73	79	75	73	71																			
6	88	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67																			
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63																			
8	80	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	60	59																			
9	77	67	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56																			
10	73	64	58	55	72	64	58	55	63	58	54	62	58	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	349313
5°	347279
10°	337618
15°	315869
20°	281738
25°	224232
30°	156441
35°	83901
40°	40769
45°	19048
50°	9748
55°	6709
60°	6710
65°	6771
70°	7068
75°	7434
80°	8240
85°	5661

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19048 cd/sqm



TEST NUMBER: P886204

CATALOG NUMBER: ML204LSFL95FS1E-TIR1D55WFL-TL2RDMW-468LM-5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.1	11.8
10°-20°	172.0	30.8
20°-30°	185.9	33.3
30°-40°	92.5	16.6
40°-50°	23.8	4.3
50°-60°	7.6	1.4
60°-70°	5.5	1.0
70°-80°	3.9	0.7
80°-90°	1.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	424.0	75.9
0°-40°	516.5	92.4
0°-60°	547.9	98.1
0°-90°	558.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	558.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	708	
5°	701	66
15°	618	172
25°	412	186
35°	139	93
45°	27	24
55°	8	8
65°	6	6
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P886204
CATALOG NUMBER: ML204LSFL95FS1E-TIR1D55WFL-TL2RDMW-468LM-5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	708.0
2.5°	707.0
5°	701.2
7.5°	690.5
10°	673.9
12.5°	648.6
15°	618.4
17.5°	582.4
20°	536.6
22.5°	478.2
25°	411.9
27.5°	341.8
30°	274.6
32.5°	205.5
35°	139.3
37.5°	92.5
40°	63.3
42.5°	42.8
45°	27.3
47.5°	17.5
50°	12.7
52.5°	9.7
55°	7.8
57.5°	6.8
60°	6.8
62.5°	5.8
65°	5.8
67.5°	4.9
70°	4.9
72.5°	3.9
75°	3.9
77.5°	2.9
80°	2.9
82.5°	1.9
85°	1.0
87.5°	1.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)