

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P886212

Luminaire Tested: ML204LSFL95FS1E-TIR1D55WFL-TL2RDSL-468LM-3500K

Issue Date: 6/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P886212  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2402-314-84)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 6/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML204LSFL95FS1E-TIR1D55WFL-TL2RDSL-468LM-3500K  
Description: 2IN ROUND ML FLEX, SELECTABLE CCT, WITH 55D TIR, METALLIC SILVER TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 95CRI / 3500K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 507.4 lumens  
Efficiency: N/A  
Efficacy: 63.4 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.81  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P886212  
CATALOG NUMBER: ML204LSFL95FS1E-TIR1D55WFL-TL2RDSL-468LM-3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P886212

CATALOG NUMBER: ML204LSFL95FS1E-TIR1D55WFL-TL2RDSL-468LM-3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94																			
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88																			
3	103	97	93	89	102	96	92	88	93	90	87	91	88	86	89	86	84	83																			
4	99	92	86	82	97	90	86	82	88	84	81	86	83	80	84	81	79	78																			
5	94	86	81	77	92	85	80	76	83	79	76	82	78	75	80	77	74	73																			
6	90	81	76	72	88	80	75	71	79	74	71	78	74	70	76	73	70	69																			
7	86	77	71	67	84	76	71	67	75	70	67	74	69	66	73	69	66	65																			
8	82	73	67	63	81	72	67	63	71	66	63	70	66	63	69	65	62	61																			
9	78	69	63	60	77	68	63	59	68	63	59	67	62	59	66	62	59	58																			
10	75	66	60	56	74	65	60	56	64	59	56	64	59	56	63	59	56	55																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	334215
5°	331480
10°	320534
15°	297532
20°	263099
25°	208989
30°	144249
35°	78119
40°	36325
45°	15001
50°	5526
55°	2322
60°	1776
65°	1051
70°	1298
75°	1716
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 15001 cd/sqm



TEST NUMBER: P886212

CATALOG NUMBER: ML204LSFL95FS1E-TIR1D55WFL-TL2RDSL-468LM-3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	62.9	12.4
10°-20°	161.9	31.9
20°-30°	173.2	34.1
30°-40°	85.6	16.9
40°-50°	19.2	3.8
50°-60°	3.0	0.6
60°-70°	1.0	0.2
70°-80°	0.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	398.0	78.4
0°-40°	483.7	95.3
0°-60°	505.8	99.7
0°-90°	507.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	507.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	677	
5°	669	63
15°	582	162
25°	384	173
35°	130	86
45°	22	19
55°	3	3
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P886212

CATALOG NUMBER: ML204LSFL95FS1E-TIR1D55WFL-TL2RDSL-468LM-3500K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	677.4
2.5°	676.5
5°	669.3
7.5°	656.8
10°	639.8
12.5°	612.9
15°	582.5
17.5°	546.7
20°	501.1
22.5°	446.5
25°	383.9
27.5°	318.5
30°	253.2
32.5°	191.5
35°	129.7
37.5°	85.0
40°	56.4
42.5°	35.8
45°	21.5
47.5°	12.5
50°	7.2
52.5°	4.5
55°	2.7
57.5°	1.8
60°	1.8
62.5°	0.9
65°	0.9
67.5°	0.9
70°	0.9
72.5°	0.9
75°	0.9
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)