

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P886545

Luminaire Tested: ML310LSFL95FS1E-TIR4D25NFL-TL3RDMB-510LM-4000K

Issue Date: 7/18/2024

Test Information

Test Method: LM-79-2019
Report Number: P886545
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2402-314-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/18/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML310LSFL95FS1E-TIR4D25NFL-TL3RDMB-510LM-4000K
Description: 3IN ROUND ML FLEX, SELECTABLE CCT, WITH 25D TIR, MATTE BLACK TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 95CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 581.3 lumens
Efficiency: N/A
Efficacy: 72.7 lumens/watt
Spacing Criteria (0/90/45): 0.47 / 0.47 / 0.5
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P886545
CATALOG NUMBER: ML310LSFL95FS1E-TIR4D25NFL-TL3RDMB-510LM-4000K

Luminous Intensity Polar Plot





TEST NUMBER: P886545

CATALOG NUMBER: ML310LSFL95FS1E-TIR4D25NFL-TL3RDDB-510LM-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	109	112	111	109	107	107	105	104		103	102	101		100	99	98	96
2	111	107	104	101	109	105	103	100	102	100	98		100	98	96		97	95	94	93
3	107	102	99	96	105	101	98	95	99	96	93		96	94	92		94	92	91	89
4	104	98	94	91	102	97	93	90	95	92	89		93	90	88		91	89	87	86
5	100	94	90	87	99	93	89	86	92	88	86		90	87	85		89	86	84	83
6	97	91	86	83	96	90	86	83	88	85	82		87	84	82		86	83	81	80
7	94	87	83	80	93	87	83	80	86	82	79		85	81	79		84	81	78	77
8	91	84	80	77	90	84	80	77	83	79	76		82	79	76		81	78	76	75
9	89	81	77	74	88	81	77	74	80	77	74		79	76	74		79	76	73	73
10	86	79	75	72	85	79	74	72	78	74	72		77	74	71		77	73	71	70

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	449218
5°	416618
10°	321415
15°	212419
20°	134342
25°	65810
30°	24308
35°	6532
40°	1403
45°	558
50°	205
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 558 cd/sqm



TEST NUMBER: P886545

CATALOG NUMBER: ML310LSFL95FS1E-TIR4D25NFL-TL3RDMB-510LM-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.1	28.6
10°-20°	261.0	44.9
20°-30°	132.0	22.7
30°-40°	20.4	3.5
40°-50°	1.7	0.3
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	559.2	96.2
0°-40°	579.5	99.7
0°-60°	581.3	100.0
0°-90°	581.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	581.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2049	
5°	1893	166
15°	936	261
25°	272	132
35°	24	20
45°	2	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P886545
CATALOG NUMBER: ML310LSFL95FS1E-TIR4D25NFL-TL3RDMB-510LM-4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2048.6
2.5°	2016.2
5°	1892.7
7.5°	1694.1
10°	1443.5
12.5°	1177.7
15°	935.7
17.5°	738.3
20°	575.7
22.5°	419.9
25°	272.0
27.5°	169.9
30°	96.0
32.5°	51.9
35°	24.4
37.5°	9.8
40°	4.9
42.5°	3.1
45°	1.8
47.5°	1.2
50°	0.6
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)