

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P886335

Luminaire Tested: ML204LSFL9FS1E-TIR1D40FL-TL2RDMWB-550LM-2700K

Issue Date: 6/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P886335
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2402-314-80)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 6/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML204LSFL9FS1E-TIR1D40FL-TL2RDMWB-550LM-2700K
Description: 2IN ROUND ML FLEX, SELECTABLE CCT, WITH 40D TIR, MATTE WHITE BAFFLED TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 597.7 lumens
Efficiency: N/A
Efficacy: 75.7 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.68
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P886335
CATALOG NUMBER: ML204LSFL9FS1E-TIR1D40FL-TL2RDMWB-550LM-2700K

Luminous Intensity Polar Plot





TEST NUMBER: P886335

CATALOG NUMBER: ML204LSFL9FS1E-TIR1D40FL-TL2RDMWB-550LM-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94																			
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	94	92	90	88																			
3	104	98	93	90	102	96	92	89	94	90	87	91	89	86	89	87	85	83																			
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	79																			
5	95	87	82	78	93	86	81	78	85	80	77	83	79	76	81	78	76	74																			
6	91	83	77	73	89	82	77	73	80	76	73	79	75	72	78	74	72	70																			
7	87	79	73	69	86	78	73	69	77	72	69	76	71	68	74	71	68	67																			
8	83	75	69	66	82	74	69	65	73	69	65	72	68	65	71	67	65	63																			
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	64	62	60																			
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	65	62	59	58																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	527028
5°	516164
10°	474989
15°	396930
20°	305103
25°	208554
30°	131602
35°	67458
40°	31559
45°	14653
50°	8443
55°	6881
60°	5921
65°	5837
70°	5770
75°	5719
80°	5683
85°	5661

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14653 cd/sqm



TEST NUMBER: P886335

CATALOG NUMBER: ML204LSFL9FS1E-TIR1D40FL-TL2RDMWB-550LM-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.4	16.1
10°-20°	213.5	35.7
20°-30°	176.7	29.6
30°-40°	75.4	12.6
40°-50°	18.6	3.1
50°-60°	7.2	1.2
60°-70°	5.2	0.9
70°-80°	3.4	0.6
80°-90°	1.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	486.7	81.4
0°-40°	562.2	94.1
0°-60°	588.0	98.4
0°-90°	597.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	597.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1068	
5°	1042	96
15°	777	214
25°	383	177
35°	112	75
45°	21	19
55°	8	7
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P886335

CATALOG NUMBER: ML204LSFL9FS1E-TIR1D40FL-TL2RDMWB-550LM-2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1068.2
2.5°	1065.2
5°	1042.2
7.5°	1002.2
10°	948.1
12.5°	868.1
15°	777.1
17.5°	679.1
20°	581.1
22.5°	483.1
25°	383.1
27.5°	297.0
30°	231.0
32.5°	170.0
35°	112.0
37.5°	73.0
40°	49.0
42.5°	34.0
45°	21.0
47.5°	13.0
50°	11.0
52.5°	9.0
55°	8.0
57.5°	7.0
60°	6.0
62.5°	6.0
65°	5.0
67.5°	5.0
70°	4.0
72.5°	4.0
75°	3.0
77.5°	3.0
80°	2.0
82.5°	2.0
85°	1.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)