

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P886554

Luminaire Tested: ML310LSFL95FS1E-TIR4D25NFL-TL3RDMB-850LM-3500K

Issue Date: 7/18/2024

Test Information

Test Method: LM-79-2019
Report Number: P886554
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2402-314-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/18/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML310LSFL95FS1E-TIR4D25NFL-TL3RDMB-850LM-3500K
Description: 3IN ROUND ML FLEX, SELECTABLE CCT, WITH 25D TIR, MATTE BLACK TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 95CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 924.2 lumens
Efficiency: N/A
Efficacy: 68.0 lumens/watt
Spacing Criteria (0/90/45): 0.47 / 0.47 / 0.5
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct


Input Watts (W): 13.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P886554

CATALOG NUMBER: ML310LSFL95FS1E-TIR4D25NFL-TL3RDMB-850LM-3500K

Luminous Intensity Polar Plot





TEST NUMBER: P886554

CATALOG NUMBER: ML310LSFL95FS1E-TIR4D25NFL-TL3RDDB-850LM-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	109	112	111	109	107	107	105	104	103	102	101	100	99	98	96				96															
2	111	107	104	101	109	105	103	100	102	100	98	100	98	96	97	95	94	93				93															
3	107	102	99	96	105	101	98	95	99	96	93	96	94	92	94	92	91	89				89															
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86				86															
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	83				83															
6	97	91	86	83	96	90	86	83	88	85	82	87	84	82	86	83	81	80				80															
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	78	77				77															
8	91	84	80	77	90	84	80	77	83	79	76	82	79	76	81	78	76	75				75															
9	89	81	77	74	88	81	77	74	80	77	74	79	76	74	79	76	73	73				73															
10	86	79	75	72	85	79	74	72	78	74	72	77	74	71	77	73	71	70				70															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	714307
5°	662490
10°	511102
15°	337754
20°	213612
25°	104619
30°	38639
35°	10413
40°	2233
45°	899
50°	341
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 899 cd/sqm



TEST NUMBER: P886554

CATALOG NUMBER: ML310LSFL95FS1E-TIR4D25NFL-TL3RDMB-850LM-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	264.2	28.6
10°-20°	415.1	44.9
20°-30°	209.8	22.7
30°-40°	32.4	3.5
40°-50°	2.7	0.3
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	889.1	96.2
0°-40°	921.5	99.7
0°-60°	924.2	100.0
0°-90°	924.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	924.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3258	
5°	3010	264
15°	1488	415
25°	432	210
35°	39	32
45°	3	3
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P886554

CATALOG NUMBER: ML310LSFL95FS1E-TIR4D25NFL-TL3RDMB-850LM-3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	3257.5
2.5°	3206.0
5°	3009.7
7.5°	2693.8
10°	2295.4
12.5°	1872.6
15°	1487.8
17.5°	1173.9
20°	915.4
22.5°	667.6
25°	432.4
27.5°	270.2
30°	152.6
32.5°	82.6
35°	38.9
37.5°	15.5
40°	7.8
42.5°	4.9
45°	2.9
47.5°	1.9
50°	1.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)