

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P886441

Luminaire Tested: ML204LSFLD2W1E-TIR1D25NFL-TL2RDMB-400LM-3000K

Issue Date: 7/18/2024

Test Information

Test Method: LM-79-2019
Report Number: P886441
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2402-314-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/18/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML204LSFLD2W1E-TIR1D25NFL-TL2RDMB-400LM-3000K
Description: 2IN ROUND ML FLEX, SELECTABLE CCT, WITH 25D TIR, MATTE BLACK TRIM
Light Source: (1) D2W LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 309.6 lumens
Efficiency: N/A
Efficacy: 49.9 lumens/watt
Spacing Criteria (0/90/45): 0.45 / 0.45 / 0.52
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 6.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P886441

CATALOG NUMBER: ML204LSFLD2W1E-TIR1D25NFL-TL2RDMB-400LM-3000K

Luminous Intensity Polar Plot





TEST NUMBER: P886441

CATALOG NUMBER: ML204LSFLD2W1E-TIR1D25NFL-TL2RDMB-400LM-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	112	110	108	112	110	108	107	106	105	103		102	101	100		99	98	97	96
2	110	106	103	100	108	105	102	99	101	99	97		99	97	95		96	94	93	91
3	106	101	97	94	104	100	96	93	97	94	92		95	92	90		93	91	89	87
4	102	96	92	88	101	95	91	88	93	90	87		91	88	86		89	87	85	84
5	98	92	87	84	97	91	87	83	89	86	83		88	85	82		86	84	81	80
6	95	88	83	80	94	87	83	79	86	82	79		84	81	78		83	80	78	77
7	92	84	80	76	90	84	79	76	83	79	76		81	78	75		80	77	75	74
8	88	81	76	73	87	80	76	73	79	75	73		79	75	72		78	74	72	71
9	86	78	73	70	85	77	73	70	77	73	70		76	72	70		75	72	69	68
10	83	75	70	67	82	75	70	67	74	70	67		73	70	67		73	69	67	66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	485979
5°	426868
10°	325143
15°	226635
20°	161031
25°	98642
30°	39253
35°	17708
40°	11464
45°	5931
50°	614
55°	688
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5931 cd/sqm



TEST NUMBER: P886441

CATALOG NUMBER: ML204LSFLD2W1E-TIR1D25NFL-TL2RDDB-400LM-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.8	24.5
10°-20°	124.7	40.3
20°-30°	81.4	26.3
30°-40°	21.1	6.8
40°-50°	6.2	2.0
50°-60°	0.4	0.1
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	281.8	91.0
0°-40°	302.9	97.9
0°-60°	309.6	100.0
0°-90°	309.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	309.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	985	
5°	862	76
15°	444	125
25°	181	81
35°	29	21
45°	8	6
55°	1	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P886441

CATALOG NUMBER: ML204LSFLD2W1E-TIR1D25NFL-TL2RDMB-400LM-3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	985.0
2.5°	959.5
5°	861.9
7.5°	761.2
10°	649.0
12.5°	539.8
15°	443.7
17.5°	367.8
20°	306.7
22.5°	245.5
25°	181.2
27.5°	117.7
30°	68.9
32.5°	41.8
35°	29.4
37.5°	23.2
40°	17.8
42.5°	13.9
45°	8.5
47.5°	1.5
50°	0.8
52.5°	0.8
55°	0.8
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)