

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P886488

Luminaire Tested: ML204LSFLD2W1E-TIR1D55WFL-TL2RDMB-400LM-3500K

Issue Date: 6/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P886488
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2402-314-85)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 6/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML204LSFLD2W1E-TIR1D55WFL-TL2RDDB-400LM-3500K
Description: 2IN ROUND ML FLEX, SELECTABLE CCT, WITH 55D TIR, MATTE BLACK TRIM
Light Source: (1) D2W LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 390.9 lumens
Efficiency: N/A
Efficacy: 63.0 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.81
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 6.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P886488
CATALOG NUMBER: ML204LSFLD2W1E-TIR1D55WFL-TL2RDMB-400LM-3500K

Luminous Intensity Polar Plot





TEST NUMBER: P886488

CATALOG NUMBER: ML204LSFLD2W1E-TIR1D55WFL-TL2RDDB-400LM-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94																			
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	89																			
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83																			
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	80	78																			
5	94	87	81	77	93	86	81	77	84	80	76	82	78	75	81	77	75	73																			
6	90	82	76	72	89	81	76	72	80	75	71	78	74	71	77	73	71	69																			
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65																			
8	82	73	68	64	81	73	67	64	72	67	63	71	66	63	70	66	63	62																			
9	79	69	64	60	77	69	64	60	68	63	60	67	63	60	66	62	60	58																			
10	75	66	61	57	74	66	60	57	65	60	57	64	60	57	63	59	56	55																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	259074
5°	257537
10°	249694
15°	232764
20°	207077
25°	163152
30°	113542
35°	58725
40°	26535
45°	10048
50°	2763
55°	602
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10048 cd/sqm



TEST NUMBER: P886488

CATALOG NUMBER: ML204LSFLD2W1E-TIR1D55WFL-TL2RDDB-400LM-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.0	12.5
10°-20°	126.8	32.4
20°-30°	135.6	34.7
30°-40°	65.5	16.8
40°-50°	13.0	3.3
50°-60°	1.0	0.3
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	311.3	79.6
0°-40°	376.8	96.4
0°-60°	390.9	100.0
0°-90°	390.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	390.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	525	
5°	520	49
15°	456	127
25°	300	136
35°	98	66
45°	14	13
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P886488

CATALOG NUMBER: ML204LSFLD2W1E-TIR1D55WFL-TL2RDMB-400LM-3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	525.1
2.5°	525.1
5°	520.0
7.5°	511.4
10°	498.4
12.5°	478.9
15°	455.7
17.5°	429.0
20°	394.4
22.5°	348.9
25°	299.7
27.5°	249.2
30°	199.3
32.5°	149.5
35°	97.5
37.5°	62.8
40°	41.2
42.5°	25.3
45°	14.4
47.5°	7.2
50°	3.6
52.5°	2.2
55°	0.7
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)