

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P886718

Luminaire Tested: ML310LSFL9FS1E-TIR4D40FL-TL3RDMW-1000LM-3000K

Issue Date: 7/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P886718
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2402-314-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML310LSFL9FS1E-TIR4D40FL-TL3RDMW-1000LM-3000K
Description: 3IN ROUND ML FLEX, SELECTABLE CCT, WITH 40D TIR, MATTE WHITE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1241.6 lumens
Efficiency: N/A
Efficacy: 90.0 lumens/watt
Spacing Criteria (0/90/45): 0.67 / 0.67 / 0.62
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P886718
CATALOG NUMBER: ML310LSFL9FS1E-TIR4D40FL-TL3RDMW-1000LM-3000K

Luminous Intensity Polar Plot





TEST NUMBER: P886718

CATALOG NUMBER: ML310LSFL9FS1E-TIR4D40FL-TL3RDMW-1000LM-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95					95			
2	110	105	102	99	108	104	101	98	101	98	96	98	96	94	95	93	92	90					90			
3	105	100	96	92	103	99	95	92	96	93	90	94	91	89	92	89	87	86					86			
4	101	95	90	87	100	94	90	86	92	88	85	90	87	84	88	86	83	82					82			
5	97	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79					79			
6	94	87	82	78	93	86	81	78	84	80	77	83	80	77	82	79	76	75					75			
7	91	83	78	75	89	82	78	74	81	77	74	80	76	74	79	76	73	72					72			
8	87	80	75	71	86	79	74	71	78	74	71	77	73	71	76	73	70	69					69			
9	84	76	72	68	83	76	71	68	75	71	68	74	71	68	74	70	68	67					67			
10	81	74	69	66	81	73	69	66	72	68	65	72	68	65	71	68	65	64					64			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	608285
5°	590313
10°	539514
15°	460025
20°	336099
25°	180639
30°	62921
35°	14964
40°	7128
45°	4807
50°	4605
55°	5161
60°	5000
65°	5396
70°	5321
75°	5253
80°	5177
85°	5284

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 62.5°
 Luminance: 5414 cd/sqm



TEST NUMBER: P886718

CATALOG NUMBER: ML310LSFL9FS1E-TIR4D40FL-TL3RDMW-1000LM-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	247.6	19.9
10°-20°	550.4	44.3
20°-30°	348.7	28.1
30°-40°	51.6	4.2
40°-50°	12.8	1.0
50°-60°	11.6	0.9
60°-70°	10.1	0.8
70°-80°	6.5	0.5
80°-90°	2.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1146.7	92.4
0°-40°	1198.3	96.5
0°-60°	1222.7	98.5
0°-90°	1241.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1241.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2774	
5°	2682	248
15°	2026	550
25°	747	349
35°	56	52
45°	16	13
55°	14	12
65°	10	10
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P886718

CATALOG NUMBER: ML310LSFL9FS1E-TIR4D40FL-TL3RDMW-1000LM-3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2774.0
2.5°	2757.4
5°	2681.8
7.5°	2565.8
10°	2423.0
12.5°	2238.6
15°	2026.4
17.5°	1766.5
20°	1440.3
22.5°	1089.3
25°	746.6
27.5°	474.2
30°	248.5
32.5°	113.9
35°	55.9
37.5°	37.3
40°	24.9
42.5°	17.6
45°	15.5
47.5°	14.5
50°	13.5
52.5°	13.5
55°	13.5
57.5°	12.4
60°	11.4
62.5°	11.4
65°	10.4
67.5°	9.3
70°	8.3
72.5°	7.2
75°	6.2
77.5°	5.2
80°	4.1
82.5°	3.1
85°	2.1
87.5°	1.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)