

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P300525

Luminaire Tested: **ML4D09_27D2WE - TIR50WFL55 - TL43R2GBNBB - TL44S2GBNBB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P300525
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1902-156-39)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: ML4D09_27D2WE - TIR50WFL55 - TL43R2GBNBB - TL44S2GBNBB
Description: ML4 2700K, 900LM DIM-TO-WARM, 55 DEG WFL OPTIC, WITH ROUND/SQUARE
DIFFUSED CLEAR LENS, BRUSH NICKEL FLANGE, BLACK LENS FRAME
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 503.0 lumens
Efficiency: N/A
Efficacy: 44.9 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.73
Luminous Opening: Circular (Dia: 0.19' x H: 0')
CIE Type: Direct


Input Watts (W): 11.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P300525

CATALOG NUMBER: ML4D09_27D2WE - TIR50WFL55 - TL43R2GBNBB - TL44S2GBNBB

Luminous Intensity Polar Plot





TEST NUMBER: P300525

CATALOG NUMBER: ML4D09_27D2WE - TIR50WFL55 - TL43R2GBNBB - TL44S2GBNBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |
| 1 | 114 | 111 | 109 | 107 | 111 | 109 | 107 | 105 | 105 | 103 | 102 | 101 | 100 | 99 | 98 | 97 | 96 | 94 |
| 2 | 108 | 104 | 100 | 97 | 106 | 102 | 99 | 96 | 99 | 96 | 94 | 96 | 94 | 92 | 93 | 91 | 90 | 88 |
| 3 | 103 | 97 | 93 | 89 | 101 | 96 | 92 | 88 | 93 | 90 | 87 | 91 | 88 | 85 | 89 | 86 | 84 | 82 |
| 4 | 99 | 91 | 86 | 82 | 97 | 90 | 85 | 82 | 88 | 84 | 81 | 86 | 83 | 80 | 84 | 81 | 79 | 77 |
| 5 | 94 | 86 | 81 | 76 | 92 | 85 | 80 | 76 | 83 | 79 | 75 | 82 | 78 | 75 | 80 | 77 | 74 | 73 |
| 6 | 90 | 81 | 76 | 72 | 88 | 80 | 75 | 71 | 79 | 74 | 71 | 78 | 73 | 70 | 76 | 73 | 70 | 68 |
| 7 | 86 | 77 | 71 | 67 | 84 | 76 | 71 | 67 | 75 | 70 | 67 | 74 | 70 | 66 | 73 | 69 | 66 | 65 |
| 8 | 82 | 73 | 67 | 63 | 81 | 72 | 67 | 63 | 71 | 66 | 63 | 70 | 66 | 63 | 69 | 65 | 62 | 61 |
| 9 | 78 | 69 | 64 | 60 | 77 | 69 | 63 | 60 | 68 | 63 | 60 | 67 | 63 | 59 | 66 | 62 | 59 | 58 |
| 10 | 75 | 66 | 60 | 57 | 74 | 66 | 60 | 57 | 65 | 60 | 57 | 64 | 60 | 56 | 63 | 59 | 56 | 55 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 307539 |
| 5° | 299322 |
| 10° | 276261 |
| 15° | 241303 |
| 20° | 197842 |
| 25° | 147105 |
| 30° | 95880 |
| 35° | 54252 |
| 40° | 29007 |
| 45° | 15988 |
| 50° | 9704 |
| 55° | 6117 |
| 60° | 3898 |
| 65° | 2767 |
| 70° | 2280 |
| 75° | 1506 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P300525

CATALOG NUMBER: ML4D09_27D2WE - TIR50WFL55 - TL43R2GBNBB - TL44S2GBNBB

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 70.9 | 14.1 |
| 10°-20° | 165.1 | 32.8 |
| 20°-30° | 155.4 | 30.9 |
| 30°-40° | 74.7 | 14.9 |
| 40°-50° | 24.3 | 4.8 |
| 50°-60° | 8.5 | 1.7 |
| 60°-70° | 3.1 | 0.6 |
| 70°-80° | 1.1 | 0.2 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 391.3 | 77.8 |
| 0°-40° | 466.1 | 92.7 |
| 0°-60° | 498.9 | 99.2 |
| 0°-90° | 503.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 503.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 789 | |
| 5° | 765 | 71 |
| 15° | 598 | 165 |
| 25° | 342 | 155 |
| 35° | 114 | 75 |
| 45° | 29 | 24 |
| 55° | 9 | 9 |
| 65° | 3 | 3 |
| 75° | 1 | 1 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P300525

CATALOG NUMBER: ML4D09_27D2WE - TIR50WFL55 - TL43R2GBNBB - TL44S2GBNBB

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|-------|
| 0° | 788.9 |
| 2.5° | 782.9 |
| 5° | 764.9 |
| 7.5° | 735.9 |
| 10° | 697.9 |
| 12.5° | 650.9 |
| 15° | 597.9 |
| 17.5° | 538.9 |
| 20° | 476.9 |
| 22.5° | 410.9 |
| 25° | 342.0 |
| 27.5° | 276.0 |
| 30° | 213.0 |
| 32.5° | 158.0 |
| 35° | 114.0 |
| 37.5° | 81.0 |
| 40° | 57.0 |
| 42.5° | 41.0 |
| 45° | 29.0 |
| 47.5° | 21.0 |
| 50° | 16.0 |
| 52.5° | 12.0 |
| 55° | 9.0 |
| 57.5° | 7.0 |
| 60° | 5.0 |
| 62.5° | 4.0 |
| 65° | 3.0 |
| 67.5° | 2.0 |
| 70° | 2.0 |
| 72.5° | 1.0 |
| 75° | 1.0 |
| 77.5° | 1.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

(END OF REPORT)