

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P886749

Luminaire Tested: ML310LSFL9FS1E-TIR4D55WFL-TL3RDMW-1000LM-3500K

Issue Date: 7/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P886749  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2402-314-7)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 7/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML310LSFL9FS1E-TIR4D55WFL-TL3RDMW-1000LM-3500K  
Description: 3IN ROUND ML FLEX, SELECTABLE CCT, WITH 55D TIR, MATTE WHITE TRIM  
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1225.4 lumens  
Efficiency: N/A  
Efficacy: 88.8 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.76  
Luminous Opening: Circular (Dia: 0.25' x H: 0')CIE Type: Direct

Input Watts (W): 13.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P886749  
CATALOG NUMBER: ML310LSFL9FS1E-TIR4D55WFL-TL3RDMW-1000LM-3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P886749

CATALOG NUMBER: ML310LSFL9FS1E-TIR4D55WFL-TL3RDMW-1000LM-3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88			
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	84	83			
4	99	92	87	83	97	91	86	82	89	85	82	87	83	81	85	82	80	78			
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74			
6	91	82	77	73	89	82	76	73	80	76	72	79	75	72	78	74	71	70			
7	87	78	73	69	85	78	72	69	76	72	68	75	71	68	74	70	68	66			
8	83	74	69	65	82	74	69	65	73	68	65	72	68	65	71	67	64	63			
9	80	71	65	62	79	70	65	62	70	65	62	69	64	61	68	64	61	60			
10	76	68	62	59	76	67	62	59	66	62	59	66	61	58	65	61	58	57			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	415866
5°	407351
10°	382781
15°	349491
20°	307840
25°	247272
30°	125336
35°	43500
40°	13454
45°	6636
50°	6550
55°	6958
60°	7017
65°	7212
70°	7565
75°	7286
80°	6693
85°	5284

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 77.5°  
 Luminance: 7598 cd/sqm



TEST NUMBER: P886749

CATALOG NUMBER: ML310LSFL9FS1E-TIR4D55WFL-TL3RDMW-1000LM-3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	172.4	14.1
10°-20°	428.4	35.0
20°-30°	442.3	36.1
30°-40°	121.7	9.9
40°-50°	19.0	1.6
50°-60°	15.9	1.3
60°-70°	13.8	1.1
70°-80°	9.0	0.7
80°-90°	2.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1043.2	85.1
0°-40°	1164.9	95.1
0°-60°	1199.8	97.9
0°-90°	1225.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1225.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1896	
5°	1851	172
15°	1540	428
25°	1022	442
35°	162	122
45°	21	19
55°	18	16
65°	14	14
75°	9	9
85°	2	3
90°	0	



TEST NUMBER: P886749

CATALOG NUMBER: ML310LSFL9FS1E-TIR4D55WFL-TL3RDMW-100LM-3500K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1896.5
2.5°	1889.0
5°	1850.6
7.5°	1792.8
10°	1719.1
12.5°	1633.5
15°	1539.5
17.5°	1434.7
20°	1319.2
22.5°	1195.2
25°	1022.0
27.5°	793.3
30°	495.0
32.5°	288.6
35°	162.5
37.5°	86.6
40°	47.0
42.5°	24.6
45°	21.4
47.5°	20.3
50°	19.2
52.5°	18.2
55°	18.2
57.5°	17.1
60°	16.0
62.5°	15.0
65°	13.9
67.5°	12.8
70°	11.8
72.5°	9.6
75°	8.6
77.5°	7.5
80°	5.3
82.5°	4.3
85°	2.1
87.5°	1.1
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)