

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P300530

Luminaire Tested: **ML4D09_27D2WE - TIR50WFL55 - TL41RBN - TL42SBN**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P300530
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1902-156-44)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: ML4D09_27D2WE - TIR50WFL55 - TL41RBN - TL42SBN
Description: ML4 2700K, 900LM DIM-TO-WARM, 55 DEG WFL OPTIC, WITH ROUND/SQUARE PINHOLE BRUSH NICKEL FLANGE
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 541.0 lumens
Efficiency: N/A
Efficacy: 48.3 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.73
Luminous Opening: Circular (Dia: 0.19' x H: 0')
CIE Type: Direct


Input Watts (W): 11.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P300530

CATALOG NUMBER: ML4D09_27D2WE - TIR50WFL55 - TL41RBN - TL42SBN

Luminous Intensity Polar Plot





TEST NUMBER: P300530

CATALOG NUMBER: ML4D09_27D2WE - TIR50WFL55 - TL41RBN - TL42SBN

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102		102	100	99		98	97	96	95
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94	92	91	89
3	104	98	94	90	102	97	93	90	94	91	88		92	89	87		90	87	85	84
4	100	93	88	84	98	92	87	83	90	86	82		88	84	82		86	83	81	79
5	95	88	82	79	94	87	82	78	85	81	77		83	80	77		82	79	76	75
6	91	83	78	74	90	82	77	74	81	76	73		79	76	73		78	75	72	71
7	87	79	73	70	86	78	73	69	77	72	69		76	72	69		75	71	68	67
8	84	75	69	66	82	74	69	66	73	69	65		72	68	65		71	68	65	64
9	80	71	66	62	79	71	66	62	70	65	62		69	65	62		68	64	62	60
10	77	68	63	59	76	68	63	59	67	62	59		66	62	59		65	62	59	58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	351239
5°	341976
10°	315014
15°	275123
20°	225513
25°	170935
30°	107268
35°	50969
40°	20356
45°	9924
50°	5458
55°	2719
60°	1559
65°	922
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P300530

CATALOG NUMBER: ML4D09_27D2WE - TIR50WFL55 - TL41RBN - TL42SBN

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.0	15.0
10°-20°	188.2	34.8
20°-30°	178.7	33.0
30°-40°	72.6	13.4
40°-50°	15.5	2.9
50°-60°	4.3	0.8
60°-70°	0.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	447.9	82.8
0°-40°	520.5	96.2
0°-60°	540.3	99.9
0°-90°	541.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	541.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	901	
5°	874	81
15°	682	188
25°	397	179
35°	107	73
45°	18	15
55°	4	4
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P300530

CATALOG NUMBER: ML4D09_27D2WE - TIR50WFL55 - TL41RBN - TL42SBN

CANDELA DISTRIBUTION (FULL):

	0°
0°	901.0
2.5°	893.9
5°	873.9
7.5°	841.9
10°	795.8
12.5°	742.8
15°	681.7
17.5°	613.7
20°	543.6
22.5°	472.5
25°	397.4
27.5°	319.3
30°	238.3
32.5°	165.2
35°	107.1
37.5°	66.1
40°	40.0
42.5°	26.0
45°	18.0
47.5°	13.0
50°	9.0
52.5°	7.0
55°	4.0
57.5°	3.0
60°	2.0
62.5°	1.0
65°	1.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)