

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P886784

Luminaire Tested: ML310LSFLD2W1E-TIR4D25NFL-TL3RDDB-600LM-2700K

Issue Date: 7/18/2024

Test Information

Test Method: LM-79-2019
Report Number: P886784
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2402-314-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/18/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML310LSFLD2W1E-TIR4D25NFL-TL3RDMB-600LM-2700K
Description: 3IN ROUND ML FLEX, SELECTABLE CCT, WITH 25D TIR, MATTE BLACK TRIM
Light Source: (1) D2W LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 599.0 lumens
Efficiency: N/A
Efficacy: 63.1 lumens/watt
Spacing Criteria (0/90/45): 0.47 / 0.47 / 0.5
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct


Input Watts (W): 9.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P886784

CATALOG NUMBER: ML310LSFLD2W1E-TIR4D25NFL-TL3RDMB-600LM-2700K

Luminous Intensity Polar Plot





TEST NUMBER: P886784

CATALOG NUMBER: ML310LSFLD2W1E-TIR4D25NFL-TL3RDMB-600LM-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	115	113	111	109	112	111	109	107	107	105	104	103	102	101	100	99	98	96	96	95	94	93	92	91	90	89	88	87	86	85	84	83	82	81	80	79	78	77	76	75	74	73	72	71	70									
2	111	107	104	101	109	105	103	100	102	100	98	96	94	92	90	88	86	84	82	80	78	76	74	72	70	68	66	64	62	60	58	56	54	52	50	48	46	44	42	40	38	36	34	32	30	28	26	24	22	20				
3	107	102	99	96	105	101	98	95	99	96	93	90	88	86	84	82	80	78	76	74	72	70	68	66	64	62	60	58	56	54	52	50	48	46	44	42	40	38	36	34	32	30	28	26	24	22	20							
4	104	98	94	91	102	97	93	90	95	92	89	86	84	82	80	78	76	74	72	70	68	66	64	62	60	58	56	54	52	50	48	46	44	42	40	38	36	34	32	30	28	26	24	22	20									
5	100	94	90	87	99	93	89	86	92	88	86	84	82	80	78	76	74	72	70	68	66	64	62	60	58	56	54	52	50	48	46	44	42	40	38	36	34	32	30	28	26	24	22	20										
6	97	91	86	83	96	90	86	83	88	85	82	80	78	76	74	72	70	68	66	64	62	60	58	56	54	52	50	48	46	44	42	40	38	36	34	32	30	28	26	24	22	20												
7	94	87	83	80	93	87	83	80	86	82	79	77	75	73	71	69	67	65	63	61	59	57	55	53	51	49	47	45	43	41	39	37	35	33	31	29	27	25	23	21	19	17	15	13	11	9	7	5	3	1				
8	91	84	80	77	90	84	80	77	83	79	76	74	72	70	68	66	64	62	60	58	56	54	52	50	48	46	44	42	40	38	36	34	32	30	28	26	24	22	20	18	16	14	12	10	8	6	4	2	0					
9	89	81	77	74	88	81	77	74	80	77	74	72	70	68	66	64	62	60	58	56	54	52	50	48	46	44	42	40	38	36	34	32	30	28	26	24	22	20	18	16	14	12	10	8	6	4	2	0						
10	86	79	75	72	85	79	74	72	78	74	72	70	68	66	64	62	60	58	56	54	52	50	48	46	44	42	40	38	36	34	32	30	28	26	24	22	20	18	16	14	12	10	8	6	4	2	0							

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	462923
5°	429341
10°	331234
15°	218889
20°	138449
25°	67818
30°	25042
35°	6746
40°	1431
45°	589
50°	205
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 589 cd/sqm



TEST NUMBER: P886784

CATALOG NUMBER: ML310LSFLD2W1E-TIR4D25NFL-TL3RDMB-600LM-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.2	28.6
10°-20°	269.0	44.9
20°-30°	136.0	22.7
30°-40°	21.0	3.5
40°-50°	1.7	0.3
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	576.2	96.2
0°-40°	597.2	99.7
0°-60°	599.0	100.0
0°-90°	599.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	599.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2111	
5°	1950	171
15°	964	269
25°	280	136
35°	25	21
45°	2	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P886784

CATALOG NUMBER: ML310LSFLD2W1E-TIR4D25NFL-TL3RDMB-600LM-2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2111.1
2.5°	2077.8
5°	1950.5
7.5°	1745.8
10°	1487.6
12.5°	1213.7
15°	964.2
17.5°	760.8
20°	593.3
22.5°	432.7
25°	280.3
27.5°	175.1
30°	98.9
32.5°	53.5
35°	25.2
37.5°	10.1
40°	5.0
42.5°	3.1
45°	1.9
47.5°	1.3
50°	0.6
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)