

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P601377

Luminaire Tested: **ML4DM06WFL9FS1E - TIR4D55WFL - TL43R2G_ TL44S2G_ 5000K**

Issue Date: 7/29/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P601377
 Test Lab: COOPER LIGHTING SOLUTIONS
 Issue Date: 7/29/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO
 Catalog Number: ML4DM06WFL9FS1E - TIR4D55WFL - TL43R2G_ TL44S2G_ 5000K
 Description: DIRECT MOUNT, 55D OPTIC, DIFFUSE CLEAR LENS TRIM
 Light Source: (1) SELECTABLE LUMEN LED 90CRI / 5000K CCT
 Ballast/Driver: -

Summary

Lumens per Lamp: N/A
 Luminaire Lumens: 881.0 lumens
 Efficiency: N/A
 Efficacy: 106.1 lumens/watt
 Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.83
 Luminous Opening: Circular (Dia: 0.21' x H: 0')
 CIE Type: Direct


Input Watts (W): 8.3
 Input Voltage (V): NR
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT



Meas		Calibration Due Date	
Instrument	Identificatio		
Photometer	GONIO 1 11111111	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P601377
CATALOG NUMBER: ML4DM06WFL9FS1E - TIR4D55WFL - TL43R2G_ TL44S2G_ 5000K

Luminous Intensity Polar Plot



TEST NUMBER: P601377
 CATALOG NUMBER: ML4DM06WFL9FS1E - TIR4D55WFL - TL43R2G_ TL44S2G_ 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94	94	94	94
2	108	104	100	97	106	102	99	96	99	96	93	96	94	91	93	91	90	88	88	88	88
3	103	97	92	89	101	96	91	88	93	89	86	91	88	85	89	86	84	82	82	82	82
4	98	91	86	82	97	90	85	81	88	84	80	86	82	79	84	81	79	77	77	77	77
5	94	86	80	76	92	85	80	76	83	78	75	81	77	74	80	76	74	72	72	72	72
6	89	81	75	71	88	80	75	71	78	74	70	77	73	70	76	72	69	68	68	68	68
7	85	76	70	66	84	76	70	66	74	69	66	73	69	66	72	68	65	64	64	64	64
8	81	72	66	62	80	71	66	62	70	65	62	69	65	62	68	64	61	60	60	60	60
9	77	68	63	59	76	68	62	59	67	62	58	66	61	58	65	61	58	57	57	57	57
10	74	65	59	55	73	64	59	55	64	59	55	63	58	55	62	58	55	54	54	54	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	344026
5°	341822
10°	337309
15°	320889
20°	291775
25°	239635
30°	164113
35°	87388
40°	42168
45°	19157
50°	8646
55°	4239
60°	2084
65°	822
70°	1016
75°	1342
80°	0
85°	0

TEST NUMBER: P601377
 CATALOG NUMBER: ML4DM06WFL9FS1E - TIR4D55WFL - TL43R2G_ TL44S2G_ 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.1	11.6
10°-20°	274.0	31.1
20°-30°	307.3	34.9
30°-40°	150.7	17.1
40°-50°	37.1	4.2
50°-60°	7.4	0.8
60°-70°	1.6	0.2
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	683.4	77.6
0°-40°	834.1	94.7
0°-60°	878.6	99.7
0°-90°	881.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	881.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1090	
5°	1078	102
15°	982	274
25°	688	307
35°	227	151
45°	43	37
55°	8	7
65°	1	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P601377
CATALOG NUMBER: ML4DM06WFL9FS1E - TIR4D55WFL - TL43R2G_ TL44S2G_ 5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1089.5
2.5°	1080.6
5°	1078.4
7.5°	1069.6
10°	1052.0
12.5°	1024.5
15°	981.6
17.5°	936.5
20°	868.3
22.5°	786.8
25°	687.8
27.5°	571.1
30°	450.1
32.5°	331.2
35°	226.7
37.5°	153.0
40°	102.3
42.5°	67.1
45°	42.9
47.5°	26.4
50°	17.6
52.5°	11.0
55°	7.7
57.5°	4.4
60°	3.3
62.5°	2.2
65°	1.1
67.5°	1.1
70°	1.1
72.5°	1.1
75°	1.1
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)