

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P601468

Luminaire Tested: **ML4DM10LSWFL9FS1E - TIR4D55WFL - TL43R2G_ TL44S2G_ 3000K**

Issue Date: 7/29/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P601468
 Test Lab: COOPER LIGHTING SOLUTIONS
 Issue Date: 7/29/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO
 Catalog Number: ML4DM10LSWFL9FS1E - TIR4D55WFL - TL43R2G_ TL44S2G_ 3000K
 Description: DIRECT MOUNT, 55D OPTIC, DIFFUSE CLEAR LENS TRIM
 Light Source: (1) SELECTABLE LUMEN LED 90CRI / 3000K CCT
 Ballast/Driver: -

Summary

Lumens per Lamp: N/A
 Luminaire Lumens: 1096.8 lumens
 Efficiency: N/A
 Efficacy: 91.4 lumens/watt
 Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.83
 Luminous Opening: Circular (Dia: 0.21' x H: 0')
 CIE Type: Direct


Input Watts (W): 12
 Input Voltage (V): NR
 Input Current (A_{in}): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT



Meas			
Instrument	Identificatio		Calibration Due Date
Photometer	GONIO 1 11111111	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P601468
CATALOG NUMBER: ML4DM10LSWFL9FS1E - TIR4D55WFL - TL43R2G_ TL44S2G_ 3000K

Luminous Intensity Polar Plot



TEST NUMBER: P601468

CATALOG NUMBER: ML4DM10LSWFL9FS1E - TIR4D55WFL - TL43R2G_ TL44S2G_ 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94	94	94	94
2	108	104	100	97	106	102	99	96	99	96	93	96	94	91	93	91	90	88	88	88	88
3	103	97	92	89	101	96	91	88	93	89	86	91	88	85	89	86	84	82	82	82	82
4	98	91	86	82	97	90	85	81	88	84	80	86	82	79	84	81	79	77	77	77	77
5	94	86	80	76	92	85	80	76	83	78	75	81	77	74	80	76	74	72	72	72	72
6	89	81	75	71	88	80	75	71	78	74	70	77	73	70	76	72	69	68	68	68	68
7	85	76	70	66	84	76	70	66	74	69	66	73	69	66	72	68	65	64	64	64	64
8	81	72	66	62	80	71	66	62	70	65	62	69	65	62	68	64	61	60	60	60	60
9	77	68	63	59	76	68	62	59	67	62	58	66	61	58	65	61	58	57	57	57	57
10	74	65	59	55	73	64	59	55	64	59	55	63	58	55	62	58	55	54	54	54	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	428241
5°	425534
10°	419937
15°	399477
20°	363215
25°	298307
30°	204293
35°	108782
40°	52515
45°	23846
50°	10758
55°	5285
60°	2589
65°	1046
70°	1293
75°	1708
80°	0
85°	0

TEST NUMBER: P601468

CATALOG NUMBER: ML4DM10LSWFL9FS1E - TIR4D55WFL - TL43R2G_ TL44S2G_ 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.1	11.6
10°-20°	341.1	31.1
20°-30°	382.5	34.9
30°-40°	187.6	17.1
40°-50°	46.2	4.2
50°-60°	9.2	0.8
60°-70°	2.0	0.2
70°-80°	0.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	850.7	77.6
0°-40°	1038.4	94.7
0°-60°	1093.8	99.7
0°-90°	1096.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1096.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1356	
5°	1342	127
15°	1222	341
25°	856	383
35°	282	188
45°	53	46
55°	10	9
65°	1	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P601468

CATALOG NUMBER: ML4DM10LSWFL9FS1E - TIR4D55WFL - TL43R2G_ TL44S2G_ 3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1356.2
2.5°	1345.3
5°	1342.5
7.5°	1331.6
10°	1309.7
12.5°	1275.4
15°	1222.0
17.5°	1165.8
20°	1080.9
22.5°	979.5
25°	856.2
27.5°	711.0
30°	560.3
32.5°	412.4
35°	282.2
37.5°	190.4
40°	127.4
42.5°	83.6
45°	53.4
47.5°	32.9
50°	21.9
52.5°	13.7
55°	9.6
57.5°	5.5
60°	4.1
62.5°	2.7
65°	1.4
67.5°	1.4
70°	1.4
72.5°	1.4
75°	1.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)