

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P886535

Luminaire Tested: ML310LSFL95FS1E-TIR4D25AWW-TL3SWMW-1000LM-4000K

Issue Date: 7/8/2024

Test Information

Test Method: LM-79-2019
Report Number: P886535
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2402-314-22)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/8/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML310LSFL95FS1E-TIR4D25AWW-TL3SWMW-1000LM-4000K
Description: 3IN SQUARE ML FLEX, SELECTABLE CCT, WITH WW TIR, MATTE WHITE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 95CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 830.9 lumens
Efficiency: N/A
Efficacy: 61.1 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 0.81 / 1.01
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct


Input Watts (W): 13.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P886535

CATALOG NUMBER: ML310LSFL95FS1E-TIR4D25AWW-TL3SWMW-1000LM-4000K

Luminous Intensity Polar Plot





TEST NUMBER: P886535

CATALOG NUMBER: ML310LSFL95FS1E-TIR4D25AWW-TL3SWMW-1000LM-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|----|----|---|--|---|
| RF | 20 | | | | | 20 | | | | | 20 | | | | | 20 | | | | | | | | | | |
| RC | 80 | | | | | 70 | | | | | 50 | | | | | 30 | | | | | 10 | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | | | |
| 1 | 112 | 109 | 106 | 104 | 110 | 107 | 104 | 102 | 103 | 101 | 99 | 99 | 97 | 96 | 96 | 94 | 93 | 91 | | | | | | | | |
| 2 | 105 | 100 | 95 | 91 | 103 | 98 | 94 | 90 | 95 | 91 | 88 | 92 | 89 | 86 | 89 | 86 | 84 | 82 | | | | | | | | |
| 3 | 99 | 91 | 85 | 81 | 97 | 90 | 84 | 80 | 87 | 83 | 79 | 85 | 81 | 77 | 82 | 79 | 76 | 74 | | | | | | | | |
| 4 | 93 | 84 | 77 | 72 | 91 | 83 | 77 | 72 | 80 | 75 | 71 | 78 | 74 | 70 | 76 | 73 | 69 | 68 | | | | | | | | |
| 5 | 87 | 77 | 70 | 65 | 85 | 76 | 70 | 65 | 74 | 69 | 64 | 73 | 68 | 64 | 71 | 67 | 63 | 62 | | | | | | | | |
| 6 | 82 | 72 | 65 | 60 | 80 | 71 | 64 | 59 | 69 | 63 | 59 | 68 | 62 | 58 | 66 | 62 | 58 | 56 | | | | | | | | |
| 7 | 77 | 66 | 59 | 55 | 76 | 66 | 59 | 54 | 64 | 58 | 54 | 63 | 58 | 54 | 62 | 57 | 53 | 52 | | | | | | | | |
| 8 | 73 | 62 | 55 | 50 | 71 | 61 | 55 | 50 | 60 | 54 | 50 | 59 | 54 | 50 | 58 | 53 | 49 | 48 | | | | | | | | |
| 9 | 69 | 58 | 51 | 46 | 67 | 57 | 51 | 46 | 56 | 50 | 46 | 55 | 50 | 46 | 54 | 49 | 46 | 44 | | | | | | | | |
| 10 | 65 | 54 | 47 | 43 | 64 | 54 | 47 | 43 | 53 | 47 | 43 | 52 | 47 | 43 | 51 | 46 | 43 | 41 | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | 0° | 45° | 90° | 135° | 180° |
|-----|--------|--------|--------|--------|--------|
| 0° | 113012 | 113012 | 113012 | 113012 | 113012 |
| 5° | 137215 | 129487 | 112234 | 98525 | 92111 |
| 10° | 162830 | 143270 | 105452 | 77909 | 69130 |
| 15° | 184628 | 150804 | 94997 | 60104 | 51528 |
| 20° | 196215 | 150332 | 82566 | 46717 | 38983 |
| 25° | 193713 | 142520 | 69398 | 36219 | 29929 |
| 30° | 172794 | 127801 | 56677 | 27742 | 24341 |
| 35° | 142189 | 108108 | 43458 | 21718 | 20457 |
| 40° | 106250 | 85387 | 31812 | 17828 | 17828 |
| 45° | 68659 | 63533 | 22724 | 14419 | 15637 |
| 50° | 39252 | 44624 | 16933 | 11816 | 13986 |
| 55° | 21379 | 28315 | 11740 | 10539 | 12040 |
| 60° | 11401 | 16068 | 9334 | 9334 | 10368 |
| 65° | 6561 | 9414 | 7784 | 7784 | 8191 |
| 70° | 4028 | 5791 | 6546 | 7050 | 6546 |
| 75° | 1996 | 3660 | 5323 | 5989 | 4658 |
| 80° | 992 | 1984 | 2975 | 4959 | 4959 |
| 85° | 0 | 1976 | 3952 | 5928 | 5928 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°
 Vertical Angle: 45°
 Luminance: 71363 cd/sqm



TEST NUMBER: P886535

CATALOG NUMBER: ML310LSFL95FS1E-TIR4D25AWW-TL3SWMW-1000LM-4000K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 62.1 | 7.5 |
| 10°-20° | 167.0 | 20.1 |
| 20°-30° | 216.0 | 26.0 |
| 30°-40° | 188.8 | 22.7 |
| 40°-50° | 114.8 | 13.8 |
| 50°-60° | 51.8 | 6.2 |
| 60°-70° | 20.9 | 2.5 |
| 70°-80° | 7.7 | 0.9 |
| 80°-90° | 2.0 | 0.2 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 445.1 | 53.6 |
| 0°-40° | 633.9 | 76.3 |
| 0°-60° | 800.4 | 96.3 |
| 0°-90° | 830.9 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 830.9 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | 45° | 90° | 135° | 180° | Flux |
|-----|------|-----|-----|------|------|------|
| 0° | 656 | 656 | 656 | 656 | 656 | |
| 5° | 794 | 749 | 649 | 570 | 533 | 80 |
| 15° | 1036 | 846 | 533 | 337 | 289 | 292 |
| 25° | 1019 | 750 | 365 | 191 | 158 | 460 |
| 35° | 676 | 514 | 207 | 103 | 97 | 418 |
| 45° | 282 | 261 | 93 | 59 | 64 | 222 |
| 55° | 71 | 94 | 39 | 35 | 40 | 70 |
| 65° | 16 | 23 | 19 | 19 | 20 | 17 |
| 75° | 3 | 6 | 8 | 9 | 7 | 4 |
| 85° | 0 | 1 | 2 | 3 | 3 | 0 |
| 90° | 0 | 0 | 0 | 0 | 0 | |



TEST NUMBER: P886535

CATALOG NUMBER: ML310LSFL95FS1E-TIR4D25AWW-TL3SWMW-1000LM-4000K

CANDELA DISTRIBUTION (FULL):

| | 0° | 10° | 20° | 30° | 40° | 50° | 60° | 70° | 80° | 90° | 112.5° |
|-------|--------|--------|--------|-------|-------|-------|-------|-------|-------|-------|--------|
| 0° | 656.2 | 656.2 | 656.2 | 656.2 | 656.2 | 656.2 | 656.2 | 656.2 | 656.2 | 656.2 | 656.2 |
| 1° | 672.2 | 671.2 | 669.2 | 667.2 | 668.2 | 667.2 | 664.2 | 663.2 | 663.2 | 661.2 | 660.2 |
| 2° | 704.4 | 700.3 | 696.3 | 698.3 | 694.3 | 688.3 | 680.3 | 673.2 | 666.2 | 660.2 | 645.2 |
| 3° | 734.5 | 730.4 | 730.4 | 725.4 | 715.4 | 705.4 | 694.3 | 681.3 | 670.2 | 660.2 | 635.1 |
| 4° | 762.5 | 760.5 | 756.5 | 745.5 | 739.5 | 723.4 | 706.4 | 689.3 | 672.2 | 655.2 | 620.1 |
| 5° | 793.7 | 793.7 | 784.6 | 774.6 | 758.5 | 739.5 | 717.4 | 693.3 | 671.2 | 649.2 | 605.0 |
| 6° | 825.8 | 825.8 | 813.7 | 798.7 | 779.6 | 752.5 | 726.4 | 700.3 | 669.2 | 642.1 | 588.0 |
| 7° | 857.9 | 852.8 | 841.8 | 822.7 | 798.7 | 767.6 | 733.4 | 701.3 | 665.2 | 635.1 | 570.9 |
| 8° | 882.9 | 877.9 | 863.9 | 843.8 | 812.7 | 777.6 | 740.5 | 701.3 | 661.2 | 625.1 | 552.8 |
| 9° | 913.0 | 906.0 | 892.0 | 863.9 | 828.8 | 788.6 | 744.5 | 699.3 | 655.2 | 614.1 | 533.8 |
| 10° | 931.1 | 931.1 | 914.1 | 884.0 | 842.8 | 795.7 | 747.5 | 698.3 | 649.2 | 603.0 | 514.7 |
| 11° | 963.2 | 955.2 | 930.1 | 901.0 | 855.9 | 803.7 | 748.5 | 693.3 | 640.1 | 590.0 | 495.7 |
| 12° | 981.3 | 973.3 | 951.2 | 915.1 | 865.9 | 808.7 | 747.5 | 687.3 | 629.1 | 576.9 | 477.6 |
| 13° | 1001.3 | 994.3 | 968.2 | 926.1 | 873.9 | 809.7 | 745.5 | 681.3 | 619.1 | 562.9 | 457.5 |
| 14° | 1017.4 | 1011.4 | 983.3 | 937.1 | 879.9 | 811.7 | 741.5 | 673.2 | 606.0 | 547.8 | 435.5 |
| 15° | 1035.5 | 1024.4 | 993.3 | 944.2 | 880.9 | 810.7 | 735.5 | 663.2 | 595.0 | 532.8 | 420.4 |
| 16° | 1046.5 | 1036.5 | 1002.3 | 949.2 | 881.9 | 808.7 | 729.4 | 652.2 | 580.9 | 517.7 | 398.3 |
| 17° | 1057.5 | 1047.5 | 1009.4 | 953.2 | 880.9 | 802.7 | 721.4 | 641.1 | 569.9 | 500.7 | 379.3 |
| 18° | 1065.6 | 1054.5 | 1015.4 | 953.2 | 877.9 | 795.7 | 709.4 | 628.1 | 552.8 | 484.6 | 362.2 |
| 19° | 1069.6 | 1056.5 | 1015.4 | 952.2 | 873.9 | 786.6 | 699.3 | 615.1 | 536.8 | 467.6 | 343.1 |
| 20° | 1070.6 | 1056.5 | 1016.4 | 948.2 | 864.9 | 775.6 | 685.3 | 601.0 | 519.7 | 450.5 | 325.1 |
| 21° | 1067.6 | 1053.5 | 1010.4 | 942.1 | 857.9 | 763.6 | 672.2 | 582.9 | 502.7 | 430.4 | 308.0 |
| 22.5° | 1056.5 | 1041.5 | 996.3 | 926.1 | 837.8 | 744.5 | 649.2 | 557.9 | 478.6 | 407.4 | 283.9 |
| 23° | 1050.5 | 1037.5 | 991.3 | 920.1 | 832.8 | 735.5 | 639.1 | 550.8 | 466.6 | 398.3 | 276.9 |
| 24° | 1035.5 | 1023.4 | 977.3 | 906.0 | 816.7 | 721.4 | 621.1 | 533.8 | 451.5 | 380.3 | 260.9 |
| 25° | 1019.4 | 1000.3 | 959.2 | 888.0 | 798.7 | 701.3 | 605.0 | 514.7 | 434.5 | 365.2 | 245.8 |
| 26° | 990.3 | 976.3 | 936.1 | 865.9 | 780.6 | 681.3 | 586.0 | 494.7 | 416.4 | 345.2 | 233.8 |
| 27° | 962.2 | 952.2 | 914.1 | 843.8 | 761.5 | 662.2 | 566.9 | 477.6 | 394.3 | 329.1 | 217.7 |
| 28° | 936.1 | 925.1 | 882.9 | 817.7 | 737.5 | 642.1 | 542.8 | 458.5 | 379.3 | 314.0 | 205.7 |
| 29° | 902.0 | 894.0 | 854.9 | 796.7 | 712.4 | 619.1 | 523.7 | 438.5 | 362.2 | 298.0 | 193.6 |
| 30° | 868.9 | 859.9 | 821.7 | 765.6 | 689.3 | 596.0 | 503.7 | 419.4 | 345.2 | 285.0 | 183.6 |
| 32.5° | 773.6 | 770.6 | 736.5 | 688.3 | 619.1 | 534.8 | 450.5 | 370.2 | 302.0 | 247.8 | 158.5 |
| 35° | 676.3 | 673.2 | 642.1 | 606.0 | 551.8 | 476.6 | 395.3 | 322.1 | 257.9 | 206.7 | 133.4 |
| 37.5° | 569.9 | 566.9 | 551.8 | 519.7 | 479.6 | 411.4 | 341.1 | 275.9 | 214.7 | 173.6 | 112.4 |
| 40° | 472.6 | 469.6 | 462.5 | 439.5 | 408.4 | 351.2 | 290.0 | 226.8 | 177.6 | 141.5 | 92.3 |
| 42.5° | 369.2 | 373.2 | 371.2 | 363.2 | 343.1 | 293.0 | 242.8 | 188.6 | 146.5 | 114.4 | 76.3 |
| 45° | 281.9 | 283.9 | 289.0 | 293.0 | 278.9 | 242.8 | 198.7 | 149.5 | 114.4 | 93.3 | 63.2 |
| 47.5° | 204.7 | 209.7 | 220.7 | 228.8 | 224.8 | 197.7 | 157.5 | 119.4 | 93.3 | 77.3 | 54.2 |
| 50° | 146.5 | 149.5 | 160.5 | 177.6 | 177.6 | 155.5 | 122.4 | 91.3 | 75.3 | 63.2 | 48.2 |
| 52.5° | 105.4 | 107.4 | 117.4 | 130.4 | 134.4 | 118.4 | 94.3 | 72.2 | 59.2 | 49.2 | 40.1 |
| 55° | 71.2 | 74.2 | 84.3 | 98.3 | 98.3 | 90.3 | 69.2 | 54.2 | 45.2 | 39.1 | 33.1 |
| 57.5° | 48.2 | 51.2 | 58.2 | 70.2 | 70.2 | 64.2 | 52.2 | 40.1 | 35.1 | 31.1 | 28.1 |
| 60° | 33.1 | 34.1 | 42.1 | 48.2 | 49.2 | 44.1 | 37.1 | 31.1 | 28.1 | 27.1 | 25.1 |



TEST NUMBER: P886535

CATALOG NUMBER: ML310LSFL95FS1E-TIR4D25AWW-TL3SWMW-1000LM-4000K

CANDELA DISTRIBUTION (continued):

| | 0° | 10° | 20° | 30° | 40° | 50° | 60° | 70° | 80° | 90° | 112.5° |
|-------|------|------|------|------|------|------|------|------|------|------|--------|
| 67.5° | 11.0 | 12.0 | 13.0 | 15.1 | 16.1 | 16.1 | 16.1 | 17.1 | 17.1 | 16.1 | 17.1 |
| 70° | 8.0 | 8.0 | 9.0 | 10.0 | 11.0 | 12.0 | 12.0 | 14.0 | 13.0 | 13.0 | 14.0 |
| 72.5° | 5.0 | 6.0 | 6.0 | 7.0 | 8.0 | 8.0 | 10.0 | 10.0 | 10.0 | 10.0 | 11.0 |
| 75° | 3.0 | 4.0 | 4.0 | 4.0 | 5.0 | 6.0 | 7.0 | 7.0 | 7.0 | 8.0 | 9.0 |
| 77.5° | 2.0 | 2.0 | 3.0 | 3.0 | 3.0 | 4.0 | 5.0 | 5.0 | 5.0 | 5.0 | 6.0 |
| 80° | 1.0 | 1.0 | 1.0 | 2.0 | 2.0 | 2.0 | 3.0 | 3.0 | 3.0 | 3.0 | 4.0 |
| 82.5° | 1.0 | 1.0 | 1.0 | 1.0 | 1.0 | 2.0 | 2.0 | 2.0 | 3.0 | 3.0 | 3.0 |
| 85° | 0.0 | 0.0 | 0.0 | 1.0 | 1.0 | 1.0 | 1.0 | 2.0 | 2.0 | 2.0 | 2.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 1.0 | 1.0 | 1.0 | 1.0 | 1.0 | 1.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



TEST NUMBER: P886535

CATALOG NUMBER: ML310LSFL95FS1E-TIR4D25AWW-TL3SWMW-1000LM-4000K

CANDELA DISTRIBUTION (continued):

| | 135° | 157.5° | 180° |
|-------|-------|--------|-------|
| 0° | 656.2 | 656.2 | 656.2 |
| 1° | 656.2 | 655.2 | 649.2 |
| 2° | 634.1 | 625.1 | 625.1 |
| 3° | 612.0 | 600.0 | 597.0 |
| 4° | 591.0 | 568.9 | 565.9 |
| 5° | 569.9 | 541.8 | 532.8 |
| 6° | 545.8 | 513.7 | 501.7 |
| 7° | 522.7 | 485.6 | 476.6 |
| 8° | 495.7 | 459.5 | 444.5 |
| 9° | 468.6 | 432.4 | 417.4 |
| 10° | 445.5 | 406.4 | 395.3 |
| 11° | 422.4 | 382.3 | 367.2 |
| 12° | 398.3 | 359.2 | 347.2 |
| 13° | 379.3 | 337.1 | 326.1 |
| 14° | 357.2 | 320.1 | 307.0 |
| 15° | 337.1 | 299.0 | 289.0 |
| 16° | 320.1 | 282.9 | 271.9 |
| 17° | 300.0 | 266.9 | 255.9 |
| 18° | 285.0 | 251.8 | 240.8 |
| 19° | 268.9 | 236.8 | 227.8 |
| 20° | 254.9 | 224.8 | 212.7 |
| 21° | 240.8 | 209.7 | 201.7 |
| 22.5° | 219.7 | 192.6 | 183.6 |
| 23° | 212.7 | 184.6 | 177.6 |
| 24° | 201.7 | 175.6 | 166.6 |
| 25° | 190.6 | 164.5 | 157.5 |
| 26° | 179.6 | 154.5 | 148.5 |
| 27° | 169.6 | 146.5 | 141.5 |
| 28° | 157.5 | 137.5 | 134.4 |
| 29° | 148.5 | 130.4 | 128.4 |
| 30° | 139.5 | 124.4 | 122.4 |
| 32.5° | 120.4 | 109.4 | 108.4 |
| 35° | 103.3 | 96.3 | 97.3 |
| 37.5° | 90.3 | 86.3 | 88.3 |
| 40° | 79.3 | 76.3 | 79.3 |
| 42.5° | 68.2 | 68.2 | 72.2 |
| 45° | 59.2 | 62.2 | 64.2 |
| 47.5° | 51.2 | 56.2 | 58.2 |
| 50° | 44.1 | 51.2 | 52.2 |
| 52.5° | 39.1 | 46.2 | 45.2 |
| 55° | 35.1 | 40.1 | 40.1 |
| 57.5° | 31.1 | 35.1 | 34.1 |
| 60° | 27.1 | 30.1 | 30.1 |



TEST NUMBER: P886535

CATALOG NUMBER: ML310LSFL95FS1E-TIR4D25AWW-TL3SWMW-1000LM-4000K

CANDELA DISTRIBUTION (continued):

| | 135° | 157.5° | 180° |
|-------|------|--------|------|
| 67.5° | 16.1 | 18.1 | 16.1 |
| 70° | 14.0 | 14.0 | 13.0 |
| 72.5° | 11.0 | 11.0 | 10.0 |
| 75° | 9.0 | 8.0 | 7.0 |
| 77.5° | 7.0 | 6.0 | 6.0 |
| 80° | 5.0 | 5.0 | 5.0 |
| 82.5° | 4.0 | 4.0 | 4.0 |
| 85° | 3.0 | 3.0 | 3.0 |
| 87.5° | 2.0 | 2.0 | 2.0 |
| 90° | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





| | | | | | | | | | | | |
|-------|------|------|------|------|------|------|------|------|------|------|------|
| 62.5° | 22.1 | 24.1 | 29.1 | 34.1 | 35.1 | 31.1 | 27.1 | 25.1 | 23.1 | 23.1 | 22.1 |
| 65° | 16.1 | 17.1 | 20.1 | 23.1 | 24.1 | 22.1 | 20.1 | 20.1 | 20.1 | 19.1 | 19.1 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



| | | | |
|-------|------|------|------|
| 62.5° | 23.1 | 25.1 | 25.1 |
| 65° | 19.1 | 21.1 | 20.1 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)