

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: A1914649A001

Luminaire Tested:

Test Date: 2019-08-29



Test Information

Test Method: LM-41-14
Report Number: A1914649A001
Test Lab: EVERFINE
Test Date: 2019-08-29
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number:
Description: RA3069FS1EWH*
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 585.0 lumens
Efficiency: N/A
Efficacy: 79.5 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.13 / 1.19
Luminous Opening: Point Source (0m x 0m x 0m)
CIE Type: Direct

Input Watts (W): 7.35753
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: A1914649A001
CATALOG NUMBER:

Luminous Intensity Polar Plot





TEST NUMBER: A1914649A001

CATALOG NUMBER:

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66
4	87	76	69	63	85	75	68	62	73	66	61	70	65	61	68	64	60	58
5	81	69	61	55	79	68	60	55	66	59	54	64	58	54	62	57	53	51
6	75	63	55	49	73	62	54	49	60	53	48	59	53	48	57	52	48	46
7	70	58	50	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34
10	58	45	38	33	57	45	38	33	44	37	33	43	37	33	42	37	33	31

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	Luminaire represents a point source (luminous area is zero).			
5°	No luminance values can be calculated.			
10°				
15°				
20°				
25°				
30°				
35°				
40°				
45°				
50°				
55°				
60°				
65°				
70°				
75°				
80°				
85°				



TEST NUMBER: A1914649A001

CATALOG NUMBER:

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.7	4.7
10°-20°	77.9	13.3
20°-30°	112.3	19.2
30°-40°	121.4	20.7
40°-50°	104.1	17.8
50°-60°	72.6	12.4
60°-70°	42.5	7.3
70°-80°	20.9	3.6
80°-90°	5.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.1	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	217.9	37.2
0°-40°	339.2	58.0
0°-60°	516.0	88.2
0°-90°	584.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	585.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	294	294	294	294	294	
5°	288	294	292	290	288	28
15°	274	281	277	270	274	77
25°	240	255	250	233	240	110
35°	186	208	201	182	186	117
45°	128	147	141	124	128	99
55°	76	88	84	75	76	68
65°	40	46	44	40	40	40
75°	19	20	20	18	19	20
85°	5	5	5	5	5	5
90°	0	0	0	0	0	0
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0



TEST NUMBER: A1914649A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	294.2	294.2	294.2	294.2	294.2	294.2	294.2	294.2	294.2	294.2	294.2
0.5°	294.0	295.1	292.6	295.9	294.7	294.2	296.5	294.2	296.8	294.0	291.5
1°	295.4	295.1	290.8	295.9	293.3	294.6	294.4	296.3	293.5	295.3	292.1
1.5°	292.0	294.4	291.1	294.9	294.0	294.2	294.4	294.0	294.8	292.7	291.2
2°	295.2	295.0	291.1	295.1	293.4	292.8	294.6	294.1	295.2	294.6	292.2
2.5°	293.0	295.5	290.8	293.8	293.1	292.3	294.2	294.2	294.4	293.1	291.9
3°	292.3	294.8	289.0	293.6	294.3	294.5	294.9	293.8	293.9	294.2	290.3
3.5°	291.6	294.3	290.0	293.6	293.0	294.6	291.9	293.3	293.1	294.5	291.9
4°	291.0	293.7	292.7	295.3	293.0	296.0	293.2	292.5	295.2	294.4	289.0
4.5°	289.7	293.5	291.3	294.5	292.1	292.2	294.2	292.4	294.9	292.5	289.3
5°	288.4	292.7	290.0	292.4	293.7	292.2	294.6	293.3	291.5	294.5	289.4
5.5°	289.9	291.1	290.7	296.1	291.9	291.9	294.8	291.8	291.1	291.7	289.4
6°	292.6	291.0	290.0	293.2	292.3	291.4	292.4	292.9	290.0	292.8	288.4
6.5°	289.6	292.4	291.2	294.5	292.3	291.4	294.6	291.9	291.9	289.9	288.0
7°	289.6	290.6	289.8	293.0	292.0	292.3	294.8	291.1	291.8	290.3	287.8
7.5°	288.7	290.9	287.2	292.1	291.5	292.5	293.1	291.5	292.0	289.4	287.4
8°	285.0	288.6	287.9	291.2	291.3	290.7	291.3	289.6	289.0	289.3	286.6
8.5°	287.8	287.8	287.7	291.2	291.4	290.6	291.3	288.9	287.1	289.0	285.1
9°	287.2	287.9	287.3	290.5	291.1	290.0	293.7	289.5	288.0	289.2	284.9
9.5°	287.6	287.4	287.6	288.6	289.7	290.2	292.1	289.8	286.6	286.3	284.1
10°	284.3	286.2	285.6	290.0	288.6	288.6	289.4	288.5	286.9	285.0	284.4
10.5°	283.7	285.8	286.2	289.9	288.5	288.6	288.6	287.3	288.8	285.2	283.2
11°	281.8	286.1	285.5	288.2	287.5	287.8	288.3	287.7	286.8	285.1	282.1
11.5°	283.8	284.5	284.1	287.7	286.4	286.8	287.0	287.2	287.5	286.3	280.9
12°	281.6	283.3	282.8	288.1	285.4	286.6	287.0	286.0	284.0	284.8	280.3
12.5°	279.0	282.2	285.4	286.8	286.5	285.9	285.9	283.9	283.5	283.3	278.2
13°	278.0	280.7	279.9	286.6	285.1	285.5	285.5	284.6	282.8	281.8	278.2
13.5°	275.4	280.0	280.1	286.0	283.4	284.8	285.1	282.8	281.8	281.2	276.1
14°	275.6	278.7	279.0	284.3	282.5	282.7	283.2	282.5	280.7	281.2	274.5
14.5°	274.7	278.4	277.8	283.2	282.2	281.7	284.5	280.9	279.1	280.2	273.6
15°	274.4	276.8	277.8	284.3	281.4	281.3	282.5	281.2	277.3	278.8	272.9
15.5°	272.8	275.7	275.5	279.8	281.3	279.8	281.0	280.3	278.2	276.0	271.9
16°	270.4	275.1	275.1	278.2	279.6	277.4	280.6	276.2	276.2	275.6	270.8
16.5°	269.1	273.3	275.4	280.9	278.7	278.0	279.1	275.1	274.4	276.6	269.4
17°	267.1	272.5	273.1	280.6	278.7	276.7	277.6	273.9	274.8	273.3	268.5
17.5°	266.0	268.7	271.4	277.4	275.6	277.2	276.8	276.5	274.2	272.4	267.0
18°	265.0	269.5	271.0	272.4	275.6	275.1	275.8	275.2	271.7	271.1	266.9
18.5°	264.0	267.0	268.0	273.5	274.8	273.2	275.3	273.8	271.5	269.3	264.2
19°	262.2	266.5	266.6	274.1	273.7	272.6	273.0	271.6	268.9	267.5	263.7
19.5°	260.7	265.4	265.6	273.4	272.2	273.0	272.8	269.5	267.2	266.7	262.7
20°	259.1	264.9	264.0	267.9	271.3	270.7	272.8	266.6	265.3	265.6	260.4
20.5°	257.5	262.3	263.3	268.2	269.7	269.2	271.1	265.9	265.3	263.6	260.4
21°	256.9	259.4	261.5	267.2	267.1	268.4	266.9	266.7	263.5	261.7	257.3
21.5°	254.6	256.3	261.2	264.4	265.4	266.5	267.1	264.4	261.0	260.3	255.4
22°	251.5	255.5	259.1	262.0	265.2	265.8	263.8	260.6	260.0	257.8	253.5



TEST NUMBER: A1914649A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
22.5°	250.7	256.4	256.2	260.8	263.2	263.6	262.4	260.5	258.3	256.8	252.0
23°	249.4	253.8	254.9	260.0	259.4	261.7	261.4	260.4	255.7	255.2	249.4
23.5°	246.2	251.7	252.9	257.3	258.6	259.8	259.3	257.0	253.1	252.6	246.9
24°	244.8	248.3	251.3	257.1	257.9	256.8	258.0	254.9	251.0	251.1	246.9
24.5°	242.3	246.4	250.9	255.0	256.6	256.0	255.4	253.5	251.4	249.1	243.9
25°	240.2	244.9	248.2	254.0	255.1	254.0	253.1	251.4	249.8	246.9	242.1
25.5°	237.7	242.1	245.1	251.0	253.6	251.3	252.3	250.0	247.4	244.7	239.8
26°	234.9	240.3	242.5	250.0	250.2	250.1	250.6	249.5	243.5	242.9	237.1
26.5°	232.4	239.3	240.3	246.9	248.8	248.4	248.1	246.3	243.2	240.3	235.2
27°	229.9	236.8	239.3	244.9	246.4	246.6	245.9	243.3	240.5	238.0	232.6
27.5°	228.9	234.2	236.2	242.7	244.7	244.2	244.9	241.4	238.8	236.2	230.7
28°	226.4	231.6	233.3	240.1	241.6	242.4	241.8	238.6	237.5	233.4	227.2
28.5°	224.2	228.8	230.9	237.9	240.5	241.0	239.2	236.0	234.8	230.9	225.5
29°	221.5	226.1	229.2	235.3	237.5	238.0	237.0	234.7	231.6	229.0	223.4
29.5°	218.4	224.6	227.2	233.2	234.9	235.9	235.3	233.2	229.8	226.6	220.0
30°	216.1	221.8	225.9	232.7	233.5	234.0	233.0	230.2	227.1	224.3	218.1
30.5°	213.3	219.3	222.7	229.4	231.3	231.8	231.2	228.3	224.7	221.5	214.6
31°	210.1	217.6	220.0	226.6	228.7	228.2	228.2	225.4	223.2	219.2	212.6
31.5°	207.1	214.4	217.2	223.2	226.0	226.5	226.0	222.4	220.3	217.1	210.3
32°	204.4	209.7	214.0	220.9	223.6	223.5	223.2	219.4	216.9	214.1	207.1
32.5°	201.7	207.6	211.6	219.9	220.8	221.6	220.3	217.9	213.2	211.6	204.2
33°	198.1	205.5	208.7	217.3	218.6	219.1	217.3	214.0	213.2	208.6	201.4
33.5°	195.0	203.8	206.6	214.0	216.3	217.1	215.3	211.2	208.5	206.0	198.8
34°	192.2	200.7	204.8	210.7	213.9	212.9	213.0	209.8	207.1	202.8	196.2
34.5°	189.0	197.6	202.5	207.4	210.9	211.1	210.2	206.5	204.7	199.8	193.4
35°	186.2	194.4	199.6	204.6	208.3	208.1	207.2	203.4	200.8	196.9	190.8
35.5°	183.8	191.0	195.6	202.2	205.3	205.2	204.8	200.7	197.8	195.1	188.4
36°	181.4	189.2	192.9	198.9	202.9	202.3	202.0	198.1	195.8	191.8	186.0
36.5°	179.0	186.2	189.9	196.3	199.5	200.2	199.1	196.2	191.9	189.2	183.1
37°	176.0	182.8	187.0	193.6	196.3	197.2	195.5	193.1	188.5	186.0	180.1
37.5°	172.8	179.6	184.3	190.9	193.5	194.4	193.0	189.2	186.2	182.8	177.0
38°	169.5	176.2	181.4	187.9	190.7	191.6	190.0	186.9	183.5	179.5	174.1
38.5°	166.4	173.8	178.2	184.7	187.7	188.6	187.2	184.0	180.6	176.6	171.0
39°	163.7	170.6	175.3	181.6	184.6	185.6	184.1	181.4	177.6	173.4	167.7
39.5°	160.4	166.6	172.2	179.0	181.4	182.6	181.0	178.0	174.3	170.4	164.5
40°	157.6	164.0	169.0	176.0	177.4	179.4	178.2	174.9	171.1	167.4	161.4
40.5°	155.0	162.0	166.0	173.1	175.4	176.4	175.4	172.4	168.3	163.7	158.4
41°	151.7	158.9	162.9	169.9	172.1	173.2	172.5	168.8	165.4	161.0	155.6
41.5°	148.8	155.5	160.1	166.8	169.3	170.2	169.5	165.0	162.3	158.2	152.6
42°	145.8	152.2	156.8	163.6	166.2	167.0	166.3	163.0	159.0	154.8	149.8
42.5°	142.8	149.3	153.7	160.4	162.7	163.8	163.1	159.8	156.2	152.1	146.5
43°	139.4	145.8	150.6	157.1	159.5	160.5	160.0	157.0	152.9	149.1	143.4
43.5°	136.5	144.0	147.6	154.3	156.2	157.4	157.0	153.6	149.8	146.1	140.4
44°	133.5	141.6	144.5	151.1	153.2	154.4	153.8	150.5	146.7	143.2	137.6
44.5°	130.8	137.9	141.6	148.0	149.8	151.2	150.7	147.4	143.8	140.2	134.4



TEST NUMBER: A1914649A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
45°	127.8	134.8	138.6	144.8	146.6	147.9	147.5	144.4	140.6	137.0	131.3
45.5°	124.6	131.6	135.6	141.6	143.8	144.8	144.4	141.2	137.3	133.8	128.4
46°	121.6	128.2	132.7	138.6	140.7	141.9	141.2	138.0	134.1	130.8	125.8
46.5°	119.0	124.8	129.4	135.5	138.1	138.6	137.8	135.0	131.2	128.0	123.1
47°	116.0	122.4	126.4	132.1	134.6	135.4	134.7	131.9	128.2	125.0	120.1
47.5°	113.2	119.8	123.2	129.0	131.5	132.2	131.5	128.9	125.4	122.1	117.3
48°	110.5	116.5	120.3	125.7	128.0	129.1	128.6	125.7	122.6	119.2	114.6
48.5°	108.2	113.4	117.5	122.8	125.5	126.0	125.5	122.8	119.5	116.4	111.6
49°	105.1	110.1	114.5	119.8	122.0	122.9	122.6	119.7	116.8	113.5	108.9
49.5°	102.6	107.5	111.5	116.6	118.8	119.8	119.5	116.7	114.2	110.7	106.0
50°	100.2	104.8	108.4	113.5	116.0	116.8	116.5	113.8	111.5	107.7	103.4
50.5°	97.4	102.0	105.7	110.5	113.0	113.8	113.6	111.2	108.7	104.9	100.4
51°	94.7	99.3	103.0	107.8	110.3	110.9	110.5	108.4	106.0	102.1	97.8
51.5°	92.1	96.6	100.1	104.7	107.4	108.3	107.6	105.3	103.2	99.4	95.3
52°	89.9	94.2	97.3	102.1	104.7	105.5	104.8	102.4	100.0	96.7	93.0
52.5°	87.5	91.4	94.9	99.4	102.0	102.5	101.9	99.7	97.0	94.0	90.5
53°	85.1	89.0	92.0	96.5	99.0	99.6	99.1	97.1	94.2	91.6	88.2
53.5°	82.6	86.5	89.4	93.7	96.2	96.9	96.3	94.4	91.6	89.2	85.9
54°	80.3	84.1	87.1	91.0	93.4	94.2	93.6	91.8	89.2	86.8	83.5
54.5°	78.1	81.8	84.6	88.6	90.7	91.5	90.8	89.4	86.8	84.5	81.0
55°	75.9	79.3	82.2	86.2	88.1	89.0	88.5	86.9	84.4	82.0	78.9
55.5°	73.6	77.2	79.7	83.2	85.5	86.2	86.0	84.3	82.0	79.6	76.6
56°	71.5	74.7	77.2	81.2	83.1	83.7	83.5	81.7	79.6	77.3	74.4
56.5°	69.4	72.6	75.2	78.9	80.7	81.2	81.1	79.3	77.3	75.0	72.5
57°	67.3	70.4	72.7	76.2	78.3	78.8	78.7	76.8	74.9	72.8	70.4
57.5°	65.4	68.4	70.8	73.8	75.8	76.4	76.3	74.3	72.5	70.6	68.4
58°	63.4	66.2	68.6	71.7	73.5	74.0	73.9	72.0	70.2	68.6	66.3
58.5°	61.4	64.2	66.5	69.4	71.1	71.7	71.5	69.9	68.1	66.2	64.1
59°	59.6	62.3	64.3	67.3	68.8	69.5	69.1	67.6	66.1	64.2	62.0
59.5°	57.7	60.2	62.3	65.1	66.5	67.2	66.9	65.4	63.9	62.2	60.1
60°	55.9	58.4	60.4	63.0	64.4	65.0	64.7	63.2	61.9	60.3	58.1
60.5°	54.1	56.6	58.4	61.1	62.3	62.8	62.6	61.4	59.9	58.3	56.3
61°	52.6	54.9	56.5	59.1	60.3	60.6	60.5	59.4	57.8	56.4	54.5
61.5°	50.8	53.0	54.7	57.2	58.3	58.7	58.5	57.3	56.0	54.8	52.7
62°	49.3	51.3	53.0	55.5	56.3	56.7	56.6	55.4	54.2	53.0	50.9
62.5°	47.6	49.6	51.2	53.6	54.5	54.9	54.7	53.6	52.3	51.1	49.3
63°	46.0	47.9	49.6	51.7	52.7	53.0	52.8	51.7	50.6	49.4	47.7
63.5°	44.5	46.3	48.0	50.0	50.8	51.1	51.0	50.0	48.8	47.7	46.0
64°	43.1	44.9	46.4	48.2	49.0	49.3	49.2	48.2	47.1	46.0	44.4
64.5°	41.6	43.2	44.7	46.6	47.2	47.6	47.4	46.6	45.4	44.4	42.9
65°	40.2	41.8	43.2	45.0	45.5	45.9	45.7	44.8	43.9	42.9	41.5
65.5°	38.9	40.4	41.6	43.4	44.0	44.2	44.0	43.3	42.3	41.4	40.0
66°	37.6	39.0	40.2	41.8	42.4	42.5	42.4	41.6	40.7	39.9	38.6
66.5°	36.4	37.6	38.8	40.3	40.9	41.1	40.8	40.1	39.2	38.4	37.3
67°	35.1	36.3	37.4	38.8	39.4	39.4	39.3	38.6	37.9	37.0	35.8



TEST NUMBER: A1914649A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
67.5°	33.8	35.1	36.0	37.5	37.8	38.0	37.8	37.2	36.5	35.6	34.5
68°	32.7	33.8	34.6	36.1	36.4	36.5	36.2	35.8	35.2	34.3	33.3
68.5°	31.5	32.6	33.4	34.7	34.9	34.9	34.8	34.4	33.9	33.0	32.0
69°	30.4	31.5	32.2	33.5	33.6	33.6	33.6	33.1	32.6	31.8	30.9
69.5°	29.3	30.2	31.0	32.2	32.3	32.3	32.3	31.8	31.4	30.6	29.7
70°	28.3	29.2	29.8	31.0	31.1	31.1	31.0	30.6	30.1	29.5	28.5
70.5°	27.2	28.1	28.8	29.8	29.7	29.8	29.8	29.4	29.0	28.4	27.4
71°	26.2	27.0	27.7	28.7	28.5	28.6	28.6	28.2	27.9	27.4	26.4
71.5°	25.3	26.0	26.5	27.5	27.4	27.4	27.5	27.2	26.7	26.2	25.3
72°	24.1	25.0	25.5	26.4	26.3	26.4	26.4	26.1	25.6	25.2	24.3
72.5°	23.2	23.9	24.5	25.4	25.2	25.4	25.4	25.0	24.6	24.2	23.4
73°	22.4	23.1	23.5	24.2	24.2	24.3	24.3	24.1	23.7	23.3	22.5
73.5°	21.7	22.3	22.5	23.2	23.2	23.4	23.4	23.1	22.8	22.3	21.5
74°	20.8	21.4	21.8	22.3	22.2	22.3	22.3	22.1	21.9	21.4	20.8
74.5°	19.9	20.5	20.7	21.4	21.2	21.3	21.4	21.3	21.0	20.7	19.9
75°	19.1	19.6	19.9	20.4	20.4	20.6	20.5	20.4	20.1	19.9	19.1
75.5°	18.2	18.8	18.9	19.5	19.6	19.7	19.8	19.6	19.2	18.9	18.6
76°	17.5	17.9	18.0	18.5	18.6	18.7	18.9	18.8	18.4	18.1	17.6
76.5°	16.6	17.1	17.2	17.7	17.7	17.8	17.8	17.8	17.5	17.3	16.8
77°	15.8	16.3	16.3	16.7	16.8	16.9	17.0	16.8	16.7	16.7	16.1
77.5°	15.2	15.4	15.5	15.9	16.0	16.0	16.1	16.0	15.9	15.8	15.5
78°	14.4	14.6	14.6	15.0	15.1	15.2	15.2	15.1	15.0	15.0	14.6
78.5°	13.7	13.8	13.9	14.3	14.3	14.4	14.6	14.6	14.5	14.4	13.8
79°	12.8	13.1	13.1	13.4	13.5	13.5	13.6	13.6	13.4	13.5	13.2
79.5°	12.2	12.3	12.3	12.6	12.6	12.7	12.7	12.7	12.8	12.7	12.4
80°	11.5	11.6	11.6	11.8	11.9	11.8	11.9	11.9	12.0	12.0	11.7
80.5°	10.9	11.0	10.8	11.0	11.2	11.1	11.2	11.3	11.4	11.3	11.1
81°	10.3	10.4	10.1	10.3	10.3	10.3	10.4	10.4	10.4	10.6	10.4
81.5°	9.7	9.8	9.5	9.4	9.5	9.4	9.5	9.6	9.7	10.2	9.8
82°	9.0	9.1	8.9	8.9	8.8	8.7	8.7	8.8	9.2	9.4	9.1
82.5°	8.3	8.4	8.2	8.3	8.2	8.4	8.4	8.3	8.4	8.6	8.5
83°	7.6	7.8	7.6	7.6	7.4	7.4	7.5	7.6	8.0	8.2	8.1
83.5°	6.9	7.0	6.9	6.9	6.9	6.8	7.0	7.1	7.1	7.2	7.1
84°	6.3	6.3	6.3	6.3	6.1	6.1	6.2	6.3	6.4	6.5	6.4
84.5°	5.6	5.7	5.6	5.7	5.5	5.4	5.6	5.6	5.8	6.1	6.0
85°	4.8	4.9	5.0	4.9	4.9	5.0	5.1	5.0	5.0	5.0	5.0
85.5°	4.2	4.3	4.4	4.3	4.2	4.2	4.2	4.2	4.2	4.3	4.3
86°	3.6	3.7	3.6	3.6	3.8	3.6	3.7	3.8	3.8	3.8	3.8
86.5°	2.9	3.0	2.9	2.9	2.8	3.0	2.9	2.8	2.9	2.8	2.9
87°	2.2	2.3	2.2	2.3	2.2	2.1	2.1	2.1	2.2	2.2	2.1
87.5°	1.6	1.6	1.6	1.6	1.7	1.7	1.6	1.6	1.5	1.6	1.8
88°	1.0	1.0	1.0	1.0	0.8	0.8	0.8	0.8	0.8	0.8	0.8
88.5°	0.4	0.4	0.5	0.5	0.2	0.1	0.1	0.1	0.1	0.1	0.1
89°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
89.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1914649A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
91°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
91.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
93°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
93.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
94°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
94.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
96°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
96.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
101°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
101.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
103°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
103.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
104°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
104.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
106°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
106.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
108°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
108.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
109°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
109.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
111°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
111.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
112°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1914649A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
113°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
113.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
114°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
114.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
116°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
116.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
118°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
118.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
119°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
119.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
121°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
121.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
123°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
123.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
124°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
124.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
126°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
126.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
128°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
128.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
129°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
129.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
131°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
131.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
133°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
133.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
134°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
134.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1914649A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
136°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
136.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
138°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
138.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
139°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
139.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140.5°	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
141°	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
141.5°	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142°	0.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.2	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
143°	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
143.5°	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
144°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
144.5°	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.2	0.1	0.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145.5°	0.2	0.1	0.2	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
146°	0.2	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
146.5°	0.2	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147°	0.2	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.2	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
148°	0.2	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
148.5°	0.2	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
149°	0.2	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
149.5°	0.2	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.2	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150.5°	0.2	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.0	0.1	0.0
151°	0.2	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.0	0.1	0.0
151.5°	0.2	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152°	0.2	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.2	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.1	0.0	0.0
153°	0.2	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.1	0.1	0.0
153.5°	0.2	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.1	0.1	0.0
154°	0.2	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.1	0.1	0.0
154.5°	0.2	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.1	0.1	0.0
155°	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.0
155.5°	0.2	0.2	0.2	0.1	0.1	0.1	0.0	0.1	0.1	0.1	0.0
156°	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0
156.5°	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.0
157°	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.1



TEST NUMBER: A1914649A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
157.5°	0.2	0.2	0.2	0.1	0.1	0.2	0.1	0.1	0.2	0.2	0.1
158°	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.3	0.2	0.1
158.5°	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.3	0.2	0.1
159°	0.2	0.2	0.2	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.1
159.5°	0.2	0.2	0.2	0.1	0.1	0.3	0.1	0.2	0.2	0.2	0.2
160°	0.2	0.2	0.2	0.1	0.1	0.3	0.3	0.1	0.2	0.2	0.2
160.5°	0.2	0.2	0.2	0.1	0.1	0.2	0.2	0.1	0.2	0.2	0.2
161°	0.2	0.2	0.2	0.1	0.1	0.2	0.2	0.1	0.2	0.2	0.2
161.5°	0.2	0.2	0.2	0.1	0.1	0.2	0.2	0.1	0.2	0.2	0.2
162°	0.2	0.2	0.2	0.1	0.1	0.2	0.2	0.1	0.2	0.2	0.2
162.5°	0.2	0.2	0.2	0.1	0.1	0.2	0.3	0.1	0.2	0.2	0.2
163°	0.2	0.2	0.2	0.1	0.1	0.2	0.2	0.1	0.2	0.2	0.2
163.5°	0.2	0.2	0.2	0.1	0.1	0.2	0.2	0.1	0.2	0.2	0.2
164°	0.2	0.2	0.2	0.1	0.1	0.2	0.2	0.1	0.2	0.2	0.2
164.5°	0.2	0.2	0.2	0.1	0.1	0.2	0.1	0.1	0.2	0.2	0.2
165°	0.2	0.2	0.2	0.1	0.1	0.2	0.1	0.1	0.2	0.2	0.2
165.5°	0.2	0.2	0.2	0.1	0.1	0.2	0.1	0.1	0.2	0.2	0.2
166°	0.2	0.2	0.2	0.1	0.2	0.2	0.1	0.1	0.2	0.2	0.2
166.5°	0.2	0.2	0.2	0.1	0.1	0.2	0.1	0.1	0.2	0.2	0.2
167°	0.2	0.2	0.2	0.1	0.1	0.2	0.1	0.1	0.2	0.2	0.2
167.5°	0.2	0.2	0.2	0.1	0.1	0.2	0.1	0.1	0.2	0.2	0.2
168°	0.2	0.2	0.2	0.1	0.1	0.2	0.1	0.1	0.2	0.2	0.2
168.5°	0.2	0.2	0.2	0.1	0.1	0.2	0.1	0.1	0.2	0.2	0.2
169°	0.2	0.2	0.2	0.1	0.1	0.2	0.1	0.1	0.2	0.2	0.2
169.5°	0.2	0.2	0.2	0.1	0.1	0.2	0.1	0.1	0.2	0.2	0.2
170°	0.2	0.2	0.2	0.1	0.1	0.2	0.1	0.1	0.2	0.2	0.2
170.5°	0.2	0.2	0.2	0.1	0.1	0.2	0.1	0.1	0.2	0.2	0.2
171°	0.2	0.2	0.2	0.1	0.1	0.2	0.1	0.1	0.2	0.2	0.2
171.5°	0.2	0.2	0.2	0.1	0.1	0.2	0.1	0.1	0.2	0.2	0.2
172°	0.2	0.2	0.2	0.1	0.1	0.2	0.1	0.1	0.2	0.2	0.2
172.5°	0.2	0.2	0.2	0.1	0.1	0.2	0.1	0.1	0.2	0.2	0.2
173°	0.2	0.2	0.2	0.1	0.1	0.2	0.1	0.1	0.2	0.2	0.2
173.5°	0.2	0.2	0.2	0.1	0.1	0.2	0.1	0.1	0.2	0.2	0.2
174°	0.2	0.2	0.2	0.1	0.1	0.2	0.1	0.1	0.2	0.2	0.2
174.5°	0.2	0.2	0.2	0.1	0.1	0.2	0.1	0.1	0.2	0.2	0.2
175°	0.2	0.2	0.2	0.1	0.1	0.2	0.1	0.1	0.2	0.2	0.2
175.5°	0.2	0.2	0.2	0.1	0.1	0.2	0.1	0.1	0.2	0.2	0.2
176°	0.2	0.2	0.2	0.1	0.1	0.2	0.1	0.1	0.2	0.2	0.2
176.5°	0.2	0.2	0.2	0.1	0.1	0.2	0.1	0.1	0.2	0.2	0.2
177°	0.2	0.2	0.2	0.1	0.1	0.2	0.1	0.1	0.2	0.2	0.2
177.5°	0.2	0.2	0.2	0.1	0.1	0.2	0.1	0.1	0.2	0.2	0.2
178°	0.2	0.2	0.2	0.1	0.1	0.2	0.1	0.1	0.2	0.2	0.2
178.5°	0.2	0.2	0.2	0.1	0.1	0.2	0.1	0.1	0.2	0.2	0.2
179°	0.2	0.2	0.2	0.1	0.1	0.2	0.1	0.1	0.2	0.2	0.2
179.5°	0.2	0.2	0.2	0.1	0.1	0.2	0.1	0.1	0.2	0.2	0.2



TEST NUMBER: A1914649A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
180°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2



TEST NUMBER: A1914649A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	294.2	294.2	294.2	294.2	294.2	294.2
0.5°	293.8	293.4	290.1	295.5	293.6	294.0
1°	295.1	293.6	291.9	294.3	294.8	295.4
1.5°	295.5	292.4	290.8	293.2	294.0	292.0
2°	293.5	292.5	290.4	293.7	292.6	295.2
2.5°	293.4	292.5	292.1	293.1	290.3	293.0
3°	294.0	290.9	292.7	292.7	292.1	292.3
3.5°	293.6	291.1	289.5	292.1	291.3	291.6
4°	293.4	290.9	290.3	291.3	290.7	291.0
4.5°	292.6	290.3	289.3	291.2	289.3	289.7
5°	292.7	289.8	292.4	290.6	290.4	288.4
5.5°	291.8	289.0	291.8	290.0	288.9	289.9
6°	291.4	288.3	290.0	289.0	289.2	292.6
6.5°	290.6	287.3	289.1	289.7	289.1	289.6
7°	288.9	288.9	286.1	289.1	289.3	289.6
7.5°	289.1	286.8	286.0	289.0	288.5	288.7
8°	287.7	286.3	287.4	288.2	287.8	285.0
8.5°	289.0	284.8	286.0	285.7	287.5	287.8
9°	286.6	285.1	284.1	286.1	285.2	287.2
9.5°	283.9	283.5	283.1	286.4	284.1	287.6
10°	283.6	282.2	284.1	283.2	284.8	284.3
10.5°	281.7	281.6	281.8	282.0	283.5	283.7
11°	282.8	279.4	281.7	280.3	281.8	281.8
11.5°	282.7	279.1	281.3	280.4	281.2	283.8
12°	278.0	279.6	279.6	279.0	278.5	281.6
12.5°	280.8	276.7	278.8	277.6	277.3	279.0
13°	279.1	275.6	276.8	276.4	277.3	278.0
13.5°	277.3	274.6	274.2	276.3	276.5	275.4
14°	277.6	273.0	272.5	274.2	273.6	275.6
14.5°	276.3	271.6	272.0	272.4	272.3	274.7
15°	273.9	270.4	271.2	271.8	272.2	274.4
15.5°	273.3	269.8	269.1	270.4	269.9	272.8
16°	271.8	267.7	268.0	268.1	268.6	270.4
16.5°	270.6	266.1	265.9	265.3	268.3	269.1
17°	272.0	265.6	264.0	265.6	266.7	267.1
17.5°	271.0	264.0	263.2	262.7	264.8	266.0
18°	266.0	262.0	262.3	260.7	263.9	265.0
18.5°	263.4	260.3	261.4	259.1	262.4	264.0
19°	263.6	258.9	260.6	257.1	260.2	262.2
19.5°	261.5	257.9	257.5	256.4	257.1	260.7
20°	259.0	255.2	254.8	255.0	256.5	259.1
20.5°	258.2	252.8	253.0	253.7	255.5	257.5
21°	257.5	251.1	250.2	252.0	253.7	256.9
21.5°	256.9	249.5	249.0	248.1	251.1	254.6
22°	252.0	248.7	246.5	247.6	248.2	251.5



TEST NUMBER: A1914649A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
22.5°	251.3	245.9	244.3	244.3	246.7	250.7
23°	248.8	244.4	242.7	243.7	244.8	249.4
23.5°	246.7	241.5	241.0	242.4	242.8	246.2
24°	245.7	238.8	238.9	239.3	240.4	244.8
24.5°	242.7	237.9	236.5	237.9	238.2	242.3
25°	240.7	233.4	233.6	235.8	236.0	240.2
25.5°	238.7	231.3	231.8	232.4	233.6	237.7
26°	236.7	229.7	229.1	229.4	230.7	234.9
26.5°	233.7	227.4	225.9	226.6	228.6	232.4
27°	231.5	225.1	223.8	224.3	226.5	229.9
27.5°	228.7	222.3	221.3	222.6	224.0	228.9
28°	225.9	220.4	219.3	219.5	221.3	226.4
28.5°	223.7	217.8	216.2	216.8	218.2	224.2
29°	221.5	214.9	214.1	214.8	216.0	221.5
29.5°	219.2	212.3	210.2	211.5	213.7	218.4
30°	216.7	210.1	208.1	209.3	210.9	216.1
30.5°	214.2	207.5	204.9	206.0	208.0	213.3
31°	211.7	205.1	202.0	204.0	205.3	210.1
31.5°	208.9	201.9	199.8	200.8	202.6	207.1
32°	206.1	199.6	197.2	197.4	199.9	204.4
32.5°	203.3	196.7	194.5	195.2	197.0	201.7
33°	200.4	194.0	192.1	191.8	193.9	198.1
33.5°	197.5	191.2	188.9	189.5	190.9	195.0
34°	194.7	188.2	185.7	186.9	187.9	192.2
34.5°	192.1	185.1	183.6	184.3	184.6	189.0
35°	189.2	182.5	180.8	180.0	182.0	186.2
35.5°	185.8	179.7	177.4	177.4	179.3	183.8
36°	182.8	176.4	174.6	174.6	176.9	181.4
36.5°	179.8	173.4	172.0	171.5	173.7	179.0
37°	177.4	170.7	168.9	168.6	170.5	176.0
37.5°	174.2	167.7	166.6	165.4	167.6	172.8
38°	171.2	164.6	163.0	162.3	164.3	169.5
38.5°	168.1	162.1	159.7	159.2	161.4	166.4
39°	164.9	159.0	156.5	156.4	158.3	163.7
39.5°	161.7	155.8	154.3	153.8	155.5	160.4
40°	159.6	152.9	151.1	150.6	152.6	157.6
40.5°	156.7	150.0	147.9	147.6	149.3	155.0
41°	153.5	147.4	145.1	145.0	146.4	151.7
41.5°	150.3	144.3	142.5	141.6	143.3	148.8
42°	147.4	141.4	139.3	138.5	140.5	145.8
42.5°	144.4	138.5	136.5	135.8	137.5	142.8
43°	141.1	136.1	133.6	132.9	134.5	139.4
43.5°	138.1	133.3	130.9	130.4	131.4	136.5
44°	134.8	130.1	127.9	127.4	128.5	133.5
44.5°	131.8	127.2	124.8	124.6	125.8	130.8



TEST NUMBER: A1914649A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
45°	128.8	124.2	122.1	121.9	123.0	127.8
45.5°	125.9	121.7	119.3	119.2	120.3	124.6
46°	122.7	119.0	116.7	116.5	117.6	121.6
46.5°	120.3	116.0	114.3	113.8	114.6	119.0
47°	117.6	113.4	111.2	111.2	111.7	116.0
47.5°	114.7	110.6	108.7	108.4	109.0	113.2
48°	111.9	107.8	106.1	105.8	106.7	110.5
48.5°	109.3	105.3	103.6	103.2	104.0	108.2
49°	106.7	102.7	100.9	100.4	101.7	105.1
49.5°	104.2	100.1	98.4	97.7	98.9	102.6
50°	101.4	97.6	95.7	95.5	96.4	100.2
50.5°	98.5	95.1	93.3	93.0	93.6	97.4
51°	95.9	92.7	90.8	90.7	91.2	94.7
51.5°	93.4	90.3	88.7	88.2	89.0	92.1
52°	91.0	88.2	86.5	85.9	86.6	89.9
52.5°	88.9	85.8	84.0	83.6	84.3	87.5
53°	86.3	83.1	81.6	81.5	81.8	85.1
53.5°	83.7	80.9	79.4	79.1	79.6	82.6
54°	81.8	78.9	77.2	77.1	77.5	80.3
54.5°	79.6	76.8	75.1	74.7	75.5	78.1
55°	77.4	74.6	72.9	72.5	73.3	75.9
55.5°	75.0	72.3	70.9	70.6	71.2	73.6
56°	72.8	70.3	68.7	68.8	69.1	71.5
56.5°	70.7	68.3	66.8	66.8	67.2	69.4
57°	68.6	66.2	64.9	64.8	65.2	67.3
57.5°	66.6	64.2	62.9	62.9	63.2	65.4
58°	64.7	62.3	61.0	61.0	61.4	63.4
58.5°	62.8	60.4	59.4	59.1	59.6	61.4
59°	60.9	58.6	57.7	57.3	57.7	59.6
59.5°	59.0	56.8	55.9	55.7	56.0	57.7
60°	57.2	55.3	54.1	53.8	54.3	55.9
60.5°	55.4	53.5	52.4	52.1	52.7	54.1
61°	53.8	51.8	50.7	50.6	51.1	52.6
61.5°	52.0	50.1	49.2	48.9	49.4	50.8
62°	50.2	48.4	47.5	47.4	47.8	49.3
62.5°	48.4	46.8	46.1	45.9	46.3	47.6
63°	46.8	45.3	44.5	44.4	44.8	46.0
63.5°	45.2	43.9	43.1	42.9	43.3	44.5
64°	43.6	42.5	41.6	41.5	41.9	43.1
64.5°	42.2	40.9	40.3	40.1	40.5	41.6
65°	40.7	39.5	38.9	38.8	39.1	40.2
65.5°	39.2	38.2	37.6	37.4	37.8	38.9
66°	37.8	36.9	36.3	36.2	36.6	37.6
66.5°	36.6	35.7	34.9	35.0	35.3	36.4
67°	35.4	34.4	33.7	33.7	34.1	35.1



TEST NUMBER: A1914649A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
67.5°	34.0	33.3	32.4	32.6	32.9	33.8
68°	32.7	32.2	31.4	31.5	31.8	32.7
68.5°	31.5	30.8	30.2	30.4	30.7	31.5
69°	30.4	29.7	29.2	29.2	29.6	30.4
69.5°	29.2	28.5	28.1	28.2	28.6	29.3
70°	28.1	27.4	26.8	27.1	27.5	28.3
70.5°	27.1	26.4	26.0	26.2	26.5	27.2
71°	25.9	25.4	25.1	25.2	25.5	26.2
71.5°	25.0	24.4	24.1	24.2	24.6	25.3
72°	23.9	23.5	23.2	23.4	23.8	24.1
72.5°	22.9	22.6	22.3	22.4	22.8	23.2
73°	22.0	21.8	21.6	21.6	22.0	22.4
73.5°	21.2	21.0	20.7	20.8	21.2	21.7
74°	20.3	20.0	19.8	20.0	20.3	20.8
74.5°	19.5	19.3	19.1	19.2	19.4	19.9
75°	18.8	18.5	18.3	18.4	18.6	19.1
75.5°	18.0	17.7	17.4	17.6	17.8	18.2
76°	17.2	16.9	16.7	16.8	17.0	17.5
76.5°	16.5	16.1	16.0	16.1	16.3	16.6
77°	15.7	15.5	15.3	15.4	15.5	15.8
77.5°	15.0	14.7	14.6	14.7	14.7	15.2
78°	14.5	14.1	13.9	14.0	14.0	14.4
78.5°	13.6	13.4	13.3	13.3	13.3	13.7
79°	12.9	12.7	12.6	12.6	12.7	12.8
79.5°	12.3	12.1	12.1	11.9	12.1	12.2
80°	11.6	11.5	11.4	11.4	11.4	11.5
80.5°	11.1	10.9	10.9	10.8	10.8	10.9
81°	10.4	10.2	10.2	10.2	10.2	10.3
81.5°	9.7	9.5	9.5	9.5	9.5	9.7
82°	9.2	8.9	8.8	8.9	8.9	9.0
82.5°	8.4	8.2	8.1	8.2	8.2	8.3
83°	7.9	7.5	7.5	7.5	7.5	7.6
83.5°	7.1	6.8	6.8	6.8	6.9	6.9
84°	6.3	6.2	6.1	6.1	6.2	6.3
84.5°	5.7	5.4	5.4	5.4	5.5	5.6
85°	4.9	4.8	4.8	4.8	4.8	4.8
85.5°	4.2	4.0	4.1	4.1	4.2	4.2
86°	3.8	3.4	3.4	3.4	3.5	3.6
86.5°	2.9	2.7	2.7	2.8	2.8	2.9
87°	2.1	2.1	2.1	2.1	2.1	2.2
87.5°	1.5	1.5	1.5	1.5	1.6	1.6
88°	0.8	0.8	0.8	0.9	0.9	1.0
88.5°	0.1	0.4	0.4	0.4	0.4	0.4
89°	0.0	0.0	0.0	0.0	0.0	0.0
89.5°	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1914649A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
90°	0.0	0.0	0.0	0.0	0.0	0.0
90.5°	0.0	0.0	0.0	0.0	0.0	0.0
91°	0.0	0.0	0.0	0.0	0.0	0.0
91.5°	0.0	0.0	0.0	0.0	0.0	0.0
92°	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0
93°	0.0	0.0	0.0	0.0	0.0	0.0
93.5°	0.0	0.0	0.0	0.0	0.0	0.0
94°	0.0	0.0	0.0	0.0	0.0	0.0
94.5°	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0
95.5°	0.0	0.0	0.0	0.0	0.0	0.0
96°	0.0	0.0	0.0	0.0	0.0	0.0
96.5°	0.0	0.0	0.0	0.0	0.0	0.0
97°	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0
98°	0.0	0.0	0.0	0.0	0.0	0.0
98.5°	0.0	0.0	0.0	0.0	0.0	0.0
99°	0.0	0.0	0.0	0.0	0.0	0.0
99.5°	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0
100.5°	0.0	0.0	0.0	0.0	0.0	0.0
101°	0.0	0.0	0.0	0.0	0.0	0.0
101.5°	0.0	0.0	0.0	0.0	0.0	0.0
102°	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0
103°	0.0	0.0	0.0	0.0	0.0	0.0
103.5°	0.0	0.0	0.0	0.0	0.0	0.0
104°	0.0	0.0	0.0	0.0	0.0	0.0
104.5°	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0
105.5°	0.0	0.0	0.0	0.0	0.0	0.0
106°	0.0	0.0	0.0	0.0	0.0	0.0
106.5°	0.0	0.0	0.0	0.0	0.0	0.0
107°	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0
108°	0.0	0.0	0.0	0.0	0.0	0.0
108.5°	0.0	0.0	0.0	0.0	0.0	0.0
109°	0.0	0.0	0.0	0.0	0.0	0.0
109.5°	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0
110.5°	0.0	0.0	0.0	0.0	0.0	0.0
111°	0.0	0.0	0.0	0.0	0.0	0.0
111.5°	0.0	0.0	0.0	0.0	0.0	0.0
112°	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1914649A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0
113°	0.0	0.0	0.0	0.0	0.0	0.0
113.5°	0.0	0.0	0.0	0.0	0.0	0.0
114°	0.0	0.0	0.0	0.0	0.0	0.0
114.5°	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0
115.5°	0.0	0.0	0.0	0.0	0.0	0.0
116°	0.0	0.0	0.0	0.0	0.0	0.0
116.5°	0.0	0.0	0.0	0.0	0.0	0.0
117°	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0
118°	0.0	0.0	0.0	0.0	0.0	0.0
118.5°	0.0	0.0	0.0	0.0	0.0	0.0
119°	0.0	0.0	0.0	0.0	0.0	0.0
119.5°	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0
120.5°	0.0	0.0	0.0	0.0	0.0	0.0
121°	0.0	0.0	0.0	0.0	0.0	0.0
121.5°	0.0	0.0	0.0	0.0	0.0	0.0
122°	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0
123°	0.0	0.0	0.0	0.0	0.0	0.0
123.5°	0.0	0.0	0.0	0.0	0.0	0.0
124°	0.0	0.0	0.0	0.0	0.0	0.0
124.5°	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0
125.5°	0.0	0.0	0.0	0.0	0.0	0.0
126°	0.0	0.0	0.0	0.0	0.0	0.0
126.5°	0.0	0.0	0.0	0.0	0.0	0.0
127°	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0
128°	0.0	0.0	0.0	0.0	0.0	0.0
128.5°	0.0	0.0	0.0	0.0	0.0	0.0
129°	0.0	0.0	0.0	0.0	0.0	0.0
129.5°	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0
130.5°	0.0	0.0	0.0	0.0	0.0	0.0
131°	0.0	0.0	0.0	0.0	0.0	0.0
131.5°	0.0	0.0	0.0	0.0	0.0	0.0
132°	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0
133°	0.0	0.0	0.0	0.0	0.0	0.0
133.5°	0.0	0.0	0.0	0.0	0.0	0.0
134°	0.0	0.0	0.0	0.0	0.0	0.0
134.5°	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1914649A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
135°	0.0	0.0	0.0	0.0	0.0	0.0
135.5°	0.0	0.0	0.0	0.0	0.0	0.0
136°	0.0	0.0	0.0	0.0	0.0	0.0
136.5°	0.0	0.1	0.0	0.0	0.1	0.0
137°	0.0	0.0	0.0	0.0	0.1	0.0
137.5°	0.0	0.0	0.0	0.1	0.1	0.0
138°	0.0	0.1	0.0	0.1	0.1	0.0
138.5°	0.0	0.1	0.0	0.0	0.1	0.0
139°	0.0	0.0	0.1	0.1	0.1	0.0
139.5°	0.0	0.1	0.1	0.2	0.2	0.0
140°	0.0	0.1	0.1	0.1	0.1	0.0
140.5°	0.0	0.1	0.1	0.1	0.1	0.1
141°	0.0	0.2	0.1	0.1	0.1	0.1
141.5°	0.0	0.2	0.1	0.1	0.1	0.1
142°	0.0	0.1	0.1	0.2	0.1	0.2
142.5°	0.0	0.1	0.1	0.1	0.1	0.2
143°	0.0	0.1	0.1	0.1	0.2	0.1
143.5°	0.0	0.1	0.1	0.1	0.2	0.1
144°	0.0	0.1	0.1	0.2	0.2	0.1
144.5°	0.0	0.1	0.1	0.1	0.2	0.1
145°	0.0	0.2	0.1	0.2	0.2	0.2
145.5°	0.0	0.1	0.1	0.2	0.2	0.2
146°	0.0	0.1	0.1	0.1	0.2	0.2
146.5°	0.0	0.3	0.1	0.1	0.2	0.2
147°	0.0	0.3	0.1	0.1	0.2	0.2
147.5°	0.0	0.3	0.1	0.1	0.2	0.2
148°	0.0	0.3	0.1	0.1	0.2	0.2
148.5°	0.0	0.2	0.1	0.1	0.2	0.2
149°	0.0	0.2	0.1	0.1	0.2	0.2
149.5°	0.0	0.2	0.1	0.1	0.2	0.2
150°	0.0	0.2	0.1	0.1	0.2	0.2
150.5°	0.0	0.2	0.1	0.1	0.2	0.2
151°	0.0	0.2	0.1	0.1	0.2	0.2
151.5°	0.0	0.2	0.1	0.1	0.2	0.2
152°	0.0	0.2	0.1	0.1	0.2	0.2
152.5°	0.0	0.2	0.1	0.1	0.2	0.2
153°	0.0	0.2	0.1	0.1	0.2	0.2
153.5°	0.0	0.2	0.1	0.1	0.2	0.2
154°	0.1	0.2	0.1	0.1	0.2	0.2
154.5°	0.1	0.2	0.1	0.1	0.2	0.2
155°	0.0	0.2	0.1	0.1	0.2	0.2
155.5°	0.0	0.2	0.1	0.1	0.2	0.2
156°	0.1	0.2	0.1	0.1	0.2	0.2
156.5°	0.1	0.2	0.1	0.1	0.2	0.2
157°	0.1	0.2	0.1	0.1	0.2	0.2



TEST NUMBER: A1914649A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
157.5°	0.1	0.2	0.1	0.1	0.2	0.2
158°	0.1	0.2	0.1	0.1	0.2	0.2
158.5°	0.1	0.2	0.1	0.1	0.2	0.2
159°	0.1	0.2	0.1	0.1	0.2	0.2
159.5°	0.3	0.2	0.1	0.1	0.2	0.2
160°	0.3	0.2	0.1	0.1	0.2	0.2
160.5°	0.2	0.2	0.1	0.1	0.2	0.2
161°	0.2	0.2	0.1	0.1	0.2	0.2
161.5°	0.2	0.2	0.1	0.1	0.2	0.2
162°	0.2	0.2	0.1	0.1	0.2	0.2
162.5°	0.2	0.2	0.1	0.1	0.2	0.2
163°	0.2	0.2	0.1	0.1	0.2	0.2
163.5°	0.2	0.2	0.1	0.1	0.2	0.2
164°	0.2	0.2	0.1	0.1	0.2	0.2
164.5°	0.2	0.2	0.1	0.1	0.2	0.2
165°	0.2	0.2	0.1	0.1	0.2	0.2
165.5°	0.2	0.2	0.1	0.1	0.2	0.2
166°	0.2	0.2	0.1	0.1	0.2	0.2
166.5°	0.2	0.2	0.1	0.1	0.2	0.2
167°	0.2	0.2	0.1	0.1	0.2	0.2
167.5°	0.2	0.2	0.1	0.1	0.2	0.2
168°	0.2	0.2	0.1	0.1	0.2	0.2
168.5°	0.2	0.2	0.1	0.1	0.2	0.2
169°	0.2	0.2	0.1	0.1	0.2	0.2
169.5°	0.2	0.2	0.1	0.1	0.2	0.2
170°	0.2	0.2	0.1	0.1	0.2	0.2
170.5°	0.2	0.2	0.1	0.1	0.2	0.2
171°	0.2	0.2	0.1	0.1	0.2	0.2
171.5°	0.2	0.2	0.1	0.1	0.2	0.2
172°	0.2	0.2	0.1	0.1	0.2	0.2
172.5°	0.2	0.2	0.1	0.1	0.2	0.2
173°	0.2	0.2	0.1	0.1	0.2	0.2
173.5°	0.2	0.2	0.1	0.1	0.2	0.2
174°	0.2	0.2	0.1	0.1	0.2	0.2
174.5°	0.2	0.2	0.1	0.1	0.2	0.2
175°	0.2	0.2	0.1	0.1	0.2	0.2
175.5°	0.2	0.2	0.1	0.1	0.2	0.2
176°	0.2	0.2	0.1	0.1	0.2	0.2
176.5°	0.2	0.2	0.1	0.1	0.2	0.2
177°	0.2	0.2	0.1	0.1	0.2	0.2
177.5°	0.2	0.2	0.1	0.1	0.2	0.2
178°	0.2	0.2	0.1	0.1	0.2	0.2
178.5°	0.2	0.2	0.1	0.1	0.2	0.2
179°	0.2	0.2	0.1	0.1	0.2	0.2
179.5°	0.2	0.2	0.1	0.1	0.2	0.2



TEST NUMBER: A1914649A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
180°	0.2	0.2	0.2	0.2	0.2	0.2

(END OF REPORT)