

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: A1913066A001

Luminaire Tested:

Test Date: 2019-08-09



Test Information

Test Method: LM-41-14
Report Number: A1913066A001
Test Lab: EVERFINE
Test Date: 2019-08-09
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number:
Description: DL-NB31bA08CR1-25zz
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 573.4 lumens
Efficiency: N/A
Efficacy: 80.0 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.11 / 1.16
Luminous Opening: Point Source (0m x 0m x 0m)
CIE Type: Direct

Input Watts (W): 7.17117
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: A1913066A001
CATALOG NUMBER:

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270° - - - 135°-315°



TEST NUMBER: A1913066A001

CATALOG NUMBER:

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	104	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	71	70
4	89	79	72	67	87	78	71	66	76	70	65	74	69	65	72	67	64	62
5	83	72	65	59	81	71	64	59	69	63	58	68	62	58	66	61	57	55
6	78	66	59	53	76	65	58	53	64	57	52	62	56	52	61	56	52	50
7	73	61	53	48	71	60	53	48	59	52	47	57	51	47	56	51	47	45
8	68	56	49	43	67	55	48	43	54	48	43	53	47	43	52	47	43	41
9	64	52	45	40	63	51	44	40	50	44	39	49	44	39	48	43	39	38
10	60	48	41	37	59	48	41	36	47	41	36	46	40	36	45	40	36	34

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	Luminaire represents a point source (luminous area is zero).			
5°	No luminance values can be calculated.			
10°				
15°				
20°				
25°				
30°				
35°				
40°				
45°				
50°				
55°				
60°				
65°				
70°				
75°				
80°				
85°				



TEST NUMBER: A1913066A001

CATALOG NUMBER:

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	31.4	5.5
10°-20°	87.1	15.2
20°-30°	123.4	21.5
30°-40°	130.3	22.7
40°-50°	101.1	17.6
50°-60°	58.7	10.2
60°-70°	28.1	4.9
70°-80°	10.8	1.9
80°-90°	2.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	242.0	42.2
0°-40°	372.3	64.9
0°-60°	532.1	92.8
0°-90°	573.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	573.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	333	333	333	333	333	
5°	331	336	331	332	331	31
15°	310	318	307	305	310	87
25°	270	280	264	261	270	124
35°	211	226	203	197	211	130
45°	120	154	106	123	120	93
55°	49	83	46	62	49	45
65°	18	37	18	28	18	19
75°	5	14	5	10	5	6
85°	1	4	0	2	1	1
90°	0	0	0	0	0	0
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0



TEST NUMBER: A1913066A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	333.4	333.4	333.4	333.4	333.4	333.4	333.4	333.4	333.4	333.4	333.4
0.5°	333.4	335.6	337.8	333.4	335.1	335.7	335.8	333.6	334.4	335.3	334.8
1°	333.3	336.1	334.0	334.0	338.1	335.9	331.6	334.0	332.2	334.2	332.8
1.5°	334.0	335.7	336.8	334.1	336.7	334.6	335.1	334.2	332.0	332.9	333.6
2°	332.3	334.5	334.9	334.1	336.6	333.5	334.8	334.8	331.9	334.4	334.2
2.5°	332.6	334.2	334.8	333.7	337.4	336.1	334.6	333.5	331.6	334.5	332.9
3°	332.8	336.2	337.1	333.7	335.1	334.9	333.4	334.2	332.8	333.6	333.2
3.5°	332.5	336.2	335.7	333.7	337.0	333.4	334.2	333.7	331.9	333.5	332.3
4°	330.6	333.5	335.0	334.1	336.4	333.5	333.2	332.1	331.0	331.1	332.3
4.5°	328.9	333.0	333.7	333.6	337.2	334.6	332.9	332.6	330.5	334.6	332.2
5°	330.7	329.8	336.9	333.0	335.6	335.0	331.3	331.9	331.2	331.0	330.9
5.5°	330.0	332.2	334.3	331.3	334.5	332.6	332.2	331.4	329.6	329.0	330.3
6°	328.0	332.9	334.2	332.5	336.2	332.3	331.3	330.5	329.2	329.7	331.0
6.5°	328.3	331.6	332.2	330.1	334.7	332.1	332.1	329.5	328.4	327.4	329.9
7°	327.2	330.8	331.1	329.9	333.2	332.0	329.9	329.4	328.6	324.7	328.7
7.5°	326.9	329.5	330.4	329.0	332.5	330.1	328.2	328.2	326.9	326.8	327.1
8°	324.2	328.9	329.6	329.0	332.2	329.3	328.6	328.2	325.9	326.8	325.6
8.5°	323.1	327.4	328.3	328.8	333.6	328.3	329.2	326.1	324.5	325.3	326.1
9°	324.6	327.4	328.5	327.5	329.8	327.7	328.5	325.8	323.0	324.6	324.0
9.5°	324.0	326.9	327.0	328.7	332.8	327.1	325.7	325.0	322.5	322.8	322.7
10°	322.8	323.8	326.2	328.0	329.2	326.8	326.2	324.1	320.6	320.9	322.4
10.5°	321.8	324.7	327.2	324.6	331.2	325.8	325.4	323.2	319.4	320.4	322.1
11°	319.1	322.3	322.7	326.0	327.5	324.1	323.0	321.7	318.6	318.8	318.4
11.5°	318.0	321.9	320.9	322.4	327.6	323.3	322.8	320.8	317.7	318.0	315.0
12°	317.2	321.0	323.9	323.8	326.2	322.4	322.5	319.1	316.6	316.1	314.5
12.5°	315.5	319.6	322.7	322.5	324.6	321.1	320.7	319.3	315.3	315.6	313.5
13°	315.3	318.1	318.6	321.9	323.5	320.8	320.4	318.7	313.8	313.0	312.4
13.5°	313.5	317.5	318.9	318.6	322.0	318.5	318.7	314.8	311.7	312.6	312.6
14°	312.6	315.9	317.5	318.1	321.1	316.6	316.2	312.7	311.5	310.0	310.4
14.5°	310.2	314.9	315.8	316.8	318.7	315.1	313.8	312.4	308.9	308.6	308.4
15°	309.8	312.9	314.2	315.4	317.5	313.4	312.1	310.9	306.6	307.4	306.1
15.5°	307.9	310.2	313.3	312.8	316.9	313.0	311.8	309.6	305.9	306.2	305.4
16°	303.7	309.9	310.9	311.5	315.6	310.9	311.7	307.4	304.5	304.2	302.5
16.5°	303.3	307.9	308.8	309.5	313.7	310.9	308.7	305.6	302.4	300.7	299.1
17°	302.5	305.2	305.9	307.7	311.3	309.3	307.0	304.0	300.4	299.8	298.2
17.5°	300.1	304.5	305.4	306.1	310.8	305.7	305.8	302.3	298.2	296.6	295.0
18°	299.3	302.6	303.2	305.5	308.7	303.6	304.6	301.5	296.4	295.1	293.9
18.5°	297.7	300.5	304.4	303.5	306.5	303.8	302.1	299.9	294.6	293.0	292.6
19°	296.7	299.4	303.4	301.4	304.7	301.1	300.5	297.5	292.7	291.4	290.6
19.5°	293.9	296.2	300.0	298.5	304.6	300.0	297.9	295.7	290.6	288.7	288.1
20°	292.3	294.2	296.5	296.8	302.1	298.3	294.8	293.4	289.0	286.6	285.7
20.5°	289.7	292.0	295.6	295.7	299.6	294.3	293.0	290.6	286.8	284.1	284.0
21°	288.1	291.5	293.1	293.1	297.7	292.2	291.9	288.3	284.2	282.3	281.7
21.5°	286.0	289.8	292.0	291.5	295.7	291.6	289.4	285.8	282.3	280.7	279.0
22°	282.8	286.6	289.8	289.4	293.8	290.2	288.5	284.7	279.1	278.1	276.8



TEST NUMBER: A1913066A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
22.5°	280.5	285.5	286.6	287.4	292.1	287.5	285.4	282.6	276.8	275.3	274.1
23°	279.0	283.5	285.0	286.0	288.2	285.0	282.9	280.8	275.2	274.2	270.0
23.5°	276.1	281.4	282.8	283.4	286.6	283.8	281.1	277.3	271.7	271.8	268.6
24°	274.5	278.1	280.7	280.8	284.7	280.2	279.5	274.8	270.0	269.3	266.1
24.5°	271.0	275.1	279.1	277.9	281.8	279.9	276.6	272.5	267.3	265.4	263.8
25°	270.2	272.9	276.8	277.5	279.7	276.7	274.2	269.8	264.2	263.3	261.9
25.5°	267.5	270.9	274.0	274.5	278.7	274.6	271.7	267.5	261.6	260.7	259.5
26°	265.3	268.8	270.9	271.2	275.2	271.8	268.6	264.6	259.2	258.3	256.7
26.5°	262.7	266.2	268.6	269.1	273.6	269.6	267.0	262.9	257.2	256.5	253.9
27°	259.8	264.0	264.5	268.0	272.3	266.7	263.4	260.0	253.8	252.3	251.0
27.5°	258.3	261.1	263.8	264.4	269.3	264.2	261.7	257.7	252.0	250.4	247.9
28°	254.3	259.0	261.4	261.8	266.0	262.1	259.2	255.0	249.5	248.4	245.2
28.5°	252.3	256.5	258.7	259.3	263.2	258.7	255.4	252.1	247.4	244.8	243.0
29°	249.5	254.2	256.4	256.6	260.0	256.5	252.6	249.1	244.2	242.1	240.4
29.5°	247.3	251.4	252.8	253.9	258.7	253.8	250.4	246.7	241.0	238.7	237.6
30°	244.0	248.3	251.0	251.0	255.4	251.1	246.7	243.6	238.3	235.6	234.2
30.5°	241.0	245.6	247.4	248.3	253.2	248.7	244.1	240.6	235.9	232.7	231.5
31°	238.6	242.6	244.8	245.4	250.8	245.9	241.7	237.9	232.3	229.6	227.2
31.5°	235.5	239.7	241.2	242.0	247.3	242.7	239.2	234.8	228.8	226.6	224.5
32°	232.6	236.9	238.5	239.6	243.9	239.9	237.0	232.0	225.6	223.8	221.0
32.5°	229.1	233.8	236.0	236.7	241.3	237.1	234.1	229.3	221.8	220.8	218.0
33°	225.9	230.6	232.7	233.5	237.8	233.9	230.5	225.9	217.6	216.4	214.7
33.5°	221.6	227.3	229.8	230.5	234.5	231.8	227.8	221.9	213.7	213.2	211.1
34°	218.3	224.0	227.5	227.3	231.3	228.2	224.7	218.6	210.0	209.5	207.4
34.5°	214.9	220.8	223.7	223.9	228.6	224.9	221.1	215.2	206.0	205.9	204.0
35°	210.7	217.5	221.2	220.8	225.5	221.9	217.2	211.5	202.8	201.4	199.7
35.5°	206.5	213.5	217.9	218.1	220.9	218.2	213.5	207.6	197.4	197.6	196.2
36°	202.1	210.4	214.7	214.8	218.4	215.0	210.3	203.8	193.5	193.5	192.9
36.5°	198.6	207.0	210.4	211.6	215.4	211.4	207.1	199.5	188.7	189.8	188.7
37°	194.6	203.1	207.2	208.3	212.0	207.8	203.9	195.2	183.9	185.8	184.8
37.5°	190.6	199.1	204.2	205.0	209.5	204.7	200.2	191.4	179.4	181.4	181.2
38°	185.3	194.8	200.7	201.3	205.7	201.4	196.3	187.9	174.1	177.1	177.5
38.5°	180.4	191.0	196.9	198.0	201.8	197.3	193.0	183.6	169.3	172.2	173.9
39°	176.6	186.8	193.7	194.6	198.5	193.7	189.7	178.5	164.7	167.6	170.0
39.5°	172.7	182.8	190.3	190.9	194.7	190.5	185.5	173.2	159.8	163.1	165.8
40°	168.5	178.7	185.9	187.3	191.2	186.5	181.4	169.0	154.8	158.8	161.9
40.5°	163.2	174.4	182.4	183.3	187.7	183.1	177.7	164.6	149.6	154.5	157.9
41°	158.4	169.9	178.8	179.7	184.3	179.0	174.1	160.4	144.6	149.7	154.2
41.5°	153.6	165.9	174.8	175.8	180.6	175.3	170.3	154.9	139.6	145.4	150.3
42°	149.4	161.3	171.0	172.3	176.5	171.9	166.6	150.8	134.4	140.8	146.9
42.5°	144.0	157.4	167.3	168.8	173.0	167.5	162.9	146.2	129.4	136.5	142.6
43°	138.9	153.0	163.9	165.3	168.5	164.0	158.6	141.6	124.6	132.3	138.7
43.5°	134.4	148.4	159.5	161.5	165.0	160.6	155.1	137.7	119.6	127.6	134.7
44°	129.4	144.0	156.1	157.7	161.3	157.2	151.2	132.7	114.8	123.2	130.8
44.5°	124.8	140.0	152.9	154.4	157.5	152.8	147.1	127.9	110.4	118.8	127.0



TEST NUMBER: A1913066A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
45°	120.3	135.7	149.4	150.8	153.7	149.4	143.2	123.8	105.9	114.4	123.3
45.5°	115.6	131.3	145.5	147.0	149.9	145.4	139.1	119.2	101.4	110.3	119.4
46°	111.2	127.2	141.4	143.2	145.8	142.0	135.2	115.4	97.3	106.2	115.6
46.5°	106.9	122.8	137.9	139.6	142.5	138.0	131.2	110.8	93.3	101.9	111.8
47°	102.6	118.7	133.8	136.1	138.2	134.4	127.4	107.0	89.4	98.1	108.5
47.5°	98.2	114.5	130.4	132.5	134.3	130.1	123.7	102.6	85.8	94.3	105.1
48°	93.8	110.4	127.1	129.0	130.8	126.6	120.0	98.8	82.4	90.9	101.9
48.5°	90.0	106.2	123.4	125.5	126.9	123.1	116.3	94.9	79.1	87.5	98.6
49°	86.1	102.3	119.3	121.9	123.3	119.1	112.7	91.4	75.9	84.2	95.3
49.5°	82.2	98.1	115.6	118.6	119.4	115.6	109.1	88.2	72.6	80.9	92.0
50°	78.5	94.4	112.1	115.2	115.9	112.1	105.4	84.8	69.6	77.7	88.8
50.5°	74.8	90.7	108.6	111.8	112.4	108.7	102.0	81.5	66.6	74.4	85.7
51°	71.5	87.2	105.2	108.5	108.9	105.4	98.6	78.4	63.9	71.5	83.0
51.5°	68.2	83.7	101.8	105.2	105.7	102.0	95.4	75.3	61.3	68.7	80.0
52°	65.0	80.4	98.5	101.7	102.4	98.8	92.2	72.4	58.9	65.9	77.0
52.5°	61.9	76.9	95.1	98.3	99.0	95.5	89.2	69.4	56.4	63.1	74.2
53°	58.8	73.6	91.8	94.9	95.7	92.3	86.1	66.7	54.3	60.5	71.3
53.5°	56.0	70.5	88.6	91.6	92.5	89.5	82.9	64.3	52.2	57.9	68.6
54°	53.5	67.3	85.4	88.6	89.4	86.4	79.9	61.7	50.0	55.6	66.0
54.5°	51.2	64.2	82.2	85.6	86.2	83.1	76.9	59.2	48.0	53.6	63.6
55°	48.8	61.6	79.1	82.6	83.3	80.1	74.1	56.9	46.4	51.3	61.1
55.5°	46.7	58.7	76.4	79.5	80.2	77.3	71.4	54.8	44.4	49.2	58.6
56°	44.8	56.2	73.3	76.9	77.2	74.5	68.7	52.6	42.7	47.1	56.2
56.5°	42.8	53.8	70.4	74.0	74.2	71.7	66.1	50.4	41.1	45.3	54.3
57°	40.8	51.5	67.3	71.0	71.6	69.0	63.3	48.4	39.3	43.4	52.2
57.5°	39.1	49.1	64.7	68.2	68.8	66.5	61.0	46.5	37.8	41.6	50.1
58°	37.4	47.0	62.1	65.6	66.2	64.0	58.6	44.7	36.4	40.0	48.0
58.5°	35.7	45.1	59.4	62.8	63.6	61.4	56.2	42.9	34.8	38.5	46.0
59°	34.1	43.1	57.0	60.5	61.2	59.1	54.1	41.2	33.5	36.9	44.2
59.5°	32.5	41.1	54.8	58.1	58.7	56.8	52.0	39.6	32.1	35.2	42.4
60°	31.0	39.3	52.4	55.8	56.4	54.6	49.9	38.1	30.6	33.8	40.6
60.5°	29.5	37.6	50.1	53.5	54.2	52.5	47.9	36.5	29.3	32.4	39.0
61°	28.2	35.8	47.8	51.3	52.0	50.4	45.8	35.0	28.0	31.0	37.4
61.5°	26.8	34.2	45.8	49.2	49.8	48.3	44.0	33.6	26.6	29.7	35.8
62°	25.4	32.7	43.7	47.2	47.8	46.5	42.2	32.1	25.4	28.5	34.4
62.5°	24.2	31.2	41.9	45.3	45.9	44.6	40.5	30.8	24.2	27.2	33.0
63°	23.0	29.6	40.0	43.4	44.0	42.8	38.8	29.5	23.0	26.0	31.6
63.5°	21.8	28.3	38.1	41.6	42.2	41.1	37.1	28.3	21.9	24.7	30.3
64°	20.6	27.0	36.4	39.8	40.4	39.3	35.5	27.1	20.8	23.5	29.0
64.5°	19.4	25.7	34.8	38.1	38.7	37.8	34.0	25.7	19.7	22.4	27.8
65°	18.4	24.4	33.3	36.5	37.0	36.3	32.7	24.6	18.5	21.4	26.7
65.5°	17.2	23.2	31.8	35.0	35.4	34.9	31.4	23.4	17.5	20.4	25.5
66°	16.3	22.2	30.4	33.6	34.0	33.4	30.1	22.3	16.4	19.4	24.4
66.5°	15.5	21.1	28.9	32.2	32.6	32.0	28.8	21.3	15.5	18.6	23.3
67°	14.8	20.1	27.5	30.7	31.2	30.7	27.6	20.4	14.5	17.7	22.3



TEST NUMBER: A1913066A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
67.5°	14.2	19.0	26.3	29.5	29.9	29.4	26.5	19.4	13.9	16.7	21.3
68°	13.4	18.2	25.1	28.1	28.6	28.3	25.2	18.6	13.3	15.8	20.3
68.5°	12.7	17.2	23.9	27.1	27.3	27.0	24.1	17.6	12.5	14.9	19.4
69°	12.2	16.4	22.8	25.8	26.0	25.8	23.0	16.7	11.9	14.2	18.5
69.5°	11.5	15.5	21.8	24.6	24.9	24.7	22.0	15.9	11.4	13.6	17.7
70°	10.9	14.8	20.8	23.4	23.7	23.6	21.1	15.1	10.9	12.6	16.6
70.5°	10.3	13.9	19.7	22.4	22.6	22.5	20.2	14.6	10.3	11.9	15.8
71°	9.7	13.1	18.7	21.5	21.6	21.4	19.2	13.6	9.6	11.4	14.8
71.5°	9.1	12.4	17.7	20.5	20.7	20.6	18.2	12.8	9.2	10.6	13.9
72°	8.5	11.7	16.8	19.5	19.9	19.9	17.3	12.1	8.5	10.1	13.3
72.5°	8.0	11.0	15.8	18.5	18.9	18.8	16.4	11.4	8.2	9.5	12.4
73°	7.4	10.3	15.0	17.6	17.9	17.8	15.6	10.7	7.5	8.7	11.7
73.5°	6.8	9.7	14.2	16.8	16.9	16.9	14.6	10.3	7.0	8.3	11.0
74°	6.4	9.0	13.3	16.0	16.1	16.0	13.8	9.3	6.4	7.5	10.4
74.5°	5.9	8.4	12.5	15.0	15.2	15.3	13.0	8.8	6.3	7.0	9.6
75°	5.3	7.9	11.9	14.2	14.5	14.6	12.3	8.3	5.4	6.4	8.9
75.5°	4.9	7.3	11.1	13.5	13.6	13.7	11.7	7.6	5.0	6.2	8.4
76°	4.5	6.8	10.4	12.7	12.9	12.9	10.8	7.1	4.4	5.5	8.3
76.5°	4.0	6.3	9.8	12.1	12.2	12.2	10.4	6.4	4.1	5.2	7.5
77°	3.5	5.9	9.3	11.4	11.5	11.5	9.5	6.1	3.6	4.8	7.3
77.5°	3.0	5.5	8.8	10.9	10.8	10.9	9.1	5.5	3.2	4.3	6.8
78°	2.6	5.0	8.4	10.4	10.4	10.4	8.5	5.1	2.7	4.1	6.3
78.5°	2.4	4.6	8.0	9.9	9.8	9.8	8.4	4.7	2.2	3.8	6.3
79°	2.1	4.4	7.5	9.3	9.3	9.5	7.8	4.3	2.0	3.3	5.6
79.5°	2.0	4.1	7.0	8.8	8.8	9.0	7.4	4.2	1.5	3.1	5.3
80°	1.9	3.8	6.7	8.3	8.5	8.4	7.2	4.2	1.2	2.9	5.0
80.5°	1.8	3.5	6.2	7.8	7.8	8.2	6.4	3.3	1.1	2.5	4.5
81°	1.7	3.3	5.9	7.3	7.3	7.5	6.1	3.1	1.0	2.3	4.3
81.5°	1.6	3.1	5.4	6.8	6.7	7.1	5.6	2.9	0.9	2.2	4.3
82°	1.5	2.9	5.0	6.3	6.3	6.5	5.3	2.8	0.9	2.2	3.4
82.5°	1.4	2.5	4.5	5.9	6.1	6.3	5.1	2.4	0.9	2.2	3.2
83°	1.3	2.4	4.3	5.2	5.4	5.6	4.7	2.1	0.8	1.8	3.0
83.5°	0.9	2.1	3.6	5.1	5.0	5.3	4.2	2.1	0.5	1.3	2.6
84°	0.9	2.1	3.6	4.6	4.5	4.8	4.3	2.2	0.3	1.1	2.1
84.5°	0.9	1.9	3.3	4.2	4.3	4.2	3.4	2.0	0.1	1.1	2.2
85°	0.6	1.6	2.9	3.7	4.1	4.2	3.2	1.3	0.1	0.9	2.1
85.5°	0.4	1.5	2.6	3.3	3.2	3.4	2.8	1.2	0.1	0.9	1.2
86°	0.2	1.2	2.3	2.9	2.9	3.0	2.4	0.9	0.1	0.7	1.1
86.5°	0.1	1.0	2.0	2.5	2.3	2.7	2.1	0.9	0.1	0.4	0.9
87°	0.1	0.9	1.6	2.1	2.1	2.2	2.1	0.8	0.0	0.1	0.3
87.5°	0.0	0.7	1.3	1.8	2.0	2.0	1.9	0.5	0.0	0.1	0.0
88°	0.0	0.4	1.0	1.4	1.2	1.4	1.2	0.2	0.0	0.0	0.0
88.5°	0.0	0.2	0.7	1.1	0.8	1.1	0.9	0.1	0.0	0.1	0.0
89°	0.0	0.1	0.3	0.7	0.6	0.9	0.7	0.0	0.0	0.0	0.0
89.5°	0.0	0.0	0.1	0.4	0.1	0.4	0.3	0.0	0.0	0.0	0.0



TEST NUMBER: A1913066A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
91°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
91.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
93°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
93.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
94°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
94.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
96°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
96.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
101°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
101.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
103°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
103.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
104°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
104.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
106°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
106.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
108°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
108.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
109°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
109.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
111°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
111.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
112°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1913066A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
113°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
113.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
114°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
114.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
116°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
116.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
118°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
118.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
119°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
119.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
121°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
121.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
123°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
123.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
124°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
124.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
126°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
126.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
128°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
128.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
129°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
129.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
131°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
131.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
133°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
133.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
134°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
134.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1913066A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
136°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
136.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
138°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
138.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
139°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
139.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
141°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
141.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
143°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
143.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
144°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
144.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145.5°	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
146°	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
146.5°	0.2	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147°	0.2	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
148°	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
148.5°	0.1	0.1	0.0	0.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
149°	0.1	0.1	0.0	0.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
149.5°	0.1	0.1	0.0	0.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150.5°	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
151°	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
151.5°	0.1	0.1	0.0	0.2	0.0	0.0	0.0	0.1	0.0	0.0	0.0
152°	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.1	0.0	0.0	0.0
152.5°	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
153°	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
153.5°	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.1	0.1	0.0	0.0
154°	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.1	0.1	0.0	0.0
154.5°	0.1	0.1	0.0	0.1	0.1	0.0	0.0	0.1	0.1	0.0	0.0
155°	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.1	0.1	0.1	0.0
155.5°	0.1	0.1	0.0	0.1	0.1	0.0	0.0	0.1	0.1	0.0	0.0
156°	0.1	0.1	0.0	0.1	0.1	0.0	0.0	0.1	0.1	0.0	0.0
156.5°	0.1	0.1	0.0	0.1	0.1	0.0	0.0	0.1	0.1	0.0	0.1
157°	0.1	0.1	0.0	0.1	0.1	0.1	0.0	0.1	0.1	0.1	0.1



TEST NUMBER: A1913066A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
157.5°	0.1	0.1	0.0	0.1	0.2	0.0	0.1	0.1	0.1	0.2	0.1
158°	0.1	0.1	0.0	0.1	0.1	0.0	0.1	0.1	0.1	0.2	0.2
158.5°	0.1	0.1	0.0	0.1	0.2	0.1	0.1	0.1	0.1	0.2	0.2
159°	0.1	0.1	0.0	0.1	0.2	0.1	0.1	0.1	0.1	0.2	0.1
159.5°	0.1	0.1	0.0	0.1	0.2	0.1	0.1	0.1	0.1	0.2	0.2
160°	0.1	0.1	0.0	0.1	0.2	0.1	0.1	0.1	0.1	0.2	0.2
160.5°	0.1	0.1	0.0	0.1	0.2	0.1	0.1	0.1	0.1	0.2	0.2
161°	0.1	0.1	0.0	0.1	0.2	0.1	0.1	0.1	0.1	0.2	0.1
161.5°	0.1	0.1	0.0	0.1	0.2	0.1	0.2	0.1	0.1	0.2	0.1
162°	0.1	0.1	0.0	0.1	0.2	0.1	0.2	0.1	0.1	0.2	0.1
162.5°	0.1	0.1	0.0	0.1	0.1	0.1	0.2	0.0	0.1	0.2	0.1
163°	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1
163.5°	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1
164°	0.1	0.1	0.0	0.1	0.1	0.0	0.1	0.0	0.1	0.1	0.1
164.5°	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1
165°	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1
165.5°	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1
166°	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1
166.5°	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1
167°	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1
167.5°	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1
168°	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1
168.5°	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1
169°	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1
169.5°	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1
170°	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1
170.5°	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1
171°	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1
171.5°	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1
172°	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1
172.5°	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1
173°	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1
173.5°	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1
174°	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1
174.5°	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1
175°	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1
175.5°	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1
176°	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1
176.5°	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1
177°	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1
177.5°	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1
178°	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1
178.5°	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1
179°	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1
179.5°	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1



TEST NUMBER: A1913066A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
180°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1



TEST NUMBER: A1913066A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	333.4	333.4	333.4	333.4	333.4	333.4
0.5°	333.9	337.6	336.3	334.5	333.1	333.4
1°	333.5	334.9	333.5	332.2	333.1	333.3
1.5°	332.8	335.4	332.8	333.8	333.1	334.0
2°	334.4	335.4	334.0	331.7	333.1	332.3
2.5°	334.4	333.5	331.7	334.1	333.4	332.6
3°	334.6	335.0	330.1	333.4	332.6	332.8
3.5°	333.0	333.4	332.0	333.1	332.7	332.5
4°	332.1	333.6	331.7	331.9	333.0	330.6
4.5°	331.1	333.7	331.7	330.6	332.3	328.9
5°	331.4	332.2	331.0	331.7	331.4	330.7
5.5°	331.2	332.5	329.1	329.8	331.4	330.0
6°	329.8	332.4	327.2	328.2	330.4	328.0
6.5°	329.0	329.8	326.9	327.1	330.0	328.3
7°	326.9	329.2	324.9	327.2	327.5	327.2
7.5°	324.6	329.2	324.7	324.6	327.0	326.9
8°	324.3	326.0	324.8	324.8	327.2	324.2
8.5°	323.0	328.1	323.4	326.0	324.6	323.1
9°	322.1	324.4	322.8	323.6	324.2	324.6
9.5°	319.7	323.6	322.1	321.7	323.2	324.0
10°	319.7	320.9	319.5	321.0	321.0	322.8
10.5°	318.6	319.8	319.1	319.0	321.2	321.8
11°	317.1	318.3	315.1	318.5	318.6	319.1
11.5°	316.1	317.0	316.0	315.8	318.6	318.0
12°	315.5	314.3	315.1	315.1	317.3	317.2
12.5°	312.6	312.0	314.7	312.4	318.2	315.5
13°	311.3	313.8	309.1	312.1	315.9	315.3
13.5°	310.5	311.3	309.0	312.2	313.2	313.5
14°	309.5	309.8	307.5	309.2	312.0	312.6
14.5°	308.6	307.8	306.1	307.5	308.7	310.2
15°	305.2	304.8	303.7	305.5	308.9	309.8
15.5°	302.9	303.6	303.6	304.7	308.1	307.9
16°	301.2	302.6	301.9	302.2	305.1	303.7
16.5°	298.8	300.0	299.6	300.5	302.3	303.3
17°	297.8	299.3	296.6	299.5	302.2	302.5
17.5°	296.6	295.9	294.6	297.1	300.9	300.1
18°	293.4	294.3	293.7	295.2	298.8	299.3
18.5°	292.1	292.6	292.3	293.8	296.5	297.7
19°	289.7	288.9	291.0	291.3	295.9	296.7
19.5°	287.0	285.2	286.6	289.3	293.0	293.9
20°	285.7	283.9	285.4	288.2	291.2	292.3
20.5°	282.6	282.3	281.0	284.8	287.8	289.7
21°	280.2	280.8	277.8	282.8	287.3	288.1
21.5°	276.8	278.9	276.1	280.4	285.1	286.0
22°	275.8	276.2	275.6	278.3	281.1	282.8



TEST NUMBER: A1913066A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
22.5°	271.9	273.6	272.5	276.3	280.2	280.5
23°	270.3	270.4	270.2	273.9	278.1	279.0
23.5°	268.2	268.7	267.6	271.3	276.2	276.1
24°	266.0	265.9	265.2	269.6	273.8	274.5
24.5°	263.0	263.8	263.9	267.0	270.8	271.0
25°	260.3	261.4	261.8	264.0	267.5	270.2
25.5°	258.3	257.7	257.9	261.1	265.5	267.5
26°	255.5	255.8	255.4	259.3	264.3	265.3
26.5°	252.6	252.9	252.9	256.5	261.2	262.7
27°	250.1	250.6	249.7	253.5	258.3	259.8
27.5°	246.8	247.4	247.2	250.9	255.0	258.3
28°	244.1	244.2	245.5	248.4	253.0	254.3
28.5°	241.7	240.8	242.6	245.3	250.1	252.3
29°	239.0	238.0	239.4	242.6	247.6	249.5
29.5°	236.1	234.6	236.1	239.3	245.2	247.3
30°	232.8	231.4	232.9	236.3	242.6	244.0
30.5°	229.5	229.1	229.9	233.7	239.9	241.0
31°	226.1	225.9	226.6	230.9	235.7	238.6
31.5°	222.7	222.8	223.5	227.7	232.0	235.5
32°	219.4	219.4	220.6	224.4	228.8	232.6
32.5°	216.2	215.1	217.3	221.1	226.0	229.1
33°	212.9	212.5	213.9	218.0	223.3	225.9
33.5°	209.4	209.1	209.9	214.8	220.0	221.6
34°	205.9	205.3	206.6	211.6	216.3	218.3
34.5°	202.5	201.3	202.9	208.1	212.5	214.9
35°	198.7	196.7	199.6	204.3	209.1	210.7
35.5°	194.9	193.0	196.1	201.0	205.6	206.5
36°	191.5	189.9	192.2	197.2	202.1	202.1
36.5°	187.7	186.4	188.6	193.5	197.6	198.6
37°	184.0	182.6	185.2	189.7	193.8	194.6
37.5°	180.5	179.2	181.2	186.2	190.0	190.6
38°	176.2	175.7	177.0	182.4	186.1	185.3
38.5°	171.6	172.4	173.5	178.6	181.7	180.4
39°	168.1	168.5	169.9	175.0	178.1	176.6
39.5°	164.4	164.3	166.4	171.1	174.1	172.7
40°	160.7	160.5	162.8	167.3	170.4	168.5
40.5°	157.0	156.8	159.2	163.7	165.9	163.2
41°	153.3	152.7	155.5	159.7	161.2	158.4
41.5°	149.4	148.7	151.5	155.8	157.4	153.6
42°	145.7	144.6	147.8	152.0	153.1	149.4
42.5°	141.9	141.3	144.2	148.4	149.3	144.0
43°	138.2	138.1	140.4	144.8	144.9	138.9
43.5°	134.1	134.7	136.5	141.2	140.3	134.4
44°	130.6	130.8	132.7	137.3	135.9	129.4
44.5°	126.9	127.0	129.0	133.4	131.5	124.8



TEST NUMBER: A1913066A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
45°	123.2	123.3	125.3	129.6	127.3	120.3
45.5°	119.6	119.8	121.8	125.8	122.9	115.6
46°	115.9	116.2	118.4	122.6	118.8	111.2
46.5°	112.3	112.7	114.7	118.7	114.4	106.9
47°	108.9	109.3	111.3	114.8	110.6	102.6
47.5°	105.6	105.8	107.7	111.5	106.5	98.2
48°	102.1	102.6	104.4	107.9	102.7	93.8
48.5°	98.9	99.2	101.2	104.5	98.6	90.0
49°	95.8	95.9	97.9	101.0	95.0	86.1
49.5°	92.6	92.7	94.6	97.6	91.3	82.2
50°	89.5	89.7	91.4	94.4	87.8	78.5
50.5°	86.6	86.6	88.3	91.0	84.1	74.8
51°	83.8	83.6	85.4	87.7	80.4	71.5
51.5°	80.6	80.8	82.6	84.4	77.2	68.2
52°	77.8	77.9	79.3	81.2	73.9	65.0
52.5°	75.0	75.1	76.7	78.2	70.6	61.9
53°	72.2	72.2	73.7	75.4	67.3	58.8
53.5°	69.8	69.5	71.1	72.4	64.3	56.0
54°	67.1	67.0	68.5	69.4	61.4	53.5
54.5°	64.7	64.5	65.9	66.6	58.5	51.2
55°	62.3	62.1	63.4	64.0	56.1	48.8
55.5°	60.0	59.9	60.9	61.5	53.8	46.7
56°	57.7	57.6	58.4	58.9	51.5	44.8
56.5°	55.5	55.4	56.4	56.5	49.0	42.8
57°	53.4	53.1	54.3	54.2	46.8	40.8
57.5°	51.4	51.1	52.2	51.9	44.7	39.1
58°	49.4	49.3	50.1	49.7	42.7	37.4
58.5°	47.5	47.3	48.2	47.6	40.8	35.7
59°	45.7	45.5	46.1	45.7	39.0	34.1
59.5°	43.9	43.8	44.3	43.8	37.2	32.5
60°	42.1	42.1	42.6	41.8	35.6	31.0
60.5°	40.5	40.5	40.8	40.0	33.8	29.5
61°	38.9	38.9	39.2	38.3	32.3	28.2
61.5°	37.5	37.3	37.8	36.7	30.7	26.8
62°	35.9	35.9	36.2	35.0	29.3	25.4
62.5°	34.5	34.6	34.6	33.4	27.9	24.2
63°	33.1	33.1	33.3	31.9	26.5	23.0
63.5°	31.8	31.7	31.9	30.6	25.1	21.8
64°	30.5	30.4	30.6	29.3	24.0	20.6
64.5°	29.3	29.3	29.3	28.0	22.8	19.4
65°	28.2	28.2	28.1	26.8	21.8	18.4
65.5°	26.9	27.0	27.0	25.5	20.7	17.2
66°	25.8	25.8	25.8	24.3	19.6	16.3
66.5°	24.6	24.8	24.7	23.3	18.5	15.5
67°	23.6	23.7	23.6	22.2	17.6	14.8



TEST NUMBER: A1913066A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
67.5°	22.6	22.6	22.5	21.2	16.7	14.2
68°	21.5	21.8	21.6	20.2	15.9	13.4
68.5°	20.7	20.8	20.6	19.2	15.0	12.7
69°	19.8	19.8	19.7	18.4	14.3	12.2
69.5°	18.7	18.9	18.7	17.3	13.5	11.5
70°	17.8	17.8	17.7	16.4	12.7	10.9
70.5°	16.9	17.0	16.9	15.5	12.0	10.3
71°	16.0	16.2	16.0	14.7	11.2	9.7
71.5°	15.2	15.3	15.2	13.8	10.6	9.1
72°	14.7	14.5	14.4	13.0	9.9	8.5
72.5°	13.6	13.6	13.6	12.2	9.3	8.0
73°	12.8	12.9	12.8	11.5	8.8	7.4
73.5°	12.1	12.2	12.1	10.8	8.2	6.8
74°	11.4	11.5	11.4	10.1	7.6	6.4
74.5°	10.7	11.0	11.0	9.5	7.0	5.9
75°	10.3	10.5	10.5	9.1	6.6	5.3
75.5°	9.7	10.0	9.9	8.7	6.1	4.9
76°	9.3	9.5	9.4	8.2	5.7	4.5
76.5°	8.7	9.0	8.8	7.7	5.3	4.0
77°	8.3	8.5	8.3	7.2	4.9	3.5
77.5°	8.1	8.0	7.9	6.8	4.7	3.0
78°	7.4	7.5	7.4	6.4	4.2	2.6
78.5°	7.0	7.0	6.9	6.0	3.9	2.4
79°	6.4	6.6	6.4	5.7	3.7	2.1
79.5°	6.2	6.0	6.0	5.3	3.3	2.0
80°	5.4	5.6	5.5	4.8	3.1	1.9
80.5°	5.1	5.2	5.1	4.6	2.9	1.8
81°	4.8	4.8	4.7	4.1	2.7	1.7
81.5°	4.2	4.3	4.2	3.7	2.5	1.6
82°	4.2	3.9	3.9	3.5	2.3	1.5
82.5°	3.4	3.5	3.5	3.1	2.1	1.4
83°	3.0	3.0	3.0	2.7	1.9	1.3
83.5°	2.8	2.6	2.5	2.5	1.7	0.9
84°	2.2	2.3	2.2	2.1	1.6	0.9
84.5°	2.0	1.9	1.9	1.9	1.4	0.9
85°	1.6	1.5	1.5	1.5	1.1	0.6
85.5°	1.1	1.2	1.0	1.2	1.0	0.4
86°	0.8	0.8	0.8	0.9	0.8	0.2
86.5°	0.3	0.5	0.5	0.6	0.6	0.1
87°	0.0	0.2	0.1	0.3	0.5	0.1
87.5°	0.0	0.0	0.0	0.0	0.3	0.0
88°	0.0	0.0	0.0	0.0	0.1	0.0
88.5°	0.0	0.0	0.0	0.0	0.1	0.0
89°	0.0	0.0	0.0	0.0	0.0	0.0
89.5°	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1913066A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
90°	0.0	0.0	0.0	0.0	0.0	0.0
90.5°	0.0	0.0	0.0	0.0	0.0	0.0
91°	0.0	0.0	0.0	0.0	0.0	0.0
91.5°	0.0	0.0	0.0	0.0	0.0	0.0
92°	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0
93°	0.0	0.0	0.0	0.0	0.0	0.0
93.5°	0.0	0.0	0.0	0.0	0.0	0.0
94°	0.0	0.0	0.0	0.0	0.0	0.0
94.5°	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0
95.5°	0.0	0.0	0.0	0.0	0.0	0.0
96°	0.0	0.0	0.0	0.0	0.0	0.0
96.5°	0.0	0.0	0.0	0.0	0.0	0.0
97°	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0
98°	0.0	0.0	0.0	0.0	0.0	0.0
98.5°	0.0	0.0	0.0	0.0	0.0	0.0
99°	0.0	0.0	0.0	0.0	0.0	0.0
99.5°	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0
100.5°	0.0	0.0	0.0	0.0	0.0	0.0
101°	0.0	0.0	0.0	0.0	0.0	0.0
101.5°	0.0	0.0	0.0	0.0	0.0	0.0
102°	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0
103°	0.0	0.0	0.0	0.0	0.0	0.0
103.5°	0.0	0.0	0.0	0.0	0.0	0.0
104°	0.0	0.0	0.0	0.0	0.0	0.0
104.5°	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0
105.5°	0.0	0.0	0.0	0.0	0.0	0.0
106°	0.0	0.0	0.0	0.0	0.0	0.0
106.5°	0.0	0.0	0.0	0.0	0.0	0.0
107°	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0
108°	0.0	0.0	0.0	0.0	0.0	0.0
108.5°	0.0	0.0	0.0	0.0	0.0	0.0
109°	0.0	0.0	0.0	0.0	0.0	0.0
109.5°	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0
110.5°	0.0	0.0	0.0	0.0	0.0	0.0
111°	0.0	0.0	0.0	0.0	0.0	0.0
111.5°	0.0	0.0	0.0	0.0	0.0	0.0
112°	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1913066A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0
113°	0.0	0.0	0.0	0.0	0.0	0.0
113.5°	0.0	0.0	0.0	0.0	0.0	0.0
114°	0.0	0.0	0.0	0.0	0.0	0.0
114.5°	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0
115.5°	0.0	0.0	0.0	0.0	0.0	0.0
116°	0.0	0.0	0.0	0.0	0.0	0.0
116.5°	0.0	0.0	0.0	0.0	0.0	0.0
117°	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0
118°	0.0	0.0	0.0	0.0	0.0	0.0
118.5°	0.0	0.0	0.0	0.0	0.0	0.0
119°	0.0	0.0	0.0	0.0	0.0	0.0
119.5°	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0
120.5°	0.0	0.0	0.0	0.0	0.0	0.0
121°	0.0	0.0	0.0	0.0	0.0	0.0
121.5°	0.0	0.0	0.0	0.0	0.0	0.0
122°	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0
123°	0.0	0.0	0.0	0.0	0.0	0.0
123.5°	0.0	0.0	0.0	0.0	0.0	0.0
124°	0.0	0.0	0.0	0.0	0.0	0.0
124.5°	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0
125.5°	0.0	0.0	0.0	0.0	0.0	0.0
126°	0.0	0.0	0.0	0.0	0.0	0.0
126.5°	0.0	0.0	0.0	0.0	0.0	0.0
127°	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0
128°	0.0	0.0	0.0	0.0	0.0	0.0
128.5°	0.0	0.0	0.0	0.0	0.0	0.0
129°	0.0	0.0	0.0	0.0	0.0	0.0
129.5°	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0
130.5°	0.0	0.0	0.0	0.0	0.0	0.0
131°	0.0	0.0	0.0	0.0	0.0	0.0
131.5°	0.0	0.0	0.0	0.0	0.0	0.0
132°	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0
133°	0.0	0.0	0.0	0.0	0.0	0.0
133.5°	0.0	0.0	0.0	0.0	0.0	0.0
134°	0.0	0.0	0.0	0.0	0.0	0.0
134.5°	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1913066A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
135°	0.0	0.0	0.0	0.0	0.0	0.0
135.5°	0.0	0.0	0.0	0.0	0.0	0.0
136°	0.0	0.0	0.0	0.0	0.0	0.0
136.5°	0.0	0.0	0.0	0.0	0.0	0.0
137°	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0
138°	0.0	0.0	0.0	0.0	0.0	0.0
138.5°	0.0	0.0	0.0	0.0	0.0	0.0
139°	0.0	0.0	0.0	0.0	0.0	0.0
139.5°	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0
140.5°	0.0	0.0	0.0	0.0	0.0	0.0
141°	0.0	0.0	0.0	0.0	0.0	0.0
141.5°	0.0	0.0	0.0	0.0	0.0	0.0
142°	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0
143°	0.0	0.0	0.0	0.0	0.0	0.0
143.5°	0.0	0.0	0.0	0.0	0.0	0.0
144°	0.0	0.0	0.0	0.0	0.0	0.0
144.5°	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.1
145.5°	0.0	0.0	0.0	0.0	0.1	0.1
146°	0.0	0.1	0.0	0.0	0.1	0.1
146.5°	0.0	0.1	0.1	0.0	0.1	0.2
147°	0.0	0.1	0.1	0.0	0.1	0.2
147.5°	0.0	0.2	0.1	0.0	0.0	0.1
148°	0.0	0.2	0.2	0.0	0.1	0.1
148.5°	0.0	0.1	0.2	0.0	0.1	0.1
149°	0.0	0.1	0.1	0.0	0.1	0.1
149.5°	0.0	0.1	0.1	0.0	0.1	0.1
150°	0.0	0.1	0.1	0.0	0.1	0.1
150.5°	0.0	0.1	0.1	0.0	0.1	0.1
151°	0.0	0.1	0.1	0.0	0.1	0.1
151.5°	0.0	0.1	0.1	0.0	0.1	0.1
152°	0.0	0.1	0.1	0.0	0.1	0.1
152.5°	0.0	0.1	0.1	0.0	0.1	0.1
153°	0.0	0.1	0.1	0.0	0.1	0.1
153.5°	0.0	0.1	0.1	0.0	0.1	0.1
154°	0.0	0.1	0.1	0.0	0.1	0.1
154.5°	0.0	0.1	0.1	0.0	0.1	0.1
155°	0.1	0.1	0.1	0.0	0.1	0.1
155.5°	0.0	0.1	0.2	0.0	0.1	0.1
156°	0.0	0.1	0.2	0.0	0.1	0.1
156.5°	0.0	0.1	0.1	0.0	0.1	0.1
157°	0.1	0.1	0.1	0.0	0.1	0.1



TEST NUMBER: A1913066A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
157.5°	0.0	0.1	0.1	0.0	0.1	0.1
158°	0.1	0.1	0.1	0.0	0.1	0.1
158.5°	0.1	0.1	0.1	0.0	0.1	0.1
159°	0.1	0.1	0.1	0.0	0.1	0.1
159.5°	0.1	0.1	0.1	0.0	0.1	0.1
160°	0.1	0.1	0.1	0.0	0.1	0.1
160.5°	0.1	0.1	0.1	0.0	0.1	0.1
161°	0.1	0.1	0.1	0.0	0.1	0.1
161.5°	0.1	0.1	0.1	0.0	0.1	0.1
162°	0.1	0.1	0.1	0.0	0.1	0.1
162.5°	0.1	0.1	0.1	0.0	0.1	0.1
163°	0.1	0.1	0.1	0.0	0.1	0.1
163.5°	0.0	0.1	0.1	0.0	0.1	0.1
164°	0.0	0.1	0.1	0.0	0.1	0.1
164.5°	0.0	0.1	0.1	0.0	0.1	0.1
165°	0.0	0.1	0.1	0.0	0.1	0.1
165.5°	0.0	0.1	0.1	0.0	0.1	0.1
166°	0.0	0.1	0.1	0.0	0.1	0.1
166.5°	0.0	0.1	0.1	0.0	0.1	0.1
167°	0.0	0.1	0.1	0.0	0.1	0.1
167.5°	0.0	0.1	0.1	0.0	0.1	0.1
168°	0.0	0.1	0.1	0.0	0.1	0.1
168.5°	0.0	0.1	0.1	0.0	0.1	0.1
169°	0.0	0.1	0.1	0.0	0.1	0.1
169.5°	0.0	0.1	0.1	0.0	0.1	0.1
170°	0.0	0.1	0.1	0.0	0.1	0.1
170.5°	0.0	0.1	0.1	0.0	0.1	0.1
171°	0.0	0.1	0.1	0.0	0.1	0.1
171.5°	0.0	0.1	0.1	0.0	0.1	0.1
172°	0.0	0.1	0.1	0.0	0.1	0.1
172.5°	0.0	0.1	0.1	0.0	0.1	0.1
173°	0.0	0.1	0.1	0.0	0.1	0.1
173.5°	0.0	0.1	0.1	0.0	0.1	0.1
174°	0.0	0.1	0.1	0.0	0.1	0.1
174.5°	0.0	0.1	0.1	0.0	0.1	0.1
175°	0.0	0.1	0.1	0.0	0.1	0.1
175.5°	0.0	0.1	0.1	0.0	0.1	0.1
176°	0.0	0.1	0.1	0.0	0.1	0.1
176.5°	0.0	0.1	0.1	0.0	0.1	0.1
177°	0.0	0.1	0.1	0.0	0.1	0.1
177.5°	0.0	0.1	0.1	0.0	0.1	0.1
178°	0.0	0.1	0.1	0.0	0.1	0.1
178.5°	0.0	0.1	0.1	0.0	0.1	0.1
179°	0.0	0.1	0.1	0.0	0.1	0.1
179.5°	0.0	0.1	0.1	0.0	0.1	0.1



TEST NUMBER: A1913066A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
180°	0.1	0.1	0.1	0.1	0.1	0.1

(END OF REPORT)