

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P677540

Luminaire Tested: ML4DM08LSFL95FS1E-TL40R2GMW-3500K

Issue Date: 4/25/2023

Test Information

Test Method: LM-79-2019
Report Number: P677540
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2304-979-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/25/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML4DM08LSFL95FS1E-TL40R2GMW-3500K
Description: DIRECT MOUNT, CONICAL LENS TRIM
Light Source: (1) SELECTABLE LUMEN LED 95CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 545.2 lumens
Efficiency: N/A
Efficacy: 52.9 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.15 / 1.23
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P677540
CATALOG NUMBER: ML4DM08LSFL95FS1E-TL40R2GMW-3500K

Luminous Intensity Polar Plot





TEST NUMBER: P677540

CATALOG NUMBER: ML4DM08LSFL95FS1E-TL40R2GMW-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88				88															
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77				77															
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67				67															
4	88	77	70	64	86	76	69	63	74	67	62	71	66	62	69	65	61	59				59															
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52				52															
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47				47															
7	70	58	50	45	69	57	50	45	56	49	44	55	48	44	53	48	44	42				42															
8	66	53	46	40	64	53	45	40	52	45	40	50	44	40	49	44	40	38				38															
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34				34															
10	58	46	38	34	57	45	38	33	44	38	33	43	37	33	43	37	33	31				31															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	33858
5°	33678
10°	33279
15°	32959
20°	32054
25°	30989
30°	29910
35°	28384
40°	26487
45°	23828
50°	20398
55°	16602
60°	12483
65°	9223
70°	6852
75°	6624
80°	5398
85°	5378

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 23828 cd/sqm



TEST NUMBER: P677540

CATALOG NUMBER: ML4DM08LSFL95FS1E-TL40R2GMW-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.8	4.7
10°-20°	72.5	13.3
20°-30°	105.0	19.3
30°-40°	117.7	21.6
40°-50°	105.0	19.3
50°-60°	69.1	12.7
60°-70°	32.3	5.9
70°-80°	14.2	2.6
80°-90°	3.8	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	203.3	37.3
0°-40°	320.9	58.9
0°-60°	494.9	90.8
0°-90°	545.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	545.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	274	
5°	272	26
15°	258	72
25°	228	105
35°	188	118
45°	137	105
55°	77	69
65°	32	32
75°	14	14
85°	4	4
90°	0	



TEST NUMBER: P677540

CATALOG NUMBER: ML4DM08LSFL95FS1E-TL40R2GMW-3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	274.5
2.5°	272.0
5°	272.0
7.5°	270.7
10°	265.7
12.5°	261.9
15°	258.1
17.5°	251.8
20°	244.2
22.5°	236.6
25°	227.7
27.5°	220.1
30°	210.0
32.5°	199.9
35°	188.5
37.5°	177.1
40°	164.5
42.5°	151.8
45°	136.6
47.5°	121.5
50°	106.3
52.5°	91.1
55°	77.2
57.5°	63.3
60°	50.6
62.5°	40.5
65°	31.6
67.5°	24.0
70°	19.0
72.5°	16.4
75°	13.9
77.5°	10.1
80°	7.6
82.5°	5.1
85°	3.8
87.5°	1.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)