

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P601319

Luminaire Tested: **ML4DM06AWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 2700K**

Issue Date: 7/29/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P601319
 Test Lab: COOPER LIGHTING SOLUTIONS
 Issue Date: 7/29/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO
 Catalog Number: ML4DM06AWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 2700K
 Description: DIRECT MOUNT, 25D WW OPTIC, OPEN TRIM
 Light Source: (1) SELECTABLE LUMEN LED 90CRI / 2700K CCT
 Ballast/Driver: -

Summary

Lumens per Lamp: N/A
 Luminaire Lumens: 497.0 lumens
 Efficiency: N/A
 Efficacy: 59.9 lumens/watt
 Spacing Criteria (0/90/45): 1.31 / 0.61 / 0.81
 Luminous Opening: Circular (Dia: 0.21' x H: 0')
 CIE Type: Direct


Input Watts (W): 8.3
 Input Voltage (V): NR
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT



Meas		Calibration Due Date	
Instrument	Identificatio		
Photometer	GONIO 1 11111111	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P601319
CATALOG NUMBER: ML4DM06AWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 2700K

Luminous Intensity Polar Plot



TEST NUMBER: P601319

CATALOG NUMBER: ML4DM06AWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93	93	93	93	
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85	85	85	85	
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78	78	78	78	
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72	72	72	72	
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66	66	66	66	
6	85	75	69	64	83	75	68	64	73	68	64	72	67	63	70	66	63	61	61	61	61	
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57	57	57	57	
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53	53	53	53	
9	72	62	56	51	71	61	55	51	60	55	51	60	54	51	59	54	51	49	49	49	49	
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46	46	46	46	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	156904	156904	156904
5°	202703	152083	116709
10°	260934	129537	77305
15°	314220	103040	56979
20°	354747	79370	41332
25°	373772	58742	30939
30°	344524	41894	24940
35°	270683	28256	21664
40°	201113	17106	19126
45°	129859	11655	17103
50°	76044	8400	15229
55°	40353	5836	13433
60°	16988	3094	11810
65°	6052	2466	9115
70°	739	1477	5262
75°	976	976	0
80°	0	0	0
85°	0	0	0

TEST NUMBER: P601319
 CATALOG NUMBER: ML4DM06AWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.8	9.2
10°-20°	118.6	23.9
20°-30°	144.9	29.2
30°-40°	108.5	21.8
40°-50°	53.8	10.8
50°-60°	19.8	4.0
60°-70°	4.9	1.0
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	309.3	62.2
0°-40°	417.8	84.1
0°-60°	491.4	98.9
0°-90°	497.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	497.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	497	497	497	497	497	
5°	640	575	480	394	368	67
15°	961	604	315	191	174	273
25°	1073	431	169	85	89	481
35°	702	207	73	39	56	443
45°	291	68	26	22	38	232
55°	73	19	11	9	24	70
65°	8	2	3	3	12	10
75°	1	1	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	

TEST NUMBER: P601319

CATALOG NUMBER: ML4DM06AWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 2700K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	45°	67.5°	90°	112.5°	135°
0°	496.9	496.9	496.9	496.9	496.9	496.9	496.9	496.9	496.9	496.9	496.9
2.5°	559.6	559.6	566.1	555.6	555.6	552.3	528.7	514.8	499.3	476.5	449.7
5°	639.5	655.8	642.7	624.8	635.4	630.5	575.1	524.6	479.8	435.8	393.5
7.5°	742.1	746.2	734.8	712.0	707.1	703.8	608.5	525.4	447.2	381.2	332.4
10°	813.8	819.5	814.6	806.5	778.8	772.2	619.1	494.5	404.0	334.0	275.3
12.5°	905.8	904.2	896.9	873.2	841.5	832.5	612.6	466.8	358.4	281.0	225.6
15°	961.2	971.0	960.4	897.7	883.0	860.2	604.4	429.3	315.2	243.6	191.4
17.5°	1009.3	1005.2	984.8	944.9	907.5	887.1	572.7	374.7	277.0	202.8	158.0
20°	1055.7	1056.5	1024.8	975.9	915.6	879.0	525.4	337.2	236.2	167.0	131.2
22.5°	1076.9	1075.3	1034.5	962.0	892.0	854.5	480.6	294.9	197.9	135.2	105.1
25°	1072.8	1043.5	1016.6	931.1	852.1	806.5	430.9	258.2	168.6	114.0	84.7
27.5°	1020.7	1006.0	960.4	874.9	783.6	737.2	369.0	220.8	140.9	89.6	69.2
30°	944.9	927.8	873.2	802.4	682.6	646.0	314.4	180.8	114.9	76.6	57.0
32.5°	832.5	819.5	763.3	670.4	576.7	535.2	260.7	144.2	92.9	56.2	46.4
35°	702.2	701.4	651.7	575.9	478.2	435.8	206.9	115.7	73.3	44.8	39.1
37.5°	602.8	581.6	532.7	462.7	380.4	345.4	162.1	90.4	54.6	35.0	32.6
40°	487.9	479.0	427.7	368.2	295.7	269.6	119.7	67.6	41.5	28.5	29.3
42.5°	392.6	380.4	338.1	280.2	228.9	207.7	91.2	52.1	32.6	24.4	26.1
45°	290.8	285.1	260.7	208.5	169.4	154.8	67.6	40.7	26.1	20.4	22.0
47.5°	211.8	205.3	188.2	154.8	123.0	114.0	52.1	31.8	21.2	16.3	17.1
50°	154.8	150.7	139.3	112.4	90.4	83.1	39.1	24.4	17.1	13.0	14.7
52.5°	106.7	108.3	98.6	79.8	64.4	59.5	29.3	17.9	13.8	10.6	12.2
55°	73.3	71.7	67.6	52.1	41.5	38.3	18.7	12.2	10.6	8.1	9.0
57.5°	44.8	44.8	41.5	32.6	26.1	24.4	11.4	8.1	7.3	5.7	7.3
60°	26.9	26.9	22.8	18.7	15.5	13.8	6.5	4.9	4.9	4.1	5.7
62.5°	14.7	14.7	13.0	10.6	8.1	7.3	4.1	4.1	3.3	3.3	4.9
65°	8.1	7.3	6.5	4.9	4.1	4.1	2.4	3.3	3.3	3.3	3.3
67.5°	3.3	3.3	3.3	2.4	2.4	2.4	1.6	2.4	2.4	2.4	2.4
70°	0.8	1.6	1.6	1.6	0.8	0.8	1.6	1.6	1.6	1.6	1.6
72.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
75°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.8	0.8	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P601319
 CATALOG NUMBER: ML4DM06AWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 2700K

CANDELA DISTRIBUTION (continued):

	157.5°	180°
0°	496.9	496.9
2.5°	450.5	443.1
5°	377.2	368.2
7.5°	299.8	294.1
10°	245.2	241.1
12.5°	206.9	204.5
15°	175.1	174.3
17.5°	147.4	145.0
20°	120.6	123.0
22.5°	99.4	97.8
25°	83.9	88.8
27.5°	71.7	78.2
30°	62.7	68.4
32.5°	53.8	62.7
35°	47.2	56.2
37.5°	42.4	50.5
40°	39.1	46.4
42.5°	34.2	43.2
45°	30.1	38.3
47.5°	26.1	34.2
50°	23.6	31.0
52.5°	20.4	27.7
55°	17.1	24.4
57.5°	15.5	22.0
60°	13.0	18.7
62.5°	9.8	15.5
65°	7.3	12.2
67.5°	4.9	9.0
70°	2.4	5.7
72.5°	0.8	1.6
75°	0.0	0.0
77.5°	0.0	0.0
80°	0.0	0.0
82.5°	0.0	0.0
85°	0.0	0.0
87.5°	0.0	0.0
90°	0.0	0.0

(END OF REPORT)