

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P601327

Luminaire Tested: **ML4DM06AWW9FS1E - TIR4D25AWW - TL43R2G_ TL44S2G_ 4000K**

Issue Date: 7/29/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P601327
 Test Lab: COOPER LIGHTING SOLUTIONS
 Issue Date: 7/29/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO
 Catalog Number: ML4DM06AWW9FS1E - TIR4D25AWW - TL43R2G_ TL44S2G_ 4000K
 Description: DIRECT MOUNT, 25D WW OPTIC, DIFFUSE CLEAR LENS TRIM
 Light Source: (1) SELECTABLE LUMEN LED 90CRI / 4000K CCT
 Ballast/Driver: -

Summary

Lumens per Lamp: N/A
 Luminaire Lumens: 611.7 lumens
 Efficiency: N/A
 Efficacy: 73.7 lumens/watt
 Spacing Criteria (0/90/45): 1.33 / 0.62 / 0.83
 Luminous Opening: Circular (Dia: 0.21' x H: 0')
 CIE Type: Direct


Input Watts (W): 8.3
 Input Voltage (V): NR
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT



Meas			
Instrument	Identificatio		Calibration Due Date
Photometer	GONIO 1 11111111	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P601327
CATALOG NUMBER: ML4DM06AWW9FS1E - TIR4D25AWW - TL43R2G_ TL44S2G_ 4000K

Luminous Intensity Polar Plot



TEST NUMBER: P601327

CATALOG NUMBER: ML4DM06AWW9FS1E - TIR4D25AWW - TL43R2G_ TL44S2G_ 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85
3	101	94	88	84	99	92	87	83	89	85	82	87	83	80	85	82	79	78
4	95	87	81	76	93	85	80	75	83	78	75	81	77	74	79	76	73	71
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65
6	84	75	68	64	83	74	68	63	72	67	63	71	66	62	70	65	62	60
7	80	70	63	59	78	69	63	58	68	62	58	66	62	58	65	61	57	56
8	76	65	59	54	74	65	58	54	64	58	54	62	57	54	61	57	53	52
9	72	61	55	51	70	61	55	50	60	54	50	59	54	50	58	53	50	48
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	186365	186365	186365
5°	241057	180040	139150
10°	313037	159388	95966
15°	372736	126218	68454
20°	430791	95970	46204
25°	439656	72225	37942
30°	411103	52468	29680
35°	337178	35464	26521
40°	251567	23125	23125
45°	169559	15585	20318
50°	99231	11446	17685
55°	52409	8148	13983
60°	25388	4673	10673
65°	10311	3138	7098
70°	4893	1939	3878
75°	2562	1342	0
80°	2000	2000	0
85°	0	0	0

TEST NUMBER: P601327

CATALOG NUMBER: ML4DM06AWW9FS1E - TIR4D25AWW - TL43R2G_ TL44S2G_ 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.8	9.0
10°-20°	141.9	23.2
20°-30°	173.8	28.4
30°-40°	136.2	22.3
40°-50°	70.2	11.5
50°-60°	26.6	4.4
60°-70°	6.8	1.1
70°-80°	1.4	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	370.4	60.6
0°-40°	506.6	82.8
0°-60°	603.4	98.6
0°-90°	611.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	611.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	590	590	590	590	590	
5°	760	689	568	481	439	79
15°	1140	726	386	232	209	326
25°	1262	518	207	108	109	573
35°	875	275	92	51	69	543
45°	380	95	35	28	46	295
55°	95	30	15	13	25	92
65°	14	5	4	4	10	17
75°	2	1	1	1	0	3
85°	0	0	0	0	0	0
90°	0	0	0	0	0	

TEST NUMBER: P601327

CATALOG NUMBER: ML4DM06AWW9FS1E - TIR4D25AWW - TL43R2G_ TL44S2G_ 4000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	45°	67.5°	90°	112.5°	135°
0°	590.2	590.2	590.2	590.2	590.2	590.2	590.2	590.2	590.2	590.2	590.2
2.5°	665.3	662.1	679.1	654.7	638.9	660.0	641.0	618.8	595.5	556.4	536.3
5°	760.5	762.6	765.8	758.4	755.2	753.1	688.6	628.3	568.0	508.8	481.3
7.5°	869.4	849.4	862.0	833.5	838.8	824.0	733.0	618.8	540.5	464.3	399.8
10°	976.3	954.1	964.6	938.2	931.9	919.2	758.4	593.4	497.1	394.5	339.5
12.5°	1067.2	1057.7	1047.1	1011.2	998.5	963.6	758.4	559.5	435.8	340.6	277.1
15°	1140.2	1130.7	1119.1	1072.5	1033.4	1002.7	725.6	511.9	386.1	291.9	231.6
17.5°	1200.5	1163.5	1164.6	1097.9	1064.1	1023.9	693.9	463.3	334.2	244.3	196.7
20°	1282.0	1214.3	1202.6	1131.8	1068.3	1023.9	637.8	410.4	285.6	206.3	161.8
22.5°	1269.3	1209.0	1222.7	1118.0	1050.3	1032.3	575.4	354.3	245.4	173.5	130.1
25°	1261.9	1218.5	1195.2	1083.1	1001.7	944.5	518.3	309.9	207.3	142.8	107.9
27.5°	1230.1	1164.6	1129.6	1016.5	926.6	880.0	450.6	262.3	173.5	113.2	91.0
30°	1127.5	1079.9	1042.9	924.4	829.3	784.8	390.3	217.9	143.9	93.1	71.9
32.5°	1016.5	975.2	918.1	820.8	711.8	668.5	323.7	186.2	117.4	74.0	60.3
35°	874.7	840.9	786.9	688.6	583.9	564.8	275.0	149.1	92.0	59.2	50.8
37.5°	737.2	707.6	652.6	563.8	482.3	454.8	222.1	119.5	74.0	48.7	43.4
40°	610.3	575.4	539.4	452.7	386.1	356.5	170.3	93.1	56.1	39.1	37.0
42.5°	485.5	464.3	425.2	361.7	296.2	277.1	126.9	69.8	44.4	32.8	31.7
45°	379.7	357.5	320.5	278.2	223.2	208.4	95.2	53.9	34.9	26.4	27.5
47.5°	277.1	266.5	242.2	206.3	170.3	153.4	71.9	42.3	27.5	22.2	23.3
50°	202.0	191.4	179.8	147.0	118.5	114.2	53.9	32.8	23.3	18.0	19.0
52.5°	139.6	138.6	125.9	104.7	86.7	79.3	41.3	25.4	19.0	14.8	15.9
55°	95.2	94.1	85.7	73.0	61.3	56.1	29.6	19.0	14.8	11.6	12.7
57.5°	61.3	62.4	57.1	49.7	40.2	37.0	20.1	13.8	10.6	8.5	9.5
60°	40.2	40.2	34.9	31.7	25.4	23.3	13.8	9.5	7.4	6.3	7.4
62.5°	24.3	25.4	22.2	18.0	15.9	13.8	8.5	6.3	5.3	4.2	5.3
65°	13.8	14.8	12.7	10.6	9.5	8.5	5.3	4.2	4.2	3.2	4.2
67.5°	8.5	8.5	7.4	6.3	5.3	5.3	3.2	3.2	3.2	3.2	3.2
70°	5.3	5.3	4.2	4.2	3.2	3.2	2.1	3.2	2.1	2.1	2.1
72.5°	3.2	3.2	2.1	2.1	2.1	2.1	2.1	2.1	2.1	1.1	1.1
75°	2.1	2.1	2.1	2.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1
77.5°	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	0.0
80°	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P601327
 CATALOG NUMBER: ML4DM06AWW9FS1E - TIR4D25AWW - TL43R2G_ TL44S2G_ 4000K

CANDELA DISTRIBUTION (continued):

	157.5°	180°
0°	590.2	590.2
2.5°	523.6	525.7
5°	451.6	439.0
7.5°	375.5	355.4
10°	303.6	299.3
12.5°	256.0	250.7
15°	214.7	209.4
17.5°	179.8	170.3
20°	150.2	137.5
22.5°	124.8	125.9
25°	106.8	108.9
27.5°	92.0	94.1
30°	77.2	81.4
32.5°	69.8	76.2
35°	60.3	68.8
37.5°	53.9	62.4
40°	47.6	56.1
42.5°	42.3	50.8
45°	37.0	45.5
47.5°	32.8	41.3
50°	27.5	36.0
52.5°	23.3	30.7
55°	19.0	25.4
57.5°	15.9	21.2
60°	12.7	16.9
62.5°	9.5	12.7
65°	6.3	9.5
67.5°	4.2	6.3
70°	3.2	4.2
72.5°	1.1	2.1
75°	0.0	0.0
77.5°	0.0	0.0
80°	0.0	0.0
82.5°	0.0	0.0
85°	0.0	0.0
87.5°	0.0	0.0
90°	0.0	0.0

(END OF REPORT)