

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P601334

Luminaire Tested: **ML4DM06AWWD2W1E - TIR4D25AWW - TL41R_ TL42S_ 2700K**

Issue Date: 7/29/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P601334
 Test Lab: COOPER LIGHTING SOLUTIONS
 Issue Date: 7/29/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO
 Catalog Number: ML4DM06AWWD2W1E - TIR4D25AWW - TL41R_ TL42S_ 2700K
 Description: DIRECT MOUNT, 25D WW OPTIC, OPEN TRIM
 Light Source: (1) SELECTABLE LUMEN LED D2W / 2700K CCT
 Ballast/Driver: -

Summary

Lumens per Lamp: N/A
 Luminaire Lumens: 388.9 lumens
 Efficiency: N/A
 Efficacy: 46.9 lumens/watt
 Spacing Criteria (0/90/45): 1.31 / 0.61 / 0.81
 Luminous Opening: Circular (Dia: 0.21' x H: 0')
 CIE Type: Direct


Input Watts (W): 8.3
 Input Voltage (V): NR
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT



Meas		Calibration Due Date	
Instrument	Identificatio		
Photometer	GONIO 1 11111111	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P601334
CATALOG NUMBER: ML4DM06AWWD2W1E - TIR4D25AWW - TL41R_ TL42S_ 2700K

Luminous Intensity Polar Plot



TEST NUMBER: P601334

CATALOG NUMBER: ML4DM06AWWD2W1E - TIR4D25AWW - TL41R_ TL42S_ 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66
6	85	75	69	64	83	75	68	64	73	68	64	72	67	63	70	66	63	61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53
9	72	62	56	51	71	61	55	51	60	55	51	60	54	51	59	54	51	49
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	122801	122801	122801
5°	158612	119023	91319
10°	204181	101385	60504
15°	245897	80647	44590
20°	277628	62132	32360
25°	292489	45990	24214
30°	269632	32779	19507
35°	211820	22126	16961
40°	157379	13397	14963
45°	101637	9110	13397
50°	59490	6583	11888
55°	31600	4569	10515
60°	13262	2400	9283
65°	4782	1868	7173
70°	554	1200	4155
75°	732	732	0
80°	0	0	0
85°	0	0	0

TEST NUMBER: P601334

CATALOG NUMBER: ML4DM06AWWD2W1E - TIR4D25AWW - TL41R_ TL42S_ 2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.9	9.2
10°-20°	92.8	23.9
20°-30°	113.4	29.2
30°-40°	84.9	21.8
40°-50°	42.1	10.8
50°-60°	15.5	4.0
60°-70°	3.8	1.0
70°-80°	0.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	242.1	62.2
0°-40°	327.0	84.1
0°-60°	384.5	98.9
0°-90°	388.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	388.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	389	389	389	389	389	
5°	500	450	376	308	288	52
15°	752	473	247	150	136	214
25°	840	337	132	66	70	376
35°	550	162	57	31	44	346
45°	228	53	20	17	30	181
55°	57	15	8	7	19	55
65°	6	2	2	2	10	8
75°	1	1	1	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0

TEST NUMBER: P601334

CATALOG NUMBER: ML4DM06AWWD2W1E - TIR4D25AWW - TL41R_ TL42S_ 2700K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	45°	67.5°	90°	112.5°	135°
0°	388.9	388.9	388.9	388.9	388.9	388.9	388.9	388.9	388.9	388.9	388.9
2.5°	437.9	437.9	443.0	434.8	434.8	432.2	413.7	402.9	390.8	372.9	351.9
5°	500.4	513.2	503.0	488.9	497.2	493.4	450.1	410.5	375.5	341.0	307.9
7.5°	580.7	583.9	575.0	557.1	553.3	550.8	476.2	411.2	350.0	298.3	260.1
10°	636.8	641.3	637.5	631.1	609.4	604.3	484.5	386.9	316.2	261.4	215.5
12.5°	708.9	707.6	701.9	683.4	658.5	651.5	479.4	365.3	280.5	219.9	176.6
15°	752.2	759.9	751.6	702.5	691.0	673.2	473.0	335.9	246.7	190.6	149.8
17.5°	789.8	786.6	770.7	739.5	710.1	694.2	448.1	293.2	216.7	158.7	123.7
20°	826.2	826.8	801.9	763.7	716.5	687.8	411.2	263.9	184.9	130.7	102.6
22.5°	842.7	841.5	809.6	752.8	698.0	668.7	376.1	230.8	154.9	105.8	82.2
25°	839.5	816.6	795.6	728.6	666.8	631.1	337.2	202.1	132.0	89.2	66.3
27.5°	798.7	787.3	751.6	684.6	613.2	576.9	288.8	172.8	110.3	70.1	54.2
30°	739.5	726.1	683.4	627.9	534.2	505.5	246.1	141.5	89.9	59.9	44.6
32.5°	651.5	641.3	597.3	524.6	451.3	418.8	204.0	112.8	72.7	44.0	36.3
35°	549.5	548.9	510.0	450.7	374.2	341.0	161.9	90.5	57.4	35.1	30.6
37.5°	471.7	455.2	416.9	362.1	297.7	270.3	126.9	70.8	42.7	27.4	25.5
40°	381.8	374.8	334.7	288.1	231.4	211.0	93.7	52.9	32.5	22.3	22.9
42.5°	307.3	297.7	264.5	219.3	179.1	162.6	71.4	40.8	25.5	19.1	20.4
45°	227.6	223.1	204.0	163.2	132.6	121.1	52.9	31.9	20.4	15.9	17.2
47.5°	165.7	160.6	147.3	121.1	96.3	89.2	40.8	24.9	16.6	12.7	13.4
50°	121.1	117.9	109.0	88.0	70.8	65.0	30.6	19.1	13.4	10.2	11.5
52.5°	83.5	84.8	77.1	62.5	50.4	46.5	22.9	14.0	10.8	8.3	9.6
55°	57.4	56.1	52.9	40.8	32.5	30.0	14.7	9.6	8.3	6.4	7.0
57.5°	35.1	35.1	32.5	25.5	20.4	19.1	8.9	6.4	5.7	4.5	5.7
60°	21.0	21.0	17.8	14.7	12.1	10.8	5.1	3.8	3.8	3.2	4.5
62.5°	11.5	11.5	10.2	8.3	6.4	5.7	3.2	3.2	2.5	2.5	3.8
65°	6.4	5.7	5.1	3.8	3.2	3.2	1.9	2.5	2.5	2.5	2.5
67.5°	2.5	2.5	2.5	1.9	1.9	1.9	1.3	1.9	1.9	1.9	1.9
70°	0.6	1.3	1.3	1.3	0.6	0.6	1.3	1.3	1.3	1.3	1.3
72.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
75°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.6	0.6	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P601334
 CATALOG NUMBER: ML4DM06AWWD2W1E - TIR4D25AWW - TL41R_ TL42S_ 2700K

CANDELA DISTRIBUTION (continued):

	157.5°	180°
0°	388.9	388.9
2.5°	352.5	346.8
5°	295.1	288.1
7.5°	234.6	230.1
10°	191.9	188.7
12.5°	161.9	160.0
15°	137.1	136.4
17.5°	115.4	113.5
20°	94.3	96.3
22.5°	77.8	76.5
25°	65.7	69.5
27.5°	56.1	61.2
30°	49.1	53.5
32.5°	42.1	49.1
35°	37.0	44.0
37.5°	33.1	39.5
40°	30.6	36.3
42.5°	26.8	33.8
45°	23.6	30.0
47.5°	20.4	26.8
50°	18.5	24.2
52.5°	15.9	21.7
55°	13.4	19.1
57.5°	12.1	17.2
60°	10.2	14.7
62.5°	7.6	12.1
65°	5.7	9.6
67.5°	3.8	7.0
70°	1.9	4.5
72.5°	0.6	1.3
75°	0.0	0.0
77.5°	0.0	0.0
80°	0.0	0.0
82.5°	0.0	0.0
85°	0.0	0.0
87.5°	0.0	0.0
90°	0.0	0.0

(END OF REPORT)