

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: HALO

Report Number: P601386

Luminaire Tested: **ML4DM08LSAWW95FS1E - TIR4D25AWW - TL41R\_ TL42S\_ 5000K**

Issue Date: 7/29/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

**Test Information**

Test Method: LM-79-08  
 Report Number: P601386  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Issue Date: 7/29/2022  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: HALO  
 Catalog Number: ML4DM08LSAWW95FS1E - TIR4D25AWW - TL41R\_ TL42S\_ 5000K  
 Description: DIRECT MOUNT, 25D WW OPTIC, OPEN TRIM  
 Light Source: (1) SELECTABLE LUMEN LED 95CRI / 5000K CCT  
 Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
 Luminaire Lumens: 653.9 lumens  
 Efficiency: N/A  
 Efficacy: 63.5 lumens/watt  
 Spacing Criteria (0/90/45): 1.31 / 0.61 / 0.81  
 Luminous Opening: Circular (Dia: 0.21' x H: 0')  
 CIE Type: Direct


Input Watts (W): 10.3  
 Input Voltage (V): NR  
 Input Current (Ain): NR  
 Voltage Rise (V): NR  
 Power Factor: NR  
 Total Harmonic Distortion (THDi): NR  
 Frequency (hertz): 60  
 Stabilization Time: NR  
 Operation Time: NR  
 Ambient Temperature (°C): NR  
 Test Distance: 25 FT



Meas		Calibration Due Date	
Instrument	Identificatio		
Photometer	GONIO 1 11111111	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P601386  
CATALOG NUMBER: ML4DM08LSAWW95FS1E - TIR4D25AWW - TL41R\_ TL42S\_ 5000K

### Luminous Intensity Polar Plot



TEST NUMBER: P601386

CATALOG NUMBER: ML4DM08LSAWW95FS1E - TIR4D25AWW - TL41R\_ TL42S\_ 5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20														
RC	80					70					50					30					10					0									
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0								
RCR																																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100								
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93									93								
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85									85								
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78									78								
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72									72								
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66									66								
6	85	75	69	64	83	75	68	64	73	68	64	72	67	63	70	66	63	61									61								
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57									57								
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53									53								
9	72	62	56	51	71	61	55	51	60	55	51	60	54	51	59	54	51	49									49								
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46									46								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	206447	206447	206447
5°	266668	200104	153541
10°	343305	170450	101706
15°	413436	135600	74992
20°	466746	104438	54370
25°	491778	77312	40694
30°	453288	55093	32815
35°	356105	37199	28525
40°	264634	22547	25186
45°	170854	15317	22507
50°	100017	11053	19994
55°	53125	7652	17727
60°	22356	4042	15599
65°	7995	3213	12029
70°	1016	1939	6924
75°	1342	1342	0
80°	0	0	0
85°	0	0	0

TEST NUMBER: P601386  
 CATALOG NUMBER: ML4DM08LSAWW95FS1E - TIR4D25AWW - TL41R\_ TL42S\_ 5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	60.3	9.2
10°-20°	156.0	23.9
20°-30°	190.7	29.2
30°-40°	142.7	21.8
40°-50°	70.7	10.8
50°-60°	26.1	4.0
60°-70°	6.5	1.0
70°-80°	0.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
<b>0°-30°</b>	<b>407.0</b>	<b>62.2</b>
<b>0°-40°</b>	<b>549.7</b>	<b>84.1</b>
<b>0°-60°</b>	<b>646.5</b>	<b>98.9</b>
<b>0°-90°</b>	<b>653.9</b>	<b>100.0</b>
90°-120°	0.0	0.0
90°-150°	0.0	0.0
<b>90°-180°</b>	<b>0.0</b>	<b>0.0</b>
<b>0°-180°</b>	<b>653.9</b>	<b>100.0</b>

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	654	654	654	654	654	
5°	841	757	631	518	484	88
15°	1265	795	415	252	229	360
25°	1412	567	222	112	117	633
35°	924	272	96	51	74	582
45°	383	89	34	29	50	305
55°	96	25	14	12	32	92
65°	11	3	4	4	16	13
75°	1	1	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	

TEST NUMBER: P601386

CATALOG NUMBER: ML4DM08LSAWW95FS1E - TIR4D25AWW - TL41R\_ TL42S\_ 5000K

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	45°	67.5°	90°	112.5°	135°
0°	653.8	653.8	653.8	653.8	653.8	653.8	653.8	653.8	653.8	653.8	653.8
2.5°	736.3	736.3	744.9	730.9	730.9	726.6	695.6	677.3	657.0	627.0	591.6
5°	841.3	862.8	845.6	822.0	836.0	829.5	756.7	690.2	631.3	573.4	517.7
7.5°	976.4	981.7	966.7	936.7	930.3	926.0	800.6	691.3	588.4	501.6	437.3
10°	1070.7	1078.2	1071.8	1061.0	1024.6	1016.0	814.5	650.6	531.6	439.4	362.3
12.5°	1191.8	1189.6	1180.0	1148.9	1107.1	1095.3	806.0	614.1	471.6	369.8	296.9
15°	1264.7	1277.5	1263.6	1181.1	1161.8	1131.8	795.2	564.8	414.8	320.5	251.9
17.5°	1327.9	1322.5	1295.7	1243.2	1193.9	1167.1	753.4	493.0	364.4	266.9	207.9
20°	1389.0	1390.1	1348.3	1284.0	1204.6	1156.4	691.3	443.7	310.8	219.7	172.6
22.5°	1416.9	1414.7	1361.1	1265.7	1173.6	1124.3	632.3	388.0	260.4	177.9	138.3
25°	1411.5	1372.9	1337.5	1225.0	1121.1	1061.0	567.0	339.7	221.9	150.0	111.5
27.5°	1342.9	1323.6	1263.6	1151.1	1031.0	969.9	485.5	290.4	185.4	117.9	91.1
30°	1243.2	1220.7	1148.9	1055.7	898.1	849.9	413.7	237.9	151.1	100.7	75.0
32.5°	1095.3	1078.2	1004.2	882.1	758.8	704.1	343.0	189.7	122.2	74.0	61.1
35°	923.8	922.8	857.4	757.7	629.1	573.4	272.2	152.2	96.5	58.9	51.4
37.5°	793.1	765.2	700.9	608.8	500.5	454.4	213.3	119.0	71.8	46.1	42.9
40°	642.0	630.2	562.7	484.4	389.0	354.7	157.5	89.0	54.7	37.5	38.6
42.5°	516.6	500.5	444.8	368.7	301.2	273.3	120.0	68.6	42.9	32.2	34.3
45°	382.6	375.1	343.0	274.4	222.9	203.6	89.0	53.6	34.3	26.8	28.9
47.5°	278.7	270.1	247.6	203.6	161.8	150.0	68.6	41.8	27.9	21.4	22.5
50°	203.6	198.3	183.3	147.9	119.0	109.3	51.4	32.2	22.5	17.1	19.3
52.5°	140.4	142.5	129.7	105.0	84.7	78.2	38.6	23.6	18.2	13.9	16.1
55°	96.5	94.3	89.0	68.6	54.7	50.4	24.7	16.1	13.9	10.7	11.8
57.5°	58.9	58.9	54.7	42.9	34.3	32.2	15.0	10.7	9.6	7.5	9.6
60°	35.4	35.4	30.0	24.7	20.4	18.2	8.6	6.4	6.4	5.4	7.5
62.5°	19.3	19.3	17.1	13.9	10.7	9.6	5.4	5.4	4.3	4.3	6.4
65°	10.7	9.6	8.6	6.4	5.4	5.4	3.2	4.3	4.3	4.3	4.3
67.5°	4.3	4.3	4.3	3.2	3.2	3.2	2.1	3.2	3.2	3.2	3.2
70°	1.1	2.1	2.1	2.1	1.1	1.1	2.1	2.1	2.1	2.1	2.1
72.5°	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1
75°	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	1.1	1.1	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P601386  
 CATALOG NUMBER: ML4DM08LSAWW95FS1E - TIR4D25AWW - TL41R\_ TL42S\_ 5000K

**CANDELA DISTRIBUTION (continued):**

	157.5°	180°
0°	653.8	653.8
2.5°	592.7	583.0
5°	496.2	484.4
7.5°	394.4	386.9
10°	322.6	317.2
12.5°	272.2	269.0
15°	230.4	229.4
17.5°	194.0	190.8
20°	158.6	161.8
22.5°	130.8	128.6
25°	110.4	116.8
27.5°	94.3	102.9
30°	82.5	90.0
32.5°	70.7	82.5
35°	62.2	74.0
37.5°	55.7	66.4
40°	51.4	61.1
42.5°	45.0	56.8
45°	39.7	50.4
47.5°	34.3	45.0
50°	31.1	40.7
52.5°	26.8	36.4
55°	22.5	32.2
57.5°	20.4	28.9
60°	17.1	24.7
62.5°	12.9	20.4
65°	9.6	16.1
67.5°	6.4	11.8
70°	3.2	7.5
72.5°	1.1	2.1
75°	0.0	0.0
77.5°	0.0	0.0
80°	0.0	0.0
82.5°	0.0	0.0
85°	0.0	0.0
87.5°	0.0	0.0
90°	0.0	0.0

(END OF REPORT)