

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: HALO

Report Number: P601390

Luminaire Tested: **ML4DM08LSAWW95FS1E - TIR4D25AWW - TL43R2G\_ TL44S2G\_ 4000K**

Issue Date: 7/29/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

**Test Information**

Test Method: LM-79-08  
 Report Number: P601390  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Issue Date: 7/29/2022  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: HALO  
 Catalog Number: ML4DM08LSAWW95FS1E - TIR4D25AWW - TL43R2G\_ TL44S2G\_ 4000K  
 Description: DIRECT MOUNT, 25D WW OPTIC, DIFFUSE CLEAR LENS TRIM  
 Light Source: (1) SELECTABLE LUMEN LED 95CRI / 4000K CCT  
 Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
 Luminaire Lumens: 728.9 lumens  
 Efficiency: N/A  
 Efficacy: 70.8 lumens/watt  
 Spacing Criteria (0/90/45): 1.33 / 0.62 / 0.83  
 Luminous Opening: Circular (Dia: 0.21' x H: 0')  
 CIE Type: Direct


Input Watts (W): 10.3  
 Input Voltage (V): NR  
 Input Current (Ain): NR  
 Voltage Rise (V): NR  
 Power Factor: NR  
 Total Harmonic Distortion (THDi): NR  
 Frequency (hertz): 60  
 Stabilization Time: NR  
 Operation Time: NR  
 Ambient Temperature (°C): NR  
 Test Distance: 25 FT



Meas		Calibration Due Date	
Instrument	Identificatio		
Photometer	GONIO 1 11111111	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P601390  
CATALOG NUMBER: ML4DM08LSAWW95FS1E - TIR4D25AWW - TL43R2G\_ TL44S2G\_ 4000K

### Luminous Intensity Polar Plot



TEST NUMBER: P601390

CATALOG NUMBER: ML4DM08LSAWW95FS1E - TIR4D25AWW - TL43R2G\_ TL44S2G\_ 4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	97	95	94	92
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92	91	88	86	85
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85	85	82	79	78
3	101	94	88	84	99	92	87	83	89	85	82	87	83	80	85	82	79	78	85	82	79	78
4	95	87	81	76	93	85	80	75	83	78	75	81	77	74	79	76	73	71	79	76	73	71
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65	74	70	67	65
6	84	75	68	64	83	74	68	63	72	67	63	71	66	62	70	65	62	60	70	65	62	60
7	80	70	63	59	78	69	63	58	68	62	58	66	62	58	65	61	57	56	65	61	57	56
8	76	65	59	54	74	65	58	54	64	58	54	62	57	54	61	57	53	52	61	57	53	52
9	72	61	55	51	70	61	55	50	60	54	50	59	54	50	58	53	50	48	58	53	50	48
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45	55	50	47	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	222109	222109	222109
5°	287271	214558	165808
10°	373060	189945	114371
15°	444197	150409	81595
20°	513353	114351	55075
25°	523936	86092	45223
30°	489932	62495	35404
35°	401822	42287	31571
40°	299795	27535	27535
45°	202068	18577	24204
50°	118291	13607	21074
55°	62429	9689	16681
60°	30250	5557	12757
65°	12253	3736	8443
70°	5816	2308	4616
75°	3050	1586	0
80°	2364	2364	0
85°	0	0	0

TEST NUMBER: P601390  
 CATALOG NUMBER: ML4DM08LSAWW95FS1E - TIR4D25AWW - TL43R2G\_ TL44S2G\_ 4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	65.3	9.0
10°-20°	169.1	23.2
20°-30°	207.1	28.4
30°-40°	162.3	22.3
40°-50°	83.6	11.5
50°-60°	31.7	4.4
60°-70°	8.1	1.1
70°-80°	1.6	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	441.5	60.6
0°-40°	603.7	82.8
0°-60°	719.1	98.7
0°-90°	728.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	728.9	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	703	703	703	703	703	
5°	906	821	677	574	523	95
15°	1359	865	460	276	250	388
25°	1504	618	247	129	130	683
35°	1042	328	110	60	82	647
45°	452	113	42	33	54	352
55°	113	35	18	15	30	110
65°	16	6	5	5	11	20
75°	2	1	1	1	0	3
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0

TEST NUMBER: P601390

CATALOG NUMBER: ML4DM08LSAWW95FS1E - TIR4D25AWW - TL43R2G\_ TL44S2G\_ 4000K

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	45°	67.5°	90°	112.5°	135°
0°	703.4	703.4	703.4	703.4	703.4	703.4	703.4	703.4	703.4	703.4	703.4
2.5°	792.9	789.1	809.3	780.3	761.4	786.6	763.9	737.4	709.7	663.0	639.1
5°	906.3	908.8	912.6	903.8	900.0	897.5	820.6	748.7	676.9	606.3	573.5
7.5°	1036.1	1012.2	1027.3	993.3	999.6	981.9	873.5	737.4	644.1	553.4	476.5
10°	1163.5	1137.0	1149.6	1118.1	1110.5	1095.4	903.8	707.2	592.4	470.2	404.6
12.5°	1271.9	1260.5	1247.9	1205.1	1189.9	1148.3	903.8	666.8	519.3	405.9	330.3
15°	1358.8	1347.5	1333.6	1278.2	1231.5	1195.0	864.7	610.1	460.1	347.9	276.1
17.5°	1430.7	1386.6	1387.8	1308.4	1268.1	1220.2	826.9	552.1	398.3	291.2	234.5
20°	1527.7	1447.1	1433.2	1348.8	1273.1	1220.2	760.1	489.1	340.3	245.8	192.9
22.5°	1512.6	1440.8	1457.2	1332.4	1251.7	1230.3	685.7	422.3	292.4	206.7	155.0
25°	1503.8	1452.1	1424.4	1290.8	1193.7	1125.6	617.7	369.3	247.1	170.2	128.6
27.5°	1466.0	1387.8	1346.2	1211.4	1104.2	1048.8	537.0	312.6	206.7	134.9	108.4
30°	1343.7	1287.0	1242.9	1101.7	988.2	935.3	465.1	259.7	171.4	110.9	85.7
32.5°	1211.4	1162.2	1094.1	978.2	848.3	796.6	385.7	221.9	139.9	88.2	71.8
35°	1042.4	1002.1	937.8	820.6	695.8	673.1	327.7	177.7	109.7	70.6	60.5
37.5°	878.6	843.3	777.7	671.9	574.8	542.0	264.7	142.4	88.2	58.0	51.7
40°	727.3	685.7	642.9	539.5	460.1	424.8	202.9	110.9	66.8	46.6	44.1
42.5°	578.6	553.4	506.7	431.1	352.9	330.3	151.3	83.2	52.9	39.1	37.8
45°	452.5	426.1	381.9	331.5	266.0	248.3	113.4	64.3	41.6	31.5	32.8
47.5°	330.3	317.7	288.7	245.8	202.9	182.8	85.7	50.4	32.8	26.5	27.7
50°	240.8	228.2	214.3	175.2	141.2	136.1	64.3	39.1	27.7	21.4	22.7
52.5°	166.4	165.1	150.0	124.8	103.4	94.5	49.2	30.3	22.7	17.6	18.9
55°	113.4	112.2	102.1	87.0	73.1	66.8	35.3	22.7	17.6	13.9	15.1
57.5°	73.1	74.4	68.1	59.2	47.9	44.1	23.9	16.4	12.6	10.1	11.3
60°	47.9	47.9	41.6	37.8	30.3	27.7	16.4	11.3	8.8	7.6	8.8
62.5°	29.0	30.3	26.5	21.4	18.9	16.4	10.1	7.6	6.3	5.0	6.3
65°	16.4	17.6	15.1	12.6	11.3	10.1	6.3	5.0	5.0	3.8	5.0
67.5°	10.1	10.1	8.8	7.6	6.3	6.3	3.8	3.8	3.8	3.8	3.8
70°	6.3	6.3	5.0	5.0	3.8	3.8	2.5	3.8	2.5	2.5	2.5
72.5°	3.8	3.8	2.5	2.5	2.5	2.5	2.5	2.5	2.5	1.3	1.3
75°	2.5	2.5	2.5	2.5	1.3	1.3	1.3	1.3	1.3	1.3	1.3
77.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	0.0
80°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P601390  
 CATALOG NUMBER: ML4DM08LSAWW95FS1E - TIR4D25AWW - TL43R2G\_ TL44S2G\_ 4000K

**CANDELA DISTRIBUTION (continued):**

	157.5°	180°
0°	703.4	703.4
2.5°	624.0	626.5
5°	538.2	523.1
7.5°	447.5	423.5
10°	361.8	356.7
12.5°	305.0	298.7
15°	255.9	249.6
17.5°	214.3	202.9
20°	179.0	163.9
22.5°	148.7	150.0
25°	127.3	129.8
27.5°	109.7	112.2
30°	92.0	97.1
32.5°	83.2	90.8
35°	71.8	81.9
37.5°	64.3	74.4
40°	56.7	66.8
42.5°	50.4	60.5
45°	44.1	54.2
47.5°	39.1	49.2
50°	32.8	42.9
52.5°	27.7	36.6
55°	22.7	30.3
57.5°	18.9	25.2
60°	15.1	20.2
62.5°	11.3	15.1
65°	7.6	11.3
67.5°	5.0	7.6
70°	3.8	5.0
72.5°	1.3	2.5
75°	0.0	0.0
77.5°	0.0	0.0
80°	0.0	0.0
82.5°	0.0	0.0
85°	0.0	0.0
87.5°	0.0	0.0
90°	0.0	0.0

(END OF REPORT)