

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P601427

Luminaire Tested: **ML4DM10LSAWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 2700K**

Issue Date: 7/29/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P601427
 Test Lab: COOPER LIGHTING SOLUTIONS
 Issue Date: 7/29/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO
 Catalog Number: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 2700K
 Description: DIRECT MOUNT, 25D WW OPTIC, OPEN TRIM
 Light Source: (1) SELECTABLE LUMEN LED 90CRI / 2700K CCT
 Ballast/Driver: -

Summary

Lumens per Lamp: N/A
 Luminaire Lumens: 681.4 lumens
 Efficiency: N/A
 Efficacy: 56.8 lumens/watt
 Spacing Criteria (0/90/45): 1.31 / 0.61 / 0.81
 Luminous Opening: Circular (Dia: 0.21' x H: 0')
 CIE Type: Direct


Input Watts (W): 12
 Input Voltage (V): NR
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT



Meas		Calibration Due Date	
Instrument	Identificatio		
Photometer	GONIO 1 11111111	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P601427
CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 2700K

Luminous Intensity Polar Plot



TEST NUMBER: P601427

CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	97	97	97	93		
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	97	96	94	97	96	94	93		
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	91	89	87	91	89	87	85		
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	85	82	80	85	82	80	78		
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	80	76	73	80	76	73	72		
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	75	71	68	75	71	68	66		
6	85	75	69	64	83	75	68	64	73	68	64	72	67	63	70	66	63	70	66	63	70	66	63	61		
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	66	62	58	66	62	58	57		
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	62	58	54	62	58	54	53		
9	72	62	56	51	71	61	55	51	60	55	51	60	54	51	59	54	51	59	54	51	59	54	51	49		
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	55	51	48	55	51	48	46		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	215099	215099	215099
5°	277889	208504	160007
10°	357702	177600	106002
15°	430794	141288	78130
20°	486337	108840	56655
25°	512439	80552	42401
30°	472321	57427	34201
35°	371061	38741	29720
40°	275722	23496	26257
45°	178043	15942	23444
50°	104242	11544	20829
55°	55327	7983	18442
60°	23303	4231	16230
65°	8368	3362	12552
70°	1016	2031	7201
75°	1342	1342	0
80°	0	0	0
85°	0	0	0

TEST NUMBER: P601427
 CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.8	9.2
10°-20°	162.6	23.9
20°-30°	198.7	29.2
30°-40°	148.7	21.8
40°-50°	73.7	10.8
50°-60°	27.2	4.0
60°-70°	6.8	1.0
70°-80°	0.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	424.1	62.2
0°-40°	572.8	84.1
0°-60°	673.7	98.9
0°-90°	681.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	681.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	681	681	681	681	681	
5°	877	788	658	539	505	92
15°	1318	829	432	262	239	375
25°	1471	591	231	116	122	660
35°	963	284	100	54	77	607
45°	399	93	36	30	52	318
55°	100	26	14	12	34	96
65°	11	3	4	4	17	13
75°	1	1	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0

TEST NUMBER: P601427

CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 2700K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	45°	67.5°	90°	112.5°	135°
0°	681.2	681.2	681.2	681.2	681.2	681.2	681.2	681.2	681.2	681.2	681.2
2.5°	767.2	767.2	776.1	761.6	761.6	757.2	724.8	705.8	684.6	653.3	616.4
5°	876.7	899.0	881.1	856.6	871.1	864.4	788.4	719.2	657.8	597.5	539.4
7.5°	1017.4	1022.9	1007.3	976.0	969.3	964.9	834.2	720.3	613.1	522.6	455.6
10°	1115.6	1123.5	1116.8	1105.6	1067.6	1058.7	848.7	677.9	553.9	457.9	377.5
12.5°	1241.8	1239.6	1229.5	1197.2	1153.6	1141.3	839.8	639.9	491.4	385.3	309.3
15°	1317.8	1331.2	1316.7	1230.7	1210.6	1179.3	828.6	588.5	432.2	333.9	262.4
17.5°	1383.7	1378.1	1350.2	1295.4	1244.1	1216.1	785.1	513.7	379.7	278.1	216.7
20°	1447.3	1448.4	1404.9	1337.9	1255.2	1205.0	720.3	462.3	323.9	228.9	179.8
22.5°	1476.4	1474.1	1418.3	1318.9	1222.8	1171.5	658.9	404.3	271.4	185.4	144.1
25°	1470.8	1430.6	1393.7	1276.5	1168.1	1105.6	590.8	354.0	231.2	156.3	116.1
27.5°	1399.3	1379.2	1316.7	1199.4	1074.3	1010.7	505.9	302.6	193.2	122.8	94.9
30°	1295.4	1272.0	1197.2	1100.0	935.8	885.6	431.1	247.9	157.5	105.0	78.2
32.5°	1141.3	1123.5	1046.4	919.1	790.7	733.7	357.4	197.7	127.3	77.1	63.7
35°	962.6	961.5	893.4	789.5	655.5	597.5	283.7	158.6	100.5	61.4	53.6
37.5°	826.4	797.4	730.4	634.3	521.5	473.5	222.2	124.0	74.8	48.0	44.7
40°	668.9	656.7	586.3	504.8	405.4	369.6	164.2	92.7	57.0	39.1	40.2
42.5°	538.3	521.5	463.5	384.2	313.8	284.8	125.1	71.5	44.7	33.5	35.7
45°	398.7	390.9	357.4	285.9	232.3	212.2	92.7	55.8	35.7	27.9	30.2
47.5°	290.4	281.4	258.0	212.2	168.6	156.3	71.5	43.6	29.0	22.3	23.5
50°	212.2	206.6	191.0	154.1	124.0	113.9	53.6	33.5	23.5	17.9	20.1
52.5°	146.3	148.5	135.1	109.4	88.2	81.5	40.2	24.6	19.0	14.5	16.8
55°	100.5	98.3	92.7	71.5	57.0	52.5	25.7	16.8	14.5	11.2	12.3
57.5°	61.4	61.4	57.0	44.7	35.7	33.5	15.6	11.2	10.1	7.8	10.1
60°	36.9	36.9	31.3	25.7	21.2	19.0	8.9	6.7	6.7	5.6	7.8
62.5°	20.1	20.1	17.9	14.5	11.2	10.1	5.6	5.6	4.5	4.5	6.7
65°	11.2	10.1	8.9	6.7	5.6	5.6	3.4	4.5	4.5	4.5	4.5
67.5°	4.5	4.5	4.5	3.4	3.4	3.4	2.2	3.4	3.4	3.4	3.4
70°	1.1	2.2	2.2	2.2	1.1	1.1	2.2	2.2	2.2	2.2	2.2
72.5°	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1
75°	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	1.1	1.1	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P601427
 CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 2700K

CANDELA DISTRIBUTION (continued):

	157.5°	180°
0°	681.2	681.2
2.5°	617.6	607.5
5°	517.1	504.8
7.5°	411.0	403.1
10°	336.1	330.6
12.5°	283.7	280.3
15°	240.1	239.0
17.5°	202.1	198.8
20°	165.3	168.6
22.5°	136.2	134.0
25°	115.0	121.7
27.5°	98.3	107.2
30°	86.0	93.8
32.5°	73.7	86.0
35°	64.8	77.1
37.5°	58.1	69.2
40°	53.6	63.7
42.5°	46.9	59.2
45°	41.3	52.5
47.5°	35.7	46.9
50°	32.4	42.4
52.5°	27.9	38.0
55°	23.5	33.5
57.5°	21.2	30.2
60°	17.9	25.7
62.5°	13.4	21.2
65°	10.1	16.8
67.5°	6.7	12.3
70°	3.4	7.8
72.5°	1.1	2.2
75°	0.0	0.0
77.5°	0.0	0.0
80°	0.0	0.0
82.5°	0.0	0.0
85°	0.0	0.0
87.5°	0.0	0.0
90°	0.0	0.0

(END OF REPORT)