

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P601429

Luminaire Tested: **ML4DM10LSAWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 3500K**

Issue Date: 7/29/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P601429
 Test Lab: COOPER LIGHTING SOLUTIONS
 Issue Date: 7/29/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO
 Catalog Number: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 3500K
 Description: DIRECT MOUNT, 25D WW OPTIC, OPEN TRIM
 Light Source: (1) SELECTABLE LUMEN LED 90CRI / 3500K CCT
 Ballast/Driver: -

Summary

Lumens per Lamp: N/A
 Luminaire Lumens: 723.2 lumens
 Efficiency: N/A
 Efficacy: 60.3 lumens/watt
 Spacing Criteria (0/90/45): 1.31 / 0.61 / 0.81
 Luminous Opening: Circular (Dia: 0.21' x H: 0')
 CIE Type: Direct


Input Watts (W): 12
 Input Voltage (V): NR
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT



Meas		Calibration Due Date	
Instrument	Identificatio		
Photometer	GONIO 1 11111111	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P601429
CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 3500K

Luminous Intensity Polar Plot



TEST NUMBER: P601429

CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93	93	93	93	
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85	85	85	85	
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78	78	78	78	
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72	72	72	72	
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66	66	66	66	
6	85	75	69	64	83	75	68	64	73	68	64	72	67	63	70	66	63	61	61	61	61	
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57	57	57	57	
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53	53	53	53	
9	72	62	56	51	71	61	55	51	60	55	51	60	54	51	59	54	51	49	49	49	49	
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46	46	46	46	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	228298	228298	228298
5°	294942	221309	169833
10°	379666	188502	112511
15°	457241	149951	82936
20°	516210	115494	60149
25°	543900	85499	45014
30°	501345	60927	36316
35°	393882	41131	31532
40°	292664	24938	27865
45°	188984	16925	24873
50°	110628	12232	22106
55°	58740	8478	19599
60°	24693	4484	17241
65°	8891	3512	13300
70°	1108	2216	7663
75°	1464	1464	0
80°	0	0	0
85°	0	0	0

TEST NUMBER: P601429
 CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.7	9.2
10°-20°	172.5	23.9
20°-30°	210.9	29.2
30°-40°	157.8	21.8
40°-50°	78.2	10.8
50°-60°	28.8	4.0
60°-70°	7.2	1.0
70°-80°	1.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	450.1	62.2
0°-40°	608.0	84.1
0°-60°	715.0	98.9
0°-90°	723.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	723.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	723	723	723	723	723	
5°	930	837	698	572	536	97
15°	1399	880	459	279	254	398
25°	1561	627	245	123	129	700
35°	1022	301	107	57	82	644
45°	423	98	38	32	56	337
55°	107	27	15	13	36	101
65°	12	4	5	5	18	14
75°	1	1	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	

TEST NUMBER: P601429

CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 3500K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	45°	67.5°	90°	112.5°	135°
0°	723.0	723.0	723.0	723.0	723.0	723.0	723.0	723.0	723.0	723.0	723.0
2.5°	814.3	814.3	823.8	808.4	808.4	803.7	769.3	749.1	726.6	693.4	654.3
5°	930.5	954.2	935.2	909.1	924.6	917.4	836.8	763.4	698.2	634.2	572.5
7.5°	1079.8	1085.8	1069.2	1036.0	1028.9	1024.1	885.4	764.5	650.7	554.7	483.6
10°	1184.1	1192.4	1185.3	1173.5	1133.2	1123.7	900.8	719.5	587.9	486.0	400.6
12.5°	1318.1	1315.7	1305.0	1270.7	1224.4	1211.4	891.4	679.2	521.5	408.9	328.3
15°	1398.7	1412.9	1397.5	1306.2	1284.9	1251.7	879.5	624.7	458.7	354.4	278.6
17.5°	1468.6	1462.7	1433.1	1375.0	1320.5	1290.8	833.3	545.3	403.0	295.1	230.0
20°	1536.2	1537.4	1491.1	1420.0	1332.3	1279.0	764.5	490.7	343.7	243.0	190.8
22.5°	1567.0	1564.6	1505.4	1399.9	1297.9	1243.4	699.3	429.1	288.0	196.8	152.9
25°	1561.1	1518.4	1479.3	1354.8	1239.9	1173.5	627.0	375.7	245.4	165.9	123.3
27.5°	1485.2	1463.9	1397.5	1273.0	1140.3	1072.7	537.0	321.2	205.1	130.4	100.8
30°	1375.0	1350.1	1270.7	1167.5	993.3	940.0	457.5	263.1	167.1	111.4	83.0
32.5°	1211.4	1192.4	1110.7	975.5	839.2	778.8	379.3	209.8	135.1	81.8	67.6
35°	1021.8	1020.6	948.3	838.0	695.8	634.2	301.1	168.3	106.7	65.2	56.9
37.5°	877.1	846.3	775.2	673.3	553.5	502.6	235.9	131.6	79.4	51.0	47.4
40°	710.0	697.0	622.3	535.8	430.3	392.3	174.2	98.4	60.5	41.5	42.7
42.5°	571.3	553.5	491.9	407.8	333.1	302.3	132.8	75.9	47.4	35.6	37.9
45°	423.2	414.9	379.3	303.4	246.5	225.2	98.4	59.3	37.9	29.6	32.0
47.5°	308.2	298.7	273.8	225.2	179.0	165.9	75.9	46.2	30.8	23.7	24.9
50°	225.2	219.3	202.7	163.6	131.6	120.9	56.9	35.6	24.9	19.0	21.3
52.5°	155.3	157.6	143.4	116.2	93.6	86.5	42.7	26.1	20.2	15.4	17.8
55°	106.7	104.3	98.4	75.9	60.5	55.7	27.3	17.8	15.4	11.9	13.0
57.5°	65.2	65.2	60.5	47.4	37.9	35.6	16.6	11.9	10.7	8.3	10.7
60°	39.1	39.1	33.2	27.3	22.5	20.2	9.5	7.1	7.1	5.9	8.3
62.5°	21.3	21.3	19.0	15.4	11.9	10.7	5.9	5.9	4.7	4.7	7.1
65°	11.9	10.7	9.5	7.1	5.9	5.9	3.6	4.7	4.7	4.7	4.7
67.5°	4.7	4.7	4.7	3.6	3.6	3.6	2.4	3.6	3.6	3.6	3.6
70°	1.2	2.4	2.4	2.4	1.2	1.2	2.4	2.4	2.4	2.4	2.4
72.5°	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2
75°	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	1.2	1.2	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P601429
 CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 3500K

CANDELA DISTRIBUTION (continued):

	157.5°	180°
0°	723.0	723.0
2.5°	655.5	644.8
5°	548.8	535.8
7.5°	436.2	427.9
10°	356.8	350.9
12.5°	301.1	297.5
15°	254.8	253.7
17.5°	214.5	211.0
20°	175.4	179.0
22.5°	144.6	142.2
25°	122.1	129.2
27.5°	104.3	113.8
30°	91.3	99.6
32.5°	78.2	91.3
35°	68.7	81.8
37.5°	61.6	73.5
40°	56.9	67.6
42.5°	49.8	62.8
45°	43.9	55.7
47.5°	37.9	49.8
50°	34.4	45.0
52.5°	29.6	40.3
55°	24.9	35.6
57.5°	22.5	32.0
60°	19.0	27.3
62.5°	14.2	22.5
65°	10.7	17.8
67.5°	7.1	13.0
70°	3.6	8.3
72.5°	1.2	2.4
75°	0.0	0.0
77.5°	0.0	0.0
80°	0.0	0.0
82.5°	0.0	0.0
85°	0.0	0.0
87.5°	0.0	0.0
90°	0.0	0.0

(END OF REPORT)