

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P601431

Luminaire Tested: **ML4DM10LSAWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 5000K**

Issue Date: 7/29/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P601431
 Test Lab: COOPER LIGHTING SOLUTIONS
 Issue Date: 7/29/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO
 Catalog Number: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 5000K
 Description: DIRECT MOUNT, 25D WW OPTIC, OPEN TRIM
 Light Source: (1) SELECTABLE LUMEN LED 90CRI / 5000K CCT
 Ballast/Driver: -

Summary

Lumens per Lamp: N/A
 Luminaire Lumens: 752.2 lumens
 Efficiency: N/A
 Efficacy: 62.7 lumens/watt
 Spacing Criteria (0/90/45): 1.31 / 0.61 / 0.81
 Luminous Opening: Circular (Dia: 0.21' x H: 0')
 CIE Type: Direct


Input Watts (W): 12
 Input Voltage (V): NR
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT



Meas		Calibration Due Date	
Instrument	Identificatio		
Photometer	GONIO 1 11111111	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P601431
CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 5000K

Luminous Intensity Polar Plot



TEST NUMBER: P601431
 CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.4	9.2
10°-20°	179.5	23.9
20°-30°	219.4	29.2
30°-40°	164.2	21.8
40°-50°	81.4	10.8
50°-60°	30.0	4.0
60°-70°	7.5	1.0
70°-80°	1.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	468.2	62.2
0°-40°	632.4	84.1
0°-60°	743.7	98.9
0°-90°	752.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	752.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	752	752	752	752	752	
5°	968	870	726	596	557	101
15°	1455	915	477	290	264	414
25°	1624	652	255	128	134	728
35°	1063	313	111	59	85	670
45°	440	102	40	33	58	351
55°	111	28	16	14	37	106
65°	12	4	5	5	18	15
75°	1	1	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0

TEST NUMBER: P601431

CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 5000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	45°	67.5°	90°	112.5°	135°
0°	752.1	752.1	752.1	752.1	752.1	752.1	752.1	752.1	752.1	752.1	752.1
2.5°	847.0	847.0	856.9	840.8	840.8	835.9	800.2	779.2	755.8	721.3	680.6
5°	967.8	992.5	972.8	945.6	961.7	954.3	870.4	794.0	726.2	659.6	595.5
7.5°	1123.2	1129.3	1112.1	1077.6	1070.2	1065.2	921.0	795.2	676.9	577.0	503.0
10°	1231.7	1240.3	1232.9	1220.6	1178.7	1168.8	937.0	748.4	611.5	505.5	416.7
12.5°	1371.0	1368.5	1357.4	1321.7	1273.6	1260.0	927.1	706.5	542.5	425.4	341.5
15°	1454.8	1469.6	1453.6	1358.7	1336.5	1302.0	914.8	649.7	477.1	368.6	289.7
17.5°	1527.6	1521.4	1490.6	1430.2	1373.5	1342.6	866.7	567.1	419.2	307.0	239.2
20°	1597.8	1599.1	1551.0	1477.0	1385.8	1330.3	795.2	510.4	357.5	252.7	198.5
22.5°	1629.9	1627.4	1565.8	1456.1	1350.0	1293.3	727.4	446.3	299.6	204.7	159.0
25°	1623.7	1579.4	1538.7	1409.2	1289.6	1220.6	652.2	390.8	255.2	172.6	128.2
27.5°	1544.8	1522.6	1453.6	1324.1	1186.1	1115.8	558.5	334.1	213.3	135.6	104.8
30°	1430.2	1404.3	1321.7	1214.4	1033.2	977.7	475.9	273.7	173.8	115.9	86.3
32.5°	1260.0	1240.3	1155.2	1014.7	872.9	810.0	394.5	218.2	140.6	85.1	70.3
35°	1062.8	1061.5	986.3	871.7	723.7	659.6	313.2	175.1	111.0	67.8	59.2
37.5°	912.4	880.3	806.3	700.3	575.8	522.8	245.3	136.9	82.6	53.0	49.3
40°	738.5	725.0	647.3	557.3	447.5	408.1	181.2	102.3	62.9	43.2	44.4
42.5°	594.3	575.8	511.7	424.1	346.4	314.4	138.1	78.9	49.3	37.0	39.5
45°	440.1	431.5	394.5	315.6	256.4	234.3	102.3	61.6	39.5	30.8	33.3
47.5°	320.6	310.7	284.8	234.3	186.2	172.6	78.9	48.1	32.1	24.7	25.9
50°	234.3	228.1	210.8	170.1	136.9	125.8	59.2	37.0	25.9	19.7	22.2
52.5°	161.5	164.0	149.2	120.8	97.4	90.0	44.4	27.1	21.0	16.0	18.5
55°	111.0	108.5	102.3	78.9	62.9	57.9	28.4	18.5	16.0	12.3	13.6
57.5°	67.8	67.8	62.9	49.3	39.5	37.0	17.3	12.3	11.1	8.6	11.1
60°	40.7	40.7	34.5	28.4	23.4	21.0	9.9	7.4	7.4	6.2	8.6
62.5°	22.2	22.2	19.7	16.0	12.3	11.1	6.2	6.2	4.9	4.9	7.4
65°	12.3	11.1	9.9	7.4	6.2	6.2	3.7	4.9	4.9	4.9	4.9
67.5°	4.9	4.9	4.9	3.7	3.7	3.7	2.5	3.7	3.7	3.7	3.7
70°	1.2	2.5	2.5	2.5	1.2	1.2	2.5	2.5	2.5	2.5	2.5
72.5°	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2
75°	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	1.2	1.2	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P601431
 CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 5000K

CANDELA DISTRIBUTION (continued):

	157.5°	180°
0°	752.1	752.1
2.5°	681.8	670.7
5°	570.8	557.3
7.5°	453.7	445.1
10°	371.1	364.9
12.5°	313.2	309.5
15°	265.1	263.8
17.5°	223.2	219.5
20°	182.5	186.2
22.5°	150.4	147.9
25°	127.0	134.4
27.5°	108.5	118.4
30°	94.9	103.6
32.5°	81.4	94.9
35°	71.5	85.1
37.5°	64.1	76.4
40°	59.2	70.3
42.5°	51.8	65.3
45°	45.6	57.9
47.5°	39.5	51.8
50°	35.8	46.9
52.5°	30.8	41.9
55°	25.9	37.0
57.5°	23.4	33.3
60°	19.7	28.4
62.5°	14.8	23.4
65°	11.1	18.5
67.5°	7.4	13.6
70°	3.7	8.6
72.5°	1.2	2.5
75°	0.0	0.0
77.5°	0.0	0.0
80°	0.0	0.0
82.5°	0.0	0.0
85°	0.0	0.0
87.5°	0.0	0.0
90°	0.0	0.0

(END OF REPORT)