

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: HALO

Report Number: P601432

Luminaire Tested: **ML4DM10LSAWW9FS1E - TIR4D25AWW - TL43R2G\_ TL44S2G\_ 2700K**

Issue Date: 7/29/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

**Test Information**

Test Method: LM-79-08  
 Report Number: P601432  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Issue Date: 7/29/2022  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: HALO  
 Catalog Number: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL43R2G\_ TL44S2G\_ 2700K  
 Description: DIRECT MOUNT, 25D WW OPTIC, DIFFUSE CLEAR LENS TRIM  
 Light Source: (1) SELECTABLE LUMEN LED 90CRI / 2700K CCT  
 Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
 Luminaire Lumens: 793.8 lumens  
 Efficiency: N/A  
 Efficacy: 66.1 lumens/watt  
 Spacing Criteria (0/90/45): 1.33 / 0.62 / 0.83  
 Luminous Opening: Circular (Dia: 0.21' x H: 0')  
 CIE Type: Direct


Input Watts (W): 12  
 Input Voltage (V): NR  
 Input Current (Ain): NR  
 Voltage Rise (V): NR  
 Power Factor: NR  
 Total Harmonic Distortion (THDi): NR  
 Frequency (hertz): 60  
 Stabilization Time: NR  
 Operation Time: NR  
 Ambient Temperature (°C): NR  
 Test Distance: 25 FT



Meas			
Instrument	Identificatio		Calibration Due Date
Photometer	GONIO 1 11111111	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P601432  
CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL43R2G\_ TL44S2G\_ 2700K

### Luminous Intensity Polar Plot



TEST NUMBER: P601432

CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL43R2G\_ TL44S2G\_ 2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20														
RC	80					70					50					30					10					0									
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0								
RCR																																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100								
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92									92								
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85									85								
3	101	94	88	84	99	92	87	83	89	85	82	87	83	80	85	82	79	78									78								
4	95	87	81	76	93	85	80	75	83	78	75	81	77	74	79	76	73	71									71								
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65									65								
6	84	75	68	64	83	74	68	63	72	67	63	71	66	62	70	65	62	60									60								
7	80	70	63	59	78	69	63	58	68	62	58	66	62	58	65	61	57	56									56								
8	76	65	59	54	74	65	58	54	64	58	54	62	57	54	61	57	53	52									52								
9	72	61	55	51	70	61	55	50	60	54	50	59	54	50	58	53	50	48									48								
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45									45								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	241845	241845	241845
5°	312819	233640	180579
10°	406246	206843	124567
15°	483720	163779	88853
20°	559054	124533	59948
25°	570553	93722	49265
30°	533504	68073	38540
35°	437595	46026	34385
40°	326464	30008	30008
45°	220064	20229	26347
50°	128804	14836	22941
55°	67989	10570	18112
60°	32966	6063	13894
65°	13300	4109	9265
70°	6370	2493	5078
75°	3294	1708	0
80°	2546	2546	0
85°	0	0	0

TEST NUMBER: P601432

CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL43R2G\_ TL44S2G\_ 2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	71.2	9.0
10°-20°	184.1	23.2
20°-30°	225.5	28.4
30°-40°	176.7	22.3
40°-50°	91.1	11.5
50°-60°	34.6	4.4
60°-70°	8.8	1.1
70°-80°	1.8	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	480.7	60.6
0°-40°	657.4	82.8
0°-60°	783.1	98.7
0°-90°	793.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	793.8	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	766	766	766	766	766	
5°	987	894	737	625	570	103
15°	1480	942	501	301	272	423
25°	1638	673	269	140	141	744
35°	1135	357	119	66	89	704
45°	493	124	45	36	59	383
55°	124	38	19	16	33	120
65°	18	7	6	6	12	22
75°	3	1	1	1	0	3
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0

TEST NUMBER: P601432

CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL43R2G\_ TL44S2G\_ 2700K

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	45°	67.5°	90°	112.5°	135°
0°	765.9	765.9	765.9	765.9	765.9	765.9	765.9	765.9	765.9	765.9	765.9
2.5°	863.4	859.3	881.2	849.7	829.1	856.5	831.8	803.0	772.8	722.0	695.9
5°	986.9	989.7	993.8	984.2	980.1	977.3	893.6	815.4	737.1	660.2	624.6
7.5°	1128.3	1102.2	1118.7	1081.7	1088.5	1069.3	951.2	803.0	701.4	602.6	518.9
10°	1267.0	1238.1	1251.9	1217.5	1209.3	1192.8	984.2	770.1	645.1	512.0	440.6
12.5°	1385.0	1372.7	1358.9	1312.3	1295.8	1250.5	984.2	726.1	565.5	442.0	359.6
15°	1479.7	1467.4	1452.3	1391.9	1341.1	1301.3	941.6	664.4	501.0	378.9	300.6
17.5°	1558.0	1509.9	1511.3	1424.8	1380.9	1328.7	900.5	601.2	433.8	317.1	255.3
20°	1663.7	1575.8	1560.7	1468.7	1386.4	1328.7	827.7	532.6	370.6	267.7	210.0
22.5°	1647.2	1568.9	1586.8	1450.9	1363.0	1339.7	746.7	459.8	318.5	225.1	168.8
25°	1637.6	1581.3	1551.1	1405.6	1299.9	1225.8	672.6	402.2	269.0	185.3	140.0
27.5°	1596.4	1511.3	1466.0	1319.1	1202.4	1142.0	584.8	340.4	225.1	146.9	118.0
30°	1463.2	1401.5	1353.4	1199.7	1076.2	1018.5	506.5	282.8	186.7	120.8	93.3
32.5°	1319.1	1265.6	1191.5	1065.2	923.8	867.5	420.0	241.6	152.4	96.1	78.2
35°	1135.2	1091.3	1021.3	893.6	757.7	733.0	356.9	193.5	119.4	76.9	65.9
37.5°	956.7	918.3	846.9	731.6	625.9	590.2	288.3	155.1	96.1	63.1	56.3
40°	792.0	746.7	700.1	587.5	501.0	462.6	221.0	120.8	72.8	50.8	48.0
42.5°	630.0	602.6	551.8	469.4	384.3	359.6	164.7	90.6	57.7	42.6	41.2
45°	492.8	464.0	415.9	361.0	289.6	270.4	123.5	70.0	45.3	34.3	35.7
47.5°	359.6	345.9	314.3	267.7	221.0	199.0	93.3	54.9	35.7	28.8	30.2
50°	262.2	248.5	233.4	190.8	153.7	148.2	70.0	42.6	30.2	23.3	24.7
52.5°	181.2	179.8	163.3	135.9	112.6	102.9	53.5	32.9	24.7	19.2	20.6
55°	123.5	122.2	111.2	94.7	79.6	72.8	38.4	24.7	19.2	15.1	16.5
57.5°	79.6	81.0	74.1	64.5	52.2	48.0	26.1	17.8	13.7	11.0	12.4
60°	52.2	52.2	45.3	41.2	32.9	30.2	17.8	12.4	9.6	8.2	9.6
62.5°	31.6	32.9	28.8	23.3	20.6	17.8	11.0	8.2	6.9	5.5	6.9
65°	17.8	19.2	16.5	13.7	12.4	11.0	6.9	5.5	5.5	4.1	5.5
67.5°	11.0	11.0	9.6	8.2	6.9	6.9	4.1	4.1	4.1	4.1	4.1
70°	6.9	6.9	5.5	5.5	4.1	4.1	2.7	4.1	2.7	2.7	2.7
72.5°	4.1	4.1	2.7	2.7	2.7	2.7	2.7	2.7	2.7	1.4	1.4
75°	2.7	2.7	2.7	2.7	1.4	1.4	1.4	1.4	1.4	1.4	1.4
77.5°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	0.0
80°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P601432  
 CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL43R2G\_ TL44S2G\_ 2700K

**CANDELA DISTRIBUTION (continued):**

	157.5°	180°
0°	765.9	765.9
2.5°	679.5	682.2
5°	586.1	569.7
7.5°	487.3	461.2
10°	394.0	388.5
12.5°	332.2	325.3
15°	278.6	271.8
17.5°	233.4	221.0
20°	194.9	178.4
22.5°	162.0	163.3
25°	138.6	141.4
27.5°	119.4	122.2
30°	100.2	105.7
32.5°	90.6	98.8
35°	78.2	89.2
37.5°	70.0	81.0
40°	61.8	72.8
42.5°	54.9	65.9
45°	48.0	59.0
47.5°	42.6	53.5
50°	35.7	46.7
52.5°	30.2	39.8
55°	24.7	32.9
57.5°	20.6	27.5
60°	16.5	22.0
62.5°	12.4	16.5
65°	8.2	12.4
67.5°	5.5	8.2
70°	4.1	5.5
72.5°	1.4	2.7
75°	0.0	0.0
77.5°	0.0	0.0
80°	0.0	0.0
82.5°	0.0	0.0
85°	0.0	0.0
87.5°	0.0	0.0
90°	0.0	0.0

(END OF REPORT)