

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P601438

Luminaire Tested: **ML4DM10LSAWW9FS1E - TIR4D25AWW - TL45R6G_ TL46S6G_ 3000K**

Issue Date: 7/29/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P601438
 Test Lab: COOPER LIGHTING SOLUTIONS
 Issue Date: 7/29/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO
 Catalog Number: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL45R6G_ TL46S6G_ 3000K
 Description: DIRECT MOUNT, 25D WW OPTIC, LINEAR SPREAD LENS TRIM
 Light Source: (1) SELECTABLE LUMEN LED 90CRI / 3000K CCT
 Ballast/Driver: -

Summary

Lumens per Lamp: N/A
 Luminaire Lumens: 838.4 lumens
 Efficiency: N/A
 Efficacy: 69.9 lumens/watt
 Spacing Criteria (0/90/45): 1.21 / 0.78 / 1
 Luminous Opening: Circular (Dia: 0.21' x H: 0')
 CIE Type: Direct


Input Watts (W): 12
 Input Voltage (V): NR
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT



Meas			
Instrument	Identificatio		Calibration Due Date
Photometer	GONIO 1 11111111	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P601438
CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL45R6G_ TL46S6G_ 3000K

Luminous Intensity Polar Plot



TEST NUMBER: P601438

CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL45R6G_ TL46S6G_ 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	96	95	94	92
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	90	87	85	83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	83	80	78	76
4	94	85	79	74	92	84	78	73	82	76	72	79	75	72	78	74	71	78	74	71	69
5	88	78	72	67	86	77	71	67	76	70	66	74	69	65	72	68	65	72	68	65	63
6	83	73	66	61	81	72	65	61	70	65	60	69	64	60	67	63	59	67	63	59	58
7	78	68	61	56	77	67	60	56	65	60	55	64	59	55	63	58	55	63	58	55	53
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	59	54	51	49
9	70	59	52	48	68	58	52	48	57	52	47	56	51	47	55	51	47	55	51	47	46
10	66	55	49	44	65	55	48	44	54	48	44	53	48	44	52	47	44	52	47	44	42

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	213836	213836	213836
5°	263340	211959	171291
10°	331923	199789	120207
15°	380909	173325	86662
20°	411402	149231	64115
25°	410669	121804	48847
30°	375589	94836	40035
35°	311158	72239	33190
40°	223455	52886	29225
45°	158350	36216	24114
50°	92894	23236	19895
55°	55768	15800	15800
60°	29871	11746	11746
65°	16438	8817	7546
70°	9325	6278	4709
75°	4148	4148	0
80°	3091	3091	0
85°	0	0	0

TEST NUMBER: P601438
 CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL45R6G_ TL46S6G_ 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.1	7.7
10°-20°	174.6	20.8
20°-30°	228.2	27.2
30°-40°	195.7	23.3
40°-50°	111.9	13.4
50°-60°	45.8	5.5
60°-70°	14.6	1.7
70°-80°	3.1	0.4
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	466.9	55.7
0°-40°	662.6	79.0
0°-60°	820.3	97.8
0°-90°	838.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	838.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	677	677	677	677	677	
5°	831	780	669	566	540	86
15°	1165	919	530	319	265	329
25°	1179	812	350	167	140	539
35°	807	534	187	88	86	498
45°	355	242	81	44	54	270
55°	101	83	29	20	29	96
65°	22	19	12	8	10	24
75°	3	3	3	2	0	5
85°	0	0	0	0	0	1
90°	0	0	0	0	0	

TEST NUMBER: P601438

CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL45R6G_ TL46S6G_ 3000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	45°	67.5°	90°	112.5°	135°
0°	677.2	677.2	677.2	677.2	677.2	677.2	677.2	677.2	677.2	677.2	677.2
2.5°	743.0	758.2	753.1	761.6	759.9	744.7	729.5	705.9	682.2	668.7	638.3
5°	830.8	849.4	862.9	852.8	847.7	835.9	780.2	727.8	668.7	609.6	565.7
7.5°	945.7	940.6	955.8	925.4	927.1	922.0	841.0	739.6	648.5	562.3	499.8
10°	1035.2	1020.0	1035.2	1025.0	1004.8	981.1	883.2	734.6	623.1	515.0	430.6
12.5°	1101.0	1121.3	1121.3	1097.6	1077.4	1050.4	915.3	731.2	579.2	457.6	371.5
15°	1165.2	1171.9	1160.1	1141.5	1121.3	1065.6	918.6	709.2	530.2	401.9	319.2
17.5°	1207.4	1209.1	1204.0	1187.1	1158.4	1124.7	896.7	689.0	484.6	358.0	268.5
20°	1224.3	1210.8	1209.1	1178.7	1153.4	1123.0	878.1	640.0	444.1	305.7	233.0
22.5°	1251.3	1219.2	1219.2	1188.8	1136.5	1131.4	868.0	584.3	388.4	261.7	199.3
25°	1178.7	1173.6	1183.8	1141.5	1101.0	1092.6	812.3	542.1	349.6	226.3	167.2
27.5°	1129.7	1116.2	1102.7	1075.7	1036.8	1016.6	766.7	488.0	304.0	189.1	141.8
30°	1030.1	1030.1	1013.2	999.7	947.3	932.1	685.6	437.4	260.1	162.1	118.2
32.5°	920.3	905.1	906.8	891.6	859.5	847.7	609.6	381.6	224.6	131.7	103.0
35°	807.2	790.3	781.9	770.0	765.0	727.8	533.6	329.3	187.4	114.8	87.8
37.5°	695.7	678.8	672.1	653.5	626.5	618.1	450.9	273.6	157.0	94.6	72.6
40°	542.1	542.1	540.4	520.1	511.7	506.6	373.2	228.0	128.3	76.0	62.5
42.5°	432.3	437.4	434.0	425.5	407.0	403.6	310.7	185.8	104.7	64.2	52.3
45°	354.6	339.4	336.0	334.4	324.2	322.5	241.5	146.9	81.1	52.3	43.9
47.5°	260.1	258.4	261.7	253.3	241.5	251.6	190.8	111.5	64.2	42.2	37.2
50°	189.1	192.5	192.5	184.1	180.7	184.1	146.9	84.4	47.3	33.8	32.1
52.5°	141.8	140.2	138.5	140.2	138.5	138.5	109.8	62.5	37.2	27.0	25.3
55°	101.3	101.3	99.6	103.0	104.7	101.3	82.7	45.6	28.7	22.0	20.3
57.5°	70.9	70.9	67.5	70.9	70.9	74.3	59.1	33.8	23.6	16.9	16.9
60°	47.3	47.3	47.3	49.0	50.7	50.7	40.5	23.6	18.6	13.5	13.5
62.5°	32.1	32.1	32.1	33.8	33.8	37.2	28.7	18.6	15.2	11.8	10.1
65°	22.0	22.0	22.0	22.0	23.6	23.6	18.6	13.5	11.8	10.1	8.4
67.5°	13.5	15.2	13.5	15.2	15.2	15.2	11.8	10.1	8.4	6.8	5.1
70°	10.1	10.1	10.1	10.1	10.1	10.1	8.4	8.4	6.8	5.1	3.4
72.5°	6.8	6.8	6.8	6.8	6.8	6.8	5.1	5.1	5.1	3.4	3.4
75°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	1.7	1.7
77.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	0.0
80°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	0.0	0.0
82.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P601438
 CATALOG NUMBER: ML4DM10LSAWW9FS1E - TIR4D25AWW - TL45R6G_ TL46S6G_ 3000K

CANDELA DISTRIBUTION (continued):

	157.5°	180°
0°	677.2	677.2
2.5°	621.4	609.6
5°	526.9	540.4
7.5°	459.3	442.4
10°	385.0	374.9
12.5°	334.4	329.3
15°	276.9	265.1
17.5°	238.1	226.3
20°	199.3	190.8
22.5°	170.6	165.5
25°	146.9	140.2
27.5°	126.7	123.3
30°	109.8	109.8
32.5°	94.6	97.9
35°	84.4	86.1
37.5°	72.6	76.0
40°	67.5	70.9
42.5°	57.4	64.2
45°	49.0	54.0
47.5°	42.2	47.3
50°	35.5	40.5
52.5°	32.1	35.5
55°	27.0	28.7
57.5°	22.0	23.6
60°	16.9	18.6
62.5°	13.5	15.2
65°	10.1	10.1
67.5°	6.8	8.4
70°	3.4	5.1
72.5°	1.7	1.7
75°	1.7	0.0
77.5°	0.0	0.0
80°	0.0	0.0
82.5°	0.0	0.0
85°	0.0	0.0
87.5°	0.0	0.0
90°	0.0	0.0

(END OF REPORT)