

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P189480

Luminaire Tested: **ML4D09NFL935-TIR50FL40-TL43R2G_X_TL44S2GX**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P189480
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P189401)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: ML4D09NFL935-TIR50FL40-TL43R2G_X_TL44S2GX
Description: ML4 RECESSED DOWNLIGHT WITH 40° FLOOD OPTIC WITH LENSED ROUND (OR SQUARE)
Light Source: CITIZEN 3500K
CLU711
Ballast/Driver: UNV-120-277 ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 937.8 lumens
Efficiency: N/A
Efficacy: 78.5 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.62
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 11.95
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P189480

CATALOG NUMBER: ML4D09NFL935-TIR50FL40-TL43R2G_X_TL44S2GX

Luminous Intensity Polar Plot






TEST NUMBER: P189480

CATALOG NUMBER: ML4D09NFL935-TIR50FL40-TL43R2G_X_TL44S2GX

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85
4	100	93	89	85	98	92	88	84	90	86	83	88	85	82	87	84	82	80
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	76
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72
7	88	80	75	71	87	80	75	71	79	74	71	77	73	71	76	73	70	69
8	85	77	72	68	84	76	71	68	75	71	68	74	70	67	73	70	67	66
9	82	73	68	65	81	73	68	65	72	68	64	71	67	64	70	67	64	63
10	79	70	65	62	78	70	65	62	69	65	62	68	64	62	68	64	61	60

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P189480

CATALOG NUMBER: ML4D09NFL935-TIR50FL40-TL43R2G_X_TL44S2GX

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.9	18.4
10°-20°	366.3	39.1
20°-30°	251.5	26.8
30°-40°	93.9	10.0
40°-50°	31.7	3.4
50°-60°	12.1	1.3
60°-70°	5.7	0.6
70°-80°	2.9	0.3
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	790.7	84.3
0°-40°	884.6	94.3
0°-60°	928.5	99.0
0°-90°	937.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	937.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1905	
5°	1869	173
15°	1350	366
25°	541	251
35°	140	94
45°	39	32
55°	13	12
65°	5	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P189480

CATALOG NUMBER: ML4D09NFL935-TIR50FL40-TL43R2G_X_TL44S2GX

CANDELA DISTRIBUTION (FULL):

0°	
0°	1905.4
1°	1900.4
2°	1893.4
3°	1887.5
4°	1880.6
5°	1868.7
6°	1849.9
7°	1825.1
8°	1788.5
9°	1741.9
10°	1691.4
11°	1633.8
12°	1571.4
13°	1503.1
14°	1430.8
15°	1350.5
16°	1267.2
17°	1180.0
18°	1093.8
19°	1006.6
20°	921.5
21°	837.2
22°	758.0
23°	681.7
24°	609.3
25°	541.0
26°	479.6
27°	423.1
28°	372.5
29°	326.0
30°	283.4
32.5°	198.2
35°	139.7
37.5°	99.0
40°	71.3
42.5°	52.5
45°	38.7
47.5°	28.8
50°	21.8
52.5°	16.8
55°	12.9
57.5°	9.9
60°	8.0
62.5°	6.9
65°	5.0



TEST NUMBER: P189480

CATALOG NUMBER: ML4D09NFL935-TIR50FL40-TL43R2G_X_TL44S2GX

CANDELA DISTRIBUTION (continued):

	0°
67.5°	5.0
70°	4.0
72.5°	3.0
75°	3.0
77.5°	1.9
80°	1.9
82.5°	1.0
85°	1.0
87.5°	0.0
90°	0.0

(END OF REPORT)