

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P275360

Luminaire Tested: **ML4D09_927 - TIR45WFL55 - TL41RMW - TL42SMW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P275360
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-901-14)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: ML4D09_927 - TIR45WFL55 - TL41RMW - TL42SMW
Description: ML4 900LM 2700K, 90CRI, 55° WFL OPTIC, WITH ROUND PINHOLE MATTE WHITE FLANGE
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1007.0 lumens
Efficiency: N/A
Efficacy: 89.1 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.86
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 11.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P275360

CATALOG NUMBER: ML4D09_927 - TIR45WFL55 - TL41RMW - TL42SMW

Luminous Intensity Polar Plot





TEST NUMBER: P275360

CATALOG NUMBER: ML4D09_927 - TIR45WFL55 - TL41RMW - TL42SMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	113	110	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93					93			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86					86			
3	102	95	90	86	100	94	89	85	91	87	84	89	85	82	86	83	81	79					79			
4	96	88	83	78	94	87	82	78	85	81	77	83	79	76	81	78	75	74					74			
5	91	83	76	72	90	82	76	72	80	75	71	78	74	70	76	73	70	68					68			
6	86	77	71	67	85	76	71	66	75	70	66	73	69	65	72	68	65	63					63			
7	82	72	66	62	81	72	66	62	70	65	61	69	64	61	68	64	61	59					59			
8	78	68	62	58	77	67	62	57	66	61	57	65	60	57	64	60	57	55					55			
9	74	64	58	54	73	64	58	54	63	57	54	62	57	53	61	56	53	52					52			
10	70	61	55	51	69	60	54	50	59	54	50	58	54	50	58	53	50	49					49			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	560677
5°	565295
10°	534757
15°	481823
20°	420717
25°	359402
30°	287246
35°	197616
40°	128877
45°	79543
50°	47589
55°	26666
60°	14801
65°	7005
70°	2885
75°	0
80°	0
85°	0



TEST NUMBER: P275360

CATALOG NUMBER: ML4D09_927 - TIR45WFL55 - TL41RMW - TL42SMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.4	10.6
10°-20°	262.6	26.1
20°-30°	300.6	29.9
30°-40°	208.2	20.7
40°-50°	91.9	9.1
50°-60°	30.0	3.0
60°-70°	6.7	0.7
70°-80°	0.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	669.6	66.5
0°-40°	877.8	87.2
0°-60°	999.7	99.3
0°-90°	1007.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1007.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1136	
5°	1141	106
15°	943	263
25°	660	301
35°	328	208
45°	114	92
55°	31	30
65°	6	7
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P275360

CATALOG NUMBER: ML4D09_927 - TIR45WFL55 - TL41RMW - TL42SMW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1136.4
2.5°	1137.4
5°	1141.4
7.5°	1114.4
10°	1067.4
12.5°	1013.3
15°	943.3
17.5°	870.3
20°	801.3
22.5°	731.2
25°	660.2
27.5°	588.2
30°	504.2
32.5°	410.1
35°	328.1
37.5°	259.1
40°	200.1
42.5°	153.1
45°	114.0
47.5°	84.0
50°	62.0
52.5°	44.0
55°	31.0
57.5°	22.0
60°	15.0
62.5°	9.0
65°	6.0
67.5°	4.0
70°	2.0
72.5°	1.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)