

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P123735

Luminaire Tested: **EL406935-TL422PS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P123735
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13992)
Test Lab: INNOVATION CENTER-P1
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: EL406935-TL422PS
Description: HALO 4-INCH RECESSED LED DOWNLIGHT
WHITE BAFFLE, POLYMER LENSED SHOWER TRIM AND WHITE TRIM RING
Light Source: (1)SURFACE MOUNT LED, 3500K CCT, 90CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 760.0 lumens
Efficiency: N/A
Efficacy: 58.5 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.75
Luminous Opening: Circular (Dia: 0.29' x H: 0')
CIE Type: Direct

Input Watts (W): 13
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P123735
CATALOG NUMBER: EL406935-TL422PS

Luminous Intensity Polar Plot





TEST NUMBER: P123735

CATALOG NUMBER: EL406935-TL422PS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	110	108	105	103	103	101	100	100	98	97	96	95	94	92
2	107	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84
3	101	93	88	84	98	92	87	83	89	85	82	87	83	80	85	82	79	77
4	95	87	81	76	93	86	80	76	83	78	75	81	77	74	79	76	73	71
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	74	71	67	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	63	61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53
9	72	62	56	52	71	62	56	52	61	55	51	60	55	51	59	54	51	50
10	69	59	53	48	68	58	52	48	57	52	48	57	52	48	56	51	48	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	160540
5°	156447
10°	134994
15°	107444
20°	84779
25°	70854
30°	63323
35°	57408
40°	43723
45°	23558
50°	10802
55°	6039
60°	5220
65°	5756
70°	3533
75°	2677
80°	3989
85°	2033



TEST NUMBER: P123735

CATALOG NUMBER: EL406935-TL422PS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.7	11.5
10°-20°	179.3	23.6
20°-30°	185.7	24.4
30°-40°	177.3	23.3
40°-50°	84.7	11.1
50°-60°	22.3	2.9
60°-70°	13.3	1.8
70°-80°	7.3	1.0
80°-90°	2.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	452.7	59.6
0°-40°	630.0	82.9
0°-60°	737.1	97.0
0°-90°	760.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	760.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	996	
5°	967	88
15°	644	179
25°	399	186
35°	292	177
45°	103	85
55°	22	22
65°	15	13
75°	4	7
85°	1	2
90°	0	



TEST NUMBER: P123735

CATALOG NUMBER: EL406935-TL422PS

CANDELA DISTRIBUTION (FULL):

	0°
0°	996.5
2.5°	1001.8
5°	967.4
7.5°	906.0
10°	825.2
12.5°	733.6
15°	644.2
17.5°	561.2
20°	494.5
22.5°	440.6
25°	398.6
27.5°	366.3
30°	340.4
32.5°	318.9
35°	291.9
37.5°	254.2
40°	207.9
42.5°	150.8
45°	103.4
47.5°	66.8
50°	43.1
52.5°	31.2
55°	21.5
57.5°	18.3
60°	16.2
62.5°	15.1
65°	15.1
67.5°	11.8
70°	7.5
72.5°	10.8
75°	4.3
77.5°	6.5
80°	4.3
82.5°	3.2
85°	1.1
87.5°	2.2
90°	0.0

(END OF REPORT)