

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: A1914114A001

Luminaire Tested:

Test Date: 2019-08-26

Test Information

Test Method: LM-41-14
Report Number: A1914114A001
Test Lab: EVERFINE
Test Date: 2019-08-26
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number:
Description: DL-NJ31bA11ER1-2390 120V 10.5W 60HZ
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 717.9 lumens
Efficiency: N/A
Efficacy: 76.1 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.37
Luminous Opening: Point Source (0m x 0m x 0m)
CIE Type: Direct

Input Watts (W): 9.43143
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: A1914114A001
CATALOG NUMBER:

Luminous Intensity Polar Plot





TEST NUMBER: A1914114A001

CATALOG NUMBER:

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	104	100	96	106	102	98	94	97	94	91	94	91	89	90	88	86	84
2	99	91	84	78	96	89	82	77	85	80	75	82	77	73	79	75	72	70
3	90	79	71	65	88	78	70	64	75	68	63	72	67	62	70	65	61	59
4	82	70	61	55	80	69	61	54	66	59	54	64	58	53	62	57	52	50
5	76	63	54	47	74	62	53	47	59	52	46	57	51	46	56	50	45	43
6	70	56	47	41	68	55	47	41	54	46	40	52	45	40	50	44	40	38
7	65	51	42	36	63	50	42	36	49	41	36	47	41	35	46	40	35	33
8	60	47	38	32	59	46	38	32	45	37	32	43	37	32	42	36	31	30
9	56	43	35	29	55	42	34	29	41	34	29	40	33	29	39	33	28	27
10	53	39	32	26	51	39	31	26	38	31	26	37	31	26	36	30	26	24

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	Luminaire represents a point source (luminous area is zero).			
5°	No luminance values can be calculated.			
10°				
15°				
20°				
25°				
30°				
35°				
40°				
45°				
50°				
55°				
60°				
65°				
70°				
75°				
80°				
85°				



TEST NUMBER: A1914114A001

CATALOG NUMBER:

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	23.8	3.3
10°-20°	68.0	9.5
20°-30°	103.1	14.4
30°-40°	124.5	17.3
40°-50°	129.6	18.1
50°-60°	117.8	16.4
60°-70°	89.8	12.5
70°-80°	50.0	7.0
80°-90°	11.0	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.1	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	194.9	27.1
0°-40°	319.4	44.5
0°-60°	566.9	79.0
0°-90°	717.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	717.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	253	253	253	253	253	
5°	250	250	250	250	250	24
15°	241	243	240	240	241	68
25°	224	226	223	223	224	103
35°	200	202	198	198	200	125
45°	169	171	167	167	169	130
55°	133	135	131	130	133	118
65°	91	94	90	88	91	90
75°	47	51	48	44	47	50
85°	8	12	9	6	8	10
90°	0	0	0	0	0	0
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0



TEST NUMBER: A1914114A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	252.8	252.8	252.8	252.8	252.8	252.8	252.8	252.8	252.8	252.8	252.8
0.5°	251.8	252.1	249.7	251.5	251.7	250.5	249.8	252.5	250.6	252.5	249.6
1°	251.1	252.7	250.7	252.6	251.3	250.7	249.5	251.7	250.8	251.3	249.9
1.5°	250.7	252.5	249.4	253.2	252.8	252.7	251.1	253.3	252.0	251.4	248.8
2°	251.0	251.8	248.3	252.4	251.9	252.7	250.5	252.1	252.3	251.8	249.5
2.5°	250.9	251.1	249.4	251.9	251.4	252.5	249.1	250.0	252.6	251.5	248.0
3°	250.5	251.6	249.2	252.0	251.6	252.1	251.2	247.7	250.0	251.6	247.6
3.5°	250.0	252.6	247.2	251.8	251.1	251.6	250.4	250.6	251.0	250.5	247.9
4°	250.4	251.9	249.2	250.4	251.7	250.3	250.0	246.9	249.5	251.0	249.9
4.5°	249.9	252.9	248.8	251.3	251.4	251.3	249.5	250.6	249.5	250.3	246.0
5°	250.0	251.2	248.9	251.3	250.2	251.3	250.3	250.7	249.6	251.7	246.4
5.5°	250.4	252.0	247.2	249.8	251.4	251.4	249.8	250.4	249.6	252.1	249.0
6°	250.1	250.7	249.0	252.2	250.6	250.7	248.4	250.1	249.6	251.4	247.6
6.5°	249.2	250.3	248.6	250.0	249.5	250.6	247.9	248.8	249.5	250.1	248.0
7°	248.1	249.9	247.3	249.8	250.3	250.3	248.8	249.9	248.7	248.1	246.5
7.5°	248.6	250.8	246.3	249.8	250.8	250.4	248.6	248.2	249.3	249.0	247.1
8°	247.2	251.0	245.3	249.9	249.4	248.8	247.7	248.0	247.4	248.4	245.1
8.5°	248.0	248.7	245.6	249.1	249.4	249.1	247.9	247.8	248.0	250.0	245.0
9°	247.3	248.7	245.8	249.1	248.8	250.2	246.5	247.4	247.2	249.1	246.1
9.5°	247.6	248.6	247.7	248.5	248.7	248.0	246.2	247.4	246.2	246.5	245.8
10°	247.1	247.2	245.4	249.2	248.0	248.7	247.0	246.6	246.1	247.3	244.7
10.5°	246.0	247.5	244.7	248.0	248.3	248.4	246.0	245.8	245.9	247.5	242.3
11°	244.7	247.3	245.0	245.5	247.7	247.5	244.8	245.8	246.0	247.3	241.8
11.5°	245.1	247.4	244.4	247.6	245.8	246.2	244.6	245.8	245.1	246.8	243.1
12°	244.6	247.2	244.7	245.8	246.0	245.6	244.4	245.6	244.9	245.9	242.2
12.5°	244.2	246.5	242.9	246.5	244.1	245.4	243.6	246.0	243.5	244.4	241.6
13°	243.4	245.9	242.4	245.9	245.0	245.6	243.6	243.9	243.5	244.1	240.8
13.5°	243.2	245.4	242.0	244.2	244.9	244.2	243.0	243.1	242.7	243.1	241.3
14°	242.3	244.0	242.0	244.0	243.9	244.9	243.2	243.0	242.0	242.7	238.5
14.5°	241.4	243.3	241.3	243.8	243.2	244.2	241.4	241.9	240.7	243.0	239.1
15°	240.8	242.5	239.6	243.3	242.9	243.8	241.3	240.5	239.7	241.0	238.0
15.5°	240.9	242.3	238.7	241.0	241.6	242.1	240.8	240.9	239.6	241.3	236.5
16°	240.3	240.8	238.4	241.2	241.7	240.5	239.6	239.6	238.4	239.6	236.8
16.5°	238.7	240.0	238.1	242.0	240.6	241.0	240.5	238.9	238.0	239.1	235.9
17°	238.3	239.9	237.3	239.9	239.4	239.5	238.5	237.9	237.5	238.5	234.8
17.5°	236.7	239.3	236.5	239.0	239.3	239.6	238.0	237.4	236.7	237.4	233.8
18°	236.6	238.7	236.3	239.0	237.9	239.5	236.4	237.0	235.3	237.2	233.4
18.5°	235.6	236.5	235.4	238.5	238.1	237.8	236.6	235.1	235.4	235.9	232.4
19°	235.3	235.9	234.4	237.7	236.9	236.1	235.7	234.2	234.7	234.8	231.9
19.5°	235.1	236.3	233.8	236.9	236.2	235.4	233.8	234.2	232.9	234.5	229.9
20°	233.1	235.0	232.8	236.7	235.5	235.2	232.4	233.3	232.9	233.2	229.0
20.5°	232.8	234.2	232.0	235.5	233.6	235.7	232.2	232.5	232.9	231.8	228.9
21°	232.2	233.8	231.6	234.2	233.5	233.4	231.3	232.1	230.9	232.1	227.5
21.5°	231.0	232.7	230.3	232.3	232.1	233.4	230.9	230.7	229.7	230.5	226.6
22°	229.9	231.5	230.0	232.5	231.6	232.2	229.8	229.1	229.0	228.3	227.3



TEST NUMBER: A1914114A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
22.5°	229.3	230.6	228.3	230.6	230.6	231.1	228.2	228.0	227.3	229.2	226.2
23°	229.2	230.6	227.2	230.5	228.9	230.4	227.8	226.9	227.0	227.4	224.2
23.5°	227.0	228.4	226.8	229.1	228.2	229.6	227.5	225.7	225.7	226.8	223.1
24°	226.1	227.9	225.6	228.0	227.3	226.8	225.7	224.6	224.8	225.9	221.8
24.5°	225.7	226.8	224.6	227.2	226.9	226.4	225.4	224.6	223.7	225.1	221.6
25°	223.7	225.7	224.2	227.2	225.9	225.6	223.2	223.1	222.7	223.3	220.9
25.5°	222.1	225.0	222.9	225.4	225.1	224.7	221.8	222.0	221.5	222.9	219.1
26°	221.9	224.0	221.6	224.9	223.4	224.6	221.4	221.3	220.7	221.3	219.2
26.5°	221.4	223.0	220.9	222.6	222.6	223.0	220.3	220.8	219.5	219.1	217.6
27°	220.4	222.4	219.7	222.4	221.8	220.7	219.2	218.9	218.2	219.4	216.6
27.5°	217.8	221.0	218.7	221.0	221.1	219.4	218.1	218.8	217.3	218.9	215.2
28°	216.6	219.5	217.0	219.9	219.2	219.1	217.0	217.0	216.2	216.8	213.7
28.5°	217.0	218.3	216.2	218.6	217.4	217.9	216.4	215.8	214.8	216.1	212.6
29°	216.0	217.8	215.1	217.8	217.4	216.5	214.6	214.8	214.4	214.8	210.9
29.5°	214.4	216.6	214.0	216.9	216.0	215.8	213.4	213.4	212.8	212.2	209.4
30°	213.2	214.8	212.2	215.1	214.5	214.4	212.2	212.0	211.7	211.9	209.0
30.5°	212.5	213.6	211.1	214.3	214.3	212.9	210.8	210.5	210.2	210.6	208.0
31°	210.3	212.6	210.0	213.1	211.6	212.4	209.7	209.4	208.9	209.6	207.0
31.5°	209.1	211.2	208.8	211.5	211.1	211.2	208.4	207.9	207.3	207.6	205.8
32°	207.0	209.5	207.8	209.9	210.5	209.8	207.3	207.6	206.5	206.1	203.8
32.5°	205.2	208.6	206.3	209.0	209.3	208.1	206.5	206.1	204.9	205.2	202.3
33°	204.6	206.9	205.0	207.8	206.0	207.2	204.4	203.7	204.2	204.4	201.3
33.5°	204.3	205.6	203.2	206.2	205.1	206.2	203.4	203.3	202.3	203.2	199.6
34°	202.3	204.8	202.4	204.8	204.4	204.5	201.5	202.1	200.5	201.3	198.5
34.5°	201.4	202.7	201.4	203.8	203.4	203.4	201.0	200.5	199.5	200.2	196.9
35°	199.8	201.4	199.9	202.3	201.9	201.4	199.7	199.0	198.2	198.8	195.4
35.5°	198.5	199.9	198.4	201.1	199.9	199.8	197.8	197.7	197.0	197.1	194.1
36°	197.1	198.5	197.0	199.4	198.3	198.6	196.8	197.0	195.6	195.6	192.6
36.5°	194.6	196.6	195.2	198.1	197.0	197.7	195.3	195.0	194.1	194.1	191.3
37°	193.2	195.7	194.0	196.3	195.4	196.0	193.7	192.9	192.6	192.4	190.2
37.5°	192.4	194.4	192.7	195.9	194.2	194.1	192.2	191.9	191.3	190.4	188.4
38°	190.8	192.7	191.1	193.8	192.6	193.2	190.8	191.1	190.0	189.4	187.0
38.5°	189.6	191.2	189.2	191.6	191.7	191.3	189.4	190.4	188.3	188.3	185.0
39°	187.8	189.3	188.0	189.9	190.3	189.7	187.9	188.1	186.8	187.0	183.7
39.5°	186.8	187.6	186.8	189.0	188.3	188.0	186.3	186.8	185.2	185.8	182.6
40°	184.6	186.1	184.9	187.1	186.9	187.2	184.9	184.6	183.7	184.1	181.4
40.5°	182.6	185.0	183.4	185.7	185.4	185.4	183.2	183.4	182.2	182.2	178.7
41°	181.6	183.7	181.9	184.0	184.1	184.1	181.7	182.2	180.6	180.5	178.0
41.5°	179.9	182.0	180.2	182.6	182.6	181.6	180.2	180.3	178.9	179.1	176.2
42°	178.3	179.9	178.5	181.3	180.9	181.0	178.7	178.2	177.3	177.2	174.8
42.5°	176.6	178.7	177.0	179.2	179.3	179.5	177.2	177.0	175.6	175.2	172.6
43°	175.2	177.1	175.7	178.2	177.7	177.0	175.5	174.6	173.8	174.2	171.3
43.5°	173.4	175.2	174.0	176.5	176.2	175.8	173.6	173.3	172.2	172.0	169.8
44°	171.7	173.7	172.8	175.0	174.6	174.4	172.0	171.9	170.6	170.6	168.2
44.5°	170.2	171.9	170.8	173.0	172.8	172.7	170.4	169.9	168.9	169.3	166.9



TEST NUMBER: A1914114A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
45°	168.6	170.4	169.0	170.9	171.2	170.9	168.8	168.0	167.3	167.1	164.8
45.5°	166.6	168.4	167.4	169.7	169.5	168.8	167.1	166.6	165.5	165.9	162.7
46°	164.8	166.8	165.8	167.7	167.9	167.2	165.5	165.0	163.9	164.5	161.4
46.5°	163.3	164.8	164.2	165.9	166.0	165.7	163.8	163.0	162.2	161.8	159.5
47°	161.1	163.3	162.5	164.5	164.2	163.6	162.0	161.5	160.5	160.2	157.7
47.5°	159.6	161.4	160.9	162.8	162.3	162.0	160.2	159.7	158.8	158.4	155.7
48°	158.1	159.8	159.3	161.4	160.7	160.0	158.5	157.4	157.1	157.2	154.2
48.5°	156.4	158.3	157.4	159.3	159.0	158.4	156.8	156.1	155.5	155.1	152.5
49°	154.7	156.6	155.4	158.1	157.5	156.9	155.2	154.3	153.8	153.4	150.2
49.5°	152.9	154.6	153.8	155.9	155.6	155.0	153.3	152.5	152.0	151.0	148.7
50°	151.2	153.1	151.8	154.3	153.9	153.1	151.5	151.0	149.9	149.6	146.7
50.5°	149.1	151.2	150.3	151.8	152.0	151.2	149.7	149.4	148.0	147.9	145.1
51°	147.3	149.4	148.6	150.3	150.2	149.7	147.9	147.3	146.1	145.8	143.3
51.5°	145.2	147.7	146.4	148.4	148.4	147.6	146.1	145.5	144.1	143.9	141.4
52°	143.6	145.7	144.7	146.8	146.5	145.6	144.3	143.9	142.2	141.9	139.6
52.5°	141.9	143.7	143.2	145.0	144.7	143.6	142.4	141.7	140.3	140.4	137.6
53°	140.2	141.6	141.0	143.3	142.8	141.9	140.6	139.6	138.6	138.6	135.8
53.5°	138.5	139.7	139.0	141.2	140.8	140.5	138.7	137.9	136.7	136.7	133.9
54°	136.7	138.0	137.2	139.5	138.8	138.3	136.6	136.0	134.8	134.6	132.1
54.5°	134.4	136.3	135.3	137.5	137.2	136.3	135.0	134.1	133.0	133.0	130.1
55°	132.6	134.5	133.5	135.8	135.1	134.4	133.0	132.3	131.0	130.5	128.2
55.5°	131.1	132.4	131.6	133.8	133.1	132.8	131.0	129.9	129.0	128.7	126.4
56°	128.9	130.6	130.0	131.8	131.1	130.7	129.0	128.4	127.1	126.6	124.2
56.5°	126.8	128.4	127.8	130.1	129.3	128.6	126.9	126.1	125.0	124.5	122.4
57°	124.6	126.4	125.7	127.8	127.2	126.6	124.9	124.2	123.2	122.7	120.7
57.5°	122.7	124.5	124.0	125.7	125.1	124.5	123.0	122.0	121.2	120.6	118.3
58°	120.7	122.6	121.9	124.0	123.2	122.4	121.1	120.7	119.2	118.8	116.4
58.5°	118.7	120.4	119.8	121.8	121.3	120.5	119.3	118.8	117.2	116.2	114.2
59°	116.8	118.2	117.8	119.6	119.4	118.5	117.4	116.7	115.4	114.5	112.2
59.5°	114.5	116.3	115.6	118.2	117.5	116.6	115.5	114.8	113.4	112.5	110.1
60°	112.4	114.2	113.7	115.8	115.4	114.7	113.3	111.9	111.3	110.7	108.4
60.5°	110.5	112.0	111.8	113.5	113.2	112.8	111.2	110.3	109.4	108.6	106.3
61°	108.3	109.9	109.8	111.4	111.1	110.6	109.0	108.3	107.3	106.4	104.1
61.5°	106.0	107.9	107.6	109.6	109.0	108.4	106.8	106.0	105.2	104.4	102.2
62°	104.0	105.8	105.6	107.4	107.0	106.5	104.8	104.4	103.2	102.7	100.2
62.5°	102.1	103.5	103.4	105.3	104.9	104.6	102.9	102.2	101.1	100.0	97.7
63°	99.8	101.4	101.4	102.7	102.6	102.6	100.8	99.9	98.9	98.1	95.8
63.5°	97.4	99.3	99.2	100.6	100.6	100.5	98.8	97.9	96.8	96.1	93.6
64°	95.3	96.9	97.0	98.5	98.6	98.5	96.7	96.1	94.8	94.0	91.3
64.5°	92.9	95.0	95.0	96.5	96.6	96.3	94.6	93.9	92.6	91.7	89.3
65°	90.7	93.0	92.7	94.3	94.4	94.1	92.6	91.6	90.4	89.7	87.5
65.5°	88.9	90.7	90.5	92.0	92.2	92.1	90.5	89.4	88.4	87.5	85.5
66°	86.5	88.5	88.3	90.0	90.1	90.0	88.6	87.6	86.4	85.5	83.5
66.5°	84.5	86.4	86.3	87.7	88.1	88.0	86.3	85.7	84.2	83.4	81.2
67°	82.2	84.4	84.2	85.8	85.9	85.8	84.4	83.5	82.0	81.1	79.1



TEST NUMBER: A1914114A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
67.5°	80.0	82.1	82.1	83.7	83.8	83.7	82.2	81.1	79.8	79.0	76.9
68°	77.7	79.8	79.9	81.2	81.6	81.5	80.0	78.7	77.8	76.9	74.8
68.5°	75.8	77.5	77.7	79.0	79.4	79.4	77.8	76.9	75.7	74.6	72.7
69°	73.6	75.3	75.5	77.0	77.5	77.0	75.9	74.6	73.4	72.5	70.5
69.5°	71.4	73.2	73.3	74.8	75.2	74.9	73.5	72.4	71.2	70.3	68.6
70°	69.2	70.9	71.1	72.4	73.0	72.7	71.4	70.1	69.1	68.1	66.5
70.5°	67.2	68.5	68.9	70.2	70.6	70.6	69.3	68.1	66.8	66.0	64.4
71°	64.8	66.5	66.7	68.1	68.6	68.4	67.2	66.0	64.7	63.8	62.2
71.5°	62.4	64.1	64.4	65.7	66.4	66.2	65.0	63.8	62.5	61.6	60.0
72°	60.2	62.0	62.2	63.6	64.1	64.0	62.8	61.7	60.3	59.5	57.8
72.5°	57.9	59.8	60.0	61.3	62.0	61.9	60.5	59.6	58.1	57.3	55.8
73°	55.8	57.4	57.7	59.1	59.6	59.6	58.4	57.5	56.0	55.2	53.6
73.5°	53.5	55.3	55.6	56.8	57.5	57.4	56.2	55.4	53.9	53.0	51.4
74°	51.3	53.0	53.4	54.8	55.5	55.2	54.1	53.2	51.9	50.9	49.3
74.5°	49.1	50.7	51.2	52.5	53.2	53.0	51.9	51.0	49.8	48.7	47.3
75°	46.9	48.6	48.9	50.2	51.1	50.9	49.7	48.9	47.7	46.7	45.2
75.5°	44.8	46.2	46.7	48.0	48.9	48.8	47.6	46.8	45.6	44.5	43.1
76°	42.6	44.1	44.5	45.8	46.7	46.5	45.5	44.7	43.5	42.4	40.9
76.5°	40.4	41.9	42.4	43.5	44.5	44.4	43.4	42.5	41.3	40.3	38.8
77°	38.2	39.7	40.2	41.3	42.4	42.3	41.3	40.5	39.2	38.3	36.7
77.5°	36.0	37.5	38.2	39.0	40.2	40.2	39.2	38.4	37.1	36.1	34.7
78°	33.9	35.3	35.9	37.0	38.2	38.0	37.1	36.3	35.0	34.0	32.7
78.5°	31.8	33.2	33.8	34.9	36.2	35.9	35.1	34.2	33.0	31.9	30.7
79°	29.8	31.1	31.7	32.8	34.1	33.8	32.9	32.0	30.9	29.9	28.6
79.5°	27.7	29.0	29.6	30.6	31.9	31.7	31.0	30.0	28.9	27.8	26.6
80°	25.6	26.9	27.6	28.5	29.9	29.8	28.9	28.0	26.8	25.9	24.6
80.5°	23.7	25.0	25.6	26.5	27.9	27.8	26.9	26.0	25.0	23.9	22.7
81°	21.9	22.9	23.6	24.4	25.9	25.8	24.9	24.0	22.9	22.0	21.0
81.5°	20.0	21.1	21.8	22.5	23.9	23.8	22.9	22.1	21.1	20.2	19.1
82°	18.0	19.3	19.8	20.8	22.0	21.8	21.2	20.4	19.2	18.4	17.2
82.5°	16.3	17.4	18.0	18.9	20.3	20.1	19.4	18.5	17.6	16.6	15.5
83°	14.5	15.6	16.2	17.0	18.4	18.3	17.5	16.7	15.7	14.8	13.8
83.5°	12.8	13.9	14.4	15.2	16.7	16.5	15.7	14.9	14.0	13.1	12.2
84°	11.2	12.2	12.8	13.4	14.8	14.6	14.0	13.2	12.3	11.5	10.5
84.5°	9.6	10.6	11.2	11.8	13.2	13.0	12.3	11.6	10.7	9.9	9.0
85°	8.1	9.1	9.7	10.2	11.5	11.4	10.7	10.0	9.2	8.4	7.6
85.5°	6.8	7.6	8.2	8.8	9.8	9.7	9.2	8.4	7.7	6.9	6.1
86°	5.5	6.2	6.8	7.4	8.3	8.3	7.8	7.1	6.2	5.5	4.9
86.5°	4.3	4.9	5.5	6.0	7.0	6.8	6.3	5.8	5.0	4.2	3.7
87°	3.2	3.8	4.4	4.8	5.6	5.4	5.0	4.4	3.9	3.1	2.6
87.5°	2.3	2.8	3.3	3.7	4.3	4.2	3.9	3.2	2.6	2.0	1.8
88°	1.5	1.9	2.5	2.7	3.2	3.1	2.8	2.2	1.7	1.1	0.8
88.5°	0.8	1.2	1.6	1.8	2.2	2.0	1.8	1.2	0.7	0.4	0.0
89°	0.3	0.6	0.9	1.2	1.2	1.1	0.8	0.4	0.0	0.0	0.0
89.5°	0.0	0.2	0.4	0.6	0.5	0.3	0.1	0.0	0.0	0.0	0.0



TEST NUMBER: A1914114A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
90°	0.0	0.0	0.1	0.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
91°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
91.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
93°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
93.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
94°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
94.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
96°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
96.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
101°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
101.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
103°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
103.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
104°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
104.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
106°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
106.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
108°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
108.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
109°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
109.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
111°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
111.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
112°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1914114A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
113°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
113.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
114°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
114.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
116°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
116.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
118°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
118.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
119°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
119.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
121°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
121.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
123°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
123.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
124°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
124.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
126°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
126.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
128°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
128.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
129°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
129.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
131°	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
131.5°	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
133°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
133.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
134°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
134.5°	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1914114A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
135°	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
136°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
136.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
138°	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
138.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
139°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
139.5°	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
141°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
141.5°	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.1	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
143°	0.1	0.0	0.0	0.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
143.5°	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
144°	0.1	0.0	0.0	0.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
144.5°	0.0	0.0	0.1	0.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145.5°	0.0	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
146°	0.0	0.1	0.1	0.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
146.5°	0.1	0.1	0.1	0.2	0.0	0.0	0.0	0.0	0.1	0.0	0.0
147°	0.0	0.2	0.1	0.1	0.0	0.0	0.0	0.1	0.0	0.0	0.0
147.5°	0.0	0.1	0.1	0.1	0.0	0.0	0.0	0.1	0.0	0.0	0.0
148°	0.0	0.1	0.1	0.2	0.0	0.0	0.0	0.1	0.0	0.0	0.0
148.5°	0.1	0.2	0.1	0.2	0.0	0.0	0.0	0.1	0.1	0.0	0.0
149°	0.1	0.2	0.1	0.1	0.0	0.0	0.0	0.1	0.0	0.0	0.0
149.5°	0.1	0.2	0.1	0.1	0.0	0.0	0.0	0.1	0.0	0.0	0.0
150°	0.1	0.2	0.1	0.1	0.0	0.0	0.1	0.1	0.0	0.0	0.0
150.5°	0.1	0.2	0.1	0.1	0.0	0.0	0.1	0.1	0.0	0.1	0.0
151°	0.1	0.2	0.3	0.1	0.0	0.1	0.0	0.1	0.1	0.0	0.0
151.5°	0.1	0.2	0.3	0.1	0.0	0.0	0.1	0.1	0.0	0.1	0.0
152°	0.2	0.2	0.2	0.1	0.0	0.1	0.0	0.1	0.0	0.1	0.0
152.5°	0.2	0.2	0.2	0.2	0.0	0.0	0.1	0.1	0.1	0.1	0.0
153°	0.1	0.2	0.2	0.2	0.0	0.1	0.1	0.1	0.0	0.1	0.0
153.5°	0.1	0.2	0.2	0.2	0.0	0.1	0.1	0.1	0.0	0.1	0.0
154°	0.1	0.2	0.2	0.2	0.0	0.1	0.1	0.2	0.1	0.1	0.0
154.5°	0.1	0.2	0.2	0.2	0.1	0.1	0.1	0.2	0.1	0.1	0.0
155°	0.1	0.2	0.2	0.2	0.1	0.1	0.1	0.2	0.1	0.1	0.0
155.5°	0.1	0.2	0.2	0.2	0.0	0.1	0.1	0.3	0.1	0.2	0.0
156°	0.1	0.2	0.2	0.2	0.0	0.1	0.1	0.3	0.2	0.1	0.0
156.5°	0.1	0.2	0.2	0.2	0.0	0.2	0.1	0.2	0.2	0.2	0.0
157°	0.1	0.2	0.2	0.2	0.1	0.1	0.2	0.2	0.1	0.1	0.0



TEST NUMBER: A1914114A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
157.5°	0.1	0.2	0.2	0.2	0.1	0.1	0.2	0.2	0.1	0.2	0.0
158°	0.1	0.2	0.2	0.2	0.1	0.1	0.2	0.2	0.2	0.2	0.0
158.5°	0.1	0.2	0.2	0.2	0.1	0.1	0.2	0.2	0.2	0.2	0.1
159°	0.1	0.2	0.2	0.2	0.1	0.1	0.2	0.2	0.1	0.2	0.2
159.5°	0.1	0.2	0.2	0.2	0.1	0.1	0.2	0.2	0.1	0.3	0.2
160°	0.1	0.2	0.2	0.2	0.2	0.1	0.2	0.2	0.1	0.2	0.1
160.5°	0.1	0.2	0.1	0.2	0.2	0.1	0.2	0.2	0.1	0.2	0.3
161°	0.1	0.2	0.1	0.2	0.2	0.1	0.3	0.2	0.1	0.2	0.3
161.5°	0.1	0.2	0.1	0.2	0.2	0.1	0.2	0.2	0.1	0.2	0.2
162°	0.1	0.2	0.1	0.2	0.2	0.1	0.2	0.2	0.1	0.2	0.2
162.5°	0.1	0.2	0.1	0.2	0.2	0.1	0.2	0.2	0.1	0.2	0.1
163°	0.1	0.2	0.1	0.2	0.2	0.1	0.2	0.2	0.1	0.2	0.1
163.5°	0.1	0.2	0.1	0.2	0.2	0.1	0.2	0.2	0.1	0.2	0.1
164°	0.1	0.2	0.1	0.2	0.2	0.1	0.2	0.2	0.1	0.2	0.1
164.5°	0.1	0.2	0.1	0.2	0.2	0.1	0.2	0.2	0.1	0.2	0.1
165°	0.1	0.2	0.1	0.2	0.2	0.1	0.2	0.2	0.1	0.2	0.1
165.5°	0.1	0.2	0.1	0.2	0.2	0.1	0.2	0.2	0.1	0.2	0.1
166°	0.1	0.2	0.1	0.2	0.2	0.1	0.2	0.2	0.1	0.2	0.1
166.5°	0.1	0.2	0.1	0.2	0.2	0.1	0.2	0.2	0.1	0.2	0.1
167°	0.1	0.2	0.1	0.2	0.2	0.1	0.2	0.2	0.1	0.2	0.1
167.5°	0.1	0.2	0.1	0.2	0.2	0.1	0.2	0.2	0.1	0.2	0.1
168°	0.1	0.2	0.1	0.2	0.2	0.1	0.2	0.2	0.1	0.2	0.1
168.5°	0.1	0.2	0.1	0.2	0.2	0.1	0.2	0.2	0.1	0.2	0.1
169°	0.1	0.2	0.1	0.2	0.2	0.1	0.2	0.2	0.1	0.2	0.1
169.5°	0.1	0.2	0.1	0.2	0.2	0.1	0.2	0.2	0.1	0.2	0.1
170°	0.1	0.2	0.1	0.2	0.2	0.1	0.2	0.2	0.1	0.2	0.1
170.5°	0.1	0.2	0.1	0.2	0.2	0.1	0.2	0.2	0.1	0.2	0.1
171°	0.1	0.2	0.1	0.2	0.2	0.1	0.2	0.2	0.1	0.2	0.1
171.5°	0.1	0.2	0.1	0.2	0.2	0.1	0.2	0.2	0.1	0.2	0.1
172°	0.1	0.2	0.1	0.2	0.2	0.1	0.2	0.2	0.1	0.2	0.1
172.5°	0.1	0.2	0.1	0.2	0.2	0.1	0.2	0.2	0.1	0.2	0.1
173°	0.1	0.2	0.1	0.2	0.2	0.1	0.2	0.2	0.1	0.2	0.1
173.5°	0.1	0.2	0.1	0.2	0.2	0.1	0.2	0.2	0.1	0.2	0.0
174°	0.1	0.2	0.1	0.2	0.2	0.1	0.2	0.2	0.1	0.2	0.1
174.5°	0.1	0.2	0.1	0.2	0.2	0.1	0.2	0.2	0.1	0.2	0.1
175°	0.1	0.2	0.1	0.2	0.2	0.1	0.2	0.2	0.1	0.2	0.1
175.5°	0.1	0.2	0.1	0.2	0.2	0.1	0.2	0.2	0.1	0.2	0.1
176°	0.1	0.2	0.1	0.2	0.2	0.1	0.2	0.2	0.1	0.2	0.1
176.5°	0.1	0.2	0.1	0.2	0.2	0.1	0.2	0.2	0.1	0.2	0.1
177°	0.1	0.2	0.1	0.2	0.2	0.1	0.2	0.2	0.1	0.2	0.1
177.5°	0.1	0.2	0.1	0.2	0.2	0.1	0.2	0.2	0.1	0.2	0.1
178°	0.1	0.2	0.1	0.2	0.2	0.1	0.2	0.2	0.1	0.2	0.1
178.5°	0.1	0.2	0.1	0.2	0.2	0.1	0.2	0.2	0.1	0.2	0.1
179°	0.3	0.2	0.1	0.2	0.2	0.1	0.2	0.2	0.1	0.2	0.1
179.5°	0.2	0.1	0.1	0.2	0.2	0.1	0.2	0.2	0.1	0.2	0.1



TEST NUMBER: A1914114A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
180°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1



TEST NUMBER: A1914114A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	252.8	252.8	252.8	252.8	252.8	252.8
0.5°	251.9	252.1	252.5	249.3	251.8	251.8
1°	251.8	250.7	251.8	249.8	249.5	251.1
1.5°	250.7	252.3	251.8	250.7	251.6	250.7
2°	250.8	253.2	252.5	250.0	251.4	251.0
2.5°	251.5	252.7	251.2	251.9	248.2	250.9
3°	251.2	252.4	251.2	250.6	248.9	250.5
3.5°	250.1	252.2	252.0	250.4	250.4	250.0
4°	251.5	251.4	251.4	250.1	248.6	250.4
4.5°	250.3	248.6	250.6	248.4	248.8	249.9
5°	251.5	250.0	249.7	248.3	247.8	250.0
5.5°	250.3	250.1	250.5	248.0	248.3	250.4
6°	249.0	250.3	250.1	249.8	249.0	250.1
6.5°	250.3	250.8	250.2	249.6	249.0	249.2
7°	249.4	249.8	250.1	247.8	249.0	248.1
7.5°	248.9	249.0	249.3	248.6	247.6	248.6
8°	248.5	249.0	248.3	246.4	247.9	247.2
8.5°	248.3	248.6	248.3	246.4	247.2	248.0
9°	247.5	247.1	247.6	247.4	246.1	247.3
9.5°	246.9	245.6	247.5	246.4	248.1	247.6
10°	247.3	247.5	246.3	246.2	246.2	247.1
10.5°	244.9	245.7	246.4	244.9	246.4	246.0
11°	246.2	245.0	246.3	244.8	244.6	244.7
11.5°	245.3	244.8	245.5	244.8	245.6	245.1
12°	244.7	244.0	245.2	244.1	245.6	244.6
12.5°	243.8	243.6	243.3	242.6	244.0	244.2
13°	244.0	243.2	241.8	242.0	242.2	243.4
13.5°	242.4	243.1	241.6	240.7	240.2	243.2
14°	242.2	240.8	241.9	240.4	240.7	242.3
14.5°	241.1	240.3	241.9	239.2	241.0	241.4
15°	239.7	240.0	240.4	239.4	240.2	240.8
15.5°	240.0	239.5	240.8	238.8	239.6	240.9
16°	239.7	240.1	239.6	237.9	238.4	240.3
16.5°	238.7	238.1	239.1	237.2	238.0	238.7
17°	237.7	237.9	237.6	236.1	236.8	238.3
17.5°	237.6	237.3	237.4	237.0	236.3	236.7
18°	235.5	236.0	236.8	235.8	235.2	236.6
18.5°	235.7	235.1	236.5	234.9	234.5	235.6
19°	234.8	235.0	235.6	234.5	234.3	235.3
19.5°	234.4	233.1	233.7	233.0	233.9	235.1
20°	231.8	233.4	233.3	231.7	232.4	233.1
20.5°	231.7	232.9	232.3	230.1	231.7	232.8
21°	230.0	232.0	231.7	230.3	230.7	232.2
21.5°	228.4	230.7	230.9	229.2	230.2	231.0
22°	227.9	229.3	228.8	228.4	229.4	229.9



TEST NUMBER: A1914114A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
22.5°	227.5	227.2	228.5	227.1	228.2	229.3
23°	226.7	226.8	227.4	226.0	227.8	229.2
23.5°	225.5	226.2	226.4	225.0	226.6	227.0
24°	224.4	224.8	225.8	223.8	225.9	226.1
24.5°	222.8	223.9	223.8	223.0	224.2	225.7
25°	221.6	223.2	223.6	220.8	223.2	223.7
25.5°	220.8	221.9	222.3	220.1	222.4	222.1
26°	219.9	220.7	220.8	219.5	221.3	221.9
26.5°	219.4	219.3	218.6	218.6	219.4	221.4
27°	217.5	218.5	218.1	218.3	218.4	220.4
27.5°	216.6	217.0	217.3	216.8	217.2	217.8
28°	215.0	215.8	217.1	215.5	216.6	216.6
28.5°	214.2	214.8	215.3	214.6	215.6	217.0
29°	212.4	213.9	214.6	212.6	214.2	216.0
29.5°	211.9	212.6	212.4	211.9	213.2	214.4
30°	210.0	211.0	211.5	210.6	212.7	213.2
30.5°	208.4	209.8	210.8	209.6	210.8	212.5
31°	207.2	208.6	209.6	208.0	209.6	210.3
31.5°	205.9	206.8	208.1	206.2	207.6	209.1
32°	205.0	205.5	206.2	205.2	206.5	207.0
32.5°	204.0	204.4	204.6	204.5	205.1	205.2
33°	203.1	203.2	203.3	202.5	204.2	204.6
33.5°	200.7	201.6	201.7	201.6	202.7	204.3
34°	199.6	200.7	200.3	199.2	200.9	202.3
34.5°	198.2	199.2	199.1	198.6	200.0	201.4
35°	197.1	197.5	197.6	197.4	198.5	199.8
35.5°	195.7	196.2	196.6	195.6	196.9	198.5
36°	194.4	194.3	194.8	194.3	195.7	197.1
36.5°	192.9	193.1	193.3	193.5	194.2	194.6
37°	191.3	191.6	192.0	191.7	192.8	193.2
37.5°	190.0	190.4	190.6	189.9	191.6	192.4
38°	188.4	188.8	189.1	188.5	189.8	190.8
38.5°	186.8	187.1	187.7	187.0	188.2	189.6
39°	185.3	185.8	186.1	185.5	186.7	187.8
39.5°	183.5	184.1	184.7	183.8	185.3	186.8
40°	182.0	182.9	183.0	182.2	183.5	184.6
40.5°	180.4	181.4	181.2	180.6	182.0	182.6
41°	178.9	179.9	180.0	178.8	180.4	181.6
41.5°	177.3	178.0	178.3	177.2	178.5	179.9
42°	175.6	176.4	176.6	175.6	176.9	178.3
42.5°	174.2	175.2	175.3	174.0	175.6	176.6
43°	172.5	173.4	173.5	172.4	173.8	175.2
43.5°	170.6	171.6	171.7	170.8	171.8	173.4
44°	168.8	170.4	170.0	169.1	170.1	171.7
44.5°	167.2	168.5	168.5	167.4	168.5	170.2



TEST NUMBER: A1914114A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
45°	165.5	166.6	166.8	165.7	167.0	168.6
45.5°	163.6	165.0	165.2	164.2	165.6	166.6
46°	161.9	163.4	163.2	162.5	163.8	164.8
46.5°	160.3	161.4	161.6	160.9	162.2	163.3
47°	158.7	159.8	159.9	159.2	160.3	161.1
47.5°	157.1	158.2	158.3	157.7	158.7	159.6
48°	155.3	156.1	156.6	156.1	157.2	158.1
48.5°	153.4	154.2	154.9	154.4	155.4	156.4
49°	151.6	152.4	152.9	152.8	153.6	154.7
49.5°	149.7	150.9	151.1	150.8	152.0	152.9
50°	147.8	149.0	149.4	149.0	150.3	151.2
50.5°	146.0	147.0	147.4	147.2	148.6	149.1
51°	144.2	145.2	145.8	145.4	146.6	147.3
51.5°	142.3	143.2	143.9	143.2	144.9	145.2
52°	140.5	141.3	141.6	141.5	142.9	143.6
52.5°	138.5	139.3	139.9	139.5	140.8	141.9
53°	136.6	137.5	138.0	137.6	138.9	140.2
53.5°	134.6	135.6	135.9	136.0	137.0	138.5
54°	132.5	133.8	133.9	133.9	135.0	136.7
54.5°	130.6	131.7	132.2	132.1	133.2	134.4
55°	128.7	129.6	130.1	130.2	131.3	132.6
55.5°	126.8	127.8	128.0	128.2	129.2	131.1
56°	124.8	125.7	126.2	126.4	127.2	128.9
56.5°	123.0	123.8	124.3	124.6	125.6	126.8
57°	120.8	121.7	122.4	122.5	123.3	124.6
57.5°	118.8	119.5	120.3	120.4	121.3	122.7
58°	116.9	117.8	118.1	118.6	119.4	120.7
58.5°	114.9	115.6	116.2	116.4	117.5	118.7
59°	112.8	113.5	113.9	114.5	115.3	116.8
59.5°	110.6	111.4	112.0	112.2	113.2	114.5
60°	108.5	109.3	109.8	110.2	111.3	112.4
60.5°	106.4	107.2	107.4	108.1	109.1	110.5
61°	104.3	105.0	105.4	105.9	107.0	108.3
61.5°	102.4	103.0	103.4	103.8	104.8	106.0
62°	100.4	100.8	101.1	101.6	102.7	104.0
62.5°	98.3	98.7	98.8	99.7	100.4	102.1
63°	96.3	96.5	96.8	97.4	98.3	99.8
63.5°	94.2	94.5	94.7	95.3	96.1	97.4
64°	92.1	92.4	92.6	92.8	94.1	95.3
64.5°	90.0	90.4	90.5	90.7	92.0	92.9
65°	88.0	88.1	88.4	88.6	90.0	90.7
65.5°	85.9	85.9	86.3	86.5	88.0	88.9
66°	83.8	83.7	84.1	84.1	85.8	86.5
66.5°	81.7	81.5	81.8	81.8	83.5	84.5
67°	79.6	79.3	79.7	79.8	81.4	82.2



TEST NUMBER: A1914114A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
67.5°	77.4	77.1	77.5	77.7	79.1	80.0
68°	75.2	74.8	75.2	75.4	77.0	77.7
68.5°	73.0	72.7	73.0	73.0	74.5	75.8
69°	70.7	70.3	70.8	70.9	72.3	73.6
69.5°	68.4	68.2	68.7	68.8	69.9	71.4
70°	66.2	66.0	66.4	66.6	67.7	69.2
70.5°	64.1	63.7	64.1	64.3	65.5	67.2
71°	62.0	61.4	61.7	62.1	63.3	64.8
71.5°	59.8	59.1	59.5	59.9	61.1	62.4
72°	57.6	57.0	57.4	57.6	58.9	60.2
72.5°	55.6	55.0	55.3	55.6	56.6	57.9
73°	53.5	52.7	53.0	53.3	54.5	55.8
73.5°	51.4	50.6	50.8	51.2	52.3	53.5
74°	49.2	48.3	48.5	48.8	50.0	51.3
74.5°	47.0	46.0	46.3	46.7	47.9	49.1
75°	45.0	43.8	44.0	44.5	45.8	46.9
75.5°	42.7	41.7	41.8	42.3	43.6	44.8
76°	40.6	39.4	39.7	40.3	41.3	42.6
76.5°	38.4	37.2	37.6	38.0	39.1	40.4
77°	36.4	35.1	35.4	35.8	37.0	38.2
77.5°	34.3	33.0	33.3	33.7	34.8	36.0
78°	32.2	30.9	31.2	31.6	32.7	33.9
78.5°	30.2	28.8	29.0	29.6	30.7	31.8
79°	28.1	26.8	27.0	27.5	28.5	29.8
79.5°	26.1	24.8	25.1	25.5	26.5	27.7
80°	24.1	22.8	23.0	23.6	24.4	25.6
80.5°	22.2	21.0	21.2	21.7	22.5	23.7
81°	20.4	19.2	19.3	19.9	20.7	21.9
81.5°	18.6	17.4	17.5	18.0	18.8	20.0
82°	16.8	15.4	15.6	16.1	17.0	18.0
82.5°	15.1	13.8	13.9	14.4	15.4	16.3
83°	13.4	12.1	12.3	12.7	13.5	14.5
83.5°	11.7	10.4	10.6	11.1	11.8	12.8
84°	10.1	9.0	9.1	9.5	10.3	11.2
84.5°	8.5	7.6	7.7	8.0	9.0	9.6
85°	7.1	6.1	6.3	6.8	7.3	8.1
85.5°	6.0	4.9	5.1	5.4	6.0	6.8
86°	4.5	3.8	3.9	4.3	4.8	5.5
86.5°	3.3	2.8	2.9	3.2	3.7	4.3
87°	2.2	2.0	2.0	2.2	2.6	3.2
87.5°	1.3	1.1	1.2	1.5	1.8	2.3
88°	0.6	0.6	0.6	0.8	1.1	1.5
88.5°	0.0	0.3	0.1	0.3	0.5	0.8
89°	0.0	0.0	0.0	0.0	0.1	0.3
89.5°	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1914114A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
90°	0.0	0.0	0.0	0.0	0.0	0.0
90.5°	0.0	0.0	0.0	0.0	0.0	0.0
91°	0.0	0.0	0.0	0.0	0.0	0.0
91.5°	0.0	0.0	0.0	0.0	0.0	0.0
92°	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0
93°	0.0	0.0	0.0	0.0	0.0	0.0
93.5°	0.0	0.0	0.0	0.0	0.0	0.0
94°	0.0	0.0	0.0	0.0	0.0	0.0
94.5°	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0
95.5°	0.0	0.0	0.0	0.0	0.0	0.0
96°	0.0	0.0	0.0	0.0	0.0	0.0
96.5°	0.0	0.0	0.0	0.0	0.0	0.0
97°	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0
98°	0.0	0.0	0.0	0.0	0.0	0.0
98.5°	0.0	0.0	0.0	0.0	0.0	0.0
99°	0.0	0.0	0.0	0.0	0.0	0.0
99.5°	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0
100.5°	0.0	0.0	0.0	0.0	0.0	0.0
101°	0.0	0.0	0.0	0.0	0.0	0.0
101.5°	0.0	0.0	0.0	0.0	0.0	0.0
102°	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0
103°	0.0	0.0	0.0	0.0	0.0	0.0
103.5°	0.0	0.0	0.0	0.0	0.0	0.0
104°	0.0	0.0	0.0	0.0	0.0	0.0
104.5°	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0
105.5°	0.0	0.0	0.0	0.0	0.0	0.0
106°	0.0	0.0	0.0	0.0	0.0	0.0
106.5°	0.0	0.0	0.0	0.0	0.0	0.0
107°	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0
108°	0.0	0.0	0.0	0.0	0.0	0.0
108.5°	0.0	0.0	0.0	0.0	0.0	0.0
109°	0.0	0.0	0.0	0.0	0.0	0.0
109.5°	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0
110.5°	0.0	0.0	0.0	0.0	0.0	0.0
111°	0.0	0.0	0.0	0.0	0.0	0.0
111.5°	0.0	0.0	0.0	0.0	0.0	0.0
112°	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1914114A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0
113°	0.0	0.0	0.0	0.0	0.0	0.0
113.5°	0.0	0.0	0.0	0.0	0.0	0.0
114°	0.0	0.0	0.0	0.0	0.0	0.0
114.5°	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0
115.5°	0.0	0.0	0.0	0.0	0.0	0.0
116°	0.0	0.0	0.0	0.0	0.0	0.0
116.5°	0.0	0.0	0.0	0.0	0.0	0.0
117°	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0
118°	0.0	0.0	0.0	0.0	0.0	0.0
118.5°	0.0	0.0	0.0	0.0	0.0	0.0
119°	0.0	0.0	0.0	0.0	0.0	0.0
119.5°	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0
120.5°	0.0	0.0	0.0	0.0	0.0	0.0
121°	0.0	0.0	0.0	0.0	0.0	0.0
121.5°	0.0	0.0	0.0	0.0	0.0	0.0
122°	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0
123°	0.0	0.0	0.0	0.0	0.0	0.0
123.5°	0.0	0.0	0.0	0.0	0.0	0.0
124°	0.0	0.0	0.0	0.0	0.0	0.0
124.5°	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0
125.5°	0.0	0.0	0.0	0.0	0.0	0.0
126°	0.0	0.0	0.0	0.0	0.0	0.0
126.5°	0.0	0.0	0.0	0.0	0.0	0.0
127°	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0
128°	0.0	0.1	0.0	0.0	0.0	0.0
128.5°	0.0	0.0	0.0	0.0	0.0	0.0
129°	0.0	0.0	0.0	0.0	0.0	0.0
129.5°	0.0	0.1	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.1	0.0	0.0
130.5°	0.0	0.1	0.1	0.0	0.0	0.0
131°	0.0	0.0	0.1	0.0	0.0	0.1
131.5°	0.0	0.1	0.1	0.0	0.0	0.1
132°	0.0	0.1	0.1	0.0	0.1	0.0
132.5°	0.0	0.1	0.1	0.0	0.1	0.0
133°	0.0	0.1	0.1	0.0	0.0	0.0
133.5°	0.0	0.1	0.2	0.1	0.0	0.0
134°	0.0	0.2	0.1	0.1	0.0	0.0
134.5°	0.0	0.2	0.2	0.0	0.0	0.1



TEST NUMBER: A1914114A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
135°	0.0	0.1	0.1	0.1	0.1	0.1
135.5°	0.0	0.1	0.1	0.1	0.0	0.0
136°	0.0	0.1	0.2	0.1	0.1	0.0
136.5°	0.0	0.1	0.1	0.0	0.0	0.0
137°	0.0	0.2	0.1	0.1	0.1	0.0
137.5°	0.0	0.2	0.1	0.1	0.0	0.0
138°	0.0	0.2	0.1	0.1	0.0	0.1
138.5°	0.0	0.1	0.1	0.1	0.1	0.0
139°	0.0	0.2	0.1	0.1	0.1	0.0
139.5°	0.0	0.1	0.1	0.1	0.0	0.0
140°	0.0	0.1	0.0	0.2	0.0	0.0
140.5°	0.0	0.1	0.1	0.1	0.1	0.0
141°	0.0	0.1	0.1	0.2	0.0	0.0
141.5°	0.0	0.1	0.1	0.1	0.0	0.0
142°	0.0	0.1	0.1	0.1	0.0	0.0
142.5°	0.0	0.1	0.3	0.1	0.0	0.1
143°	0.0	0.1	0.1	0.1	0.0	0.1
143.5°	0.0	0.1	0.2	0.1	0.1	0.0
144°	0.0	0.1	0.2	0.1	0.2	0.1
144.5°	0.0	0.1	0.2	0.1	0.2	0.0
145°	0.0	0.1	0.1	0.1	0.1	0.0
145.5°	0.0	0.1	0.3	0.1	0.1	0.0
146°	0.0	0.1	0.3	0.1	0.1	0.0
146.5°	0.0	0.1	0.3	0.1	0.1	0.1
147°	0.0	0.1	0.1	0.2	0.1	0.0
147.5°	0.0	0.1	0.2	0.1	0.1	0.0
148°	0.0	0.1	0.2	0.1	0.1	0.0
148.5°	0.0	0.1	0.2	0.1	0.1	0.1
149°	0.0	0.1	0.2	0.1	0.1	0.1
149.5°	0.0	0.1	0.2	0.1	0.1	0.1
150°	0.0	0.1	0.2	0.1	0.1	0.1
150.5°	0.0	0.1	0.2	0.2	0.1	0.1
151°	0.0	0.1	0.2	0.2	0.1	0.1
151.5°	0.0	0.1	0.2	0.2	0.1	0.1
152°	0.0	0.1	0.2	0.2	0.1	0.2
152.5°	0.0	0.1	0.2	0.2	0.1	0.2
153°	0.0	0.1	0.2	0.2	0.1	0.1
153.5°	0.0	0.1	0.2	0.2	0.1	0.1
154°	0.0	0.1	0.2	0.2	0.1	0.1
154.5°	0.1	0.1	0.2	0.2	0.1	0.1
155°	0.0	0.1	0.2	0.2	0.1	0.1
155.5°	0.0	0.1	0.2	0.2	0.1	0.1
156°	0.1	0.1	0.2	0.2	0.1	0.1
156.5°	0.1	0.1	0.2	0.2	0.1	0.1
157°	0.1	0.1	0.2	0.2	0.1	0.1



TEST NUMBER: A1914114A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
157.5°	0.1	0.1	0.2	0.2	0.1	0.1
158°	0.1	0.1	0.2	0.2	0.1	0.1
158.5°	0.1	0.1	0.2	0.2	0.1	0.1
159°	0.2	0.1	0.2	0.2	0.1	0.1
159.5°	0.1	0.1	0.2	0.2	0.1	0.1
160°	0.1	0.1	0.2	0.2	0.1	0.1
160.5°	0.0	0.1	0.2	0.2	0.1	0.1
161°	0.0	0.1	0.2	0.2	0.1	0.1
161.5°	0.1	0.1	0.2	0.2	0.1	0.1
162°	0.0	0.1	0.2	0.2	0.1	0.1
162.5°	0.0	0.1	0.2	0.2	0.1	0.1
163°	0.0	0.1	0.2	0.2	0.1	0.1
163.5°	0.1	0.1	0.2	0.2	0.1	0.1
164°	0.0	0.1	0.2	0.2	0.1	0.1
164.5°	0.0	0.1	0.2	0.2	0.1	0.1
165°	0.0	0.1	0.2	0.2	0.1	0.1
165.5°	0.1	0.1	0.2	0.2	0.1	0.1
166°	0.1	0.1	0.2	0.2	0.1	0.1
166.5°	0.1	0.1	0.2	0.2	0.1	0.1
167°	0.1	0.1	0.2	0.2	0.1	0.1
167.5°	0.1	0.1	0.2	0.2	0.1	0.1
168°	0.0	0.1	0.2	0.2	0.1	0.1
168.5°	0.0	0.1	0.2	0.2	0.1	0.1
169°	0.0	0.1	0.2	0.2	0.1	0.1
169.5°	0.0	0.1	0.2	0.2	0.1	0.1
170°	0.0	0.1	0.2	0.2	0.1	0.1
170.5°	0.0	0.1	0.2	0.2	0.1	0.1
171°	0.0	0.1	0.2	0.2	0.1	0.1
171.5°	0.1	0.1	0.2	0.2	0.1	0.1
172°	0.1	0.1	0.2	0.2	0.1	0.1
172.5°	0.2	0.1	0.2	0.2	0.1	0.1
173°	0.1	0.1	0.2	0.2	0.1	0.1
173.5°	0.1	0.1	0.2	0.2	0.1	0.1
174°	0.1	0.1	0.2	0.2	0.1	0.1
174.5°	0.1	0.1	0.2	0.2	0.1	0.1
175°	0.1	0.1	0.2	0.2	0.1	0.1
175.5°	0.1	0.1	0.2	0.2	0.1	0.1
176°	0.1	0.1	0.2	0.2	0.1	0.1
176.5°	0.1	0.1	0.2	0.2	0.1	0.1
177°	0.1	0.1	0.2	0.2	0.1	0.1
177.5°	0.1	0.1	0.2	0.2	0.1	0.1
178°	0.1	0.1	0.2	0.2	0.2	0.1
178.5°	0.1	0.1	0.2	0.2	0.2	0.1
179°	0.1	0.1	0.2	0.2	0.1	0.3
179.5°	0.1	0.1	0.2	0.2	0.1	0.2



TEST NUMBER: A1914114A001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
180°	0.1	0.1	0.1	0.1	0.1	0.1

(END OF REPORT)