

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: A1914114B001

Luminaire Tested:

Test Date: 2019-08-26

Test Information

Test Method: LM-41-14
Report Number: A1914114B001
Test Lab: EVERFINE
Test Date: 2019-08-26
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number:
Description: DL-NJ31bA11ER1-3590 120V 10.5W 60HZ
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 748.9 lumens
Efficiency: N/A
Efficacy: 76.4 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.37
Luminous Opening: Point Source (0m x 0m x 0m)
CIE Type: Direct

Input Watts (W): 9.79946
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: A1914114B001
CATALOG NUMBER:

Luminous Intensity Polar Plot





TEST NUMBER: A1914114B001

CATALOG NUMBER:

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	104	100	96	106	102	98	94	97	94	91	94	91	89	90	88	86	84
2	99	91	84	78	96	89	82	77	85	80	75	82	77	73	79	75	72	70
3	90	79	71	65	88	78	70	64	75	68	63	72	66	62	69	65	61	59
4	82	70	61	55	80	69	61	54	66	59	54	64	58	53	62	57	52	50
5	76	63	54	47	74	62	53	47	59	52	46	57	51	46	56	50	45	43
6	70	56	47	41	68	55	47	41	54	46	40	52	45	40	50	44	40	38
7	65	51	42	36	63	50	42	36	49	41	36	47	41	35	46	40	35	33
8	60	47	38	32	59	46	38	32	45	37	32	43	37	32	42	36	31	30
9	56	43	35	29	55	42	34	29	41	34	29	40	33	29	39	33	28	27
10	53	39	32	26	51	39	31	26	38	31	26	37	30	26	36	30	26	24

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	Luminaire represents a point source (luminous area is zero).			
5°	No luminance values can be calculated.			
10°				
15°				
20°				
25°				
30°				
35°				
40°				
45°				
50°				
55°				
60°				
65°				
70°				
75°				
80°				
85°				



TEST NUMBER: A1914114B001

CATALOG NUMBER:

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.8	3.3
10°-20°	70.9	9.5
20°-30°	107.5	14.4
30°-40°	129.9	17.3
40°-50°	135.2	18.1
50°-60°	122.9	16.4
60°-70°	93.7	12.5
70°-80°	52.3	7.0
80°-90°	11.6	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.1	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	203.1	27.1
0°-40°	333.0	44.5
0°-60°	591.1	78.9
0°-90°	748.8	100.0
90°-120°	0.0	0.0
90°-150°	0.1	0.0
90°-180°	0.0	0.0
0°-180°	748.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	264	264	264	264	264	
5°	261	261	261	260	261	25
15°	253	252	251	250	253	71
25°	234	234	233	231	234	108
35°	209	210	209	205	209	130
45°	176	179	176	173	176	136
55°	138	141	138	134	138	123
65°	95	99	95	91	95	94
75°	49	54	50	45	49	52
85°	8	13	10	6	8	11
90°	0	0	0	0	0	0
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0



TEST NUMBER: A1914114B001

CATALOG NUMBER:

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	263.6	263.6	263.6	263.6	263.6	263.6	263.6	263.6	263.6	263.6	263.6
0.5°	262.6	259.2	262.0	261.3	260.9	259.0	262.9	262.3	262.7	261.0	262.2
1°	261.8	260.1	262.1	261.6	261.4	260.3	261.8	263.2	262.0	262.0	262.0
1.5°	262.0	259.8	261.5	261.8	261.2	261.1	260.3	262.2	261.7	263.2	261.9
2°	262.4	262.7	261.6	261.7	261.3	262.4	260.4	262.1	261.8	261.9	261.3
2.5°	261.8	262.4	262.1	262.3	262.5	259.7	260.9	262.8	262.4	260.4	261.7
3°	261.9	260.8	261.0	262.2	261.7	262.0	261.3	261.1	262.3	261.3	259.9
3.5°	262.0	260.1	259.5	262.0	260.9	261.6	261.8	261.0	260.9	262.3	260.4
4°	262.3	259.6	262.2	261.5	261.0	259.6	259.8	261.7	260.7	259.6	260.4
4.5°	260.8	260.2	262.4	260.8	260.9	261.3	259.8	261.5	260.4	260.3	259.4
5°	261.0	262.3	261.6	262.2	260.8	259.6	261.3	262.4	261.4	260.3	261.0
5.5°	260.8	261.7	260.7	260.1	259.6	259.6	260.3	261.1	261.4	259.9	261.1
6°	260.4	260.1	260.8	261.0	259.3	260.8	260.7	259.4	260.5	258.9	259.8
6.5°	261.0	259.9	259.0	260.9	259.4	260.6	257.9	260.3	259.4	260.1	258.1
7°	259.2	261.2	260.4	263.0	258.8	259.3	260.2	261.4	258.6	259.7	260.4
7.5°	258.9	260.0	259.8	261.8	259.2	260.2	259.3	259.8	258.8	258.6	260.1
8°	258.8	258.8	259.5	260.4	259.3	258.9	260.4	259.4	258.9	258.4	259.4
8.5°	258.8	258.3	259.4	260.8	258.9	257.2	259.5	259.4	258.8	257.6	258.4
9°	258.2	258.3	258.6	259.0	257.9	257.6	258.9	259.6	257.9	257.2	256.6
9.5°	258.0	256.3	258.6	258.1	257.4	257.4	258.6	258.5	258.2	256.2	256.8
10°	257.1	255.5	258.5	257.4	257.1	256.5	257.1	256.7	257.6	256.5	256.4
10.5°	256.2	256.6	257.5	258.4	257.8	256.5	256.1	257.9	257.8	257.2	255.6
11°	256.1	254.8	257.0	256.6	257.5	257.1	256.1	256.4	256.9	255.2	254.6
11.5°	255.5	254.5	256.4	257.4	257.3	257.5	256.0	256.6	255.6	255.6	254.6
12°	254.9	255.3	254.9	257.5	256.4	254.5	255.1	254.6	254.3	253.8	254.6
12.5°	254.6	253.8	254.8	256.1	255.3	254.9	255.0	254.2	253.6	254.3	253.5
13°	254.3	254.1	254.8	256.2	254.3	254.8	254.6	253.6	253.7	254.0	252.9
13.5°	253.5	253.9	254.2	256.2	253.3	254.4	253.2	254.3	252.6	252.6	252.8
14°	253.3	254.4	252.8	255.4	253.6	253.5	252.6	253.1	253.2	252.8	250.6
14.5°	253.0	253.1	253.2	255.0	252.9	252.7	252.6	251.6	252.6	250.5	251.1
15°	253.0	251.7	252.1	254.5	251.6	251.7	251.2	252.6	250.8	249.8	250.5
15.5°	250.0	251.8	252.0	253.4	250.9	252.0	252.0	252.4	250.1	249.5	249.1
16°	250.5	251.3	250.5	253.0	251.6	251.6	251.1	249.9	250.7	249.0	246.6
16.5°	250.8	249.7	250.4	251.2	250.1	248.6	250.2	248.4	249.3	247.9	246.3
17°	249.6	249.1	248.7	250.6	247.8	248.3	248.4	248.7	248.3	247.4	248.0
17.5°	248.0	247.8	248.3	249.6	248.4	247.9	247.0	248.6	249.2	246.1	245.2
18°	248.4	247.0	248.0	248.6	247.8	248.1	246.0	246.6	246.5	246.6	245.1
18.5°	247.0	245.5	247.6	248.5	246.4	246.2	246.1	247.0	247.4	246.2	244.0
19°	245.6	243.3	246.4	247.8	246.0	244.3	245.5	246.2	246.0	244.4	243.9
19.5°	244.5	243.8	245.6	246.8	244.7	244.4	245.4	244.7	244.4	243.2	242.7
20°	243.7	243.6	245.0	245.2	243.6	245.1	245.0	244.4	244.2	242.8	241.6
20.5°	242.8	243.2	244.5	245.1	243.3	243.8	242.5	243.5	242.8	241.1	240.8
21°	241.9	242.6	243.2	244.2	242.0	241.4	241.9	241.5	242.2	240.7	240.0
21.5°	240.8	241.2	242.7	242.8	241.5	240.6	241.4	241.4	241.8	240.1	240.3
22°	240.2	240.6	241.2	242.4	239.4	239.9	239.8	241.1	240.2	237.8	237.5



TEST NUMBER: A1914114B001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
22.5°	239.8	239.8	240.3	241.4	238.1	238.9	239.6	238.6	238.1	238.0	237.2
23°	239.2	237.5	240.1	240.8	237.3	239.6	237.7	237.7	237.7	237.1	237.6
23.5°	237.3	236.6	238.5	239.4	237.3	238.2	236.8	236.3	236.6	235.0	236.3
24°	236.0	235.3	237.2	238.5	238.2	236.2	235.1	237.4	235.5	234.4	234.0
24.5°	234.9	235.2	235.4	237.5	235.7	236.8	235.0	235.3	234.7	234.0	233.2
25°	233.8	233.8	234.4	236.5	234.3	234.3	234.0	234.1	233.3	232.7	232.6
25.5°	232.8	233.1	233.4	235.1	234.1	233.5	232.8	232.8	232.6	232.5	230.1
26°	231.8	231.5	232.4	233.8	231.9	232.4	231.5	231.6	231.8	230.1	229.0
26.5°	230.6	230.2	231.3	232.3	230.7	231.8	230.6	230.4	230.3	229.0	227.6
27°	229.5	229.5	230.7	230.4	229.4	229.9	229.2	230.3	228.5	226.9	226.5
27.5°	228.0	228.3	229.7	229.9	228.3	228.4	227.9	228.9	227.7	226.8	225.0
28°	227.0	227.2	228.2	229.3	227.2	227.9	226.7	227.2	226.4	225.4	223.0
28.5°	226.2	225.6	227.4	228.2	227.1	227.1	225.6	226.3	225.6	223.5	222.7
29°	225.0	224.2	226.3	227.1	225.0	225.4	224.4	224.7	224.6	222.7	221.7
29.5°	223.7	223.7	224.8	226.3	224.2	224.5	223.7	224.1	223.3	220.6	220.4
30°	222.0	223.1	223.4	224.2	223.7	222.6	222.4	222.5	221.9	219.9	219.4
30.5°	220.7	221.0	222.4	223.0	221.8	221.2	221.2	220.7	220.0	218.4	218.3
31°	219.7	219.4	221.6	222.2	220.6	220.2	219.6	219.4	219.0	217.5	216.8
31.5°	218.0	218.5	220.2	221.0	219.5	218.9	218.7	218.2	217.9	215.8	215.1
32°	216.6	217.0	218.5	219.5	218.4	217.1	217.0	217.2	216.5	214.2	214.2
32.5°	214.7	214.9	217.1	218.5	216.4	215.9	215.4	215.8	215.2	212.8	212.4
33°	213.7	213.8	215.4	216.8	215.1	214.6	214.9	214.7	214.4	212.1	211.2
33.5°	212.9	212.8	214.5	215.2	213.9	213.4	213.3	213.2	212.9	210.4	209.9
34°	212.1	211.5	213.2	214.5	212.7	212.2	211.4	212.0	211.8	209.4	208.4
34.5°	210.2	210.4	211.3	212.7	211.1	210.7	209.8	211.1	209.8	207.6	206.9
35°	208.9	209.2	210.1	211.2	209.6	209.7	208.8	209.6	208.8	206.1	205.6
35.5°	207.1	207.3	208.9	209.7	208.4	208.3	207.6	207.8	207.2	204.4	204.1
36°	205.5	206.1	207.5	208.1	206.4	206.6	205.8	206.4	205.2	202.9	202.5
36.5°	204.0	204.4	205.6	207.1	205.1	205.4	204.4	204.8	204.1	201.3	200.7
37°	202.8	202.3	204.1	205.8	203.7	203.9	203.0	202.8	202.3	200.4	199.3
37.5°	200.9	200.8	201.8	203.8	201.8	202.6	201.5	202.0	201.1	198.3	197.8
38°	199.3	199.8	200.4	202.3	200.6	200.6	200.2	200.2	199.6	197.0	196.0
38.5°	197.8	198.0	199.2	200.6	199.3	198.9	198.4	198.6	197.7	195.4	194.6
39°	196.1	196.6	197.4	198.6	197.5	197.2	197.2	197.4	195.6	194.1	193.0
39.5°	194.3	194.6	197.0	197.3	197.0	196.1	195.5	195.6	194.0	192.2	191.6
40°	192.7	193.2	194.7	195.8	194.6	194.4	193.8	194.5	192.0	189.8	189.9
40.5°	191.2	191.0	193.1	194.2	192.6	192.8	192.4	192.3	190.6	189.4	188.2
41°	189.7	189.8	191.2	192.4	191.3	191.2	190.8	190.5	189.2	187.6	186.5
41.5°	187.7	188.7	189.7	190.8	190.0	189.8	189.2	189.2	187.7	185.2	184.8
42°	185.7	186.6	187.5	189.1	188.6	188.2	187.4	187.4	186.0	183.9	183.1
42.5°	184.4	184.8	186.1	187.5	187.3	186.4	185.9	185.7	184.2	182.2	181.5
43°	182.8	183.1	184.1	185.9	185.1	184.6	184.2	183.8	182.7	180.9	179.9
43.5°	181.0	181.5	182.8	184.5	183.7	183.0	182.5	182.0	181.0	179.4	178.0
44°	179.3	179.8	180.1	182.9	181.2	181.0	180.9	180.2	179.3	177.3	176.1
44.5°	177.6	178.0	179.4	181.2	180.0	179.9	178.9	178.4	177.4	175.6	174.4



TEST NUMBER: A1914114B001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
45°	175.6	176.2	177.9	179.3	179.4	178.1	177.0	176.9	175.8	173.4	172.6
45.5°	173.3	174.5	176.2	177.5	177.0	175.9	175.6	175.1	174.0	171.8	170.8
46°	172.4	172.8	174.4	175.8	174.6	174.7	174.0	173.7	172.3	170.1	169.1
46.5°	170.4	171.2	172.8	174.0	172.0	172.3	172.0	171.8	170.6	168.3	167.4
47°	168.7	169.2	171.1	172.2	171.1	170.7	170.2	169.7	168.8	166.5	165.6
47.5°	166.8	168.1	168.9	170.3	169.2	169.3	168.3	167.9	166.8	164.5	163.6
48°	165.1	166.2	167.5	168.5	167.3	167.1	166.3	166.0	164.9	162.7	161.4
48.5°	163.3	164.0	165.2	166.8	165.5	165.4	164.9	164.2	163.0	160.8	159.4
49°	161.3	162.0	163.9	164.8	163.8	163.7	163.1	162.8	161.2	158.8	157.6
49.5°	159.4	159.9	161.8	163.0	162.1	161.8	160.5	161.0	159.4	156.9	155.9
50°	157.4	158.5	160.2	160.9	160.0	160.0	159.2	159.1	157.4	155.1	154.3
50.5°	155.6	156.4	158.4	159.4	157.9	158.1	157.5	157.0	155.7	153.3	152.2
51°	154.2	154.5	155.6	157.6	156.1	156.1	155.7	155.0	153.8	151.5	150.3
51.5°	152.0	152.8	154.2	155.7	154.2	154.5	153.8	153.3	151.9	149.4	148.3
52°	150.2	150.7	152.5	153.9	152.6	152.6	151.8	151.6	149.7	147.2	146.4
52.5°	148.4	149.1	150.4	152.0	150.9	150.3	149.7	149.4	147.6	145.4	144.5
53°	146.4	147.1	148.4	149.7	148.8	148.5	147.6	147.3	145.6	143.3	142.6
53.5°	144.4	145.1	146.7	147.7	146.8	146.4	145.7	145.1	143.7	141.7	140.6
54°	142.2	143.1	144.8	145.7	144.7	144.5	144.1	143.2	141.8	139.7	138.4
54.5°	140.2	141.1	142.4	143.9	142.8	142.7	142.2	140.9	140.0	137.9	136.4
55°	137.9	139.3	140.7	141.7	140.9	140.7	140.0	139.1	137.9	136.0	134.4
55.5°	136.4	137.8	138.8	139.9	138.7	138.6	138.0	137.2	135.9	134.0	132.4
56°	133.9	135.5	136.7	138.1	136.6	136.7	135.8	135.0	133.8	131.6	130.6
56.5°	131.8	133.2	134.4	136.1	134.7	134.9	133.9	132.9	131.8	129.6	128.7
57°	129.6	130.8	132.4	133.7	132.7	132.5	132.0	131.0	129.6	127.3	126.6
57.5°	127.7	128.8	130.2	131.4	130.6	130.2	130.0	129.0	127.6	125.3	124.4
58°	125.7	126.7	128.3	129.3	128.5	128.2	127.6	126.9	125.4	123.3	122.3
58.5°	123.4	124.6	126.3	127.1	126.5	126.3	125.5	124.9	123.4	121.5	120.2
59°	121.5	122.4	124.1	124.8	124.5	124.1	123.5	122.9	121.4	119.2	118.1
59.5°	119.5	120.2	121.9	122.9	122.4	121.9	121.4	121.0	119.2	117.2	115.9
60°	116.9	118.0	119.7	121.0	120.3	120.1	119.3	118.9	117.1	115.1	113.8
60.5°	114.9	116.0	117.5	118.7	118.0	118.2	117.2	116.6	114.8	113.0	111.7
61°	112.6	113.7	115.3	116.7	115.9	116.0	115.0	114.3	112.6	110.8	109.6
61.5°	110.5	111.5	113.4	114.6	113.9	113.8	112.8	112.2	110.5	108.6	107.3
62°	108.2	109.4	111.1	112.3	111.9	111.6	110.6	110.1	108.3	106.5	105.2
62.5°	106.2	107.3	108.9	110.1	109.8	109.5	108.4	107.9	106.1	104.4	102.9
63°	103.9	105.0	106.7	107.7	107.6	107.3	106.2	105.8	104.0	102.2	100.8
63.5°	101.5	102.8	104.4	105.5	105.4	105.1	104.1	103.6	101.8	100.0	98.6
64°	99.4	100.5	102.2	103.2	103.3	102.8	102.0	101.3	99.6	97.8	96.4
64.5°	97.1	98.4	100.1	101.0	101.1	100.6	99.9	99.2	97.5	95.5	94.1
65°	94.8	96.1	97.8	98.9	98.8	98.4	97.8	97.0	95.3	93.3	92.0
65.5°	92.4	93.8	95.5	96.5	96.5	96.3	95.6	94.7	93.1	91.1	89.7
66°	90.1	91.5	93.3	94.4	94.3	94.1	93.3	92.4	90.8	88.8	87.6
66.5°	87.9	89.5	90.9	92.3	92.1	91.8	91.1	90.1	88.7	86.7	85.4
67°	85.7	87.2	88.8	89.9	89.8	89.6	89.1	88.0	86.6	84.6	83.3



TEST NUMBER: A1914114B001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
67.5°	83.4	84.9	86.6	87.7	87.8	87.7	87.1	85.7	84.4	82.3	81.0
68°	81.1	82.4	84.3	85.5	85.6	85.4	84.8	83.5	82.1	80.1	78.6
68.5°	78.9	80.3	82.0	83.1	83.3	83.3	82.6	81.3	80.0	77.7	76.3
69°	76.6	78.0	79.7	80.8	81.2	81.2	80.2	79.1	77.6	75.4	74.0
69.5°	74.2	75.6	77.4	78.5	78.8	78.8	78.0	76.9	75.4	73.1	71.8
70°	72.0	73.4	74.9	76.2	76.6	76.2	75.7	74.6	73.1	70.9	69.5
70.5°	69.9	71.0	72.5	73.9	74.3	74.0	73.5	72.4	70.8	68.8	67.3
71°	67.3	68.8	70.4	71.6	72.1	72.0	71.2	70.0	68.5	66.3	65.1
71.5°	65.1	66.4	68.1	69.4	69.8	69.6	68.9	67.6	66.3	64.0	62.8
72°	62.7	64.0	65.9	67.1	67.6	67.4	66.6	65.4	64.0	61.8	60.6
72.5°	60.3	61.8	63.5	64.5	65.4	65.0	64.3	63.0	61.7	59.6	58.4
73°	58.0	59.4	61.1	62.2	63.1	62.7	62.0	60.8	59.4	57.3	56.0
73.5°	55.8	57.1	58.9	60.0	60.9	60.4	59.8	58.6	57.2	55.0	53.8
74°	53.4	55.0	56.4	57.6	58.7	58.3	57.6	56.4	55.0	52.9	51.6
74.5°	51.0	52.7	54.3	55.6	56.3	56.0	55.4	54.3	52.8	50.6	49.4
75°	48.9	50.4	51.9	53.0	54.2	53.8	53.3	52.1	50.5	48.3	47.2
75.5°	46.6	48.0	49.6	50.8	51.9	51.6	51.0	50.0	48.2	46.1	44.9
76°	44.2	45.8	47.3	48.4	49.7	49.4	48.7	47.7	46.0	44.0	42.5
76.5°	41.8	43.5	45.1	46.1	47.5	47.1	46.6	45.3	43.6	41.9	40.2
77°	39.6	41.2	42.8	43.9	45.3	44.9	44.3	43.1	41.4	39.7	38.1
77.5°	37.5	38.9	40.5	41.6	43.1	42.8	42.2	41.0	39.3	37.4	36.0
78°	35.1	36.8	38.3	39.4	40.8	40.7	40.0	38.8	37.2	35.3	33.9
78.5°	33.0	34.5	36.0	37.2	38.6	38.4	37.7	36.5	34.9	33.1	31.8
79°	30.8	32.4	33.9	34.9	36.4	36.3	35.6	34.3	32.8	31.0	29.7
79.5°	28.6	30.2	31.7	32.7	34.3	34.1	33.5	32.2	30.6	28.9	27.6
80°	26.5	28.0	29.4	30.5	32.2	32.0	31.3	30.1	28.6	26.8	25.4
80.5°	24.5	25.9	27.4	28.4	30.1	29.9	29.2	28.0	26.5	24.8	23.4
81°	22.5	23.9	25.3	26.3	28.0	27.8	27.1	25.9	24.4	22.8	21.4
81.5°	20.6	22.0	23.3	24.2	25.9	25.7	25.0	23.9	22.5	21.0	19.7
82°	18.6	20.0	21.5	22.3	23.8	23.7	23.0	21.9	20.6	19.0	17.8
82.5°	16.8	18.2	19.5	20.4	21.9	21.7	21.1	20.2	18.7	17.2	16.0
83°	15.1	16.3	17.6	18.5	20.0	19.9	19.3	18.3	16.8	15.4	14.2
83.5°	13.2	14.4	15.7	16.5	18.2	17.9	17.4	16.5	15.0	13.5	12.5
84°	11.4	12.7	13.9	14.7	16.3	16.2	15.5	14.5	13.2	11.8	10.8
84.5°	10.0	11.1	12.2	13.0	14.5	14.3	13.8	12.7	11.5	10.2	9.2
85°	8.5	9.4	10.5	11.2	12.7	12.6	12.1	11.0	9.9	8.6	7.7
85.5°	6.9	8.0	9.0	9.7	11.0	10.9	10.4	9.4	8.3	7.1	6.2
86°	5.5	6.6	7.5	8.2	9.4	9.3	8.8	8.0	6.9	5.8	4.8
86.5°	4.5	5.2	6.0	6.8	8.0	7.9	7.3	6.4	5.4	4.4	3.8
87°	3.2	4.0	4.8	5.4	6.4	6.3	5.9	5.1	4.1	3.1	2.4
87.5°	2.2	3.0	3.7	4.4	5.0	5.0	4.5	4.0	3.0	2.1	1.6
88°	1.4	2.0	2.6	3.2	4.0	3.8	3.3	2.8	1.8	1.1	0.6
88.5°	0.7	1.2	1.7	2.2	2.7	2.5	2.2	1.8	1.0	0.5	0.0
89°	0.2	0.6	1.0	1.4	1.7	1.6	1.2	0.8	0.1	0.0	0.0
89.5°	0.0	0.1	0.5	0.7	0.8	0.7	0.4	0.0	0.0	0.0	0.0



TEST NUMBER: A1914114B001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
90°	0.0	0.0	0.1	0.3	0.1	0.0	0.0	0.0	0.0	0.0	0.0
90.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
91°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
91.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
93°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
93.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
94°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
94.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
96°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
96.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
101°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
101.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
103°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
103.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
104°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
104.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
106°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
106.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
108°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
108.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
109°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
109.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
111°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
111.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
112°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1914114B001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
113°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
113.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
114°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
114.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
116°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
116.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
118°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
118.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
119°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
119.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
121°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
121.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
123°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
123.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
124°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
124.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
126°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
126.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
128°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
128.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
129°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
129.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
131°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
131.5°	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
133°	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
133.5°	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
134°	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
134.5°	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1914114B001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
135°	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135.5°	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
136°	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
136.5°	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137°	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
138°	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
138.5°	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
139°	0.1	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
139.5°	0.2	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.2	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140.5°	0.1	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
141°	0.2	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
141.5°	0.2	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142°	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.1	0.0	0.0	0.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
143°	0.1	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
143.5°	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
144°	0.1	0.1	0.0	0.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
144.5°	0.1	0.1	0.1	0.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145.5°	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
146°	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
146.5°	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147°	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.1	0.1	0.0	0.0
148°	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.1	0.1	0.0	0.0
148.5°	0.2	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
149°	0.2	0.1	0.1	0.2	0.0	0.0	0.0	0.0	0.1	0.0	0.0
149.5°	0.2	0.1	0.1	0.2	0.0	0.0	0.0	0.0	0.1	0.0	0.0
150°	0.2	0.1	0.1	0.2	0.0	0.0	0.0	0.0	0.1	0.0	0.0
150.5°	0.2	0.1	0.1	0.2	0.0	0.0	0.0	0.1	0.1	0.0	0.0
151°	0.2	0.1	0.1	0.2	0.0	0.0	0.0	0.1	0.1	0.0	0.0
151.5°	0.2	0.1	0.1	0.2	0.0	0.0	0.0	0.1	0.2	0.0	0.0
152°	0.2	0.1	0.1	0.2	0.0	0.0	0.0	0.1	0.2	0.0	0.0
152.5°	0.2	0.1	0.1	0.2	0.0	0.0	0.0	0.1	0.1	0.0	0.0
153°	0.2	0.1	0.1	0.2	0.1	0.0	0.0	0.1	0.1	0.1	0.0
153.5°	0.2	0.1	0.1	0.2	0.0	0.1	0.0	0.1	0.3	0.1	0.0
154°	0.2	0.1	0.1	0.2	0.0	0.1	0.0	0.2	0.3	0.1	0.0
154.5°	0.2	0.1	0.1	0.2	0.0	0.1	0.0	0.1	0.2	0.1	0.0
155°	0.2	0.1	0.1	0.2	0.1	0.1	0.0	0.1	0.2	0.1	0.1
155.5°	0.2	0.1	0.1	0.2	0.1	0.0	0.1	0.1	0.2	0.2	0.1
156°	0.2	0.1	0.1	0.2	0.1	0.1	0.1	0.2	0.3	0.1	0.1
156.5°	0.2	0.1	0.1	0.2	0.1	0.1	0.1	0.2	0.3	0.1	0.1
157°	0.2	0.1	0.1	0.2	0.1	0.1	0.1	0.2	0.1	0.3	0.1



TEST NUMBER: A1914114B001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
157.5°	0.2	0.1	0.1	0.2	0.1	0.1	0.1	0.2	0.2	0.3	0.1
158°	0.2	0.1	0.1	0.2	0.1	0.1	0.2	0.2	0.2	0.3	0.1
158.5°	0.2	0.1	0.1	0.2	0.1	0.1	0.2	0.2	0.1	0.3	0.1
159°	0.2	0.1	0.1	0.2	0.1	0.1	0.1	0.2	0.1	0.2	0.1
159.5°	0.2	0.1	0.1	0.2	0.1	0.3	0.1	0.2	0.1	0.2	0.1
160°	0.2	0.1	0.1	0.2	0.1	0.3	0.1	0.2	0.1	0.2	0.1
160.5°	0.2	0.1	0.1	0.2	0.1	0.2	0.1	0.2	0.1	0.2	0.1
161°	0.2	0.1	0.1	0.2	0.1	0.2	0.1	0.2	0.1	0.2	0.1
161.5°	0.2	0.1	0.1	0.2	0.1	0.2	0.1	0.2	0.1	0.2	0.1
162°	0.2	0.1	0.1	0.2	0.1	0.2	0.1	0.2	0.1	0.2	0.1
162.5°	0.2	0.1	0.1	0.2	0.1	0.2	0.1	0.2	0.1	0.2	0.1
163°	0.2	0.1	0.1	0.2	0.2	0.2	0.1	0.2	0.1	0.2	0.1
163.5°	0.2	0.1	0.1	0.2	0.1	0.2	0.1	0.2	0.1	0.2	0.1
164°	0.2	0.1	0.1	0.2	0.1	0.2	0.1	0.2	0.1	0.2	0.1
164.5°	0.2	0.1	0.1	0.2	0.1	0.2	0.1	0.2	0.1	0.2	0.1
165°	0.2	0.1	0.1	0.2	0.1	0.2	0.1	0.2	0.1	0.2	0.1
165.5°	0.2	0.1	0.1	0.2	0.1	0.2	0.1	0.2	0.1	0.2	0.1
166°	0.2	0.1	0.1	0.2	0.1	0.2	0.1	0.2	0.1	0.2	0.1
166.5°	0.2	0.1	0.1	0.2	0.0	0.2	0.1	0.2	0.1	0.2	0.1
167°	0.2	0.1	0.1	0.2	0.0	0.3	0.1	0.2	0.1	0.2	0.1
167.5°	0.2	0.1	0.1	0.2	0.0	0.2	0.1	0.2	0.1	0.2	0.1
168°	0.2	0.1	0.1	0.2	0.0	0.2	0.1	0.2	0.1	0.2	0.1
168.5°	0.2	0.1	0.1	0.2	0.0	0.2	0.1	0.2	0.1	0.2	0.1
169°	0.2	0.1	0.1	0.2	0.0	0.1	0.1	0.2	0.1	0.2	0.1
169.5°	0.2	0.1	0.1	0.2	0.0	0.1	0.1	0.2	0.1	0.2	0.1
170°	0.2	0.1	0.1	0.2	0.0	0.1	0.1	0.2	0.1	0.2	0.1
170.5°	0.2	0.1	0.1	0.2	0.0	0.1	0.1	0.2	0.1	0.2	0.1
171°	0.2	0.1	0.1	0.2	0.0	0.1	0.1	0.2	0.1	0.2	0.1
171.5°	0.2	0.1	0.1	0.2	0.0	0.1	0.1	0.2	0.1	0.2	0.1
172°	0.2	0.1	0.1	0.2	0.0	0.1	0.1	0.2	0.1	0.2	0.1
172.5°	0.2	0.1	0.1	0.2	0.0	0.1	0.1	0.2	0.1	0.2	0.1
173°	0.2	0.1	0.1	0.2	0.0	0.1	0.1	0.2	0.1	0.2	0.1
173.5°	0.2	0.1	0.1	0.2	0.0	0.1	0.1	0.2	0.1	0.2	0.1
174°	0.2	0.1	0.1	0.2	0.0	0.1	0.1	0.2	0.1	0.2	0.1
174.5°	0.2	0.1	0.1	0.2	0.0	0.1	0.1	0.2	0.1	0.2	0.1
175°	0.2	0.1	0.1	0.2	0.0	0.1	0.1	0.2	0.1	0.2	0.1
175.5°	0.2	0.1	0.1	0.2	0.0	0.1	0.1	0.2	0.1	0.2	0.1
176°	0.2	0.1	0.1	0.2	0.0	0.1	0.1	0.2	0.1	0.2	0.1
176.5°	0.2	0.1	0.1	0.2	0.0	0.1	0.1	0.2	0.1	0.2	0.1
177°	0.2	0.1	0.1	0.2	0.0	0.1	0.1	0.2	0.1	0.2	0.1
177.5°	0.2	0.1	0.1	0.2	0.0	0.1	0.1	0.2	0.1	0.2	0.1
178°	0.2	0.1	0.1	0.2	0.0	0.1	0.1	0.2	0.1	0.2	0.1
178.5°	0.2	0.1	0.1	0.2	0.0	0.1	0.1	0.2	0.1	0.2	0.1
179°	0.2	0.1	0.1	0.2	0.0	0.1	0.1	0.2	0.1	0.2	0.1
179.5°	0.2	0.1	0.1	0.2	0.0	0.1	0.1	0.2	0.1	0.2	0.1



TEST NUMBER: A1914114B001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
180°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2



TEST NUMBER: A1914114B001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	263.6	263.6	263.6	263.6	263.6	263.6
0.5°	262.0	261.2	262.4	261.9	263.4	262.6
1°	262.2	260.6	262.6	261.3	263.4	261.8
1.5°	262.0	259.0	261.7	261.4	261.9	262.0
2°	261.7	260.6	259.5	261.5	261.5	262.4
2.5°	261.9	261.4	260.2	258.4	262.4	261.8
3°	261.2	259.9	259.5	261.8	262.3	261.9
3.5°	261.7	260.2	259.6	261.0	260.7	262.0
4°	259.7	261.6	261.3	261.6	260.7	262.3
4.5°	260.9	260.6	260.0	258.3	260.6	260.8
5°	261.0	260.1	260.3	260.0	260.0	261.0
5.5°	260.7	259.3	258.5	258.5	260.1	260.8
6°	261.5	258.6	259.0	258.0	260.9	260.4
6.5°	260.8	259.0	258.9	257.5	258.5	261.0
7°	259.9	259.0	257.3	256.8	258.8	259.2
7.5°	259.3	258.7	258.4	257.3	259.3	258.9
8°	259.4	257.8	258.0	256.6	259.3	258.8
8.5°	257.9	257.5	257.0	256.6	257.5	258.8
9°	258.8	257.5	256.0	257.0	257.6	258.2
9.5°	257.8	255.7	256.2	256.7	257.2	258.0
10°	257.5	255.8	255.9	255.5	257.3	257.1
10.5°	256.6	254.8	254.6	254.5	257.2	256.2
11°	254.3	253.8	254.5	254.7	256.8	256.1
11.5°	255.1	253.3	254.2	254.5	254.8	255.5
12°	254.4	253.2	253.7	254.2	254.5	254.9
12.5°	253.2	252.8	251.7	254.1	254.0	254.6
13°	253.5	253.6	250.7	252.2	254.2	254.3
13.5°	252.4	252.6	250.9	252.6	253.4	253.5
14°	251.0	250.9	250.4	251.6	252.5	253.3
14.5°	251.4	249.7	249.8	250.4	251.0	253.0
15°	250.7	249.8	249.4	249.5	250.6	253.0
15.5°	249.3	247.4	248.7	249.2	250.2	250.0
16°	249.3	248.1	247.9	248.7	249.0	250.5
16.5°	248.4	246.3	246.5	248.3	249.0	250.8
17°	247.6	245.2	246.3	247.1	248.2	249.6
17.5°	246.9	245.3	245.4	246.2	247.0	248.0
18°	245.2	244.9	245.3	246.2	245.8	248.4
18.5°	245.0	243.8	244.3	244.7	245.5	247.0
19°	244.4	242.9	243.1	244.0	245.0	245.6
19.5°	243.6	241.5	242.3	243.7	244.1	244.5
20°	242.9	240.6	241.3	242.0	243.1	243.7
20.5°	241.3	239.3	240.5	240.5	242.6	242.8
21°	239.7	239.2	239.7	239.5	241.8	241.9
21.5°	238.1	237.8	238.5	238.7	240.7	240.8
22°	238.3	236.7	237.7	237.8	240.1	240.2



TEST NUMBER: A1914114B001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
22.5°	238.3	236.8	237.4	237.0	238.6	239.8
23°	234.7	232.6	236.2	236.1	237.4	239.2
23.5°	234.4	232.1	234.3	233.7	236.3	237.3
24°	232.6	233.0	233.7	233.3	235.1	236.0
24.5°	232.6	231.9	232.3	232.3	234.0	234.9
25°	232.2	231.2	230.3	231.8	233.5	233.8
25.5°	230.4	229.5	229.7	230.9	232.3	232.8
26°	229.4	229.0	228.6	229.6	230.7	231.8
26.5°	228.0	228.3	227.2	228.2	230.1	230.6
27°	227.1	225.3	225.6	226.7	228.7	229.5
27.5°	225.2	225.0	224.8	225.7	227.6	228.0
28°	223.9	224.4	224.0	224.8	226.5	227.0
28.5°	222.5	222.3	222.4	223.8	224.7	226.2
29°	222.6	221.0	220.8	222.4	223.9	225.0
29.5°	219.7	219.2	219.9	221.1	222.8	223.7
30°	218.2	217.6	218.3	219.3	222.0	222.0
30.5°	218.0	217.2	217.1	217.8	220.7	220.7
31°	217.1	215.4	215.7	216.7	219.1	219.7
31.5°	215.2	214.5	214.4	215.5	217.8	218.0
32°	213.4	214.4	213.4	214.3	216.0	216.6
32.5°	211.8	213.8	211.9	212.9	214.6	214.7
33°	210.2	210.5	210.8	211.0	213.3	213.7
33.5°	208.9	207.6	209.0	209.8	211.9	212.9
34°	207.3	207.7	208.0	208.3	210.6	212.1
34.5°	205.9	205.8	206.5	206.8	209.4	210.2
35°	204.9	204.6	205.1	205.4	208.1	208.9
35.5°	202.9	203.5	203.4	204.2	206.1	207.1
36°	202.1	201.3	202.0	202.8	204.8	205.5
36.5°	201.0	200.0	200.1	200.9	203.0	204.0
37°	198.7	198.4	198.5	199.4	201.5	202.8
37.5°	197.4	196.6	197.0	197.9	199.8	200.9
38°	196.3	195.2	195.5	196.2	198.2	199.3
38.5°	193.9	193.0	194.2	194.0	196.9	197.8
39°	192.5	192.2	192.5	193.1	195.1	196.1
39.5°	190.7	190.8	190.8	191.4	193.4	194.3
40°	189.0	188.8	189.2	189.9	191.7	192.7
40.5°	188.1	188.0	187.7	188.2	190.0	191.2
41°	186.4	185.6	185.9	186.6	188.0	189.7
41.5°	184.7	184.3	184.1	185.2	186.4	187.7
42°	182.6	182.1	182.4	183.1	184.6	185.7
42.5°	181.1	180.3	180.8	181.5	183.0	184.4
43°	179.7	178.8	179.1	179.6	181.2	182.8
43.5°	177.6	177.4	177.2	178.0	179.4	181.0
44°	175.9	176.5	175.6	176.0	177.8	179.3
44.5°	174.0	174.3	173.8	174.5	176.1	177.6



TEST NUMBER: A1914114B001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
45°	172.2	172.6	172.1	172.5	174.4	175.6
45.5°	170.3	170.4	170.3	170.8	172.6	173.3
46°	168.4	168.3	168.4	169.1	170.9	172.4
46.5°	166.7	167.2	166.8	167.3	169.2	170.4
47°	164.9	165.5	164.9	165.4	167.4	168.7
47.5°	162.9	163.6	163.0	163.6	165.7	166.8
48°	161.1	161.2	161.0	161.7	163.8	165.1
48.5°	159.1	159.4	159.3	160.0	161.9	163.3
49°	157.4	157.0	157.6	158.2	160.3	161.3
49.5°	155.8	155.5	155.8	156.4	158.4	159.4
50°	154.0	153.9	153.9	154.2	156.8	157.4
50.5°	152.1	151.4	152.2	152.9	154.5	155.6
51°	150.1	150.1	150.2	150.5	152.8	154.2
51.5°	148.3	148.0	148.2	148.9	150.5	152.0
52°	146.1	146.1	146.2	146.8	148.5	150.2
52.5°	144.0	144.3	144.2	145.1	146.5	148.4
53°	142.0	141.9	142.2	143.0	144.6	146.4
53.5°	140.1	140.4	140.5	141.2	142.6	144.4
54°	138.1	138.6	138.3	139.2	141.0	142.2
54.5°	136.0	136.4	136.4	136.9	139.1	140.2
55°	134.0	133.9	134.4	135.0	137.0	137.9
55.5°	132.1	131.8	132.2	133.2	134.9	136.4
56°	129.8	130.1	129.9	130.8	132.6	133.9
56.5°	127.8	127.9	127.8	128.7	130.7	131.8
57°	125.6	125.5	125.7	126.5	128.8	129.6
57.5°	123.4	123.8	123.7	124.6	126.5	127.7
58°	121.4	121.9	121.4	122.7	124.4	125.7
58.5°	119.6	119.7	119.3	120.4	122.4	123.4
59°	117.6	116.8	117.4	118.2	119.9	121.5
59.5°	115.6	114.5	115.2	116.2	117.7	119.5
60°	113.2	112.4	113.0	114.0	115.5	116.9
60.5°	110.9	110.5	110.8	111.7	113.3	114.9
61°	108.6	108.1	108.7	109.6	111.2	112.6
61.5°	106.4	106.1	106.5	107.4	108.9	110.5
62°	104.2	103.9	104.3	105.1	106.7	108.2
62.5°	102.1	102.0	102.1	102.9	104.5	106.2
63°	100.1	99.6	99.7	100.7	102.2	103.9
63.5°	98.0	97.4	97.5	98.5	100.0	101.5
64°	95.8	94.9	95.1	96.1	97.8	99.4
64.5°	93.6	92.7	92.8	93.7	95.3	97.1
65°	91.4	90.6	90.6	91.5	93.1	94.8
65.5°	89.0	88.6	88.4	89.4	90.8	92.4
66°	86.9	86.3	86.1	87.1	88.6	90.1
66.5°	84.5	84.1	83.9	84.9	86.3	87.9
67°	82.3	81.6	81.6	82.4	84.0	85.7



TEST NUMBER: A1914114B001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
67.5°	79.9	79.4	79.3	80.2	81.7	83.4
68°	77.6	77.0	77.0	77.8	79.5	81.1
68.5°	75.3	74.5	74.8	75.7	77.2	78.9
69°	73.0	72.1	72.4	73.4	74.8	76.6
69.5°	71.0	69.9	70.1	70.9	72.5	74.2
70°	68.8	67.7	68.0	68.4	70.2	72.0
70.5°	66.5	65.5	65.4	66.2	68.0	69.9
71°	64.3	63.0	63.1	64.0	65.5	67.3
71.5°	61.9	60.6	60.8	61.7	63.1	65.1
72°	59.6	58.4	58.5	59.3	61.0	62.7
72.5°	57.3	56.1	56.2	57.1	58.6	60.3
73°	55.0	53.9	54.0	54.9	56.4	58.0
73.5°	52.8	51.5	51.6	52.6	54.3	55.8
74°	50.5	49.2	49.3	50.2	51.9	53.4
74.5°	48.1	46.8	47.0	48.0	49.6	51.0
75°	46.0	44.6	44.8	45.7	47.3	48.9
75.5°	43.7	42.5	42.6	43.4	45.0	46.6
76°	41.5	40.1	40.3	41.1	42.7	44.2
76.5°	39.3	38.0	38.2	38.9	40.4	41.8
77°	37.1	35.6	35.8	36.6	38.2	39.6
77.5°	35.0	33.4	33.5	34.5	35.8	37.5
78°	32.9	31.2	31.4	32.2	33.6	35.1
78.5°	30.8	29.0	29.3	30.1	31.4	33.0
79°	28.7	27.0	27.2	27.9	29.2	30.8
79.5°	26.5	24.9	25.0	25.8	27.1	28.6
80°	24.6	22.9	23.0	23.8	25.0	26.5
80.5°	22.5	21.0	21.2	21.9	22.9	24.5
81°	20.8	19.0	19.3	19.9	21.2	22.5
81.5°	18.8	17.2	17.3	18.0	19.2	20.6
82°	16.9	15.4	15.5	16.1	17.4	18.6
82.5°	15.2	13.6	13.7	14.4	15.5	16.8
83°	13.3	11.9	12.1	12.6	13.7	15.1
83.5°	11.6	10.2	10.3	11.0	12.0	13.2
84°	10.0	8.8	9.0	9.2	10.3	11.4
84.5°	8.4	7.2	7.4	7.8	8.9	10.0
85°	7.0	5.9	6.0	6.5	7.3	8.5
85.5°	5.7	4.8	4.8	5.1	5.9	6.9
86°	4.2	3.5	3.6	3.9	4.7	5.5
86.5°	3.1	2.5	2.6	2.9	3.6	4.5
87°	2.0	1.6	1.6	2.0	2.5	3.2
87.5°	1.0	0.9	0.9	1.2	1.6	2.2
88°	0.3	0.4	0.4	0.5	0.8	1.4
88.5°	0.0	0.0	0.0	0.1	0.4	0.7
89°	0.0	0.0	0.0	0.0	0.0	0.2
89.5°	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1914114B001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
90°	0.0	0.0	0.0	0.0	0.0	0.0
90.5°	0.0	0.0	0.0	0.0	0.0	0.0
91°	0.0	0.0	0.0	0.0	0.0	0.0
91.5°	0.0	0.0	0.0	0.0	0.0	0.0
92°	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0
93°	0.0	0.0	0.0	0.0	0.0	0.0
93.5°	0.0	0.0	0.0	0.0	0.0	0.0
94°	0.0	0.0	0.0	0.0	0.0	0.0
94.5°	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0
95.5°	0.0	0.0	0.0	0.0	0.0	0.0
96°	0.0	0.0	0.0	0.0	0.0	0.0
96.5°	0.0	0.0	0.0	0.0	0.0	0.0
97°	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0
98°	0.0	0.0	0.0	0.0	0.0	0.0
98.5°	0.0	0.0	0.0	0.0	0.0	0.0
99°	0.0	0.0	0.0	0.0	0.0	0.0
99.5°	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0
100.5°	0.0	0.0	0.0	0.0	0.0	0.0
101°	0.0	0.0	0.0	0.0	0.0	0.0
101.5°	0.0	0.0	0.0	0.0	0.0	0.0
102°	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0
103°	0.0	0.0	0.0	0.0	0.0	0.0
103.5°	0.0	0.0	0.0	0.0	0.0	0.0
104°	0.0	0.0	0.0	0.0	0.0	0.0
104.5°	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0
105.5°	0.0	0.0	0.0	0.0	0.0	0.0
106°	0.0	0.0	0.0	0.0	0.0	0.0
106.5°	0.0	0.0	0.0	0.0	0.0	0.0
107°	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0
108°	0.0	0.0	0.0	0.0	0.0	0.0
108.5°	0.0	0.0	0.0	0.0	0.0	0.0
109°	0.0	0.0	0.0	0.0	0.0	0.0
109.5°	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0
110.5°	0.0	0.0	0.0	0.0	0.0	0.0
111°	0.0	0.0	0.0	0.0	0.0	0.0
111.5°	0.0	0.0	0.0	0.0	0.0	0.0
112°	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1914114B001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0
113°	0.0	0.0	0.0	0.0	0.0	0.0
113.5°	0.0	0.0	0.0	0.0	0.0	0.0
114°	0.0	0.0	0.0	0.0	0.0	0.0
114.5°	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0
115.5°	0.0	0.0	0.0	0.0	0.0	0.0
116°	0.0	0.0	0.0	0.0	0.0	0.0
116.5°	0.0	0.0	0.0	0.0	0.0	0.0
117°	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0
118°	0.0	0.0	0.0	0.0	0.0	0.0
118.5°	0.0	0.0	0.0	0.0	0.0	0.0
119°	0.0	0.0	0.0	0.0	0.0	0.0
119.5°	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0
120.5°	0.0	0.0	0.0	0.0	0.0	0.0
121°	0.0	0.0	0.0	0.0	0.0	0.0
121.5°	0.0	0.0	0.0	0.0	0.0	0.0
122°	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0
123°	0.0	0.0	0.0	0.0	0.0	0.0
123.5°	0.0	0.0	0.0	0.0	0.0	0.0
124°	0.0	0.0	0.0	0.0	0.0	0.0
124.5°	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0
125.5°	0.0	0.0	0.0	0.0	0.0	0.0
126°	0.0	0.0	0.0	0.0	0.0	0.0
126.5°	0.0	0.0	0.0	0.0	0.0	0.0
127°	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0
128°	0.0	0.0	0.0	0.0	0.0	0.0
128.5°	0.0	0.0	0.0	0.0	0.0	0.0
129°	0.0	0.1	0.0	0.0	0.0	0.0
129.5°	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.1	0.0	0.0	0.1	0.0
130.5°	0.0	0.1	0.0	0.0	0.0	0.0
131°	0.0	0.1	0.0	0.0	0.1	0.0
131.5°	0.0	0.1	0.0	0.0	0.0	0.1
132°	0.0	0.1	0.0	0.0	0.0	0.0
132.5°	0.0	0.1	0.0	0.0	0.0	0.1
133°	0.0	0.1	0.0	0.0	0.1	0.1
133.5°	0.0	0.1	0.0	0.0	0.1	0.1
134°	0.0	0.1	0.1	0.0	0.1	0.1
134.5°	0.0	0.1	0.0	0.0	0.2	0.1



TEST NUMBER: A1914114B001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
135°	0.0	0.1	0.0	0.0	0.1	0.1
135.5°	0.0	0.2	0.0	0.0	0.1	0.1
136°	0.0	0.1	0.0	0.1	0.1	0.1
136.5°	0.0	0.1	0.0	0.0	0.1	0.1
137°	0.0	0.1	0.0	0.1	0.1	0.1
137.5°	0.0	0.1	0.0	0.1	0.1	0.1
138°	0.0	0.2	0.1	0.1	0.1	0.1
138.5°	0.0	0.1	0.1	0.1	0.1	0.1
139°	0.0	0.1	0.1	0.1	0.2	0.1
139.5°	0.0	0.2	0.1	0.1	0.1	0.2
140°	0.0	0.1	0.1	0.1	0.1	0.2
140.5°	0.0	0.1	0.1	0.1	0.1	0.1
141°	0.0	0.1	0.1	0.2	0.1	0.2
141.5°	0.0	0.1	0.2	0.2	0.1	0.2
142°	0.0	0.1	0.1	0.1	0.1	0.1
142.5°	0.0	0.1	0.1	0.1	0.1	0.1
143°	0.0	0.1	0.2	0.1	0.1	0.1
143.5°	0.0	0.1	0.2	0.2	0.1	0.1
144°	0.0	0.1	0.1	0.2	0.1	0.1
144.5°	0.0	0.1	0.1	0.2	0.1	0.1
145°	0.0	0.1	0.1	0.2	0.1	0.1
145.5°	0.0	0.1	0.1	0.1	0.1	0.1
146°	0.0	0.1	0.1	0.2	0.1	0.1
146.5°	0.0	0.1	0.1	0.1	0.1	0.1
147°	0.0	0.1	0.1	0.3	0.1	0.1
147.5°	0.0	0.1	0.1	0.3	0.1	0.1
148°	0.0	0.1	0.1	0.2	0.1	0.1
148.5°	0.0	0.1	0.1	0.2	0.1	0.2
149°	0.0	0.1	0.1	0.2	0.1	0.2
149.5°	0.0	0.1	0.1	0.2	0.1	0.2
150°	0.0	0.1	0.1	0.2	0.1	0.2
150.5°	0.0	0.1	0.1	0.2	0.1	0.2
151°	0.0	0.1	0.1	0.2	0.1	0.2
151.5°	0.0	0.1	0.1	0.2	0.1	0.2
152°	0.0	0.1	0.1	0.2	0.1	0.2
152.5°	0.0	0.1	0.1	0.2	0.1	0.2
153°	0.0	0.1	0.1	0.2	0.1	0.2
153.5°	0.0	0.1	0.1	0.2	0.1	0.2
154°	0.0	0.1	0.1	0.2	0.1	0.2
154.5°	0.0	0.1	0.1	0.2	0.1	0.2
155°	0.0	0.1	0.1	0.2	0.1	0.2
155.5°	0.1	0.1	0.1	0.2	0.1	0.2
156°	0.1	0.1	0.1	0.2	0.1	0.2
156.5°	0.1	0.1	0.1	0.2	0.1	0.2
157°	0.1	0.1	0.1	0.2	0.1	0.2



TEST NUMBER: A1914114B001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
157.5°	0.2	0.1	0.1	0.2	0.1	0.2
158°	0.1	0.1	0.1	0.2	0.1	0.2
158.5°	0.1	0.1	0.1	0.2	0.1	0.2
159°	0.1	0.1	0.1	0.2	0.1	0.2
159.5°	0.1	0.1	0.1	0.2	0.1	0.2
160°	0.1	0.1	0.1	0.2	0.1	0.2
160.5°	0.1	0.1	0.1	0.2	0.1	0.2
161°	0.1	0.1	0.1	0.2	0.1	0.2
161.5°	0.1	0.1	0.1	0.2	0.1	0.2
162°	0.1	0.1	0.1	0.2	0.1	0.2
162.5°	0.1	0.1	0.1	0.2	0.1	0.2
163°	0.1	0.1	0.1	0.2	0.1	0.2
163.5°	0.1	0.1	0.1	0.2	0.1	0.2
164°	0.1	0.1	0.1	0.2	0.1	0.2
164.5°	0.1	0.1	0.1	0.2	0.1	0.2
165°	0.1	0.1	0.1	0.2	0.1	0.2
165.5°	0.1	0.1	0.1	0.2	0.1	0.2
166°	0.1	0.1	0.1	0.2	0.1	0.2
166.5°	0.1	0.1	0.1	0.2	0.1	0.2
167°	0.1	0.1	0.1	0.2	0.1	0.2
167.5°	0.1	0.1	0.1	0.2	0.1	0.2
168°	0.1	0.1	0.1	0.2	0.1	0.2
168.5°	0.1	0.1	0.1	0.2	0.1	0.2
169°	0.1	0.1	0.1	0.2	0.1	0.2
169.5°	0.1	0.1	0.1	0.2	0.1	0.2
170°	0.1	0.1	0.1	0.2	0.1	0.2
170.5°	0.1	0.1	0.1	0.2	0.1	0.2
171°	0.1	0.1	0.1	0.2	0.1	0.2
171.5°	0.1	0.1	0.1	0.2	0.1	0.2
172°	0.1	0.1	0.1	0.2	0.1	0.2
172.5°	0.1	0.1	0.1	0.2	0.1	0.2
173°	0.1	0.1	0.1	0.2	0.1	0.2
173.5°	0.1	0.1	0.1	0.2	0.1	0.2
174°	0.1	0.1	0.1	0.2	0.1	0.2
174.5°	0.1	0.1	0.1	0.2	0.1	0.2
175°	0.1	0.1	0.1	0.2	0.1	0.2
175.5°	0.1	0.1	0.1	0.2	0.1	0.2
176°	0.1	0.1	0.1	0.2	0.1	0.2
176.5°	0.1	0.1	0.1	0.2	0.1	0.2
177°	0.1	0.1	0.1	0.2	0.1	0.2
177.5°	0.1	0.1	0.1	0.2	0.1	0.2
178°	0.1	0.1	0.1	0.2	0.1	0.2
178.5°	0.1	0.1	0.1	0.2	0.1	0.2
179°	0.1	0.1	0.1	0.2	0.1	0.2
179.5°	0.1	0.1	0.1	0.2	0.1	0.2



TEST NUMBER: A1914114B001

CATALOG NUMBER:

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
180°	0.2	0.2	0.2	0.2	0.2	0.2

(END OF REPORT)