

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: A1914114C001

Luminaire Tested:

Test Date: 2019-08-26

**Test Information**

Test Method: LM-41-14  
Report Number: A1914114C001  
Test Lab: EVERFINE  
Test Date: 2019-08-26  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO  
Catalog Number:  
Description: DL-NJ31bA11ER1-4690 120V 10.5W 60HZ  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 798.8 lumens  
Efficiency: N/A  
Efficacy: 82.2 lumens/watt  
Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.37  
Luminous Opening: Point Source (0m x 0m x 0m)  
CIE Type: Direct

Input Watts (W): 9.71908  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: A1914114C001  
CATALOG NUMBER:

### Luminous Intensity Polar Plot





TEST NUMBER: A1914114C001

CATALOG NUMBER:

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	109	104	100	96	106	102	98	94	97	94	91	94	91	89	90	88	86
2	99	91	84	78	96	89	82	77	85	80	75	82	77	73	79	75	72
3	90	79	71	65	88	78	70	64	75	68	63	72	67	62	70	65	61
4	82	70	61	55	80	69	61	54	66	59	54	64	58	53	62	57	52
5	76	63	54	47	74	62	53	47	59	52	46	58	51	46	56	50	45
6	70	56	47	41	68	56	47	41	54	46	40	52	45	40	50	44	40
7	65	51	42	36	63	50	42	36	49	41	36	47	41	35	46	40	35
8	60	47	38	32	59	46	38	32	45	37	32	43	37	32	42	36	32
9	56	43	35	29	55	42	34	29	41	34	29	40	33	29	39	33	28
10	53	39	32	26	51	39	31	26	38	31	26	37	31	26	36	30	26

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	Luminaire represents a point source (luminous area is zero).			
5°	No luminance values can be calculated.			
10°				
15°				
20°				
25°				
30°				
35°				
40°				
45°				
50°				
55°				
60°				
65°				
70°				
75°				
80°				
85°				



TEST NUMBER: A1914114C001

CATALOG NUMBER:

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	26.5	3.3
10°-20°	75.8	9.5
20°-30°	114.8	14.4
30°-40°	138.5	17.3
40°-50°	144.2	18.1
50°-60°	131.0	16.4
60°-70°	99.8	12.5
70°-80°	55.6	7.0
80°-90°	12.4	1.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.1	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	217.0	27.2
0°-40°	355.5	44.5
0°-60°	630.7	79.0
0°-90°	798.6	100.0
90°-120°	0.0	0.0
90°-150°	0.1	0.0
90°-180°	0.0	0.0
0°-180°	798.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	282	282	282	282	282	
5°	279	278	281	276	279	27
15°	270	271	269	266	270	76
25°	249	252	250	246	249	115
35°	222	225	223	217	222	139
45°	187	192	188	182	187	144
55°	147	152	148	142	147	131
65°	100	107	102	95	100	99
75°	51	59	54	46	51	54
85°	8	15	11	5	8	11
90°	0	1	0	0	0	0
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0



TEST NUMBER: A1914114C001

CATALOG NUMBER:

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	281.9	281.9	281.9	281.9	281.9	281.9	281.9	281.9	281.9	281.9	281.9
0.5°	280.0	280.3	277.0	282.3	281.1	282.1	281.3	282.0	282.0	281.1	277.5
1°	279.2	280.4	278.4	281.0	279.3	280.7	281.3	281.1	281.4	280.3	278.2
1.5°	281.3	278.2	279.5	277.6	281.2	278.7	281.4	280.9	281.1	280.5	277.0
2°	280.6	280.1	278.9	279.8	280.9	282.1	281.1	281.1	279.7	279.7	277.3
2.5°	281.3	279.6	276.0	283.3	279.1	280.6	278.8	279.8	278.5	279.8	275.1
3°	281.3	278.9	276.2	281.2	279.5	280.7	278.6	281.0	281.2	280.5	275.4
3.5°	280.5	278.2	279.9	282.1	280.4	279.1	279.0	280.0	280.7	280.8	276.8
4°	279.9	279.5	278.6	284.3	279.9	278.6	277.7	279.7	280.4	279.4	275.4
4.5°	278.6	279.3	276.2	279.5	279.3	280.2	278.7	279.4	280.5	279.7	277.2
5°	278.8	278.8	276.4	279.9	278.5	279.8	278.1	278.3	280.7	278.5	276.0
5.5°	278.5	277.5	275.9	278.0	278.9	279.1	278.0	280.7	280.4	278.5	275.4
6°	279.5	278.1	275.7	279.8	280.3	279.2	278.5	279.9	280.8	277.8	275.2
6.5°	278.2	279.3	276.4	279.8	279.4	279.1	279.2	278.0	279.1	277.9	275.2
7°	277.5	278.8	275.5	279.4	277.5	279.0	278.4	278.0	278.1	277.7	274.8
7.5°	278.0	277.0	276.5	278.0	277.5	277.5	277.2	277.3	278.1	276.7	274.7
8°	277.1	277.5	276.1	278.0	278.2	276.6	277.0	277.2	278.0	276.1	274.0
8.5°	276.3	277.3	275.2	278.1	278.4	277.1	276.3	276.9	277.5	276.8	272.8
9°	276.0	277.6	274.8	278.2	276.5	276.9	275.9	277.0	276.4	276.7	272.2
9.5°	274.0	274.9	273.6	277.4	275.9	275.7	275.4	277.0	275.7	275.9	270.5
10°	273.8	274.7	273.3	277.5	275.6	275.2	276.3	275.1	275.6	276.4	270.0
10.5°	274.7	274.6	273.3	277.0	275.6	275.8	276.8	275.5	275.8	274.4	271.3
11°	274.7	274.6	271.6	276.5	275.3	275.8	275.6	275.9	275.5	274.7	271.1
11.5°	274.7	273.8	271.8	276.4	274.6	274.1	273.9	272.8	275.1	274.2	269.9
12°	272.5	273.2	271.8	274.1	274.2	272.7	273.3	274.6	273.6	271.5	268.1
12.5°	272.1	273.4	271.8	274.5	274.3	273.7	273.7	275.4	273.2	271.6	270.0
13°	271.9	272.5	270.4	274.0	274.1	273.5	272.6	271.2	274.1	270.6	268.6
13.5°	270.7	270.5	269.6	274.3	272.7	270.4	271.5	273.2	272.5	270.8	267.3
14°	270.3	270.0	269.3	272.6	271.8	270.2	271.4	272.9	270.7	270.5	267.6
14.5°	270.1	269.0	268.4	271.8	271.2	270.4	270.9	272.1	269.8	269.1	267.1
15°	269.6	269.0	268.3	269.3	270.6	269.2	269.7	270.1	269.1	267.3	266.2
15.5°	268.6	269.2	266.2	269.9	270.4	269.7	269.4	269.8	268.0	267.6	265.3
16°	268.2	267.2	266.1	270.1	269.1	268.5	269.2	270.1	267.9	266.7	263.5
16.5°	266.9	267.2	266.1	269.5	268.5	266.4	267.3	268.6	266.9	265.7	264.2
17°	265.7	267.1	265.6	268.5	267.8	267.2	267.6	267.6	266.1	265.1	262.7
17.5°	264.5	266.2	264.7	267.9	267.3	265.4	265.7	266.2	264.6	264.3	261.7
18°	263.4	264.7	264.2	267.3	265.9	265.0	265.1	264.3	263.2	264.1	260.6
18.5°	262.4	263.6	263.0	265.3	265.4	263.2	263.6	263.4	263.5	263.4	260.3
19°	262.2	262.2	261.1	266.2	264.8	263.0	264.4	263.5	262.5	261.0	256.0
19.5°	261.6	261.9	260.1	264.6	263.5	262.8	262.0	263.0	261.6	260.0	256.0
20°	260.1	260.7	258.6	263.3	262.8	261.0	261.8	262.3	261.3	259.6	255.6
20.5°	259.7	260.1	258.0	263.3	262.3	261.3	260.8	260.8	259.6	258.8	254.9
21°	259.0	258.3	256.7	261.5	260.6	259.3	260.3	258.9	258.5	258.1	255.3
21.5°	257.3	257.4	255.9	261.2	258.2	259.3	258.3	258.8	258.3	256.8	252.0
22°	256.2	256.7	255.3	258.7	258.0	258.5	257.2	258.3	256.9	255.5	252.8



TEST NUMBER: A1914114C001

CATALOG NUMBER:

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
22.5°	255.0	255.9	254.8	257.7	257.6	257.0	257.2	255.4	256.0	254.9	251.4
23°	253.8	255.5	253.7	257.8	256.3	256.1	256.3	255.5	254.5	252.0	249.1
23.5°	252.8	253.8	252.9	256.5	255.1	254.1	253.7	253.4	254.5	252.4	249.2
24°	251.8	252.6	251.8	256.6	253.9	253.8	254.6	253.4	252.0	251.3	247.7
24.5°	250.3	251.3	250.9	255.9	252.8	252.6	253.4	252.3	251.2	249.4	245.9
25°	248.8	248.2	249.3	253.5	252.0	251.9	252.2	251.0	250.3	248.0	245.0
25.5°	248.2	247.3	248.0	251.5	250.8	251.6	250.1	250.2	248.9	246.3	245.5
26°	246.8	247.2	247.1	251.1	250.3	249.3	248.7	248.8	247.8	245.4	242.1
26.5°	246.1	246.3	245.7	249.3	248.7	248.3	247.6	247.6	246.4	244.1	241.9
27°	244.6	245.3	244.5	248.5	247.4	246.6	246.6	246.4	246.1	242.9	240.8
27.5°	243.2	243.6	243.1	247.5	245.9	244.5	245.5	244.4	243.8	241.4	239.2
28°	241.5	242.9	241.8	246.6	245.0	244.3	244.7	244.0	242.9	240.3	237.6
28.5°	239.6	242.5	240.6	244.5	243.6	242.7	242.9	242.5	240.7	239.0	235.6
29°	238.3	240.7	239.1	242.8	242.4	240.9	241.2	240.4	240.3	237.6	234.6
29.5°	237.3	239.6	238.3	241.2	241.5	239.5	241.1	239.8	238.4	236.4	233.5
30°	236.1	238.8	237.2	240.6	239.7	238.0	238.9	239.1	237.4	234.8	231.7
30.5°	235.3	236.9	235.8	239.3	238.2	237.6	237.4	236.8	237.3	233.6	230.0
31°	234.2	235.3	234.1	237.6	236.6	235.8	236.5	235.6	233.6	231.8	228.8
31.5°	232.2	233.1	232.8	236.1	235.3	235.0	235.2	233.3	232.9	230.7	227.5
32°	230.8	231.9	231.3	234.4	234.0	233.7	233.9	231.4	231.1	229.3	225.5
32.5°	229.2	229.7	230.9	234.0	232.5	231.8	232.9	230.7	229.7	228.3	225.0
33°	227.6	228.8	228.4	232.9	231.1	230.9	230.5	229.3	228.4	226.3	224.1
33.5°	226.1	227.2	227.6	231.0	229.7	229.3	228.4	227.8	226.9	224.7	222.3
34°	224.4	225.8	225.2	229.7	228.1	228.2	226.9	226.3	225.9	223.4	220.3
34.5°	223.5	224.4	223.8	227.8	226.6	226.3	226.3	225.2	224.2	221.7	218.8
35°	221.7	223.1	222.3	226.5	225.0	224.8	224.6	223.6	223.0	220.3	217.0
35.5°	219.6	221.7	221.0	224.6	223.5	223.1	223.0	222.5	221.2	218.9	215.2
36°	218.5	219.9	219.5	222.9	222.2	221.7	222.0	220.9	219.5	217.2	213.4
36.5°	216.9	218.6	217.6	220.9	220.8	220.8	220.8	219.3	218.0	215.8	211.7
37°	215.3	216.8	216.0	219.4	219.4	219.2	219.0	217.8	216.3	214.2	209.7
37.5°	213.5	215.4	214.7	218.2	217.6	217.4	217.1	216.3	214.7	212.5	208.6
38°	211.4	213.6	213.0	216.8	215.9	216.3	215.7	214.7	212.9	210.8	207.3
38.5°	209.8	211.8	211.4	215.1	214.1	214.2	213.9	213.0	211.2	209.1	205.6
39°	208.1	210.3	209.7	213.2	212.6	212.0	212.0	211.2	209.7	207.4	204.0
39.5°	206.4	208.5	208.1	211.6	211.2	210.9	209.8	209.5	208.2	205.8	202.1
40°	204.8	207.1	206.3	209.8	209.4	209.2	208.7	207.7	206.5	204.2	200.6
40.5°	203.5	205.2	204.7	208.0	207.5	207.4	207.0	206.0	204.8	202.4	198.5
41°	201.7	203.5	203.0	206.4	205.8	205.8	204.9	204.2	202.9	200.8	196.9
41.5°	199.5	201.8	201.0	204.6	204.0	204.7	203.5	202.4	201.0	198.8	195.2
42°	197.9	199.8	199.1	202.5	202.3	202.1	201.8	200.8	199.3	197.0	193.0
42.5°	196.2	197.8	197.4	201.2	200.6	200.7	199.1	198.9	197.6	195.2	191.4
43°	194.4	195.9	195.5	199.3	199.0	198.8	198.0	197.2	196.0	193.5	189.6
43.5°	192.4	194.1	193.7	197.5	197.3	197.2	195.7	195.4	194.1	191.7	187.8
44°	190.7	192.1	192.1	195.9	195.4	195.4	194.0	193.6	192.2	189.8	186.0
44.5°	188.8	190.2	190.1	194.2	193.4	193.7	192.6	191.7	190.1	188.0	184.2



TEST NUMBER: A1914114C001

CATALOG NUMBER:

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
45°	186.8	188.4	188.5	192.5	191.6	191.4	190.7	189.9	188.4	186.0	182.4
45.5°	185.0	186.6	186.8	190.5	190.0	189.6	188.7	188.1	186.6	184.2	180.5
46°	183.2	184.6	185.0	188.6	188.3	187.5	187.0	186.2	184.7	182.2	178.6
46.5°	181.4	182.6	183.4	186.5	186.5	185.8	184.8	184.2	182.6	180.3	176.8
47°	179.0	180.6	181.3	184.6	184.6	184.4	183.5	182.3	180.7	178.3	175.1
47.5°	177.5	178.8	178.8	182.5	182.4	181.8	181.6	180.3	178.6	176.2	173.1
48°	175.7	176.9	177.3	180.8	180.4	179.6	179.2	178.3	176.6	174.3	170.9
48.5°	173.8	175.2	175.5	179.0	178.5	178.0	177.3	176.3	174.5	172.3	168.7
49°	171.2	173.3	173.6	177.2	176.4	176.1	175.5	174.3	172.4	170.3	166.6
49.5°	169.4	171.3	171.7	175.1	174.6	175.1	173.4	172.3	170.4	168.3	164.6
50°	167.4	169.4	169.9	173.1	172.6	172.3	171.4	170.3	168.5	166.1	162.7
50.5°	165.7	167.5	168.0	171.2	170.5	170.3	169.0	168.2	166.3	164.1	160.6
51°	163.6	165.3	165.8	169.1	168.4	168.1	167.0	166.1	164.3	162.0	158.6
51.5°	161.5	163.1	163.8	167.3	166.3	166.0	164.8	164.1	162.3	160.1	156.5
52°	159.3	161.2	161.7	165.0	164.3	164.2	162.8	162.1	160.5	157.9	154.4
52.5°	157.2	159.2	159.8	162.8	162.5	162.2	161.0	160.1	158.4	155.8	152.5
53°	155.3	157.3	157.6	160.8	160.5	159.9	159.0	158.1	156.2	153.8	150.4
53.5°	152.9	155.2	155.3	158.6	158.3	157.8	156.7	156.1	154.2	151.6	148.1
54°	151.0	153.1	153.4	156.6	156.1	155.8	154.8	154.2	152.0	149.3	145.9
54.5°	149.0	150.8	151.3	154.5	154.3	153.9	152.6	152.1	149.9	147.3	143.8
55°	146.9	148.6	149.1	152.3	152.2	151.8	150.6	149.8	147.7	145.0	141.6
55.5°	144.6	146.4	147.2	150.2	150.1	149.6	148.4	147.5	145.6	142.7	139.6
56°	142.3	144.0	145.1	148.2	147.9	147.3	146.5	145.4	143.2	140.7	137.4
56.5°	140.2	141.9	142.8	146.0	145.6	145.1	144.3	143.2	140.9	138.6	135.2
57°	137.8	139.5	140.8	143.9	143.4	143.0	142.1	141.0	138.9	136.5	133.0
57.5°	135.4	137.6	138.4	141.6	141.4	141.0	139.9	138.9	136.7	134.2	130.9
58°	133.3	135.5	136.2	139.3	139.1	138.8	137.6	136.7	134.5	131.8	128.6
58.5°	131.0	133.0	134.0	137.1	136.8	136.8	135.4	134.5	132.1	129.6	126.5
59°	128.7	130.5	131.7	135.0	134.5	134.6	133.3	132.2	130.0	127.4	124.3
59.5°	126.5	128.3	129.6	132.5	132.3	132.1	131.1	129.9	127.8	125.2	122.1
60°	124.0	126.1	127.4	130.0	130.0	129.9	128.9	127.6	125.8	122.9	119.9
60.5°	121.7	123.7	125.0	128.0	127.8	127.5	126.8	125.5	123.4	120.6	117.6
61°	119.5	121.6	122.6	125.5	125.7	125.2	124.6	123.0	121.2	118.5	115.3
61.5°	117.0	119.3	120.3	123.1	123.4	122.9	122.2	120.9	118.9	116.1	113.0
62°	114.8	117.1	118.0	120.9	121.0	120.9	120.2	118.6	116.4	113.9	110.8
62.5°	112.3	114.6	115.5	118.6	118.8	118.8	117.9	116.3	114.1	111.5	108.5
63°	110.0	112.1	113.3	116.3	116.5	116.6	115.5	114.1	111.9	109.1	106.1
63.5°	107.5	109.7	111.0	113.9	114.2	114.4	113.3	111.8	109.6	106.7	103.7
64°	105.2	107.3	108.7	111.5	112.0	112.0	110.9	109.4	107.2	104.5	101.2
64.5°	102.6	105.0	106.3	109.3	109.7	109.5	108.5	107.1	104.8	102.1	98.9
65°	100.2	102.5	104.1	106.9	107.3	107.1	106.1	104.6	102.1	99.9	96.4
65.5°	97.8	100.1	101.1	104.6	104.9	104.7	103.7	102.2	100.0	97.3	94.0
66°	95.3	97.5	98.9	102.1	102.5	102.4	101.4	99.8	97.7	94.9	91.4
66.5°	92.8	95.2	96.5	99.5	100.1	100.0	99.1	97.5	95.3	92.5	89.2
67°	90.6	92.8	94.4	96.8	97.7	97.7	96.8	95.2	93.0	90.1	87.0





TEST NUMBER: A1914114C001

CATALOG NUMBER:

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
67.5°	88.2	90.2	91.8	94.7	95.4	95.2	94.4	92.7	90.6	88.0	84.6
68°	85.8	87.9	89.5	92.2	92.9	92.8	92.1	90.4	88.3	85.5	82.3
68.5°	83.4	85.6	87.1	89.8	90.6	90.5	89.6	88.0	85.9	83.1	79.9
69°	80.8	83.2	84.7	87.3	88.3	88.1	87.5	85.7	83.5	80.8	77.6
69.5°	78.4	80.7	82.2	85.1	85.9	85.7	85.0	83.2	81.0	78.3	75.2
70°	76.0	78.2	79.9	82.6	83.5	83.3	82.5	80.8	78.6	76.1	72.8
70.5°	73.2	75.8	77.4	80.2	81.1	80.9	80.0	78.5	76.2	73.8	70.4
71°	70.8	73.4	75.1	77.7	78.6	78.5	77.6	76.1	73.7	71.3	68.0
71.5°	68.3	70.9	72.5	75.2	76.3	76.0	75.2	73.8	71.3	68.8	65.8
72°	65.9	68.4	70.0	72.6	74.0	73.6	72.8	71.4	68.8	66.3	63.3
72.5°	63.3	65.9	67.5	70.2	71.6	71.3	70.4	68.9	66.4	63.8	60.9
73°	60.9	63.3	65.1	67.8	69.1	68.8	68.0	66.5	63.9	61.4	58.5
73.5°	58.4	61.0	62.6	65.2	66.7	66.4	65.6	64.1	61.6	58.9	56.0
74°	55.9	58.4	60.3	62.8	64.4	64.1	63.3	61.6	59.3	56.6	53.8
74.5°	53.5	55.9	57.7	60.1	61.9	61.6	60.8	59.0	56.8	54.2	51.3
75°	51.0	53.5	55.4	57.8	59.4	59.2	58.4	56.8	54.5	51.8	49.0
75.5°	48.6	51.2	53.1	55.5	57.0	56.8	56.0	54.6	52.2	49.3	46.7
76°	46.2	48.6	50.6	52.8	54.7	54.5	53.6	52.1	49.8	47.0	44.3
76.5°	43.7	46.2	48.1	50.4	52.3	52.2	51.2	49.6	47.3	44.7	41.9
77°	41.4	43.7	45.7	47.9	49.9	49.8	48.8	47.3	44.9	42.4	39.7
77.5°	38.8	41.5	43.4	45.5	47.5	47.5	46.4	44.9	42.6	40.1	37.4
78°	36.6	39.1	41.0	43.1	45.2	45.1	44.1	42.6	40.2	37.7	35.3
78.5°	34.2	36.7	38.5	40.7	42.8	42.8	41.8	40.2	38.0	35.5	32.9
79°	32.0	34.3	36.2	38.4	40.4	40.5	39.4	37.8	35.7	33.2	30.7
79.5°	29.7	32.0	34.0	36.0	38.2	38.1	37.2	35.6	33.4	30.9	28.4
80°	27.4	29.7	31.6	33.7	36.0	35.8	34.9	33.3	31.1	28.8	26.3
80.5°	25.2	27.5	29.5	31.3	33.6	33.7	32.7	31.1	28.9	26.5	24.1
81°	23.0	25.3	27.3	29.2	31.4	31.5	30.4	28.9	26.8	24.4	22.1
81.5°	21.1	23.2	25.1	26.9	29.2	29.2	28.3	26.5	24.6	22.4	20.2
82°	19.1	21.1	23.0	24.8	26.9	26.9	26.1	24.5	22.4	20.4	18.2
82.5°	17.0	19.2	20.9	22.5	24.9	24.8	23.9	22.4	20.5	18.4	16.3
83°	15.2	17.1	19.0	20.6	22.7	22.7	21.8	20.6	18.6	16.4	14.4
83.5°	13.3	15.2	16.9	18.6	20.8	20.8	19.9	18.5	16.6	14.5	12.5
84°	11.5	13.3	15.1	16.7	18.8	18.7	17.9	16.5	14.6	12.6	10.9
84.5°	9.8	11.6	13.2	14.8	16.8	16.8	16.0	14.6	12.8	11.0	9.2
85°	8.3	10.0	11.5	13.0	15.0	14.9	14.3	12.8	11.1	9.2	7.7
85.5°	6.8	8.3	9.9	11.2	13.1	13.0	12.3	11.1	9.4	7.8	6.1
86°	5.4	6.8	8.2	9.5	11.3	11.3	10.6	9.3	7.9	6.1	4.8
86.5°	4.1	5.5	6.8	7.9	9.7	9.6	9.0	7.8	6.2	4.8	3.6
87°	3.0	4.3	5.4	6.7	8.1	8.1	7.4	6.2	4.9	3.7	2.4
87.5°	2.0	3.1	4.2	5.1	6.6	6.5	6.0	4.9	3.8	2.4	1.5
88°	1.2	2.1	3.1	4.0	5.2	5.1	4.6	3.8	2.6	1.3	0.7
88.5°	0.6	1.3	2.0	2.9	3.9	3.9	3.4	2.5	1.5	0.6	0.0
89°	0.1	0.6	1.3	1.9	2.8	2.8	2.2	1.4	0.6	0.0	0.0
89.5°	0.0	0.2	0.6	1.1	1.7	1.8	1.2	0.6	0.0	0.0	0.0



TEST NUMBER: A1914114C001

CATALOG NUMBER:

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
90°	0.0	0.0	0.2	0.6	0.8	0.8	0.4	0.0	0.0	0.0	0.0
90.5°	0.0	0.0	0.0	0.2	0.1	0.1	0.1	0.0	0.0	0.0	0.0
91°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
91.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
93°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
93.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
94°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
94.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
96°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
96.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
101°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
101.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
103°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
103.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
104°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
104.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
106°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
106.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
108°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
108.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
109°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
109.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
111°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
111.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
112°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1914114C001

CATALOG NUMBER:

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
113°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
113.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
114°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
114.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
116°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
116.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
118°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
118.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
119°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
119.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
121°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
121.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
123°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
123.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
124°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
124.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
126°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
126.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
128°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
128.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
129°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
129.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
131°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
131.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
133°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
133.5°	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
134°	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
134.5°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1914114C001

CATALOG NUMBER:

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
135°	0.1	0.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135.5°	0.1	0.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
136°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
136.5°	0.1	0.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137°	0.1	0.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.1	0.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
138°	0.2	0.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
138.5°	0.1	0.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
139°	0.1	0.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
139.5°	0.1	0.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.3	0.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140.5°	0.3	0.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
141°	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
141.5°	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142°	0.2	0.2	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
143°	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
143.5°	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
144°	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
144.5°	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145.5°	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
146°	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
146.5°	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147°	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0
148°	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.1	0.1	0.0	0.0
148.5°	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.1	0.1	0.0	0.0
149°	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0
149.5°	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.1	0.1	0.0	0.0
150°	0.2	0.2	0.1	0.0	0.0	0.1	0.0	0.1	0.1	0.0	0.0
150.5°	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.0
151°	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1
151.5°	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1
152°	0.2	0.2	0.1	0.0	0.0	0.1	0.0	0.1	0.1	0.0	0.0
152.5°	0.2	0.2	0.1	0.0	0.0	0.1	0.0	0.2	0.2	0.1	0.0
153°	0.2	0.2	0.2	0.0	0.0	0.1	0.0	0.2	0.1	0.1	0.0
153.5°	0.2	0.2	0.2	0.0	0.1	0.1	0.0	0.1	0.1	0.1	0.1
154°	0.2	0.2	0.1	0.0	0.1	0.1	0.1	0.1	0.2	0.1	0.1
154.5°	0.2	0.2	0.1	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1
155°	0.2	0.2	0.1	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1
155.5°	0.2	0.2	0.1	0.0	0.0	0.1	0.1	0.2	0.2	0.2	0.1
156°	0.2	0.2	0.1	0.0	0.1	0.1	0.1	0.2	0.3	0.2	0.2
156.5°	0.2	0.2	0.1	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.2
157°	0.2	0.2	0.1	0.0	0.1	0.1	0.1	0.2	0.2	0.1	0.2



TEST NUMBER: A1914114C001

CATALOG NUMBER:

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
157.5°	0.2	0.2	0.1	0.0	0.1	0.1	0.1	0.2	0.2	0.3	0.3
158°	0.2	0.2	0.1	0.0	0.1	0.1	0.1	0.2	0.2	0.3	0.3
158.5°	0.2	0.2	0.1	0.0	0.1	0.1	0.1	0.2	0.2	0.2	0.2
159°	0.2	0.2	0.1	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.2
159.5°	0.2	0.2	0.1	0.0	0.1	0.3	0.2	0.2	0.2	0.2	0.2
160°	0.2	0.2	0.1	0.0	0.1	0.2	0.2	0.2	0.2	0.2	0.2
160.5°	0.2	0.2	0.1	0.0	0.1	0.2	0.2	0.2	0.2	0.2	0.2
161°	0.2	0.2	0.1	0.0	0.1	0.3	0.2	0.2	0.2	0.2	0.2
161.5°	0.2	0.2	0.1	0.0	0.1	0.3	0.2	0.2	0.2	0.2	0.2
162°	0.2	0.2	0.1	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.2
162.5°	0.2	0.2	0.1	0.0	0.1	0.2	0.2	0.2	0.2	0.2	0.2
163°	0.2	0.2	0.1	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.2
163.5°	0.2	0.2	0.1	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.2
164°	0.2	0.2	0.1	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.2
164.5°	0.2	0.2	0.1	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.2
165°	0.2	0.2	0.1	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.2
165.5°	0.2	0.2	0.1	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.2
166°	0.2	0.2	0.1	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.2
166.5°	0.2	0.2	0.1	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.2
167°	0.2	0.2	0.1	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.2
167.5°	0.2	0.2	0.1	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.2
168°	0.2	0.2	0.1	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.2
168.5°	0.2	0.2	0.1	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.2
169°	0.2	0.2	0.1	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.2
169.5°	0.2	0.2	0.1	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.2
170°	0.2	0.2	0.1	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.2
170.5°	0.2	0.2	0.1	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.2
171°	0.2	0.2	0.1	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.2
171.5°	0.2	0.2	0.1	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.2
172°	0.2	0.2	0.1	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.2
172.5°	0.2	0.2	0.1	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.2
173°	0.2	0.2	0.1	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.2
173.5°	0.2	0.2	0.1	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.2
174°	0.2	0.2	0.1	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.2
174.5°	0.2	0.2	0.1	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.2
175°	0.2	0.2	0.1	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.2
175.5°	0.2	0.2	0.1	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.2
176°	0.2	0.2	0.1	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.2
176.5°	0.2	0.2	0.1	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.2
177°	0.2	0.2	0.1	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.2
177.5°	0.2	0.2	0.1	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.2
178°	0.2	0.2	0.1	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.2
178.5°	0.2	0.2	0.1	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.2
179°	0.2	0.2	0.1	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.2
179.5°	0.2	0.2	0.1	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.2



TEST NUMBER: A1914114C001

CATALOG NUMBER:

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
180°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2



TEST NUMBER: A1914114C001

CATALOG NUMBER:

**CANDELA DISTRIBUTION (continued):**

	247.5°	270°	292.5°	315°	337.5°	360°
0°	281.9	281.9	281.9	281.9	281.9	281.9
0.5°	279.7	279.8	278.7	278.8	281.5	280.0
1°	280.3	279.8	280.4	280.2	281.2	279.2
1.5°	279.6	279.8	281.0	279.2	281.0	281.3
2°	281.4	279.2	278.2	279.6	280.4	280.6
2.5°	281.4	277.4	278.2	279.3	279.3	281.3
3°	282.6	278.7	278.2	279.4	279.9	281.3
3.5°	280.7	278.7	278.2	279.3	280.0	280.5
4°	280.9	278.0	277.7	279.2	279.0	279.9
4.5°	278.9	278.1	276.2	277.7	278.4	278.6
5°	279.3	276.1	277.0	278.4	278.9	278.8
5.5°	279.3	276.2	277.9	278.7	277.3	278.5
6°	279.3	277.2	278.0	276.3	277.2	279.5
6.5°	279.0	277.5	277.7	276.2	279.5	278.2
7°	277.0	277.3	274.3	276.6	277.0	277.5
7.5°	277.8	276.8	274.6	275.6	276.8	278.0
8°	277.1	275.4	274.7	275.4	278.6	277.1
8.5°	277.3	274.9	273.8	274.8	276.3	276.3
9°	275.6	274.9	273.9	275.1	276.3	276.0
9.5°	275.3	274.4	272.4	273.8	274.2	274.0
10°	274.9	272.6	272.9	272.8	274.4	273.8
10.5°	274.8	273.3	273.9	271.5	273.7	274.7
11°	272.8	271.3	272.6	270.7	274.6	274.7
11.5°	273.0	271.2	271.3	272.1	272.9	274.7
12°	273.4	271.1	270.3	272.3	271.9	272.5
12.5°	272.0	270.2	269.3	270.6	271.6	272.1
13°	270.6	270.1	267.8	269.3	271.1	271.9
13.5°	269.3	268.7	267.8	267.5	270.7	270.7
14°	268.9	268.2	268.1	267.6	270.2	270.3
14.5°	268.5	267.7	268.2	267.7	269.4	270.1
15°	267.0	266.3	265.6	266.0	267.5	269.6
15.5°	265.2	265.7	264.4	265.6	266.3	268.6
16°	265.2	264.1	263.4	264.0	266.3	268.2
16.5°	265.2	264.8	263.6	264.2	265.8	266.9
17°	262.7	262.4	262.5	262.1	264.5	265.7
17.5°	262.3	261.4	261.2	262.0	263.4	264.5
18°	261.3	261.2	258.6	261.1	262.4	263.4
18.5°	260.8	260.6	259.1	260.6	261.5	262.4
19°	260.1	259.8	259.0	260.0	262.1	262.2
19.5°	259.4	259.0	259.0	259.2	260.6	261.6
20°	259.0	258.6	255.6	258.2	259.4	260.1
20.5°	257.2	256.7	255.2	257.1	257.4	259.7
21°	256.1	256.6	254.5	254.6	257.2	259.0
21.5°	254.7	254.7	254.3	253.4	255.6	257.3
22°	253.5	252.9	252.6	253.2	254.8	256.2



TEST NUMBER: A1914114C001

CATALOG NUMBER:

**CANDELA DISTRIBUTION (continued):**

	247.5°	270°	292.5°	315°	337.5°	360°
22.5°	253.2	251.4	250.8	252.3	253.4	255.0
23°	251.0	250.0	250.7	251.4	253.1	253.8
23.5°	250.0	249.2	249.4	250.1	251.9	252.8
24°	248.9	248.9	248.6	248.6	250.7	251.8
24.5°	249.1	247.2	245.9	248.1	248.9	250.3
25°	246.6	246.1	245.4	246.4	248.1	248.8
25.5°	246.0	244.9	245.3	245.3	248.1	248.2
26°	244.3	243.3	243.4	244.2	245.3	246.8
26.5°	243.0	242.5	240.9	243.4	244.0	246.1
27°	242.2	240.5	239.2	241.1	243.8	244.6
27.5°	240.5	239.9	238.8	239.8	242.1	243.2
28°	238.1	237.9	238.5	238.6	241.0	241.5
28.5°	237.6	236.1	237.6	237.1	238.9	239.6
29°	236.0	236.2	236.0	235.8	237.5	238.3
29.5°	235.3	235.4	234.6	234.9	235.9	237.3
30°	233.6	233.3	232.8	233.3	234.6	236.1
30.5°	232.7	232.2	230.9	232.2	233.7	235.3
31°	230.6	230.5	229.9	230.3	232.6	234.2
31.5°	229.6	228.7	227.8	229.1	231.7	232.2
32°	227.5	226.3	227.2	226.8	229.3	230.8
32.5°	225.5	225.0	224.6	225.0	227.8	229.2
33°	224.5	223.9	224.0	224.3	225.8	227.6
33.5°	222.2	223.6	223.0	223.1	224.2	226.1
34°	220.6	221.5	220.8	221.6	223.3	224.4
34.5°	219.0	219.2	218.8	220.0	221.3	223.5
35°	217.4	217.4	217.7	217.9	219.7	221.7
35.5°	217.4	216.1	216.3	216.4	218.2	219.6
36°	216.1	214.5	214.5	214.8	216.9	218.5
36.5°	212.3	213.3	212.9	213.1	215.2	216.9
37°	211.5	210.6	211.4	211.4	213.2	215.3
37.5°	210.2	209.7	209.4	209.9	211.7	213.5
38°	208.1	208.3	207.2	208.0	209.9	211.4
38.5°	206.9	206.3	205.4	206.6	207.9	209.8
39°	204.9	204.1	203.5	205.2	206.3	208.1
39.5°	203.2	202.3	202.6	203.1	205.1	206.4
40°	201.8	201.0	201.1	201.7	203.4	204.8
40.5°	199.8	198.7	199.3	199.1	201.8	203.5
41°	197.7	197.4	197.3	197.5	199.7	201.7
41.5°	195.8	195.5	195.8	195.8	198.1	199.5
42°	194.4	193.9	193.9	193.9	196.2	197.9
42.5°	193.0	192.1	191.8	192.0	194.5	196.2
43°	190.3	190.4	189.5	190.2	192.6	194.4
43.5°	189.0	188.8	187.8	188.1	190.9	192.4
44°	187.1	186.1	185.5	186.3	189.0	190.7
44.5°	184.8	184.3	184.2	184.4	187.1	188.8





TEST NUMBER: A1914114C001

CATALOG NUMBER:

**CANDELA DISTRIBUTION (continued):**

	247.5°	270°	292.5°	315°	337.5°	360°
45°	183.3	182.5	182.1	182.8	185.1	186.8
45.5°	181.3	180.5	179.8	181.2	183.1	185.0
46°	179.5	178.6	178.0	179.4	181.2	183.2
46.5°	177.8	176.6	176.0	177.4	179.3	181.4
47°	175.6	174.6	174.8	175.6	177.2	179.0
47.5°	173.2	172.8	172.8	173.5	175.2	177.5
48°	171.1	170.8	170.8	171.4	173.1	175.7
48.5°	169.3	168.9	168.4	169.4	171.2	173.8
49°	167.1	166.8	166.4	167.4	169.3	171.2
49.5°	164.9	164.9	164.4	165.2	167.2	169.4
50°	163.1	162.8	162.7	163.4	165.3	167.4
50.5°	161.0	160.7	160.5	161.1	163.3	165.7
51°	159.1	158.7	158.2	158.9	161.2	163.6
51.5°	156.8	156.7	156.2	157.1	159.3	161.5
52°	154.5	154.7	153.8	155.0	157.2	159.3
52.5°	152.9	152.7	152.2	152.9	155.4	157.2
53°	150.3	150.2	150.1	150.8	153.2	155.3
53.5°	148.4	148.0	148.3	148.7	150.9	152.9
54°	146.3	145.9	146.0	146.6	148.6	151.0
54.5°	144.2	143.9	143.6	144.4	146.4	149.0
55°	141.8	141.8	141.3	142.3	144.2	146.9
55.5°	139.8	139.4	139.0	140.2	142.3	144.6
56°	137.5	137.2	136.8	138.0	140.0	142.3
56.5°	135.0	134.8	134.9	135.8	138.0	140.2
57°	132.9	132.5	132.4	133.5	135.6	137.8
57.5°	130.7	130.2	130.2	131.1	133.2	135.4
58°	128.3	127.9	128.0	128.7	130.9	133.3
58.5°	126.2	125.5	125.1	126.6	128.6	131.0
59°	123.9	123.2	123.1	124.4	126.3	128.7
59.5°	121.6	121.2	121.2	121.9	123.8	126.5
60°	119.1	119.0	118.4	119.4	121.6	124.0
60.5°	116.6	116.6	116.2	117.0	119.0	121.7
61°	114.2	114.1	113.7	114.3	116.9	119.5
61.5°	112.0	111.7	111.5	112.2	114.7	117.0
62°	109.8	109.3	109.1	110.0	112.4	114.8
62.5°	107.6	106.6	106.7	107.6	110.0	112.3
63°	105.2	104.1	104.2	105.4	107.6	110.0
63.5°	102.9	102.0	101.6	102.7	105.3	107.5
64°	100.6	99.6	99.4	100.3	102.7	105.2
64.5°	98.0	97.2	97.0	97.9	100.2	102.6
65°	95.8	94.7	94.5	95.4	97.6	100.2
65.5°	93.5	92.4	92.2	93.1	95.0	97.8
66°	91.0	89.8	89.6	90.7	92.7	95.3
66.5°	88.6	87.6	87.3	88.2	90.2	92.8
67°	86.5	85.0	84.9	86.0	88.0	90.6



TEST NUMBER: A1914114C001

CATALOG NUMBER:

**CANDELA DISTRIBUTION (continued):**

	247.5°	270°	292.5°	315°	337.5°	360°
67.5°	84.0	82.6	82.6	83.3	85.7	88.2
68°	81.4	80.0	80.1	80.9	83.2	85.8
68.5°	79.0	77.6	77.5	78.4	80.6	83.4
69°	76.6	75.2	75.2	76.2	78.2	80.8
69.5°	74.2	72.7	72.5	73.5	76.0	78.4
70°	71.8	70.2	70.0	71.2	73.4	76.0
70.5°	69.4	67.8	67.6	68.7	70.8	73.2
71°	66.9	65.3	65.1	66.4	68.3	70.8
71.5°	64.5	62.9	62.8	63.9	65.8	68.3
72°	62.0	60.3	60.1	61.3	63.4	65.9
72.5°	59.7	57.9	57.8	59.0	60.9	63.3
73°	57.3	55.5	55.2	56.3	58.5	60.9
73.5°	54.9	53.0	52.9	54.0	55.9	58.4
74°	52.5	50.6	50.5	51.6	53.5	55.9
74.5°	50.0	48.0	48.0	49.1	51.1	53.5
75°	47.7	45.6	45.7	46.6	48.5	51.0
75.5°	45.4	43.2	43.1	44.3	46.1	48.6
76°	43.0	40.8	40.7	41.8	43.7	46.2
76.5°	40.6	38.5	38.4	39.4	41.3	43.7
77°	38.4	36.0	36.1	37.0	38.9	41.4
77.5°	36.0	33.8	33.7	34.7	36.5	38.8
78°	33.7	31.6	31.3	32.5	34.3	36.6
78.5°	31.5	29.2	29.2	30.1	32.0	34.2
79°	29.4	26.9	26.9	27.8	29.6	32.0
79.5°	27.1	24.7	24.8	25.7	27.4	29.7
80°	25.0	22.7	22.6	23.6	25.2	27.4
80.5°	22.9	20.7	20.7	21.6	23.0	25.2
81°	21.0	18.7	18.7	19.6	21.1	23.0
81.5°	19.0	16.8	16.7	17.6	19.1	21.1
82°	16.9	14.9	14.9	15.6	17.1	19.1
82.5°	15.2	13.0	13.1	13.7	15.3	17.0
83°	13.3	11.3	11.2	12.0	13.3	15.2
83.5°	11.5	9.6	9.5	10.2	11.5	13.3
84°	9.8	8.0	8.0	8.8	9.9	11.5
84.5°	8.1	6.6	6.7	7.1	8.3	9.8
85°	6.6	5.2	5.2	5.8	6.8	8.3
85.5°	5.2	4.0	4.0	4.6	5.4	6.8
86°	3.9	2.9	2.9	3.3	4.2	5.4
86.5°	2.7	2.0	1.8	2.4	3.0	4.1
87°	1.8	1.2	1.2	1.5	2.0	3.0
87.5°	0.7	0.6	0.6	0.8	1.2	2.0
88°	0.1	0.3	0.2	0.4	0.6	1.2
88.5°	0.0	0.0	0.0	0.0	0.2	0.6
89°	0.0	0.0	0.0	0.0	0.0	0.1
89.5°	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1914114C001

CATALOG NUMBER:

**CANDELA DISTRIBUTION (continued):**

	247.5°	270°	292.5°	315°	337.5°	360°
90°	0.0	0.0	0.0	0.0	0.0	0.0
90.5°	0.0	0.0	0.0	0.0	0.0	0.0
91°	0.0	0.0	0.0	0.0	0.0	0.0
91.5°	0.0	0.0	0.0	0.0	0.0	0.0
92°	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0
93°	0.0	0.0	0.0	0.0	0.0	0.0
93.5°	0.0	0.0	0.0	0.0	0.0	0.0
94°	0.0	0.0	0.0	0.0	0.0	0.0
94.5°	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0
95.5°	0.0	0.0	0.0	0.0	0.0	0.0
96°	0.0	0.0	0.0	0.0	0.0	0.0
96.5°	0.0	0.0	0.0	0.0	0.0	0.0
97°	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0
98°	0.0	0.0	0.0	0.0	0.0	0.0
98.5°	0.0	0.0	0.0	0.0	0.0	0.0
99°	0.0	0.0	0.0	0.0	0.0	0.0
99.5°	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0
100.5°	0.0	0.0	0.0	0.0	0.0	0.0
101°	0.0	0.0	0.0	0.0	0.0	0.0
101.5°	0.0	0.0	0.0	0.0	0.0	0.0
102°	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0
103°	0.0	0.0	0.0	0.0	0.0	0.0
103.5°	0.0	0.0	0.0	0.0	0.0	0.0
104°	0.0	0.0	0.0	0.0	0.0	0.0
104.5°	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0
105.5°	0.0	0.0	0.0	0.0	0.0	0.0
106°	0.0	0.0	0.0	0.0	0.0	0.0
106.5°	0.0	0.0	0.0	0.0	0.0	0.0
107°	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0
108°	0.0	0.0	0.0	0.0	0.0	0.0
108.5°	0.0	0.0	0.0	0.0	0.0	0.0
109°	0.0	0.0	0.0	0.0	0.0	0.0
109.5°	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0
110.5°	0.0	0.0	0.0	0.0	0.0	0.0
111°	0.0	0.0	0.0	0.0	0.0	0.0
111.5°	0.0	0.0	0.0	0.0	0.0	0.0
112°	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1914114C001

CATALOG NUMBER:

**CANDELA DISTRIBUTION (continued):**

	247.5°	270°	292.5°	315°	337.5°	360°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0
113°	0.0	0.0	0.0	0.0	0.0	0.0
113.5°	0.0	0.0	0.0	0.0	0.0	0.0
114°	0.0	0.0	0.0	0.0	0.0	0.0
114.5°	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0
115.5°	0.0	0.0	0.0	0.0	0.0	0.0
116°	0.0	0.0	0.0	0.0	0.0	0.0
116.5°	0.0	0.0	0.0	0.0	0.0	0.0
117°	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0
118°	0.0	0.0	0.0	0.0	0.0	0.0
118.5°	0.0	0.0	0.0	0.0	0.0	0.0
119°	0.0	0.0	0.0	0.0	0.0	0.0
119.5°	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0
120.5°	0.0	0.0	0.0	0.0	0.0	0.0
121°	0.0	0.0	0.0	0.0	0.0	0.0
121.5°	0.0	0.0	0.0	0.0	0.0	0.0
122°	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0
123°	0.0	0.0	0.0	0.0	0.0	0.0
123.5°	0.0	0.0	0.0	0.0	0.0	0.0
124°	0.0	0.0	0.0	0.0	0.0	0.0
124.5°	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.1	0.0	0.0	0.0	0.0
125.5°	0.0	0.0	0.0	0.0	0.0	0.0
126°	0.0	0.1	0.0	0.0	0.0	0.0
126.5°	0.0	0.0	0.0	0.0	0.0	0.0
127°	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.1	0.0	0.0	0.0	0.0
128°	0.0	0.1	0.0	0.0	0.0	0.0
128.5°	0.0	0.1	0.0	0.0	0.0	0.0
129°	0.0	0.1	0.0	0.0	0.0	0.0
129.5°	0.0	0.1	0.0	0.1	0.0	0.0
130°	0.0	0.1	0.0	0.1	0.0	0.0
130.5°	0.0	0.1	0.0	0.1	0.0	0.0
131°	0.0	0.1	0.0	0.1	0.0	0.0
131.5°	0.0	0.1	0.0	0.1	0.0	0.0
132°	0.0	0.2	0.0	0.1	0.1	0.0
132.5°	0.0	0.1	0.1	0.1	0.1	0.0
133°	0.0	0.1	0.0	0.0	0.1	0.1
133.5°	0.0	0.1	0.0	0.1	0.1	0.0
134°	0.0	0.2	0.1	0.1	0.1	0.0
134.5°	0.0	0.2	0.1	0.1	0.1	0.1



TEST NUMBER: A1914114C001

CATALOG NUMBER:

**CANDELA DISTRIBUTION (continued):**

	247.5°	270°	292.5°	315°	337.5°	360°
135°	0.0	0.1	0.1	0.1	0.1	0.1
135.5°	0.0	0.1	0.1	0.1	0.2	0.1
136°	0.0	0.2	0.1	0.1	0.1	0.1
136.5°	0.0	0.1	0.2	0.1	0.1	0.1
137°	0.0	0.1	0.1	0.1	0.2	0.1
137.5°	0.0	0.1	0.1	0.1	0.1	0.1
138°	0.0	0.2	0.1	0.1	0.1	0.2
138.5°	0.0	0.2	0.1	0.1	0.2	0.1
139°	0.0	0.1	0.1	0.1	0.2	0.1
139.5°	0.0	0.1	0.1	0.1	0.1	0.1
140°	0.0	0.1	0.1	0.1	0.2	0.3
140.5°	0.0	0.1	0.1	0.1	0.1	0.3
141°	0.0	0.1	0.2	0.1	0.1	0.2
141.5°	0.0	0.1	0.1	0.1	0.2	0.2
142°	0.0	0.1	0.1	0.1	0.2	0.2
142.5°	0.0	0.1	0.2	0.1	0.1	0.2
143°	0.0	0.1	0.1	0.1	0.1	0.2
143.5°	0.0	0.1	0.1	0.1	0.1	0.2
144°	0.0	0.1	0.2	0.1	0.1	0.2
144.5°	0.0	0.1	0.3	0.1	0.2	0.2
145°	0.0	0.1	0.2	0.1	0.1	0.2
145.5°	0.0	0.1	0.2	0.1	0.1	0.2
146°	0.0	0.1	0.2	0.2	0.3	0.2
146.5°	0.0	0.1	0.2	0.2	0.3	0.2
147°	0.0	0.1	0.2	0.2	0.2	0.2
147.5°	0.0	0.1	0.2	0.2	0.2	0.2
148°	0.0	0.1	0.2	0.2	0.2	0.2
148.5°	0.0	0.1	0.2	0.2	0.2	0.2
149°	0.0	0.1	0.2	0.2	0.2	0.2
149.5°	0.0	0.1	0.2	0.2	0.2	0.2
150°	0.1	0.1	0.2	0.2	0.2	0.2
150.5°	0.0	0.1	0.2	0.2	0.2	0.2
151°	0.0	0.1	0.2	0.2	0.2	0.2
151.5°	0.0	0.1	0.2	0.2	0.2	0.2
152°	0.0	0.1	0.2	0.2	0.2	0.2
152.5°	0.0	0.1	0.2	0.2	0.2	0.2
153°	0.0	0.1	0.2	0.2	0.2	0.2
153.5°	0.1	0.1	0.2	0.2	0.2	0.2
154°	0.1	0.1	0.2	0.2	0.2	0.2
154.5°	0.1	0.1	0.2	0.2	0.2	0.2
155°	0.1	0.1	0.2	0.2	0.2	0.2
155.5°	0.1	0.1	0.2	0.2	0.2	0.2
156°	0.2	0.1	0.2	0.2	0.2	0.2
156.5°	0.2	0.1	0.2	0.2	0.2	0.2
157°	0.1	0.1	0.2	0.2	0.2	0.2



TEST NUMBER: A1914114C001

CATALOG NUMBER:

**CANDELA DISTRIBUTION (continued):**

	247.5°	270°	292.5°	315°	337.5°	360°
157.5°	0.1	0.1	0.2	0.2	0.2	0.2
158°	0.1	0.1	0.2	0.2	0.2	0.2
158.5°	0.1	0.1	0.2	0.2	0.2	0.2
159°	0.1	0.1	0.2	0.2	0.2	0.2
159.5°	0.1	0.1	0.2	0.2	0.2	0.2
160°	0.1	0.1	0.2	0.2	0.2	0.2
160.5°	0.1	0.1	0.2	0.2	0.2	0.2
161°	0.1	0.1	0.2	0.2	0.2	0.2
161.5°	0.1	0.1	0.2	0.2	0.2	0.2
162°	0.1	0.1	0.2	0.2	0.2	0.2
162.5°	0.1	0.1	0.2	0.2	0.2	0.2
163°	0.1	0.1	0.2	0.2	0.2	0.2
163.5°	0.1	0.1	0.2	0.2	0.2	0.2
164°	0.1	0.1	0.2	0.2	0.2	0.2
164.5°	0.1	0.1	0.2	0.2	0.2	0.2
165°	0.1	0.1	0.2	0.2	0.2	0.2
165.5°	0.1	0.1	0.2	0.2	0.2	0.2
166°	0.1	0.1	0.2	0.2	0.2	0.2
166.5°	0.1	0.1	0.2	0.2	0.2	0.2
167°	0.1	0.1	0.2	0.2	0.2	0.2
167.5°	0.1	0.1	0.2	0.2	0.2	0.2
168°	0.1	0.1	0.2	0.2	0.2	0.2
168.5°	0.1	0.1	0.2	0.2	0.2	0.2
169°	0.1	0.1	0.2	0.2	0.2	0.2
169.5°	0.1	0.1	0.2	0.2	0.2	0.2
170°	0.1	0.1	0.2	0.2	0.2	0.2
170.5°	0.1	0.1	0.2	0.2	0.2	0.2
171°	0.1	0.1	0.2	0.2	0.2	0.2
171.5°	0.1	0.1	0.2	0.2	0.2	0.2
172°	0.1	0.1	0.2	0.2	0.2	0.2
172.5°	0.1	0.1	0.2	0.2	0.2	0.2
173°	0.1	0.1	0.2	0.2	0.2	0.2
173.5°	0.1	0.1	0.2	0.2	0.2	0.2
174°	0.1	0.1	0.2	0.2	0.2	0.2
174.5°	0.1	0.1	0.2	0.2	0.2	0.2
175°	0.1	0.1	0.2	0.2	0.2	0.2
175.5°	0.1	0.1	0.2	0.2	0.2	0.2
176°	0.1	0.1	0.2	0.2	0.2	0.2
176.5°	0.1	0.1	0.2	0.2	0.2	0.2
177°	0.1	0.1	0.2	0.2	0.2	0.2
177.5°	0.1	0.1	0.2	0.2	0.2	0.2
178°	0.1	0.1	0.2	0.2	0.2	0.2
178.5°	0.1	0.1	0.2	0.2	0.2	0.2
179°	0.1	0.1	0.2	0.2	0.2	0.2
179.5°	0.1	0.1	0.2	0.2	0.2	0.2



TEST NUMBER: A1914114C001

CATALOG NUMBER:

**CANDELA DISTRIBUTION (continued):**

	247.5°	270°	292.5°	315°	337.5°	360°
180°	0.2	0.2	0.2	0.2	0.2	0.2

(END OF REPORT)