

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P272205

Luminaire Tested: **LA4069271EWH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P272205
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (A1805269A001)
Test Lab:
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: LA4069271EWH
Description: HALO LA 4 INCH LED LUMINAIRE
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 611.0 lumens
Efficiency: N/A
Efficacy: 71.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.27
Luminous Opening: Circular (Dia: 0.34m x H: 0m)
CIE Type: Direct

Input Watts (W): 8.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P272205
CATALOG NUMBER: LA4069271EWH

Luminous Intensity Polar Plot





TEST NUMBER: P272205

CATALOG NUMBER: LA4069271EWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	103	99	108	104	101	98	100	97	94	96	94	92	92	91	89	87					87			
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75					75			
3	93	84	76	71	91	82	75	70	79	73	69	77	72	68	74	70	66	64					64			
4	86	75	67	61	84	74	66	60	71	65	60	69	63	59	67	62	58	56					56			
5	79	68	59	53	77	66	59	53	64	58	52	62	56	52	61	55	51	49					49			
6	74	61	53	47	72	60	52	47	59	52	46	57	51	46	55	50	46	44					44			
7	69	56	48	42	67	55	47	42	54	46	41	52	46	41	51	45	41	39					39			
8	64	51	43	38	62	50	43	37	49	42	37	48	42	37	47	41	37	35					35			
9	60	47	39	34	59	47	39	34	45	39	34	44	38	34	43	38	33	32					32			
10	56	44	36	31	55	43	36	31	42	35	31	41	35	31	40	35	31	29					29			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	2983	2983	2983	2983
5°	2984	2991	2974	2966
10°	2976	2992	2956	2941
15°	2959	2984	2929	2904
20°	2930	2967	2889	2852
25°	2884	2935	2828	2774
30°	2812	2881	2741	2670
35°	2711	2797	2622	2533
40°	2575	2680	2466	2359
45°	2399	2526	2271	2145
50°	2181	2329	2029	1892
55°	1932	2089	1770	1628
60°	1679	1835	1520	1379
65°	1444	1600	1285	1147
70°	1230	1388	998	921
75°	894	1187	609	681
80°	450	983	260	400
85°	88	758	51	88



TEST NUMBER: P272205

CATALOG NUMBER: LA4069271EWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.6	4.2
10°-20°	72.8	11.9
20°-30°	108.0	17.7
30°-40°	123.6	20.2
40°-50°	115.3	18.9
50°-60°	86.6	14.2
60°-70°	52.4	8.6
70°-80°	22.4	3.7
80°-90°	3.4	0.6
90°-100°	0.1	0.0
100°-110°	0.1	0.0
110°-120°	0.1	0.0
120°-130°	0.1	0.0
130°-140°	0.1	0.0
140°-150°	0.1	0.0
150°-160°	0.1	0.0
160°-170°	0.1	0.0
170°-180°	0.0	0.0
0°-30°	206.4	33.8
0°-40°	330.0	54.0
0°-60°	531.9	87.1
0°-90°	610.2	99.9
90°-120°	0.3	0.0
90°-150°	0.6	0.1
90°-180°	1.0	0.2
0°-180°	611.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	271	271	271	271	271	
5°	270	270	269	268	270	26
15°	260	262	257	255	260	73
25°	237	242	233	228	237	109
35°	202	208	195	188	202	126
45°	154	162	146	138	154	118
55°	101	109	92	85	101	90
65°	55	61	49	44	55	55
75°	21	28	14	16	21	23
85°	1	6	0	1	1	2
90°	0	1	0	0	0	0
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0



TEST NUMBER: P272205

CATALOG NUMBER: LA4069271EWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	270.8	270.8	270.8	270.8	270.8	270.8	270.8	270.8	270.8	270.8	270.8
0.5°	270.8	270.9	270.9	271.0	271.0	270.9	270.9	270.8	270.7	270.8	270.7
1°	270.9	271.0	271.0	271.0	271.0	270.9	270.8	270.8	270.6	270.6	270.5
1.5°	270.8	271.0	271.0	271.1	271.0	270.9	270.9	270.7	270.5	270.4	270.4
2°	270.8	271.0	271.1	271.0	271.0	270.9	270.8	270.6	270.4	270.3	270.2
2.5°	270.7	270.9	271.0	271.1	271.0	270.8	270.7	270.4	270.2	270.1	269.9
3°	270.5	270.8	271.0	271.0	271.0	270.8	270.6	270.2	270.0	269.8	269.7
3.5°	270.4	270.7	270.9	270.9	270.9	270.7	270.5	270.1	269.7	269.6	269.3
4°	270.3	270.6	270.8	270.8	270.9	270.6	270.3	269.9	269.5	269.3	269.1
4.5°	270.0	270.4	270.6	270.7	270.7	270.4	270.1	269.7	269.3	269.0	268.7
5°	269.9	270.3	270.5	270.6	270.5	270.2	269.8	269.4	269.0	268.6	268.4
5.5°	269.6	270.1	270.2	270.4	270.4	270.0	269.6	269.1	268.6	268.3	268.0
6°	269.3	269.8	270.1	270.1	270.2	269.8	269.3	268.7	268.2	267.9	267.5
6.5°	269.0	269.5	269.7	269.9	269.9	269.5	269.0	268.4	267.8	267.4	267.1
7°	268.6	269.2	269.5	269.6	269.6	269.2	268.6	268.0	267.4	266.9	266.6
7.5°	268.3	268.9	269.1	269.3	269.3	268.9	268.3	267.6	267.0	266.5	266.1
8°	267.9	268.6	268.9	269.0	269.0	268.5	267.9	267.1	266.5	265.9	265.6
8.5°	267.5	268.2	268.5	268.6	268.7	268.1	267.5	266.7	266.0	265.4	265.0
9°	267.1	267.8	268.1	268.3	268.3	267.7	267.0	266.1	265.4	264.8	264.4
9.5°	266.6	267.3	267.7	267.9	267.9	267.3	266.6	265.7	265.0	264.3	263.8
10°	266.1	266.9	267.3	267.4	267.5	266.8	266.0	265.1	264.3	263.6	263.1
10.5°	265.5	266.4	266.8	267.0	267.0	266.3	265.5	264.6	263.7	263.0	262.5
11°	265.0	265.9	266.4	266.5	266.5	265.8	265.0	263.9	263.1	262.2	261.8
11.5°	264.4	265.3	265.7	266.0	266.0	265.3	264.4	263.3	262.4	261.6	261.0
12°	263.8	264.8	265.3	265.5	265.5	264.7	263.8	262.6	261.7	260.8	260.2
12.5°	263.1	264.1	264.7	264.8	264.9	264.1	263.2	262.0	261.0	260.1	259.5
13°	262.5	263.5	264.1	264.3	264.3	263.5	262.5	261.2	260.2	259.3	258.6
13.5°	261.7	262.8	263.4	263.6	263.7	262.8	261.8	260.6	259.5	258.5	257.7
14°	261.1	262.2	262.9	263.0	263.1	262.1	261.1	259.8	258.6	257.6	256.9
14.5°	260.2	261.4	262.1	262.3	262.4	261.4	260.3	259.0	257.8	256.7	255.9
15°	259.5	260.7	261.4	261.6	261.7	260.7	259.6	258.1	256.9	255.8	255.0
15.5°	258.6	259.9	260.7	260.9	261.0	260.0	258.7	257.3	256.0	254.9	254.0
16°	257.8	259.2	259.9	260.2	260.2	259.2	257.9	256.4	255.0	253.8	253.0
16.5°	256.9	258.3	259.1	259.3	259.4	258.3	257.0	255.5	254.1	252.9	252.0
17°	256.1	257.5	258.3	258.6	258.6	257.5	256.2	254.5	253.1	251.8	250.9
17.5°	255.1	256.5	257.4	257.7	257.8	256.6	255.2	253.6	252.1	250.7	249.8
18°	254.2	255.7	256.6	256.9	256.9	255.7	254.3	252.5	251.1	249.6	248.7
18.5°	253.2	254.7	255.6	255.9	256.0	254.8	253.3	251.6	250.0	248.5	247.4
19°	252.2	253.8	254.7	255.1	255.1	253.7	252.3	250.4	248.8	247.3	246.3
19.5°	251.1	252.7	253.7	254.1	254.1	252.8	251.2	249.4	247.6	246.1	245.0
20°	250.0	251.7	252.8	253.1	253.1	251.8	250.2	248.2	246.5	244.9	243.7
20.5°	248.9	250.6	251.7	252.1	252.1	250.7	249.1	247.1	245.3	243.6	242.4
21°	247.8	249.5	250.6	251.0	251.1	249.6	248.0	245.9	244.0	242.3	241.1
21.5°	246.5	248.4	249.5	249.9	250.1	248.5	246.7	244.7	242.7	240.9	239.7
22°	245.4	247.2	248.4	248.9	248.9	247.3	245.6	243.4	241.4	239.5	238.3



TEST NUMBER: P272205

CATALOG NUMBER: LA4069271EWH

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
22.5°	244.0	246.0	247.2	247.7	247.7	246.2	244.3	242.1	240.0	238.1	236.8
23°	242.8	244.7	246.0	246.6	246.6	244.9	243.1	240.7	238.6	236.7	235.3
23.5°	241.4	243.5	244.7	245.3	245.3	243.7	241.7	239.4	237.2	235.2	233.8
24°	240.1	242.1	243.5	244.1	244.1	242.4	240.4	237.9	235.7	233.7	232.3
24.5°	238.6	240.8	242.1	242.8	242.8	241.1	239.0	236.5	234.2	232.1	230.5
25°	237.3	239.4	240.8	241.5	241.5	239.7	237.7	235.0	232.7	230.5	229.0
25.5°	235.8	237.9	239.4	240.1	240.1	238.4	236.2	233.6	231.1	228.9	227.3
26°	234.3	236.5	238.1	238.7	238.7	236.9	234.8	232.0	229.5	227.3	225.7
26.5°	232.7	235.0	236.6	237.2	237.4	235.5	233.2	230.4	227.8	225.6	223.8
27°	231.2	233.5	235.1	235.8	235.9	234.0	231.6	228.8	226.2	223.8	222.2
27.5°	229.6	232.0	233.6	234.3	234.4	232.5	230.1	227.2	224.5	222.0	220.2
28°	227.9	230.4	232.1	232.8	232.9	230.9	228.4	225.5	222.8	220.2	218.5
28.5°	226.2	228.8	230.5	231.2	231.4	229.3	226.8	223.8	221.0	218.4	216.5
29°	224.6	227.2	228.9	229.7	229.7	227.6	225.1	222.0	219.1	216.5	214.8
29.5°	222.8	225.5	227.2	228.0	228.1	226.0	223.4	220.2	217.3	214.6	212.7
30°	221.1	223.7	225.5	226.3	226.5	224.3	221.7	218.4	215.5	212.8	210.8
30.5°	219.2	222.0	223.8	224.6	224.7	222.6	219.9	216.6	213.6	210.7	208.8
31°	217.4	220.1	222.1	222.9	223.0	220.8	218.1	214.7	211.7	208.8	206.8
31.5°	215.5	218.4	220.3	221.1	221.3	219.0	216.2	212.8	209.6	206.7	204.7
32°	213.7	216.5	218.6	219.3	219.5	217.1	214.3	210.9	207.7	204.6	202.6
32.5°	211.7	214.7	216.6	217.5	217.6	215.3	212.4	208.9	205.6	202.6	200.4
33°	209.8	212.7	214.8	215.7	215.7	213.4	210.5	207.0	203.6	200.5	198.3
33.5°	207.7	210.8	212.9	213.7	213.9	211.5	208.5	204.9	201.5	198.4	196.1
34°	205.7	208.8	211.0	211.8	211.9	209.5	206.6	202.8	199.4	196.2	193.9
34.5°	203.6	206.8	209.0	209.8	210.0	207.5	204.5	200.7	197.2	194.0	191.6
35°	201.6	204.7	207.0	207.9	208.0	205.5	202.5	198.7	195.0	191.7	189.4
35.5°	199.4	202.7	205.0	205.7	205.9	203.5	200.3	196.5	192.8	189.5	187.0
36°	197.3	200.5	202.9	203.8	203.9	201.4	198.2	194.3	190.6	187.2	184.8
36.5°	195.1	198.5	200.8	201.7	201.8	199.3	196.1	192.1	188.2	184.8	182.3
37°	192.9	196.3	198.8	199.6	199.7	197.1	193.9	189.8	185.9	182.4	180.0
37.5°	190.7	194.1	196.5	197.4	197.6	195.0	191.6	187.6	183.6	180.1	177.5
38°	188.4	191.9	194.4	195.3	195.4	192.8	189.4	185.2	181.2	177.7	175.2
38.5°	186.1	189.7	192.1	193.1	193.2	190.5	187.1	182.9	178.8	175.3	172.7
39°	183.8	187.3	190.0	190.8	191.0	188.2	184.8	180.6	176.4	172.8	170.3
39.5°	181.4	185.1	187.7	188.6	188.7	186.0	182.5	178.2	174.0	170.3	167.7
40°	179.1	182.7	185.4	186.4	186.4	183.7	180.1	175.8	171.5	167.8	165.2
40.5°	176.6	180.4	183.0	184.0	184.1	181.4	177.8	173.3	169.0	165.3	162.6
41°	174.2	178.0	180.7	181.6	181.8	178.9	175.3	170.9	166.6	162.7	160.1
41.5°	171.8	175.7	178.3	179.3	179.4	176.6	172.9	168.4	164.1	160.2	157.5
42°	169.3	173.3	175.9	176.9	177.1	174.1	170.4	165.9	161.5	157.6	154.9
42.5°	166.8	170.7	173.5	174.5	174.6	171.7	168.0	163.4	159.0	155.1	152.2
43°	164.2	168.3	171.1	172.0	172.2	169.3	165.5	160.8	156.4	152.4	149.6
43.5°	161.7	165.8	168.6	169.6	169.7	166.7	163.0	158.3	153.7	149.8	147.0
44°	159.2	163.3	166.1	167.1	167.3	164.3	160.4	155.7	151.1	147.1	144.3
44.5°	156.6	160.8	163.6	164.6	164.7	161.7	157.8	153.1	148.5	144.5	141.6



TEST NUMBER: P272205

CATALOG NUMBER: LA4069271EWH

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
45°	154.0	158.2	161.1	162.1	162.2	159.2	155.2	150.5	145.8	141.8	138.9
45.5°	151.4	155.6	158.5	159.5	159.6	156.6	152.6	147.8	143.1	139.2	136.2
46°	148.8	153.0	155.9	157.0	157.2	154.1	150.0	145.1	140.5	136.4	133.5
46.5°	146.2	150.4	153.3	154.3	154.5	151.4	147.4	142.5	137.8	133.7	130.9
47°	143.5	147.9	150.7	151.7	151.9	148.7	144.7	139.8	135.1	131.0	128.1
47.5°	140.9	145.1	148.1	149.1	149.2	146.1	142.0	137.1	132.3	128.3	125.3
48°	138.2	142.5	145.5	146.5	146.7	143.5	139.4	134.4	129.6	125.5	122.5
48.5°	135.5	139.8	142.8	143.8	143.9	140.8	136.6	131.6	126.9	122.8	119.8
49°	132.7	137.2	140.1	141.1	141.3	138.1	133.9	129.0	124.1	120.0	117.0
49.5°	130.1	134.5	137.4	138.4	138.6	135.4	131.2	126.3	121.3	117.2	114.3
50°	127.3	131.8	134.8	135.7	135.9	132.7	128.5	123.5	118.4	114.5	111.5
50.5°	124.6	129.1	132.0	133.0	133.2	130.0	125.7	120.8	115.6	111.8	108.9
51°	121.9	126.4	129.3	130.3	130.5	127.3	123.0	118.0	113.2	109.1	106.2
51.5°	119.2	123.6	126.6	127.5	127.8	124.5	120.2	115.3	110.4	106.4	103.6
52°	116.4	121.0	123.8	124.9	125.1	121.8	117.5	112.5	107.8	103.8	100.9
52.5°	113.8	118.2	121.1	122.1	122.3	119.0	114.7	109.8	105.1	101.1	98.4
53°	111.1	115.5	118.4	119.4	119.6	116.3	112.0	107.1	102.5	98.5	95.8
53.5°	108.5	112.9	115.7	116.7	116.8	113.6	109.3	104.5	99.8	96.0	93.2
54°	105.8	110.2	113.0	114.0	114.1	110.9	106.7	101.8	97.2	93.4	90.7
54.5°	103.2	107.5	110.4	111.3	111.4	108.2	104.0	99.2	94.7	90.9	88.2
55°	100.6	104.9	107.7	108.6	108.8	105.5	101.3	96.6	92.2	88.5	85.8
55.5°	98.0	102.3	105.0	106.0	106.1	102.9	98.8	94.1	89.7	86.0	83.4
56°	95.4	99.7	102.4	103.3	103.5	100.3	96.2	91.6	87.2	83.6	81.1
56.5°	92.9	97.0	99.8	100.7	100.9	97.7	93.7	89.1	84.8	81.2	78.7
57°	90.5	94.6	97.3	98.1	98.3	95.2	91.1	86.7	82.4	78.9	76.4
57.5°	88.0	92.1	94.7	95.6	95.7	92.7	88.7	84.3	80.1	76.6	74.2
58°	85.5	89.5	92.2	93.1	93.2	90.2	86.2	81.9	77.8	74.3	71.9
58.5°	83.2	87.1	89.8	90.5	90.7	87.7	83.9	79.6	75.5	72.1	69.7
59°	80.8	84.7	87.3	88.1	88.2	85.3	81.5	77.3	73.3	69.9	67.6
59.5°	78.6	82.4	84.9	85.6	85.8	82.9	79.1	75.0	71.1	67.8	65.5
60°	76.2	80.0	82.5	83.3	83.3	80.6	76.9	72.8	69.0	65.7	63.4
60.5°	74.0	77.7	80.2	80.9	81.0	78.2	74.6	70.5	66.8	63.6	61.4
61°	71.8	75.5	77.9	78.6	78.7	76.0	72.4	68.4	64.7	61.6	59.4
61.5°	69.6	73.3	75.6	76.2	76.4	73.7	70.2	66.2	62.7	59.6	57.5
62°	67.5	71.1	73.3	74.1	74.2	71.6	68.1	64.2	60.7	57.6	55.5
62.5°	65.4	68.8	71.1	71.8	72.0	69.4	66.0	62.1	58.7	55.7	53.6
63°	63.3	66.7	69.0	69.7	69.8	67.3	63.9	60.0	56.7	53.8	51.8
63.5°	61.4	64.7	66.9	67.5	67.6	65.1	61.9	58.0	54.8	52.0	50.0
64°	59.4	62.7	64.8	65.5	65.5	63.1	59.9	56.0	52.9	50.1	48.1
64.5°	57.4	60.7	62.7	63.4	63.5	61.1	57.9	54.1	51.1	48.3	46.4
65°	55.4	58.6	60.7	61.4	61.4	59.1	56.0	52.2	49.3	46.6	44.7
65.5°	53.4	56.7	58.8	59.3	59.4	57.2	54.1	50.3	47.5	44.9	43.0
66°	51.7	54.8	56.8	57.4	57.5	55.2	52.2	48.4	45.7	43.2	41.4
66.5°	49.9	53.0	54.9	55.5	55.6	53.4	50.4	46.6	44.0	41.5	39.7
67°	48.2	51.2	53.7	53.3	53.7	51.5	48.6	44.8	42.3	39.9	38.2



TEST NUMBER: P272205

CATALOG NUMBER: LA4069271EWH

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
67.5°	46.5	49.4	51.7	51.6	51.8	49.7	46.9	43.0	40.5	38.3	36.6
68°	44.7	47.6	49.8	49.9	50.0	48.0	45.1	41.2	38.6	36.8	35.1
68.5°	43.0	45.8	47.9	48.1	48.2	46.2	43.4	39.3	36.6	35.2	33.6
69°	41.4	44.1	45.9	46.4	46.5	44.5	41.8	37.6	34.7	33.7	32.1
69.5°	39.7	42.5	44.2	44.7	44.8	42.8	40.1	35.8	32.9	32.1	30.6
70°	38.2	40.8	42.5	43.0	43.1	41.2	38.5	34.0	31.0	30.4	29.3
70.5°	36.6	39.2	40.8	41.4	41.4	39.6	36.9	32.3	29.1	28.7	27.8
71°	35.1	37.6	39.3	39.8	39.8	38.0	35.4	30.6	27.3	27.0	26.5
71.5°	33.3	36.1	37.7	38.2	38.3	36.4	33.9	28.9	25.5	25.4	25.2
72°	31.6	34.5	36.1	36.6	36.7	34.9	32.4	27.3	23.8	23.8	23.9
72.5°	29.8	33.0	34.6	35.1	35.1	33.4	30.9	25.7	22.0	22.2	22.5
73°	28.0	31.6	33.1	33.6	33.6	32.0	29.5	24.1	20.3	20.7	21.3
73.5°	26.2	30.1	31.6	32.1	32.2	30.5	28.1	22.6	18.7	19.2	20.0
74°	24.4	28.5	30.2	30.6	30.7	29.2	26.7	21.1	17.2	17.7	18.8
74.5°	22.7	27.0	28.8	29.2	29.3	27.7	25.3	19.7	15.7	16.4	17.6
75°	21.0	25.5	27.2	27.8	27.9	26.4	24.0	18.3	14.3	15.1	16.4
75.5°	19.3	23.8	25.6	26.5	26.6	25.1	22.7	17.0	13.1	13.9	15.2
76°	17.6	22.3	24.2	25.1	25.2	23.7	21.4	15.6	11.9	12.7	14.1
76.5°	16.0	20.8	22.6	23.8	23.9	22.5	20.1	14.4	10.7	11.6	13.1
77°	14.5	19.3	21.2	22.5	22.6	21.2	18.9	13.3	9.5	10.4	12.0
77.5°	13.1	17.9	19.8	21.3	21.4	20.0	17.7	12.2	8.3	9.3	11.0
78°	11.7	16.4	18.5	20.1	20.2	18.8	16.5	11.2	7.3	8.4	9.9
78.5°	10.4	15.1	17.2	18.8	19.0	17.7	15.4	10.1	6.4	7.5	8.9
79°	9.2	13.8	16.0	17.7	17.8	16.5	14.2	9.0	5.6	6.6	8.0
79.5°	8.1	12.6	14.8	16.5	16.6	15.4	13.2	8.1	4.8	5.9	7.1
80°	7.1	11.4	13.7	15.4	15.5	14.3	12.1	7.3	4.1	5.1	6.3
80.5°	6.2	10.3	12.6	14.3	14.5	13.3	11.1	6.5	3.5	4.3	5.5
81°	5.4	9.2	11.6	13.3	13.4	12.3	10.0	5.7	2.8	3.6	4.8
81.5°	4.6	8.2	10.6	12.2	12.4	11.4	9.0	5.0	2.2	3.0	4.0
82°	3.9	7.3	9.7	11.2	11.4	10.4	8.1	4.2	1.7	2.6	3.4
82.5°	3.2	6.4	8.8	10.3	10.4	9.4	7.2	3.5	1.3	2.1	2.8
83°	2.5	5.6	7.9	9.3	9.4	8.5	6.4	3.0	1.0	1.7	2.2
83.5°	1.8	4.9	7.1	8.4	8.5	7.6	5.6	2.5	0.8	1.4	1.7
84°	1.3	4.1	6.4	7.6	7.6	6.7	4.9	2.1	0.6	1.1	1.3
84.5°	1.0	3.4	5.6	6.7	6.8	5.9	4.2	1.7	0.5	0.8	1.0
85°	0.7	2.7	5.0	5.9	6.0	5.2	3.6	1.4	0.4	0.7	0.7
85.5°	0.5	2.2	4.3	5.2	5.2	4.5	3.0	1.1	0.4	0.5	0.6
86°	0.4	1.8	3.7	4.5	4.5	3.7	2.4	0.9	0.3	0.4	0.4
86.5°	0.3	1.4	3.0	3.8	3.8	3.1	1.9	0.7	0.3	0.3	0.3
87°	0.3	1.1	2.5	3.0	3.1	2.5	1.5	0.6	0.2	0.3	0.1
87.5°	0.3	0.8	1.9	2.4	2.5	1.9	1.1	0.5	0.2	0.2	0.1
88°	0.2	0.6	1.4	1.9	1.9	1.5	0.8	0.4	0.1	0.1	0.1
88.5°	0.2	0.5	1.1	1.4	1.4	1.1	0.7	0.3	0.1	0.1	0.1
89°	0.1	0.4	0.8	1.0	1.1	0.8	0.5	0.2	0.1	0.1	0.1
89.5°	0.1	0.3	0.6	0.8	0.8	0.6	0.4	0.2	0.1	0.1	0.1



TEST NUMBER: P272205

CATALOG NUMBER: LA4069271EWH

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
90°	0.1	0.2	0.5	0.6	0.6	0.5	0.2	0.2	0.1	0.1	0.1
90.5°	0.1	0.1	0.3	0.4	0.4	0.3	0.1	0.2	0.1	0.1	0.1
91°	0.1	0.1	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1
91.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
92°	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.1	0.0
92.5°	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.1	0.0
93°	0.0	0.1	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.1	0.0
93.5°	0.0	0.1	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.1	0.0
94°	0.0	0.1	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.1	0.0
94.5°	0.0	0.1	0.1	0.1	0.0	0.1	0.1	0.1	0.0	0.1	0.0
95°	0.0	0.0	0.1	0.1	0.0	0.1	0.1	0.1	0.0	0.1	0.0
95.5°	0.0	0.0	0.1	0.1	0.0	0.1	0.1	0.0	0.0	0.1	0.0
96°	0.0	0.0	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.0
96.5°	0.0	0.0	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.0
97°	0.0	0.0	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.0
97.5°	0.1	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98°	0.1	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98.5°	0.1	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99°	0.1	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99.5°	0.1	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.1	0.0	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
100.5°	0.1	0.0	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
101°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
101.5°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
102°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
103°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
103.5°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.1	0.0
104°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.1	0.1
104.5°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.1	0.1
105°	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.1	0.1
105.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.1	0.1
106°	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.1	0.1
106.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.1	0.1
107°	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.1	0.1	0.1
107.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.1	0.1	0.1
108°	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.1	0.1	0.1
108.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1
109°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
109.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
110°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
110.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
111°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
111.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
112°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1



TEST NUMBER: P272205

CATALOG NUMBER: LA4069271EWH

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
112.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
113°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
113.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
114°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
114.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
115°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
115.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
116°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
116.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
117°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
117.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
118°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
118.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
119°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
119.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
120°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
120.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
121°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
121.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
122°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
122.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
123°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
123.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
124°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
124.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
125°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
125.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
126°	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
126.5°	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
127°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
127.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
128°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
128.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
129°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
129.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
130°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
130.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
131°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
131.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
132°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
132.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
133°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
133.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
134°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
134.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1



TEST NUMBER: P272205

CATALOG NUMBER: LA4069271EWH

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
135°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
135.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
136°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
136.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
138°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
138.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
139°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
139.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
141°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
141.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
142°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
142.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
143°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.2	0.1
143.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.2	0.2	0.1
144°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.2	0.2	0.2
144.5°	0.3	0.3	0.2	0.2	0.1	0.1	0.1	0.1	0.2	0.2	0.2
145°	0.3	0.3	0.3	0.2	0.1	0.1	0.1	0.2	0.2	0.2	0.2
145.5°	0.3	0.3	0.3	0.3	0.1	0.1	0.1	0.2	0.2	0.2	0.2
146°	0.3	0.3	0.3	0.3	0.1	0.1	0.2	0.2	0.2	0.2	0.2
146.5°	0.3	0.3	0.3	0.3	0.1	0.1	0.2	0.2	0.2	0.2	0.2
147°	0.3	0.3	0.3	0.3	0.1	0.2	0.2	0.2	0.2	0.2	0.2
147.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
148°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
148.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
149°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
149.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
150°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
150.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
151°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
151.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
152°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
152.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
153°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
153.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
154°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
154.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
155°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
155.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
156°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
156.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
157°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2



TEST NUMBER: P272205

CATALOG NUMBER: LA4069271EWH

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
157.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
158°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
158.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
159°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
159.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
160°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
160.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
161°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
161.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
162°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
162.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
163°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
163.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
164°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
164.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
165°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
165.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
166°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
166.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
167°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
167.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
168°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
168.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
169°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
169.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
170°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
170.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
171°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
171.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
172°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
172.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
173°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
173.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.3	0.3	0.3	0.3
174°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
174.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
175°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
175.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
176°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
176.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
177°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
177.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
178°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
178.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
179°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
179.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3



TEST NUMBER: P272205

CATALOG NUMBER: LA4069271EWH

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
180°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3



TEST NUMBER: P272205

CATALOG NUMBER: LA4069271EWH

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	270.8	270.8	270.8	270.8	270.8	270.8
0.5°	270.7	270.7	270.7	270.8	270.8	270.8
1°	270.6	270.5	270.6	270.6	270.7	270.9
1.5°	270.4	270.4	270.4	270.5	270.7	270.8
2°	270.2	270.2	270.2	270.3	270.5	270.8
2.5°	269.9	269.9	270.0	270.2	270.4	270.7
3°	269.6	269.6	269.8	270.0	270.3	270.5
3.5°	269.4	269.4	269.5	269.9	270.1	270.4
4°	269.0	269.1	269.2	269.5	269.9	270.3
4.5°	268.7	268.7	268.9	269.3	269.7	270.0
5°	268.3	268.3	268.6	268.9	269.4	269.9
5.5°	267.9	267.9	268.1	268.6	269.1	269.6
6°	267.4	267.4	267.8	268.3	268.8	269.3
6.5°	267.0	267.0	267.3	267.9	268.4	269.0
7°	266.5	266.5	266.8	267.4	268.1	268.6
7.5°	266.0	266.0	266.3	267.0	267.7	268.3
8°	265.4	265.5	265.8	266.5	267.2	267.9
8.5°	264.9	264.9	265.2	266.0	266.8	267.5
9°	264.3	264.3	264.7	265.4	266.3	267.1
9.5°	263.7	263.7	264.1	264.9	265.8	266.6
10°	263.0	263.0	263.5	264.3	265.3	266.1
10.5°	262.4	262.3	262.8	263.7	264.7	265.5
11°	261.6	261.6	262.2	263.0	264.1	265.0
11.5°	260.9	260.8	261.4	262.3	263.4	264.4
12°	260.1	260.1	260.7	261.6	262.8	263.8
12.5°	259.3	259.2	259.9	260.9	262.1	263.1
13°	258.4	258.4	259.0	260.2	261.4	262.5
13.5°	257.6	257.5	258.2	259.3	260.6	261.7
14°	256.7	256.6	257.4	258.5	259.9	261.1
14.5°	255.8	255.7	256.5	257.6	259.1	260.2
15°	254.8	254.7	255.5	256.8	258.2	259.5
15.5°	253.8	253.7	254.5	255.8	257.4	258.6
16°	252.8	252.7	253.5	254.9	256.5	257.8
16.5°	251.8	251.6	252.5	253.9	255.5	256.9
17°	250.7	250.5	251.4	252.9	254.6	256.1
17.5°	249.6	249.5	250.4	251.8	253.6	255.1
18°	248.4	248.3	249.2	250.8	252.6	254.2
18.5°	247.2	247.1	248.1	249.7	251.6	253.2
19°	245.9	245.8	246.9	248.5	250.5	252.2
19.5°	244.7	244.6	245.7	247.3	249.4	251.1
20°	243.4	243.3	244.3	246.1	248.2	250.0
20.5°	242.1	241.9	243.0	244.8	247.0	248.9
21°	240.7	240.6	241.7	243.7	245.8	247.8
21.5°	239.4	239.2	240.3	242.3	244.5	246.5
22°	237.9	237.7	238.9	241.0	243.2	245.4



TEST NUMBER: P272205

CATALOG NUMBER: LA4069271EWH

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
22.5°	236.5	236.3	237.5	239.5	242.0	244.0
23°	234.9	234.8	235.9	238.1	240.6	242.8
23.5°	233.4	233.2	234.5	236.6	239.2	241.4
24°	231.8	231.6	232.9	235.2	237.8	240.1
24.5°	230.2	230.0	231.4	233.6	236.3	238.6
25°	228.5	228.3	229.7	232.1	234.8	237.3
25.5°	226.9	226.7	228.2	230.5	233.3	235.8
26°	225.1	225.0	226.3	228.9	231.7	234.3
26.5°	223.4	223.2	224.7	227.2	230.1	232.7
27°	221.6	221.4	222.9	225.5	228.5	231.2
27.5°	219.8	219.6	221.2	223.8	226.9	229.6
28°	217.9	217.7	219.3	222.0	225.1	227.9
28.5°	216.1	215.9	217.5	220.1	223.5	226.2
29°	214.1	213.9	215.6	218.4	221.6	224.6
29.5°	212.1	212.0	213.7	216.5	219.8	222.8
30°	210.2	209.9	211.7	214.6	217.9	221.1
30.5°	208.2	208.0	209.7	212.6	216.2	219.2
31°	206.1	205.9	207.7	210.7	214.2	217.4
31.5°	204.0	203.8	205.8	208.7	212.4	215.5
32°	201.9	201.6	203.6	206.7	210.3	213.7
32.5°	199.8	199.6	201.6	204.7	208.4	211.7
33°	197.6	197.4	199.3	202.6	206.2	209.8
33.5°	195.5	195.2	197.2	200.5	204.2	207.7
34°	193.2	192.9	195.0	198.3	202.1	205.7
34.5°	190.9	190.7	192.8	196.2	200.0	203.6
35°	188.6	188.4	190.5	194.0	197.8	201.6
35.5°	186.3	186.2	188.3	191.7	195.8	199.4
36°	184.0	183.8	185.9	189.4	193.4	197.3
36.5°	181.6	181.4	183.7	187.1	191.3	195.1
37°	179.2	179.0	181.3	184.8	188.9	192.9
37.5°	176.8	176.6	178.9	182.5	186.6	190.7
38°	174.3	174.2	176.5	180.1	184.2	188.4
38.5°	171.9	171.7	174.1	177.8	182.0	186.1
39°	169.4	169.1	171.5	175.3	179.5	183.8
39.5°	166.9	166.7	169.2	172.8	177.2	181.4
40°	164.3	164.1	166.6	170.3	174.7	179.1
40.5°	161.8	161.6	164.1	167.9	172.3	176.6
41°	159.2	159.0	161.5	165.4	169.7	174.2
41.5°	156.6	156.4	159.0	162.9	167.3	171.8
42°	154.0	153.8	156.4	160.3	164.6	169.3
42.5°	151.4	151.1	153.8	157.8	162.2	166.8
43°	148.7	148.5	151.2	155.2	159.6	164.2
43.5°	146.0	145.9	148.6	152.6	157.1	161.7
44°	143.3	143.1	145.9	149.9	154.4	159.2
44.5°	140.6	140.4	143.3	147.3	151.9	156.6



TEST NUMBER: P272205

CATALOG NUMBER: LA4069271EWH

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
45°	137.9	137.7	140.5	144.7	149.2	154.0
45.5°	135.2	135.0	137.9	142.0	146.5	151.4
46°	132.5	132.2	135.2	139.3	143.9	148.8
46.5°	129.8	129.5	132.4	136.6	141.2	146.2
47°	127.1	126.8	129.7	133.9	138.5	143.5
47.5°	124.3	124.0	127.0	131.2	135.8	140.9
48°	121.5	121.4	124.2	128.4	133.1	138.2
48.5°	118.6	118.6	121.6	125.8	130.4	135.5
49°	115.8	115.9	118.8	122.9	127.6	132.7
49.5°	113.2	113.2	116.1	120.3	124.9	130.1
50°	110.5	110.4	113.4	117.5	122.2	127.3
50.5°	107.8	107.8	110.7	114.9	119.5	124.6
51°	105.1	105.1	108.0	112.2	116.8	121.9
51.5°	102.5	102.5	105.4	109.5	114.1	119.2
52°	99.9	99.9	102.8	106.9	111.4	116.4
52.5°	97.3	97.2	100.2	104.2	108.7	113.8
53°	94.7	94.7	97.5	101.6	106.0	111.1
53.5°	92.2	92.2	95.0	99.1	103.4	108.5
54°	89.7	89.7	92.5	96.5	100.8	105.8
54.5°	87.3	87.2	90.0	93.9	98.2	103.2
55°	84.8	84.8	87.5	91.4	95.7	100.6
55.5°	82.4	82.4	85.0	88.9	93.2	98.0
56°	80.1	80.0	82.7	86.5	90.7	95.4
56.5°	77.8	77.7	80.3	84.0	88.2	92.9
57°	75.5	75.5	78.0	81.7	85.8	90.5
57.5°	73.3	73.3	75.8	79.4	83.4	88.0
58°	71.1	71.0	73.5	77.1	81.1	85.5
58.5°	68.9	68.8	71.3	74.9	78.7	83.2
59°	66.8	66.7	69.1	72.7	76.4	80.8
59.5°	64.7	64.6	67.0	70.4	74.2	78.6
60°	62.6	62.6	64.9	68.3	72.0	76.2
60.5°	60.6	60.6	62.9	66.2	69.8	74.0
61°	58.6	58.6	60.8	64.2	67.7	71.8
61.5°	56.7	56.6	58.8	62.1	65.6	69.6
62°	54.8	54.7	56.9	60.1	63.6	67.5
62.5°	52.9	52.9	55.0	58.1	61.5	65.4
63°	51.1	51.1	53.8	56.2	59.5	63.3
63.5°	49.3	49.3	51.9	54.3	57.6	61.4
64°	47.5	47.5	49.9	52.5	55.7	59.4
64.5°	45.8	45.7	47.9	50.7	53.6	57.4
65°	44.0	44.0	45.9	48.9	51.8	55.4
65.5°	42.4	42.2	44.2	47.1	50.1	53.4
66°	40.7	40.7	42.5	45.3	48.3	51.7
66.5°	39.1	39.0	40.9	43.6	46.5	49.9
67°	37.5	37.5	39.3	41.9	44.8	48.2



TEST NUMBER: P272205

CATALOG NUMBER: LA4069271EWH

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
67.5°	36.0	35.9	37.7	40.3	43.2	46.5
68°	34.4	34.4	36.1	38.7	41.5	44.7
68.5°	33.0	32.9	34.6	37.1	39.9	43.0
69°	31.5	31.4	33.1	35.6	38.3	41.4
69.5°	30.1	30.0	31.6	34.0	36.7	39.7
70°	28.6	28.6	30.2	32.5	35.2	38.2
70.5°	27.3	27.2	28.8	31.1	33.7	36.6
71°	25.9	25.8	27.4	29.7	32.2	35.1
71.5°	24.6	24.5	26.0	28.2	30.7	33.3
72°	23.3	23.2	24.7	26.9	29.1	31.6
72.5°	22.0	21.9	23.4	25.5	27.6	29.8
73°	20.8	20.7	22.1	24.2	26.0	28.0
73.5°	19.6	19.5	20.9	22.9	24.4	26.2
74°	18.4	18.3	19.6	21.6	22.8	24.4
74.5°	17.2	17.1	18.4	20.4	21.3	22.7
75°	16.1	16.0	17.3	19.1	19.8	21.0
75.5°	15.0	14.9	16.1	17.9	18.3	19.3
76°	13.9	13.8	15.0	16.7	16.9	17.6
76.5°	12.9	12.7	13.9	15.5	15.5	16.0
77°	11.9	11.7	12.9	14.4	14.2	14.5
77.5°	10.9	10.8	11.9	13.3	13.0	13.1
78°	9.9	9.8	10.9	12.2	11.8	11.7
78.5°	8.9	8.9	9.9	11.2	10.6	10.4
79°	8.0	8.0	9.0	10.1	9.5	9.2
79.5°	7.2	7.1	8.1	9.2	8.5	8.1
80°	6.3	6.3	7.2	8.2	7.6	7.1
80.5°	5.6	5.5	6.4	7.3	6.6	6.2
81°	4.8	4.8	5.6	6.5	5.8	5.4
81.5°	4.1	4.1	4.9	5.7	5.1	4.6
82°	3.4	3.4	4.2	5.0	4.4	3.9
82.5°	2.8	2.8	3.5	4.3	3.7	3.2
83°	2.2	2.2	2.8	3.6	3.0	2.5
83.5°	1.7	1.7	2.2	2.9	2.5	1.8
84°	1.3	1.2	1.7	2.4	2.0	1.3
84.5°	0.9	0.9	1.3	1.8	1.6	1.0
85°	0.7	0.7	0.9	1.4	1.3	0.7
85.5°	0.5	0.5	0.7	1.0	1.0	0.5
86°	0.4	0.4	0.5	0.8	0.8	0.4
86.5°	0.2	0.2	0.4	0.6	0.6	0.3
87°	0.1	0.1	0.2	0.4	0.5	0.3
87.5°	0.0	0.1	0.1	0.3	0.4	0.3
88°	0.0	0.1	0.1	0.1	0.3	0.2
88.5°	0.0	0.1	0.1	0.1	0.2	0.2
89°	0.0	0.1	0.1	0.1	0.1	0.1
89.5°	0.0	0.1	0.1	0.1	0.1	0.1



TEST NUMBER: P272205

CATALOG NUMBER: LA4069271EWH

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
90°	0.0	0.1	0.1	0.1	0.1	0.1
90.5°	0.0	0.1	0.1	0.1	0.1	0.1
91°	0.0	0.1	0.1	0.1	0.1	0.1
91.5°	0.0	0.1	0.1	0.1	0.1	0.1
92°	0.0	0.1	0.1	0.1	0.1	0.1
92.5°	0.0	0.1	0.1	0.1	0.1	0.1
93°	0.0	0.1	0.1	0.1	0.1	0.0
93.5°	0.0	0.1	0.1	0.1	0.0	0.0
94°	0.0	0.1	0.1	0.1	0.0	0.0
94.5°	0.0	0.1	0.1	0.1	0.0	0.0
95°	0.0	0.1	0.1	0.1	0.0	0.0
95.5°	0.0	0.1	0.1	0.1	0.0	0.0
96°	0.0	0.1	0.1	0.1	0.0	0.0
96.5°	0.0	0.1	0.1	0.1	0.0	0.0
97°	0.0	0.1	0.1	0.1	0.1	0.0
97.5°	0.0	0.1	0.1	0.1	0.1	0.1
98°	0.0	0.1	0.1	0.1	0.1	0.1
98.5°	0.0	0.1	0.1	0.1	0.1	0.1
99°	0.0	0.1	0.1	0.1	0.1	0.1
99.5°	0.0	0.1	0.1	0.1	0.1	0.1
100°	0.0	0.1	0.1	0.1	0.1	0.1
100.5°	0.0	0.1	0.1	0.1	0.1	0.1
101°	0.0	0.1	0.1	0.1	0.1	0.1
101.5°	0.0	0.1	0.1	0.1	0.1	0.1
102°	0.0	0.1	0.1	0.1	0.1	0.1
102.5°	0.0	0.1	0.1	0.1	0.1	0.1
103°	0.0	0.1	0.1	0.1	0.1	0.1
103.5°	0.0	0.1	0.1	0.1	0.1	0.1
104°	0.0	0.1	0.1	0.1	0.1	0.1
104.5°	0.0	0.1	0.1	0.1	0.1	0.1
105°	0.1	0.1	0.1	0.1	0.1	0.1
105.5°	0.1	0.1	0.1	0.1	0.1	0.1
106°	0.1	0.1	0.1	0.1	0.1	0.1
106.5°	0.1	0.1	0.1	0.1	0.1	0.1
107°	0.1	0.1	0.1	0.1	0.1	0.1
107.5°	0.1	0.1	0.1	0.1	0.1	0.1
108°	0.1	0.1	0.1	0.1	0.1	0.1
108.5°	0.1	0.1	0.1	0.1	0.1	0.1
109°	0.1	0.1	0.1	0.1	0.1	0.1
109.5°	0.1	0.1	0.1	0.1	0.1	0.1
110°	0.1	0.1	0.1	0.1	0.1	0.1
110.5°	0.1	0.1	0.1	0.1	0.1	0.1
111°	0.1	0.1	0.1	0.1	0.1	0.1
111.5°	0.1	0.1	0.1	0.1	0.1	0.1
112°	0.1	0.1	0.1	0.1	0.1	0.1



TEST NUMBER: P272205

CATALOG NUMBER: LA4069271EWH

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
112.5°	0.1	0.1	0.1	0.1	0.1	0.1
113°	0.1	0.1	0.1	0.1	0.1	0.1
113.5°	0.1	0.1	0.1	0.1	0.1	0.1
114°	0.1	0.1	0.1	0.1	0.1	0.1
114.5°	0.1	0.1	0.1	0.1	0.1	0.1
115°	0.1	0.1	0.1	0.1	0.1	0.1
115.5°	0.1	0.1	0.1	0.1	0.1	0.1
116°	0.1	0.1	0.1	0.1	0.1	0.1
116.5°	0.1	0.1	0.1	0.1	0.1	0.1
117°	0.1	0.1	0.1	0.1	0.1	0.1
117.5°	0.1	0.1	0.1	0.1	0.1	0.1
118°	0.1	0.1	0.1	0.1	0.1	0.1
118.5°	0.1	0.1	0.1	0.1	0.1	0.1
119°	0.1	0.1	0.1	0.1	0.1	0.1
119.5°	0.1	0.1	0.1	0.1	0.1	0.1
120°	0.1	0.1	0.1	0.1	0.1	0.1
120.5°	0.1	0.1	0.1	0.1	0.1	0.1
121°	0.1	0.1	0.1	0.1	0.1	0.1
121.5°	0.1	0.1	0.1	0.1	0.1	0.1
122°	0.1	0.1	0.1	0.1	0.1	0.1
122.5°	0.1	0.1	0.1	0.1	0.1	0.1
123°	0.1	0.1	0.1	0.1	0.1	0.1
123.5°	0.1	0.1	0.1	0.1	0.1	0.1
124°	0.1	0.2	0.2	0.1	0.1	0.1
124.5°	0.1	0.2	0.2	0.2	0.1	0.1
125°	0.1	0.2	0.2	0.2	0.1	0.1
125.5°	0.1	0.2	0.2	0.2	0.2	0.1
126°	0.1	0.2	0.2	0.2	0.2	0.2
126.5°	0.1	0.2	0.2	0.2	0.2	0.2
127°	0.1	0.2	0.2	0.2	0.2	0.2
127.5°	0.1	0.2	0.2	0.2	0.2	0.2
128°	0.1	0.2	0.2	0.2	0.2	0.2
128.5°	0.1	0.2	0.2	0.2	0.2	0.2
129°	0.1	0.2	0.2	0.2	0.2	0.2
129.5°	0.1	0.2	0.2	0.2	0.2	0.2
130°	0.1	0.2	0.2	0.2	0.2	0.2
130.5°	0.1	0.2	0.2	0.2	0.2	0.2
131°	0.1	0.2	0.2	0.2	0.2	0.2
131.5°	0.1	0.2	0.2	0.2	0.2	0.2
132°	0.1	0.2	0.2	0.2	0.2	0.2
132.5°	0.1	0.2	0.2	0.2	0.2	0.2
133°	0.1	0.2	0.2	0.2	0.2	0.2
133.5°	0.1	0.2	0.2	0.2	0.2	0.2
134°	0.1	0.2	0.2	0.2	0.2	0.2
134.5°	0.1	0.2	0.2	0.2	0.2	0.2



TEST NUMBER: P272205

CATALOG NUMBER: LA4069271EWH

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
135°	0.1	0.2	0.2	0.2	0.2	0.2
135.5°	0.1	0.2	0.2	0.2	0.2	0.2
136°	0.1	0.2	0.2	0.2	0.2	0.2
136.5°	0.1	0.2	0.2	0.2	0.2	0.2
137°	0.1	0.2	0.2	0.2	0.2	0.2
137.5°	0.1	0.2	0.2	0.2	0.2	0.2
138°	0.1	0.2	0.2	0.2	0.2	0.2
138.5°	0.1	0.2	0.2	0.2	0.2	0.2
139°	0.1	0.2	0.2	0.2	0.2	0.2
139.5°	0.1	0.2	0.2	0.2	0.2	0.2
140°	0.1	0.2	0.2	0.2	0.2	0.2
140.5°	0.1	0.2	0.2	0.2	0.2	0.2
141°	0.1	0.2	0.2	0.2	0.2	0.2
141.5°	0.1	0.2	0.2	0.2	0.2	0.2
142°	0.1	0.2	0.2	0.2	0.2	0.2
142.5°	0.1	0.2	0.2	0.2	0.2	0.2
143°	0.1	0.3	0.2	0.2	0.2	0.2
143.5°	0.1	0.3	0.3	0.3	0.2	0.2
144°	0.2	0.3	0.3	0.3	0.3	0.2
144.5°	0.2	0.3	0.3	0.3	0.3	0.3
145°	0.2	0.3	0.3	0.3	0.3	0.3
145.5°	0.2	0.3	0.3	0.3	0.3	0.3
146°	0.2	0.3	0.3	0.3	0.3	0.3
146.5°	0.2	0.3	0.3	0.3	0.3	0.3
147°	0.2	0.3	0.3	0.3	0.3	0.3
147.5°	0.2	0.3	0.3	0.3	0.3	0.3
148°	0.2	0.3	0.3	0.3	0.3	0.3
148.5°	0.2	0.3	0.3	0.3	0.3	0.3
149°	0.2	0.3	0.3	0.3	0.3	0.3
149.5°	0.2	0.3	0.3	0.3	0.3	0.3
150°	0.2	0.3	0.3	0.3	0.3	0.3
150.5°	0.2	0.3	0.3	0.3	0.3	0.3
151°	0.2	0.3	0.3	0.3	0.3	0.3
151.5°	0.2	0.3	0.3	0.3	0.3	0.3
152°	0.2	0.3	0.3	0.3	0.3	0.3
152.5°	0.2	0.3	0.3	0.3	0.3	0.3
153°	0.2	0.3	0.3	0.3	0.3	0.3
153.5°	0.2	0.3	0.3	0.3	0.3	0.3
154°	0.2	0.3	0.3	0.3	0.3	0.3
154.5°	0.2	0.3	0.3	0.3	0.3	0.3
155°	0.2	0.3	0.3	0.3	0.3	0.3
155.5°	0.2	0.3	0.3	0.3	0.3	0.3
156°	0.2	0.3	0.3	0.3	0.3	0.3
156.5°	0.2	0.3	0.3	0.3	0.3	0.3
157°	0.2	0.3	0.3	0.3	0.3	0.3



TEST NUMBER: P272205

CATALOG NUMBER: LA4069271EWH

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
157.5°	0.2	0.3	0.3	0.3	0.3	0.3
158°	0.2	0.3	0.3	0.3	0.3	0.3
158.5°	0.2	0.3	0.3	0.3	0.3	0.3
159°	0.2	0.3	0.3	0.3	0.3	0.3
159.5°	0.2	0.3	0.3	0.3	0.3	0.3
160°	0.2	0.3	0.3	0.3	0.3	0.3
160.5°	0.2	0.3	0.3	0.3	0.3	0.3
161°	0.2	0.3	0.3	0.3	0.3	0.3
161.5°	0.2	0.3	0.3	0.3	0.3	0.3
162°	0.2	0.3	0.3	0.3	0.3	0.3
162.5°	0.2	0.3	0.3	0.3	0.3	0.3
163°	0.2	0.3	0.3	0.3	0.3	0.3
163.5°	0.2	0.3	0.3	0.3	0.3	0.3
164°	0.2	0.3	0.3	0.3	0.3	0.3
164.5°	0.2	0.3	0.3	0.3	0.3	0.3
165°	0.2	0.3	0.3	0.3	0.3	0.3
165.5°	0.2	0.3	0.3	0.3	0.3	0.3
166°	0.2	0.3	0.3	0.3	0.3	0.3
166.5°	0.2	0.3	0.3	0.3	0.3	0.3
167°	0.2	0.3	0.3	0.3	0.3	0.3
167.5°	0.2	0.3	0.3	0.3	0.3	0.3
168°	0.2	0.3	0.3	0.3	0.3	0.3
168.5°	0.2	0.3	0.3	0.3	0.3	0.3
169°	0.2	0.3	0.3	0.3	0.3	0.3
169.5°	0.2	0.3	0.3	0.3	0.3	0.3
170°	0.2	0.3	0.3	0.3	0.3	0.3
170.5°	0.2	0.3	0.3	0.3	0.3	0.3
171°	0.2	0.3	0.3	0.3	0.3	0.3
171.5°	0.2	0.3	0.3	0.3	0.3	0.3
172°	0.2	0.3	0.3	0.3	0.3	0.3
172.5°	0.2	0.3	0.3	0.3	0.3	0.3
173°	0.3	0.3	0.3	0.3	0.3	0.3
173.5°	0.3	0.3	0.3	0.3	0.3	0.3
174°	0.3	0.3	0.3	0.3	0.3	0.3
174.5°	0.3	0.3	0.3	0.3	0.3	0.3
175°	0.3	0.3	0.3	0.3	0.3	0.3
175.5°	0.3	0.3	0.3	0.3	0.3	0.3
176°	0.3	0.3	0.3	0.3	0.3	0.3
176.5°	0.3	0.3	0.3	0.3	0.3	0.3
177°	0.3	0.3	0.3	0.3	0.3	0.3
177.5°	0.3	0.3	0.3	0.3	0.3	0.3
178°	0.3	0.3	0.3	0.3	0.3	0.3
178.5°	0.3	0.3	0.3	0.3	0.3	0.3
179°	0.3	0.3	0.3	0.3	0.3	0.3
179.5°	0.3	0.3	0.3	0.3	0.3	0.3



TEST NUMBER: P272205

CATALOG NUMBER: LA4069271EWH

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
180°	0.3	0.3	0.3	0.3	0.3	0.3

(END OF REPORT)