

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P272206

Luminaire Tested: **LA4069301EWH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P272206
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (A1805269A001)
Test Lab:
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: LA4069301EWH
Description: HALO LA 4 INCH LED LUMINAIRE
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 613.2 lumens
Efficiency: N/A
Efficacy: 71.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.27
Luminous Opening: Circular (Dia: 0.34m x H: 0m)
CIE Type: Direct

Input Watts (W): 8.59
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P272206
CATALOG NUMBER: LA4069301EWH

Luminous Intensity Polar Plot





TEST NUMBER: P272206

CATALOG NUMBER: LA4069301EWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	103	99	108	104	101	98	100	97	94	96	94	92	92	91	89	87
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75
3	93	84	76	71	91	82	75	70	79	73	69	77	72	68	74	70	66	64
4	86	75	67	61	84	74	66	60	71	65	60	69	63	59	67	62	58	56
5	79	68	59	53	77	66	59	53	64	58	52	62	56	52	61	55	51	49
6	74	61	53	47	72	60	52	47	59	52	46	57	51	46	55	50	46	44
7	69	56	48	42	67	55	47	42	54	46	41	52	46	41	51	45	41	39
8	64	51	43	38	62	50	43	37	49	42	37	48	42	37	47	41	37	35
9	60	47	39	34	59	47	39	34	45	39	34	44	38	34	43	38	33	32
10	56	44	36	31	55	43	36	31	42	35	31	41	35	31	40	35	31	29

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	2994	2994	2994	2994
5°	2995	3002	2984	2976
10°	2987	3003	2967	2953
15°	2969	2994	2940	2916
20°	2941	2977	2900	2862
25°	2894	2946	2838	2784
30°	2821	2891	2751	2680
35°	2720	2807	2631	2543
40°	2584	2690	2476	2368
45°	2408	2534	2279	2153
50°	2190	2337	2037	1899
55°	1939	2097	1776	1636
60°	1685	1842	1524	1383
65°	1449	1608	1290	1152
70°	1233	1391	1002	924
75°	894	1192	609	681
80°	450	989	260	400
85°	88	758	51	88



TEST NUMBER: P272206

CATALOG NUMBER: LA4069301EWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.7	4.2
10°-20°	73.1	11.9
20°-30°	108.4	17.7
30°-40°	124.1	20.2
40°-50°	115.7	18.9
50°-60°	86.9	14.2
60°-70°	52.6	8.6
70°-80°	22.5	3.7
80°-90°	3.5	0.6
90°-100°	0.1	0.0
100°-110°	0.1	0.0
110°-120°	0.1	0.0
120°-130°	0.1	0.0
130°-140°	0.1	0.0
140°-150°	0.1	0.0
150°-160°	0.1	0.0
160°-170°	0.1	0.0
170°-180°	0.0	0.0
0°-30°	207.1	33.8
0°-40°	331.2	54.0
0°-60°	533.9	87.1
0°-90°	612.4	99.9
90°-120°	0.3	0.0
90°-150°	0.6	0.1
90°-180°	1.0	0.2
0°-180°	613.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	272	272	272	272	272	
5°	271	272	270	269	271	26
15°	260	263	258	256	260	73
25°	238	242	234	229	238	110
35°	202	209	196	189	202	126
45°	155	163	146	138	155	119
55°	101	109	92	85	101	90
65°	56	62	50	44	56	56
75°	21	28	14	16	21	23
85°	1	6	0	1	1	2
90°	0	1	0	0	0	0
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0



TEST NUMBER: P272206

CATALOG NUMBER: LA4069301EWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	271.8	271.8	271.8	271.8	271.8	271.8	271.8	271.8	271.8	271.8	271.8
0.5°	271.8	271.9	271.9	271.9	271.9	271.8	271.8	271.8	271.7	271.7	271.7
1°	271.9	271.9	272.0	272.0	272.0	271.9	271.8	271.7	271.6	271.6	271.5
1.5°	271.8	272.0	272.0	272.0	272.0	271.9	271.8	271.7	271.5	271.4	271.3
2°	271.8	271.9	272.1	272.0	272.0	271.9	271.8	271.5	271.3	271.3	271.2
2.5°	271.7	271.9	272.0	272.0	272.0	271.8	271.7	271.4	271.2	271.1	270.9
3°	271.5	271.8	272.0	272.0	271.9	271.8	271.6	271.2	271.0	270.8	270.7
3.5°	271.3	271.7	271.9	271.9	271.9	271.7	271.5	271.1	270.7	270.5	270.3
4°	271.2	271.6	271.8	271.8	271.8	271.6	271.3	270.9	270.5	270.2	270.0
4.5°	271.0	271.4	271.6	271.7	271.7	271.3	271.1	270.6	270.2	270.0	269.7
5°	270.9	271.3	271.5	271.5	271.5	271.2	270.8	270.3	269.9	269.6	269.3
5.5°	270.5	271.0	271.2	271.3	271.3	271.0	270.6	270.1	269.5	269.2	268.9
6°	270.3	270.8	271.1	271.1	271.1	270.7	270.3	269.7	269.2	268.8	268.5
6.5°	269.9	270.5	270.7	270.9	270.9	270.5	270.0	269.4	268.7	268.4	268.1
7°	269.6	270.2	270.5	270.6	270.6	270.2	269.6	269.0	268.4	267.9	267.6
7.5°	269.3	269.9	270.1	270.3	270.3	269.8	269.3	268.6	267.9	267.4	267.0
8°	268.9	269.5	269.8	270.0	270.0	269.5	268.9	268.1	267.4	266.9	266.5
8.5°	268.5	269.1	269.4	269.6	269.6	269.1	268.5	267.7	267.0	266.4	265.9
9°	268.0	268.8	269.1	269.2	269.3	268.6	268.0	267.1	266.4	265.8	265.4
9.5°	267.5	268.2	268.7	268.8	268.8	268.2	267.5	266.6	265.9	265.2	264.7
10°	267.1	267.8	268.3	268.4	268.5	267.7	267.0	266.1	265.3	264.6	264.1
10.5°	266.5	267.3	267.7	268.0	267.9	267.2	266.5	265.5	264.7	263.9	263.4
11°	265.9	266.8	267.3	267.5	267.4	266.7	266.0	264.9	264.0	263.2	262.7
11.5°	265.4	266.3	266.7	267.0	267.0	266.2	265.3	264.3	263.4	262.5	262.0
12°	264.7	265.7	266.3	266.4	266.5	265.6	264.8	263.6	262.6	261.8	261.2
12.5°	264.1	265.0	265.6	265.8	265.8	265.1	264.2	262.9	261.9	261.0	260.4
13°	263.4	264.5	265.1	265.2	265.2	264.4	263.5	262.2	261.1	260.2	259.5
13.5°	262.6	263.8	264.4	264.6	264.6	263.8	262.7	261.5	260.4	259.4	258.7
14°	262.0	263.2	263.9	264.0	264.0	263.1	262.0	260.7	259.5	258.5	257.8
14.5°	261.2	262.4	263.1	263.3	263.3	262.4	261.2	260.0	258.7	257.6	256.9
15°	260.4	261.7	262.4	262.6	262.6	261.7	260.5	259.0	257.8	256.7	255.9
15.5°	259.6	260.8	261.6	261.8	261.9	260.9	259.7	258.3	256.9	255.8	254.9
16°	258.7	260.1	260.9	261.1	261.2	260.1	258.8	257.3	256.0	254.8	253.9
16.5°	257.9	259.2	260.0	260.3	260.3	259.3	257.9	256.4	255.0	253.8	252.9
17°	257.0	258.4	259.3	259.5	259.6	258.4	257.1	255.4	254.0	252.7	251.8
17.5°	256.1	257.4	258.3	258.6	258.7	257.5	256.1	254.5	253.0	251.6	250.7
18°	255.1	256.6	257.5	257.8	257.8	256.6	255.2	253.5	252.0	250.5	249.6
18.5°	254.1	255.6	256.6	256.9	256.9	255.7	254.2	252.5	250.9	249.4	248.3
19°	253.1	254.7	255.6	256.0	256.0	254.7	253.2	251.3	249.7	248.2	247.2
19.5°	252.0	253.6	254.6	255.0	255.1	253.7	252.1	250.3	248.5	247.0	245.9
20°	250.9	252.6	253.7	254.0	254.0	252.7	251.1	249.1	247.4	245.7	244.6
20.5°	249.8	251.5	252.6	253.0	253.0	251.6	250.0	248.0	246.2	244.5	243.3
21°	248.7	250.4	251.6	251.9	252.0	250.5	248.9	246.8	244.9	243.2	242.0
21.5°	247.4	249.3	250.4	250.8	251.0	249.4	247.6	245.6	243.6	241.7	240.5
22°	246.3	248.1	249.3	249.8	249.8	248.2	246.5	244.2	242.2	240.4	239.2



TEST NUMBER: P272206

CATALOG NUMBER: LA4069301EWH

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
22.5°	244.9	246.9	248.1	248.6	248.6	247.1	245.2	243.0	240.9	239.0	237.6
23°	243.6	245.6	246.9	247.5	247.5	245.8	243.9	241.6	239.5	237.5	236.2
23.5°	242.3	244.4	245.6	246.2	246.2	244.5	242.6	240.2	238.1	236.0	234.6
24°	241.0	243.0	244.4	245.0	245.0	243.3	241.3	238.8	236.6	234.5	233.1
24.5°	239.5	241.7	243.0	243.6	243.7	242.0	239.9	237.4	235.0	232.9	231.4
25°	238.1	240.3	241.7	242.4	242.4	240.6	238.5	235.9	233.5	231.4	229.8
25.5°	236.6	238.8	240.3	241.0	241.0	239.3	237.1	234.4	232.0	229.7	228.1
26°	235.2	237.3	238.9	239.6	239.6	237.8	235.6	232.8	230.3	228.1	226.5
26.5°	233.5	235.9	237.4	238.1	238.2	236.3	234.1	231.3	228.7	226.4	224.7
27°	232.0	234.4	236.0	236.7	236.8	234.8	232.5	229.6	227.0	224.6	223.0
27.5°	230.4	232.8	234.4	235.2	235.3	233.3	230.9	228.0	225.3	222.8	221.0
28°	228.7	231.2	232.9	233.7	233.7	231.7	229.3	226.3	223.6	221.0	219.3
28.5°	227.1	229.6	231.3	232.1	232.2	230.1	227.6	224.6	221.8	219.2	217.3
29°	225.4	228.0	229.7	230.5	230.6	228.5	226.0	222.8	219.9	217.3	215.5
29.5°	223.6	226.3	228.0	228.8	228.9	226.8	224.2	221.0	218.1	215.4	213.4
30°	221.8	224.5	226.3	227.1	227.3	225.1	222.5	219.2	216.3	213.5	211.5
30.5°	220.0	222.8	224.6	225.4	225.5	223.4	220.6	217.4	214.4	211.5	209.5
31°	218.2	220.9	222.9	223.7	223.8	221.6	218.9	215.5	212.5	209.5	207.6
31.5°	216.3	219.2	221.1	221.9	222.1	219.8	217.0	213.6	210.4	207.5	205.4
32°	214.4	217.3	219.3	220.1	220.3	217.9	215.1	211.7	208.5	205.4	203.4
32.5°	212.4	215.5	217.4	218.3	218.4	216.0	213.2	209.7	206.4	203.3	201.1
33°	210.5	213.5	215.6	216.5	216.5	214.2	211.2	207.7	204.3	201.2	199.1
33.5°	208.5	211.5	213.7	214.4	214.7	212.3	209.3	205.7	202.2	199.1	196.8
34°	206.5	209.5	211.7	212.6	212.7	210.2	207.3	203.6	200.1	196.9	194.6
34.5°	204.4	207.6	209.7	210.6	210.7	208.3	205.2	201.5	197.9	194.7	192.3
35°	202.3	205.4	207.8	208.6	208.8	206.2	203.2	199.4	195.7	192.4	190.1
35.5°	200.1	203.4	205.7	206.4	206.7	204.2	201.0	197.2	193.4	190.1	187.7
36°	198.0	201.2	203.7	204.5	204.6	202.1	198.9	195.0	191.2	187.8	185.4
36.5°	195.8	199.2	201.5	202.4	202.6	200.0	196.8	192.8	188.9	185.5	183.0
37°	193.6	197.0	199.5	200.3	200.4	197.8	194.6	190.5	186.6	183.1	180.7
37.5°	191.3	194.8	197.3	198.2	198.3	195.7	192.3	188.3	184.2	180.7	178.2
38°	189.1	192.6	195.1	196.0	196.1	193.4	190.1	185.9	181.9	178.3	175.8
38.5°	186.8	190.4	192.8	193.8	193.9	191.2	187.8	183.5	179.5	175.9	173.3
39°	184.4	188.0	190.6	191.5	191.7	188.9	185.4	181.2	177.1	173.4	170.9
39.5°	182.1	185.8	188.3	189.3	189.4	186.6	183.1	178.9	174.7	170.9	168.3
40°	179.7	183.4	186.0	187.0	187.1	184.3	180.7	176.5	172.2	168.4	165.8
40.5°	177.3	181.0	183.7	184.6	184.8	182.0	178.4	174.0	169.6	165.9	163.2
41°	174.8	178.7	181.3	182.3	182.4	179.6	176.0	171.5	167.2	163.3	160.7
41.5°	172.4	176.3	179.0	179.9	180.1	177.2	173.5	169.0	164.6	160.8	158.1
42°	169.9	173.9	176.6	177.5	177.7	174.8	171.1	166.5	162.1	158.2	155.5
42.5°	167.4	171.3	174.1	175.1	175.2	172.4	168.6	164.0	159.5	155.6	152.8
43°	164.8	168.9	171.7	172.7	172.8	169.9	166.1	161.4	156.9	153.0	150.2
43.5°	162.3	166.4	169.2	170.2	170.3	167.3	163.5	158.8	154.3	150.4	147.5
44°	159.7	163.9	166.7	167.7	167.9	164.9	161.0	156.3	151.7	147.7	144.8
44.5°	157.2	161.4	164.2	165.2	165.3	162.3	158.4	153.6	149.0	145.0	142.1



TEST NUMBER: P272206

CATALOG NUMBER: LA4069301EWH

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
45°	154.6	158.8	161.7	162.7	162.7	159.8	155.7	151.0	146.3	142.3	139.4
45.5°	152.0	156.2	159.1	160.1	160.2	157.2	153.2	148.3	143.7	139.7	136.7
46°	149.3	153.6	156.5	157.5	157.7	154.6	150.5	145.6	141.0	136.9	134.0
46.5°	146.7	151.0	153.9	154.9	155.1	152.0	147.9	143.0	138.3	134.2	131.3
47°	144.0	148.4	151.2	152.3	152.4	149.3	145.2	140.3	135.5	131.5	128.5
47.5°	141.4	145.7	148.6	149.6	149.8	146.7	142.5	137.6	132.8	128.8	125.8
48°	138.7	143.0	146.0	147.0	147.2	144.0	139.9	134.8	130.1	126.0	123.0
48.5°	136.0	140.4	143.3	144.3	144.4	141.3	137.1	132.1	127.4	123.2	120.2
49°	133.2	137.7	140.6	141.6	141.8	138.6	134.4	129.4	124.5	120.4	117.4
49.5°	130.6	134.9	137.9	138.9	139.1	135.9	131.7	126.8	121.7	117.6	114.7
50°	127.8	132.3	135.2	136.2	136.4	133.2	128.9	124.0	118.9	114.9	112.0
50.5°	125.1	129.5	132.5	133.5	133.7	130.5	126.2	121.2	116.1	112.2	109.3
51°	122.4	126.8	129.7	130.8	131.0	127.7	123.4	118.4	113.6	109.5	106.6
51.5°	119.7	124.0	127.0	128.0	128.3	125.0	120.6	115.7	110.8	106.8	103.9
52°	116.9	121.4	124.3	125.3	125.5	122.2	117.9	112.9	108.2	104.1	101.3
52.5°	114.2	118.6	121.6	122.6	122.8	119.5	115.1	110.2	105.5	101.5	98.7
53°	111.5	115.9	118.8	119.9	120.0	116.7	112.4	107.5	102.9	98.9	96.1
53.5°	108.9	113.3	116.1	117.1	117.3	114.0	109.7	104.9	100.2	96.3	93.5
54°	106.2	110.6	113.4	114.4	114.5	111.3	107.0	102.2	97.6	93.7	91.1
54.5°	103.6	107.9	110.8	111.7	111.8	108.6	104.3	99.6	95.1	91.2	88.5
55°	101.0	105.3	108.1	109.0	109.2	105.9	101.7	97.0	92.5	88.8	86.1
55.5°	98.4	102.6	105.4	106.3	106.5	103.3	99.1	94.5	90.0	86.3	83.7
56°	95.8	100.0	102.8	103.7	103.9	100.7	96.6	92.0	87.6	83.9	81.3
56.5°	93.3	97.4	100.2	101.0	101.2	98.1	94.0	89.5	85.1	81.5	79.0
57°	90.8	94.9	97.6	98.5	98.6	95.5	91.5	87.0	82.7	79.2	76.6
57.5°	88.4	92.5	95.1	95.9	96.0	93.0	89.0	84.6	80.4	76.9	74.5
58°	85.8	89.9	92.5	93.4	93.5	90.5	86.6	82.2	78.1	74.6	72.2
58.5°	83.5	87.4	90.1	90.9	91.0	88.0	84.2	79.9	75.8	72.4	70.0
59°	81.1	85.1	87.6	88.4	88.5	85.6	81.8	77.6	73.5	70.2	67.9
59.5°	78.8	82.7	85.2	85.9	86.1	83.2	79.4	75.3	71.3	68.0	65.7
60°	76.5	80.3	82.8	83.6	83.6	80.9	77.1	73.0	69.2	65.9	63.7
60.5°	74.3	78.0	80.5	81.2	81.3	78.5	74.9	70.8	67.1	63.8	61.6
61°	72.0	75.7	78.2	78.9	79.0	76.3	72.7	68.7	64.9	61.8	59.6
61.5°	69.9	73.5	75.9	76.5	76.7	74.0	70.5	66.5	62.9	59.8	57.7
62°	67.7	71.3	73.6	74.3	74.5	71.8	68.3	64.4	60.9	57.8	55.7
62.5°	65.7	69.1	71.4	72.1	72.2	69.6	66.2	62.3	58.9	55.9	53.8
63°	63.5	66.9	69.2	69.9	70.0	67.5	64.2	60.2	56.9	54.0	52.0
63.5°	61.6	65.0	67.1	67.8	67.9	65.4	62.1	58.2	55.0	52.2	50.1
64°	59.6	62.9	65.1	65.7	65.8	63.3	60.1	56.2	53.1	50.3	48.3
64.5°	57.6	60.9	63.0	63.6	63.7	61.3	58.1	54.3	51.3	48.5	46.6
65°	55.6	58.9	60.9	61.6	61.7	59.3	56.2	52.4	49.5	46.8	44.9
65.5°	53.6	56.9	59.0	59.5	59.7	57.4	54.3	50.5	47.6	45.1	43.2
66°	51.8	55.0	57.0	57.6	57.7	55.4	52.4	48.6	45.9	43.3	41.5
66.5°	50.1	53.2	55.1	55.7	55.8	53.6	50.6	46.8	44.2	41.7	39.9
67°	48.4	51.4	53.9	53.5	53.9	51.7	48.8	45.0	42.5	40.1	38.3



TEST NUMBER: P272206

CATALOG NUMBER: LA4069301EWH

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
67.5°	46.6	49.6	51.9	51.8	52.0	49.9	47.0	43.2	40.7	38.5	36.7
68°	44.9	47.8	50.0	50.1	50.2	48.2	45.3	41.3	38.7	36.9	35.2
68.5°	43.2	46.0	48.0	48.3	48.4	46.4	43.6	39.5	36.8	35.4	33.7
69°	41.6	44.3	46.1	46.6	46.7	44.7	41.9	37.7	34.9	33.8	32.2
69.5°	39.9	42.6	44.3	44.9	44.9	43.0	40.3	35.9	33.0	32.2	30.7
70°	38.3	40.9	42.7	43.2	43.2	41.4	38.7	34.1	31.1	30.5	29.4
70.5°	36.8	39.3	41.0	41.5	41.6	39.7	37.1	32.4	29.2	28.8	27.9
71°	35.2	37.7	39.4	39.9	39.9	38.2	35.5	30.7	27.4	27.1	26.6
71.5°	33.4	36.2	37.8	38.3	38.4	36.6	34.0	29.0	25.6	25.5	25.2
72°	31.7	34.6	36.2	36.7	36.8	35.1	32.5	27.4	23.9	23.8	24.0
72.5°	29.9	33.1	34.7	35.2	35.2	33.6	31.0	25.7	22.1	22.3	22.6
73°	28.1	31.7	33.2	33.7	33.7	32.1	29.6	24.2	20.4	20.7	21.3
73.5°	26.3	30.2	31.7	32.2	32.3	30.6	28.2	22.7	18.8	19.2	20.1
74°	24.5	28.6	30.3	30.8	30.8	29.3	26.8	21.2	17.2	17.8	18.9
74.5°	22.8	27.1	28.9	29.3	29.4	27.8	25.4	19.8	15.7	16.4	17.6
75°	21.0	25.5	27.3	27.9	28.0	26.5	24.1	18.3	14.3	15.1	16.5
75.5°	19.3	23.9	25.7	26.6	26.7	25.1	22.8	17.0	13.1	13.9	15.3
76°	17.7	22.3	24.3	25.2	25.3	23.8	21.5	15.7	11.9	12.8	14.1
76.5°	16.1	20.8	22.7	23.9	24.0	22.6	20.2	14.5	10.7	11.6	13.1
77°	14.6	19.4	21.3	22.6	22.7	21.3	19.0	13.4	9.5	10.5	12.1
77.5°	13.1	17.9	19.9	21.4	21.5	20.1	17.7	12.3	8.3	9.3	11.0
78°	11.7	16.5	18.6	20.1	20.2	18.9	16.6	11.2	7.3	8.4	10.0
78.5°	10.4	15.2	17.3	18.9	19.1	17.7	15.4	10.1	6.4	7.5	8.9
79°	9.2	13.9	16.1	17.7	17.9	16.6	14.3	9.0	5.6	6.7	8.0
79.5°	8.1	12.6	14.9	16.6	16.7	15.5	13.2	8.1	4.9	5.9	7.1
80°	7.1	11.4	13.7	15.5	15.6	14.4	12.2	7.3	4.1	5.1	6.3
80.5°	6.2	10.3	12.7	14.4	14.5	13.4	11.1	6.5	3.5	4.3	5.5
81°	5.4	9.2	11.6	13.3	13.5	12.4	10.1	5.7	2.8	3.6	4.8
81.5°	4.7	8.2	10.6	12.3	12.5	11.4	9.0	5.0	2.2	3.1	4.1
82°	4.0	7.3	9.7	11.3	11.5	10.4	8.1	4.2	1.7	2.6	3.4
82.5°	3.2	6.4	8.8	10.3	10.5	9.4	7.3	3.5	1.3	2.1	2.8
83°	2.5	5.6	8.0	9.4	9.4	8.5	6.4	3.0	1.0	1.7	2.3
83.5°	1.8	4.9	7.2	8.5	8.6	7.6	5.6	2.5	0.8	1.4	1.7
84°	1.3	4.2	6.4	7.6	7.7	6.8	4.9	2.1	0.6	1.1	1.3
84.5°	1.0	3.4	5.7	6.7	6.8	6.0	4.2	1.7	0.5	0.8	1.0
85°	0.7	2.7	5.0	5.9	6.0	5.2	3.6	1.4	0.4	0.7	0.7
85.5°	0.5	2.2	4.4	5.2	5.2	4.5	3.0	1.1	0.4	0.5	0.6
86°	0.4	1.8	3.7	4.5	4.5	3.8	2.4	0.9	0.3	0.4	0.4
86.5°	0.3	1.4	3.1	3.8	3.8	3.1	1.9	0.7	0.3	0.3	0.3
87°	0.3	1.1	2.5	3.0	3.1	2.5	1.5	0.6	0.2	0.3	0.1
87.5°	0.3	0.8	1.9	2.4	2.5	1.9	1.1	0.5	0.2	0.2	0.1
88°	0.2	0.6	1.5	1.9	1.9	1.5	0.8	0.4	0.1	0.1	0.1
88.5°	0.2	0.5	1.1	1.4	1.5	1.1	0.7	0.3	0.1	0.1	0.1
89°	0.1	0.4	0.8	1.0	1.1	0.8	0.5	0.2	0.1	0.1	0.1
89.5°	0.1	0.3	0.6	0.8	0.8	0.6	0.4	0.2	0.1	0.1	0.1



TEST NUMBER: P272206

CATALOG NUMBER: LA4069301EWH

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
90°	0.1	0.2	0.5	0.6	0.6	0.5	0.2	0.2	0.1	0.1	0.1
90.5°	0.1	0.1	0.3	0.4	0.4	0.3	0.1	0.2	0.1	0.1	0.1
91°	0.1	0.1	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1
91.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
92°	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.1	0.0
92.5°	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.1	0.0
93°	0.0	0.1	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.1	0.0
93.5°	0.0	0.1	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.1	0.0
94°	0.0	0.1	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.1	0.0
94.5°	0.0	0.1	0.1	0.1	0.0	0.1	0.1	0.1	0.0	0.1	0.0
95°	0.0	0.0	0.1	0.1	0.0	0.1	0.1	0.1	0.0	0.1	0.0
95.5°	0.0	0.0	0.1	0.1	0.0	0.1	0.1	0.0	0.0	0.1	0.0
96°	0.0	0.0	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.0
96.5°	0.0	0.0	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.0
97°	0.0	0.0	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.0
97.5°	0.1	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98°	0.1	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98.5°	0.1	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99°	0.1	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99.5°	0.1	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.1	0.0	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
100.5°	0.1	0.0	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
101°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
101.5°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
102°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
103°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
103.5°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.1	0.0
104°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.1	0.1
104.5°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.1	0.1
105°	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.1	0.1
105.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.1	0.1
106°	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.1	0.1
106.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.1	0.1
107°	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.1	0.1	0.1
107.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.1	0.1	0.1
108°	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.1	0.1	0.1
108.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1
109°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
109.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
110°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
110.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
111°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
111.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
112°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1



TEST NUMBER: P272206

CATALOG NUMBER: LA4069301EWH

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
112.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
113°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
113.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
114°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
114.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
115°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
115.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
116°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
116.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
117°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
117.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
118°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
118.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
119°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
119.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
120°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
120.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
121°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
121.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
122°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
122.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
123°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
123.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
124°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
124.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
125°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
125.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
126°	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
126.5°	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
127°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
127.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
128°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
128.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
129°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
129.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
130°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
130.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
131°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
131.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
132°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
132.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
133°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
133.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
134°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
134.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1



TEST NUMBER: P272206

CATALOG NUMBER: LA4069301EWH

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
135°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
135.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
136°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
136.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
138°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
138.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
139°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
139.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
141°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
141.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
142°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
142.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
143°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.2	0.1
143.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.2	0.2	0.1
144°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.2	0.2	0.2
144.5°	0.3	0.3	0.2	0.2	0.1	0.1	0.1	0.1	0.2	0.2	0.2
145°	0.3	0.3	0.3	0.2	0.1	0.1	0.1	0.2	0.2	0.2	0.2
145.5°	0.3	0.3	0.3	0.3	0.1	0.1	0.1	0.2	0.2	0.2	0.2
146°	0.3	0.3	0.3	0.3	0.1	0.1	0.2	0.2	0.2	0.2	0.2
146.5°	0.3	0.3	0.3	0.3	0.1	0.1	0.2	0.2	0.2	0.2	0.2
147°	0.3	0.3	0.3	0.3	0.1	0.2	0.2	0.2	0.2	0.2	0.2
147.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
148°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
148.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
149°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
149.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
150°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
150.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
151°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
151.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
152°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
152.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
153°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
153.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
154°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
154.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
155°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
155.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
156°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
156.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
157°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2



TEST NUMBER: P272206

CATALOG NUMBER: LA4069301EWH

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
157.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
158°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
158.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
159°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
159.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
160°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
160.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
161°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
161.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
162°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
162.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
163°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
163.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
164°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
164.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
165°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
165.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
166°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
166.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
167°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
167.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
168°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
168.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
169°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
169.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
170°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
170.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
171°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
171.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
172°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
172.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
173°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
173.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.3	0.3	0.3	0.3
174°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
174.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
175°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
175.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
176°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
176.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
177°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
177.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
178°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
178.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
179°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
179.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3



TEST NUMBER: P272206

CATALOG NUMBER: LA4069301EWH

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
180°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3



TEST NUMBER: P272206

CATALOG NUMBER: LA4069301EWH

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	271.8	271.8	271.8	271.8	271.8	271.8
0.5°	271.7	271.7	271.7	271.8	271.8	271.8
1°	271.5	271.5	271.6	271.6	271.7	271.9
1.5°	271.3	271.3	271.3	271.5	271.7	271.8
2°	271.1	271.1	271.2	271.3	271.5	271.8
2.5°	270.9	270.9	271.0	271.2	271.4	271.7
3°	270.6	270.6	270.8	271.0	271.3	271.5
3.5°	270.3	270.3	270.5	270.8	271.1	271.3
4°	270.0	270.0	270.2	270.5	270.9	271.2
4.5°	269.7	269.6	269.8	270.2	270.6	271.0
5°	269.3	269.2	269.5	269.9	270.3	270.9
5.5°	268.9	268.9	269.1	269.6	270.1	270.5
6°	268.4	268.4	268.7	269.2	269.7	270.3
6.5°	268.0	268.0	268.3	268.8	269.4	269.9
7°	267.4	267.5	267.8	268.3	269.1	269.6
7.5°	267.0	266.9	267.3	267.9	268.7	269.3
8°	266.4	266.4	266.8	267.4	268.2	268.9
8.5°	265.8	265.9	266.2	266.9	267.8	268.5
9°	265.3	265.2	265.7	266.4	267.3	268.0
9.5°	264.7	264.6	265.1	265.8	266.7	267.5
10°	264.0	264.0	264.4	265.2	266.2	267.1
10.5°	263.3	263.3	263.8	264.6	265.6	266.5
11°	262.6	262.5	263.1	264.0	265.0	265.9
11.5°	261.9	261.8	262.4	263.3	264.4	265.4
12°	261.0	261.0	261.6	262.6	263.7	264.7
12.5°	260.2	260.2	260.8	261.8	263.1	264.1
13°	259.4	259.4	260.0	261.1	262.4	263.4
13.5°	258.5	258.4	259.2	260.3	261.6	262.6
14°	257.6	257.6	258.3	259.4	260.8	262.0
14.5°	256.7	256.6	257.4	258.6	260.0	261.2
15°	255.8	255.7	256.4	257.7	259.2	260.4
15.5°	254.8	254.6	255.5	256.8	258.3	259.6
16°	253.7	253.6	254.5	255.8	257.4	258.7
16.5°	252.7	252.6	253.4	254.8	256.5	257.9
17°	251.6	251.5	252.3	253.8	255.6	257.0
17.5°	250.5	250.4	251.3	252.8	254.6	256.1
18°	249.3	249.1	250.1	251.7	253.5	255.1
18.5°	248.1	248.0	249.0	250.6	252.5	254.1
19°	246.8	246.7	247.7	249.4	251.4	253.1
19.5°	245.6	245.5	246.6	248.2	250.3	252.0
20°	244.3	244.2	245.2	247.0	249.1	250.9
20.5°	243.0	242.8	243.9	245.7	247.9	249.8
21°	241.6	241.5	242.5	244.5	246.7	248.7
21.5°	240.3	240.0	241.2	243.1	245.4	247.4
22°	238.7	238.6	239.7	241.8	244.1	246.3



TEST NUMBER: P272206

CATALOG NUMBER: LA4069301EWH

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
22.5°	237.3	237.1	238.4	240.4	242.8	244.9
23°	235.7	235.6	236.8	239.0	241.5	243.6
23.5°	234.3	234.0	235.4	237.5	240.0	242.3
24°	232.6	232.4	233.8	236.1	238.6	241.0
24.5°	231.0	230.8	232.2	234.4	237.2	239.5
25°	229.4	229.1	230.5	232.9	235.6	238.1
25.5°	227.7	227.5	229.0	231.3	234.2	236.6
26°	225.9	225.8	227.1	229.7	232.5	235.2
26.5°	224.2	224.0	225.6	228.0	231.0	233.5
27°	222.4	222.2	223.7	226.3	229.3	232.0
27.5°	220.6	220.4	222.0	224.6	227.7	230.4
28°	218.6	218.5	220.0	222.8	225.9	228.7
28.5°	216.9	216.6	218.3	220.9	224.3	227.1
29°	214.9	214.7	216.3	219.2	222.4	225.4
29.5°	212.9	212.7	214.5	217.3	220.6	223.6
30°	210.9	210.7	212.5	215.4	218.7	221.8
30.5°	209.0	208.7	210.5	213.4	216.9	220.0
31°	206.8	206.6	208.4	211.5	214.9	218.2
31.5°	204.8	204.5	206.5	209.5	213.1	216.3
32°	202.6	202.3	204.3	207.5	211.0	214.4
32.5°	200.5	200.4	202.3	205.4	209.1	212.4
33°	198.3	198.1	200.0	203.3	207.0	210.5
33.5°	196.2	195.9	197.9	201.2	205.0	208.5
34°	193.9	193.6	195.7	199.0	202.8	206.5
34.5°	191.6	191.4	193.5	196.9	200.7	204.4
35°	189.3	189.1	191.2	194.7	198.5	202.3
35.5°	187.0	186.8	189.0	192.4	196.5	200.1
36°	184.6	184.5	186.6	190.1	194.1	198.0
36.5°	182.2	182.0	184.3	187.8	191.9	195.8
37°	179.8	179.6	181.9	185.4	189.5	193.6
37.5°	177.5	177.2	179.6	183.1	187.3	191.3
38°	174.9	174.8	177.1	180.7	184.9	189.1
38.5°	172.5	172.3	174.7	178.4	182.7	186.8
39°	170.0	169.7	172.1	175.9	180.2	184.4
39.5°	167.5	167.3	169.8	173.5	177.8	182.1
40°	164.9	164.7	167.2	171.0	175.4	179.7
40.5°	162.3	162.1	164.7	168.5	172.9	177.3
41°	159.8	159.6	162.1	166.0	170.3	174.8
41.5°	157.2	157.0	159.6	163.5	167.9	172.4
42°	154.5	154.3	156.9	160.9	165.2	169.9
42.5°	151.9	151.7	154.4	158.4	162.8	167.4
43°	149.3	149.0	151.7	155.7	160.2	164.8
43.5°	146.5	146.4	149.1	153.1	157.6	162.3
44°	143.8	143.6	146.4	150.4	154.9	159.7
44.5°	141.1	140.9	143.8	147.8	152.4	157.2



TEST NUMBER: P272206

CATALOG NUMBER: LA4069301EWH

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
45°	138.4	138.2	141.0	145.2	149.7	154.6
45.5°	135.7	135.4	138.4	142.5	147.1	152.0
46°	133.0	132.7	135.7	139.8	144.4	149.3
46.5°	130.2	130.0	132.9	137.1	141.7	146.7
47°	127.5	127.3	130.2	134.3	139.0	144.0
47.5°	124.7	124.5	127.5	131.7	136.3	141.4
48°	121.9	121.8	124.7	128.9	133.6	138.7
48.5°	119.1	119.1	122.0	126.2	130.8	136.0
49°	116.3	116.3	119.2	123.4	128.1	133.2
49.5°	113.6	113.6	116.5	120.7	125.3	130.6
50°	110.9	110.8	113.8	118.0	122.6	127.8
50.5°	108.2	108.1	111.1	115.3	119.9	125.1
51°	105.5	105.5	108.4	112.6	117.3	122.4
51.5°	102.9	102.9	105.8	109.9	114.5	119.7
52°	100.3	100.3	103.2	107.3	111.8	116.9
52.5°	97.7	97.6	100.5	104.6	109.1	114.2
53°	95.1	95.0	97.9	102.0	106.4	111.5
53.5°	92.6	92.5	95.3	99.4	103.8	108.9
54°	90.0	90.1	92.8	96.8	101.2	106.2
54.5°	87.6	87.5	90.3	94.3	98.6	103.6
55°	85.1	85.2	87.8	91.8	96.1	101.0
55.5°	82.7	82.7	85.4	89.3	93.5	98.4
56°	80.4	80.3	83.0	86.9	91.0	95.8
56.5°	78.1	78.0	80.6	84.3	88.5	93.3
57°	75.8	75.7	78.3	82.0	86.1	90.8
57.5°	73.5	73.5	76.1	79.7	83.7	88.4
58°	71.3	71.3	73.8	77.4	81.4	85.8
58.5°	69.2	69.1	71.6	75.2	79.0	83.5
59°	67.0	66.9	69.4	72.9	76.7	81.1
59.5°	64.9	64.9	67.3	70.7	74.5	78.8
60°	62.9	62.8	65.1	68.6	72.3	76.5
60.5°	60.8	60.8	63.1	66.4	70.1	74.3
61°	58.8	58.8	61.1	64.4	67.9	72.0
61.5°	56.9	56.8	59.1	62.3	65.8	69.9
62°	55.0	54.9	57.1	60.3	63.8	67.7
62.5°	53.1	53.1	55.2	58.3	61.7	65.7
63°	51.2	51.3	54.0	56.4	59.7	63.5
63.5°	49.4	49.5	52.1	54.5	57.8	61.6
64°	47.6	47.7	50.1	52.7	55.9	59.6
64.5°	45.9	45.9	48.1	50.9	53.8	57.6
65°	44.2	44.2	46.1	49.1	52.0	55.6
65.5°	42.5	42.4	44.4	47.3	50.2	53.6
66°	40.9	40.8	42.7	45.5	48.5	51.8
66.5°	39.3	39.2	41.1	43.8	46.7	50.1
67°	37.7	37.6	39.4	42.1	45.0	48.4



TEST NUMBER: P272206

CATALOG NUMBER: LA4069301EWH

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
67.5°	36.1	36.0	37.9	40.4	43.3	46.6
68°	34.6	34.5	36.3	38.8	41.6	44.9
68.5°	33.1	33.0	34.7	37.2	40.0	43.2
69°	31.6	31.5	33.2	35.7	38.4	41.6
69.5°	30.2	30.1	31.8	34.2	36.8	39.9
70°	28.7	28.7	30.3	32.7	35.3	38.3
70.5°	27.4	27.3	28.9	31.2	33.8	36.8
71°	26.0	25.9	27.5	29.8	32.3	35.2
71.5°	24.7	24.6	26.1	28.3	30.8	33.4
72°	23.4	23.3	24.8	26.9	29.2	31.7
72.5°	22.1	22.0	23.5	25.6	27.7	29.9
73°	20.9	20.8	22.2	24.3	26.1	28.1
73.5°	19.6	19.5	21.0	23.0	24.5	26.3
74°	18.4	18.3	19.7	21.7	22.9	24.5
74.5°	17.3	17.2	18.5	20.4	21.4	22.8
75°	16.2	16.0	17.3	19.2	19.9	21.0
75.5°	15.0	14.9	16.2	18.0	18.4	19.3
76°	13.9	13.8	15.1	16.8	17.0	17.7
76.5°	12.9	12.8	14.0	15.6	15.6	16.1
77°	11.9	11.8	12.9	14.5	14.3	14.6
77.5°	10.9	10.8	11.9	13.4	13.0	13.1
78°	9.9	9.8	10.9	12.3	11.8	11.7
78.5°	9.0	8.9	9.9	11.2	10.6	10.4
79°	8.1	8.0	9.0	10.2	9.5	9.2
79.5°	7.2	7.2	8.1	9.2	8.5	8.1
80°	6.4	6.3	7.2	8.3	7.6	7.1
80.5°	5.6	5.5	6.4	7.4	6.7	6.2
81°	4.8	4.8	5.6	6.5	5.8	5.4
81.5°	4.1	4.1	4.9	5.7	5.1	4.7
82°	3.4	3.5	4.2	5.0	4.4	4.0
82.5°	2.8	2.8	3.5	4.3	3.7	3.2
83°	2.2	2.2	2.8	3.6	3.0	2.5
83.5°	1.7	1.7	2.2	3.0	2.5	1.8
84°	1.3	1.2	1.7	2.4	2.0	1.3
84.5°	0.9	0.9	1.3	1.8	1.6	1.0
85°	0.7	0.7	0.9	1.4	1.3	0.7
85.5°	0.5	0.5	0.7	1.0	1.0	0.5
86°	0.4	0.4	0.5	0.8	0.8	0.4
86.5°	0.2	0.2	0.4	0.6	0.6	0.3
87°	0.1	0.1	0.2	0.4	0.5	0.3
87.5°	0.0	0.1	0.1	0.3	0.4	0.3
88°	0.0	0.1	0.1	0.1	0.3	0.2
88.5°	0.0	0.1	0.1	0.1	0.2	0.2
89°	0.0	0.1	0.1	0.1	0.1	0.1
89.5°	0.0	0.1	0.1	0.1	0.1	0.1



TEST NUMBER: P272206

CATALOG NUMBER: LA4069301EWH

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
90°	0.0	0.1	0.1	0.1	0.1	0.1
90.5°	0.0	0.1	0.1	0.1	0.1	0.1
91°	0.0	0.1	0.1	0.1	0.1	0.1
91.5°	0.0	0.1	0.1	0.1	0.1	0.1
92°	0.0	0.1	0.1	0.1	0.1	0.1
92.5°	0.0	0.1	0.1	0.1	0.1	0.1
93°	0.0	0.1	0.1	0.1	0.1	0.0
93.5°	0.0	0.1	0.1	0.1	0.0	0.0
94°	0.0	0.1	0.1	0.1	0.0	0.0
94.5°	0.0	0.1	0.1	0.1	0.0	0.0
95°	0.0	0.1	0.1	0.1	0.0	0.0
95.5°	0.0	0.1	0.1	0.1	0.0	0.0
96°	0.0	0.1	0.1	0.1	0.0	0.0
96.5°	0.0	0.1	0.1	0.1	0.0	0.0
97°	0.0	0.1	0.1	0.1	0.1	0.0
97.5°	0.0	0.1	0.1	0.1	0.1	0.1
98°	0.0	0.1	0.1	0.1	0.1	0.1
98.5°	0.0	0.1	0.1	0.1	0.1	0.1
99°	0.0	0.1	0.1	0.1	0.1	0.1
99.5°	0.0	0.1	0.1	0.1	0.1	0.1
100°	0.0	0.1	0.1	0.1	0.1	0.1
100.5°	0.0	0.1	0.1	0.1	0.1	0.1
101°	0.0	0.1	0.1	0.1	0.1	0.1
101.5°	0.0	0.1	0.1	0.1	0.1	0.1
102°	0.0	0.1	0.1	0.1	0.1	0.1
102.5°	0.0	0.1	0.1	0.1	0.1	0.1
103°	0.0	0.1	0.1	0.1	0.1	0.1
103.5°	0.0	0.1	0.1	0.1	0.1	0.1
104°	0.0	0.1	0.1	0.1	0.1	0.1
104.5°	0.0	0.1	0.1	0.1	0.1	0.1
105°	0.1	0.1	0.1	0.1	0.1	0.1
105.5°	0.1	0.1	0.1	0.1	0.1	0.1
106°	0.1	0.1	0.1	0.1	0.1	0.1
106.5°	0.1	0.1	0.1	0.1	0.1	0.1
107°	0.1	0.1	0.1	0.1	0.1	0.1
107.5°	0.1	0.1	0.1	0.1	0.1	0.1
108°	0.1	0.1	0.1	0.1	0.1	0.1
108.5°	0.1	0.1	0.1	0.1	0.1	0.1
109°	0.1	0.1	0.1	0.1	0.1	0.1
109.5°	0.1	0.1	0.1	0.1	0.1	0.1
110°	0.1	0.1	0.1	0.1	0.1	0.1
110.5°	0.1	0.1	0.1	0.1	0.1	0.1
111°	0.1	0.1	0.1	0.1	0.1	0.1
111.5°	0.1	0.1	0.1	0.1	0.1	0.1
112°	0.1	0.1	0.1	0.1	0.1	0.1



TEST NUMBER: P272206

CATALOG NUMBER: LA4069301EWH

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
112.5°	0.1	0.1	0.1	0.1	0.1	0.1
113°	0.1	0.1	0.1	0.1	0.1	0.1
113.5°	0.1	0.1	0.1	0.1	0.1	0.1
114°	0.1	0.1	0.1	0.1	0.1	0.1
114.5°	0.1	0.1	0.1	0.1	0.1	0.1
115°	0.1	0.1	0.1	0.1	0.1	0.1
115.5°	0.1	0.1	0.1	0.1	0.1	0.1
116°	0.1	0.1	0.1	0.1	0.1	0.1
116.5°	0.1	0.1	0.1	0.1	0.1	0.1
117°	0.1	0.1	0.1	0.1	0.1	0.1
117.5°	0.1	0.1	0.1	0.1	0.1	0.1
118°	0.1	0.1	0.1	0.1	0.1	0.1
118.5°	0.1	0.1	0.1	0.1	0.1	0.1
119°	0.1	0.1	0.1	0.1	0.1	0.1
119.5°	0.1	0.1	0.1	0.1	0.1	0.1
120°	0.1	0.1	0.1	0.1	0.1	0.1
120.5°	0.1	0.1	0.1	0.1	0.1	0.1
121°	0.1	0.1	0.1	0.1	0.1	0.1
121.5°	0.1	0.1	0.1	0.1	0.1	0.1
122°	0.1	0.1	0.1	0.1	0.1	0.1
122.5°	0.1	0.1	0.1	0.1	0.1	0.1
123°	0.1	0.1	0.1	0.1	0.1	0.1
123.5°	0.1	0.1	0.1	0.1	0.1	0.1
124°	0.1	0.2	0.2	0.1	0.1	0.1
124.5°	0.1	0.2	0.2	0.2	0.1	0.1
125°	0.1	0.2	0.2	0.2	0.1	0.1
125.5°	0.1	0.2	0.2	0.2	0.2	0.1
126°	0.1	0.2	0.2	0.2	0.2	0.2
126.5°	0.1	0.2	0.2	0.2	0.2	0.2
127°	0.1	0.2	0.2	0.2	0.2	0.2
127.5°	0.1	0.2	0.2	0.2	0.2	0.2
128°	0.1	0.2	0.2	0.2	0.2	0.2
128.5°	0.1	0.2	0.2	0.2	0.2	0.2
129°	0.1	0.2	0.2	0.2	0.2	0.2
129.5°	0.1	0.2	0.2	0.2	0.2	0.2
130°	0.1	0.2	0.2	0.2	0.2	0.2
130.5°	0.1	0.2	0.2	0.2	0.2	0.2
131°	0.1	0.2	0.2	0.2	0.2	0.2
131.5°	0.1	0.2	0.2	0.2	0.2	0.2
132°	0.1	0.2	0.2	0.2	0.2	0.2
132.5°	0.1	0.2	0.2	0.2	0.2	0.2
133°	0.1	0.2	0.2	0.2	0.2	0.2
133.5°	0.1	0.2	0.2	0.2	0.2	0.2
134°	0.1	0.2	0.2	0.2	0.2	0.2
134.5°	0.1	0.2	0.2	0.2	0.2	0.2



TEST NUMBER: P272206

CATALOG NUMBER: LA4069301EWH

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
135°	0.1	0.2	0.2	0.2	0.2	0.2
135.5°	0.1	0.2	0.2	0.2	0.2	0.2
136°	0.1	0.2	0.2	0.2	0.2	0.2
136.5°	0.1	0.2	0.2	0.2	0.2	0.2
137°	0.1	0.2	0.2	0.2	0.2	0.2
137.5°	0.1	0.2	0.2	0.2	0.2	0.2
138°	0.1	0.2	0.2	0.2	0.2	0.2
138.5°	0.1	0.2	0.2	0.2	0.2	0.2
139°	0.1	0.2	0.2	0.2	0.2	0.2
139.5°	0.1	0.2	0.2	0.2	0.2	0.2
140°	0.1	0.2	0.2	0.2	0.2	0.2
140.5°	0.1	0.2	0.2	0.2	0.2	0.2
141°	0.1	0.2	0.2	0.2	0.2	0.2
141.5°	0.1	0.2	0.2	0.2	0.2	0.2
142°	0.1	0.2	0.2	0.2	0.2	0.2
142.5°	0.1	0.2	0.2	0.2	0.2	0.2
143°	0.1	0.3	0.2	0.2	0.2	0.2
143.5°	0.1	0.3	0.3	0.3	0.2	0.2
144°	0.2	0.3	0.3	0.3	0.3	0.2
144.5°	0.2	0.3	0.3	0.3	0.3	0.3
145°	0.2	0.3	0.3	0.3	0.3	0.3
145.5°	0.2	0.3	0.3	0.3	0.3	0.3
146°	0.2	0.3	0.3	0.3	0.3	0.3
146.5°	0.2	0.3	0.3	0.3	0.3	0.3
147°	0.2	0.3	0.3	0.3	0.3	0.3
147.5°	0.2	0.3	0.3	0.3	0.3	0.3
148°	0.2	0.3	0.3	0.3	0.3	0.3
148.5°	0.2	0.3	0.3	0.3	0.3	0.3
149°	0.2	0.3	0.3	0.3	0.3	0.3
149.5°	0.2	0.3	0.3	0.3	0.3	0.3
150°	0.2	0.3	0.3	0.3	0.3	0.3
150.5°	0.2	0.3	0.3	0.3	0.3	0.3
151°	0.2	0.3	0.3	0.3	0.3	0.3
151.5°	0.2	0.3	0.3	0.3	0.3	0.3
152°	0.2	0.3	0.3	0.3	0.3	0.3
152.5°	0.2	0.3	0.3	0.3	0.3	0.3
153°	0.2	0.3	0.3	0.3	0.3	0.3
153.5°	0.2	0.3	0.3	0.3	0.3	0.3
154°	0.2	0.3	0.3	0.3	0.3	0.3
154.5°	0.2	0.3	0.3	0.3	0.3	0.3
155°	0.2	0.3	0.3	0.3	0.3	0.3
155.5°	0.2	0.3	0.3	0.3	0.3	0.3
156°	0.2	0.3	0.3	0.3	0.3	0.3
156.5°	0.2	0.3	0.3	0.3	0.3	0.3
157°	0.2	0.3	0.3	0.3	0.3	0.3



TEST NUMBER: P272206

CATALOG NUMBER: LA4069301EWH

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
157.5°	0.2	0.3	0.3	0.3	0.3	0.3
158°	0.2	0.3	0.3	0.3	0.3	0.3
158.5°	0.2	0.3	0.3	0.3	0.3	0.3
159°	0.2	0.3	0.3	0.3	0.3	0.3
159.5°	0.2	0.3	0.3	0.3	0.3	0.3
160°	0.2	0.3	0.3	0.3	0.3	0.3
160.5°	0.2	0.3	0.3	0.3	0.3	0.3
161°	0.2	0.3	0.3	0.3	0.3	0.3
161.5°	0.2	0.3	0.3	0.3	0.3	0.3
162°	0.2	0.3	0.3	0.3	0.3	0.3
162.5°	0.2	0.3	0.3	0.3	0.3	0.3
163°	0.2	0.3	0.3	0.3	0.3	0.3
163.5°	0.2	0.3	0.3	0.3	0.3	0.3
164°	0.2	0.3	0.3	0.3	0.3	0.3
164.5°	0.2	0.3	0.3	0.3	0.3	0.3
165°	0.2	0.3	0.3	0.3	0.3	0.3
165.5°	0.2	0.3	0.3	0.3	0.3	0.3
166°	0.2	0.3	0.3	0.3	0.3	0.3
166.5°	0.2	0.3	0.3	0.3	0.3	0.3
167°	0.2	0.3	0.3	0.3	0.3	0.3
167.5°	0.2	0.3	0.3	0.3	0.3	0.3
168°	0.2	0.3	0.3	0.3	0.3	0.3
168.5°	0.2	0.3	0.3	0.3	0.3	0.3
169°	0.2	0.3	0.3	0.3	0.3	0.3
169.5°	0.2	0.3	0.3	0.3	0.3	0.3
170°	0.2	0.3	0.3	0.3	0.3	0.3
170.5°	0.2	0.3	0.3	0.3	0.3	0.3
171°	0.2	0.3	0.3	0.3	0.3	0.3
171.5°	0.2	0.3	0.3	0.3	0.3	0.3
172°	0.2	0.3	0.3	0.3	0.3	0.3
172.5°	0.2	0.3	0.3	0.3	0.3	0.3
173°	0.3	0.3	0.3	0.3	0.3	0.3
173.5°	0.3	0.3	0.3	0.3	0.3	0.3
174°	0.3	0.3	0.3	0.3	0.3	0.3
174.5°	0.3	0.3	0.3	0.3	0.3	0.3
175°	0.3	0.3	0.3	0.3	0.3	0.3
175.5°	0.3	0.3	0.3	0.3	0.3	0.3
176°	0.3	0.3	0.3	0.3	0.3	0.3
176.5°	0.3	0.3	0.3	0.3	0.3	0.3
177°	0.3	0.3	0.3	0.3	0.3	0.3
177.5°	0.3	0.3	0.3	0.3	0.3	0.3
178°	0.3	0.3	0.3	0.3	0.3	0.3
178.5°	0.3	0.3	0.3	0.3	0.3	0.3
179°	0.3	0.3	0.3	0.3	0.3	0.3
179.5°	0.3	0.3	0.3	0.3	0.3	0.3



TEST NUMBER: P272206

CATALOG NUMBER: LA4069301EWH

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
180°	0.3	0.3	0.3	0.3	0.3	0.3

(END OF REPORT)