

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P886556

Luminaire Tested: ML310LSFL95FS1E-TIR4D25NFL-TL3RDMB-850LM-5000K

Issue Date: 7/18/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P886556  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2402-314-3)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 7/18/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML310LSFL95FS1E-TIR4D25NFL-TL3RDMB-850LM-5000K  
Description: 3IN ROUND ML FLEX, SELECTABLE CCT, WITH 25D TIR, MATTE BLACK TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 95CRI / 5000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1001.5 lumens  
Efficiency: N/A  
Efficacy: 73.6 lumens/watt  
Spacing Criteria (0/90/45): 0.47 / 0.47 / 0.5  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 13.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P886556  
CATALOG NUMBER: ML310LSFL95FS1E-TIR4D25NFL-TL3RDMB-850LM-5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P886556

CATALOG NUMBER: ML310LSFL95FS1E-TIR4D25NFL-TL3RDMB-850LM-5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	109	112	111	109	107	107	105	104	103	102	101	100	99	98	96	96	96	96
2	111	107	104	101	109	105	103	100	102	100	98	100	98	96	97	95	94	93	93	93	93
3	107	102	99	96	105	101	98	95	99	96	93	96	94	92	94	92	91	89	89	89	89
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86	86	86	86
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	83	83	83	83
6	97	91	86	83	96	90	86	83	88	85	82	87	84	82	86	83	81	80	80	80	80
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	78	77	77	77	77
8	91	84	80	77	90	84	80	77	83	79	76	82	79	76	81	78	76	75	75	75	75
9	89	81	77	74	88	81	77	74	80	77	74	79	76	74	79	76	73	73	73	73	73
10	86	79	75	72	85	79	74	72	78	74	72	77	74	71	77	73	71	70	70	70	70

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	773995
5°	717850
10°	553808
15°	365995
20°	231463
25°	113378
30°	41855
35°	11270
40°	2405
45°	992
50°	375
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 992 cd/sqm



TEST NUMBER: P886556

CATALOG NUMBER: ML310LSFL95FS1E-TIR4D25NFL-TL3RDMB-850LM-5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	286.3	28.6
10°-20°	449.8	44.9
20°-30°	227.4	22.7
30°-40°	35.1	3.5
40°-50°	2.9	0.3
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	963.4	96.2
0°-40°	998.5	99.7
0°-60°	1001.5	100.0
0°-90°	1001.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1001.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3530	
5°	3261	286
15°	1612	450
25°	469	227
35°	42	35
45°	3	3
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P886556  
CATALOG NUMBER: ML310LSFL95FS1E-TIR4D25NFL-TL3RDMB-850LM-5000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3529.7
2.5°	3473.9
5°	3261.2
7.5°	2919.0
10°	2487.2
12.5°	2029.2
15°	1612.2
17.5°	1272.0
20°	991.9
22.5°	723.4
25°	468.6
27.5°	292.7
30°	165.3
32.5°	89.5
35°	42.1
37.5°	16.8
40°	8.4
42.5°	5.3
45°	3.2
47.5°	2.1
50°	1.1
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)