

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: io LED

Report Number: A1913422A001

Luminaire Tested: **N/A**

Issue Date: 2019-08-14

**Test Information**

Test Method: LM-79-08  
Report Number: A1913422A001  
Test Lab: N/A  
Issue Date: 2019-08-14  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: N/A  
Description: LCR4089FSE010MW\*  
Light Source: N/A  
N/A  
Ballast/Driver: N/A  
N/A

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 869.2 lumens  
Efficiency: N/A  
Efficacy: 94.5 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.32  
Luminous Opening: Point Source (0m x 0m x 0m)  
CIE Type: Direct

Input Watts (W): 9.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: A1913422A001  
CATALOG NUMBER: N/A

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°    - - - 135°-315°



TEST NUMBER: A1913422A001

CATALOG NUMBER: N/A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76
3	94	84	77	71	91	83	76	71	80	74	70	77	73	68	75	71	67	65
4	86	76	68	62	84	74	67	61	72	65	60	70	64	60	67	63	59	57
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44
7	69	56	48	42	67	55	47	42	54	47	42	52	46	41	51	45	41	39
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35
9	60	47	39	34	59	47	39	34	45	39	34	44	38	34	43	38	33	32
10	56	44	36	31	55	43	36	31	42	35	31	41	35	31	40	35	30	29

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	Luminaire represents a point source (luminous area is zero).			
5°	No luminance values can be calculated.			
10°				
15°				
20°				
25°				
30°				
35°				
40°				
45°				
50°				
55°				
60°				
65°				
70°				
75°				
80°				
85°				



TEST NUMBER: A1913422A001  
 CATALOG NUMBER: N/A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	35.4	4.1
10°-20°	101.0	11.6
20°-30°	151.8	17.5
30°-40°	179.8	20.7
40°-50°	174.7	20.1
50°-60°	135.8	15.6
60°-70°	70.7	8.1
70°-80°	16.9	1.9
80°-90°	2.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.1	0.0
160°-170°	0.1	0.0
170°-180°	0.0	0.0
0°-30°	288.2	33.2
0°-40°	468.0	53.8
0°-60°	778.5	89.6
0°-90°	869.0	100.0
90°-120°	0.0	0.0
90°-150°	0.1	0.0
90°-180°	0.0	0.0
0°-180°	869.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	377	377	377	377	377	
5°	374	375	371	372	374	36
15°	361	358	359	358	361	101
25°	332	331	328	329	332	153
35°	290	290	287	286	290	181
45°	227	229	227	226	227	175
55°	152	155	152	152	152	135
65°	65	74	66	71	65	65
75°	11	14	12	14	11	12
85°	1	3	0	3	1	2
90°	0	0	0	0	0	0
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	1	1	1	0	1	0
175°	1	1	1	0	1	0
180°	0	0	0	0	0	



TEST NUMBER: A1913422A001

CATALOG NUMBER: N/A

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	376.6	376.6	376.6	376.6	376.6	376.6	376.6	376.6	376.6	376.6	376.6
0.5°	375.6	373.8	375.5	374.2	374.9	374.8	373.6	374.8	377.1	374.1	375.4
1°	375.9	373.2	375.1	376.0	374.3	374.3	375.2	373.3	375.7	372.3	374.3
1.5°	374.8	374.1	376.2	374.3	374.7	372.8	374.1	377.6	376.0	375.0	375.4
2°	373.9	375.5	373.9	373.4	375.3	376.0	372.4	373.9	375.5	375.2	374.6
2.5°	374.0	376.3	373.0	376.4	375.2	374.9	372.4	374.0	374.2	374.7	373.3
3°	373.4	375.0	375.1	374.8	374.5	373.6	371.3	374.7	374.2	375.3	372.3
3.5°	373.1	374.4	375.0	373.8	374.9	372.8	371.4	374.6	373.5	374.4	374.1
4°	373.5	374.7	374.0	375.4	374.8	371.7	370.7	375.1	374.2	372.2	373.8
4.5°	372.7	373.7	374.8	374.2	375.8	372.4	372.2	375.4	373.5	372.7	374.5
5°	373.6	373.4	373.3	375.7	374.6	371.9	373.6	375.8	371.3	373.8	373.0
5.5°	373.6	374.0	372.4	374.9	372.1	372.5	371.9	373.4	371.4	371.8	371.8
6°	372.0	372.4	372.5	372.7	372.2	371.8	370.7	372.4	370.7	371.7	371.7
6.5°	372.0	375.3	372.4	372.6	372.3	371.9	369.8	372.9	372.0	370.4	371.7
7°	371.9	372.9	372.9	371.4	370.9	370.4	369.1	370.1	371.5	370.5	370.5
7.5°	372.5	371.8	370.6	372.2	371.3	370.6	369.8	370.0	370.0	370.4	371.0
8°	371.4	370.6	369.4	371.5	371.1	370.0	370.4	371.7	369.9	370.2	368.6
8.5°	371.9	369.6	368.5	370.0	370.6	369.4	368.2	371.5	368.7	370.0	366.9
9°	373.0	371.9	370.0	369.6	369.8	370.0	366.6	368.9	367.9	369.9	366.5
9.5°	371.1	369.8	370.0	368.1	368.3	368.3	365.4	368.6	367.5	368.4	368.2
10°	369.0	369.4	367.2	368.0	368.1	366.2	368.7	366.8	365.9	364.6	367.4
10.5°	367.2	368.9	365.7	365.2	367.1	367.1	368.1	366.5	365.2	366.0	366.3
11°	368.9	367.2	366.5	366.1	366.0	365.4	364.5	366.0	365.7	364.8	366.4
11.5°	364.7	365.2	366.2	366.9	365.8	363.7	362.7	363.3	365.6	363.2	364.0
12°	365.4	364.8	364.8	365.2	365.3	363.8	363.8	364.0	364.1	363.7	362.6
12.5°	364.6	365.2	365.0	365.3	364.6	363.9	362.5	363.5	362.7	362.6	361.4
13°	362.4	363.4	362.3	362.8	364.1	363.0	359.5	362.3	363.5	361.7	361.4
13.5°	360.6	364.4	363.6	361.7	362.8	362.5	359.0	359.3	360.8	360.6	360.0
14°	361.8	362.3	360.4	359.2	361.9	360.5	358.1	358.6	361.0	359.9	358.1
14.5°	361.0	361.8	359.6	360.0	359.9	359.9	358.2	358.2	360.6	358.7	357.3
15°	360.9	361.7	359.0	359.0	357.8	358.8	356.8	357.1	358.7	357.0	357.7
15.5°	359.2	360.5	360.3	358.3	356.5	356.7	356.7	356.2	358.1	356.9	355.1
16°	355.0	359.5	357.6	356.4	356.5	356.4	354.8	355.4	357.4	355.5	354.6
16.5°	354.2	358.8	354.6	354.9	355.4	354.0	354.5	352.8	355.6	354.8	354.1
17°	356.2	357.6	355.7	355.2	354.3	352.5	355.4	352.0	354.7	352.1	351.8
17.5°	355.0	352.3	353.1	353.9	353.0	353.3	350.8	351.0	351.0	351.4	350.3
18°	353.9	352.5	354.3	353.1	352.7	349.6	350.2	349.8	349.2	351.0	348.7
18.5°	351.9	352.2	351.1	349.2	350.8	350.5	349.7	348.7	347.5	349.0	346.8
19°	349.8	350.0	348.2	349.4	350.2	347.0	347.4	347.6	348.7	347.8	346.4
19.5°	347.9	349.5	345.8	348.2	350.8	346.8	345.3	345.9	345.2	344.7	345.1
20°	347.2	346.0	345.7	345.6	346.8	344.9	344.2	344.3	343.4	343.7	343.0
20.5°	345.5	344.8	344.9	342.6	345.5	345.6	342.6	343.0	342.5	342.2	341.9
21°	343.2	344.6	343.6	342.8	343.8	343.9	342.6	343.1	340.4	340.7	341.2
21.5°	341.4	342.1	342.6	342.3	341.7	340.9	340.9	341.5	339.4	339.7	339.4
22°	340.5	340.6	341.2	341.3	340.0	339.8	339.6	338.1	337.6	338.2	338.1



TEST NUMBER: A1913422A001

CATALOG NUMBER: N/A

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
22.5°	340.2	341.6	339.5	339.5	338.2	340.0	337.7	337.4	336.5	335.8	337.0
23°	338.6	338.6	337.2	338.3	337.1	337.7	335.0	335.6	335.5	333.3	335.0
23.5°	336.0	338.4	337.0	336.8	334.7	335.4	333.6	334.0	332.4	334.0	333.2
24°	334.6	337.0	335.4	335.2	332.8	333.4	331.0	333.5	330.6	331.2	330.5
24.5°	332.9	333.6	332.0	333.6	332.5	331.7	328.7	331.0	329.0	329.2	328.0
25°	331.8	332.3	331.3	330.8	330.7	329.8	327.6	328.6	327.9	327.2	328.6
25.5°	330.4	329.0	328.9	329.0	329.0	327.9	326.0	326.4	326.2	325.7	326.1
26°	328.1	328.8	330.0	327.8	327.0	326.0	324.6	325.2	324.3	324.5	322.9
26.5°	325.6	326.4	328.1	325.5	325.0	322.4	322.2	324.2	322.6	323.7	323.2
27°	324.3	325.5	324.6	324.8	322.8	321.0	320.4	321.3	321.3	321.3	319.3
27.5°	322.0	322.2	323.5	323.1	321.4	320.4	319.1	319.4	319.2	319.8	317.4
28°	320.0	321.4	320.7	320.7	319.4	319.0	315.8	317.4	315.9	317.0	316.6
28.5°	318.0	319.8	317.8	318.2	317.4	316.9	314.9	315.2	313.7	315.2	314.0
29°	316.5	317.6	314.7	316.9	316.0	315.1	312.9	314.7	312.0	312.9	311.8
29.5°	314.8	314.7	313.4	315.2	314.0	312.1	310.5	310.6	309.1	310.3	311.2
30°	312.8	313.9	311.9	311.7	311.4	310.2	308.6	309.7	307.2	308.0	309.5
30.5°	311.0	311.7	310.2	310.1	309.7	309.5	306.4	307.6	305.2	306.2	306.1
31°	308.2	308.6	308.1	308.0	307.5	306.8	304.1	305.1	303.9	304.6	303.5
31.5°	305.4	307.3	306.2	307.6	305.5	305.0	302.8	302.6	301.9	302.6	302.1
32°	303.0	304.9	303.4	304.8	302.0	303.3	299.1	300.4	300.0	300.3	299.8
32.5°	301.1	303.1	301.7	302.4	299.6	300.0	298.2	298.2	297.2	298.4	298.0
33°	299.0	300.4	299.0	298.1	298.0	298.1	295.8	295.9	295.2	296.3	295.3
33.5°	296.9	298.0	296.6	296.7	295.8	295.4	293.5	293.9	293.2	294.1	293.0
34°	295.7	296.4	294.4	295.2	293.5	293.8	290.6	291.8	291.0	291.4	292.1
34.5°	292.2	294.8	292.1	291.9	291.2	291.8	288.2	290.0	288.8	289.9	289.4
35°	289.8	291.9	290.1	290.6	289.9	288.3	285.9	288.0	286.6	287.7	286.9
35.5°	287.3	289.1	287.9	287.7	286.8	286.2	284.2	285.4	284.4	285.4	284.1
36°	285.3	286.1	285.3	284.0	284.8	282.8	282.2	282.8	281.8	282.7	281.0
36.5°	282.0	283.0	282.7	281.7	281.5	280.9	279.4	280.1	279.5	279.6	278.3
37°	279.4	279.8	279.8	278.9	278.6	278.1	275.8	276.8	276.4	277.0	275.4
37.5°	276.5	277.5	277.2	276.1	276.5	275.1	274.0	274.2	274.1	274.3	273.1
38°	274.0	274.7	274.3	273.5	273.7	272.8	271.5	271.5	271.2	271.6	270.4
38.5°	271.7	272.1	271.4	269.7	270.8	270.2	268.0	268.7	268.0	269.1	268.0
39°	268.2	269.1	268.4	266.0	268.0	266.2	264.8	265.8	265.1	265.4	265.4
39.5°	264.1	265.3	265.2	263.0	265.1	263.2	262.0	263.1	262.4	262.6	262.3
40°	261.8	261.0	262.0	261.0	261.9	260.1	259.6	260.4	259.4	260.5	259.3
40.5°	258.6	258.1	259.1	258.0	258.9	256.9	256.6	257.4	256.2	257.9	256.6
41°	255.1	255.0	255.5	255.1	256.0	254.3	253.9	254.4	253.1	254.1	253.4
41.5°	251.6	251.9	251.8	251.7	252.5	251.4	250.2	250.9	250.1	250.6	249.7
42°	248.1	249.1	248.8	248.6	249.6	248.1	246.7	247.7	247.0	247.5	246.2
42.5°	245.1	245.8	245.6	245.4	246.2	245.4	243.7	244.2	243.8	244.1	243.0
43°	241.3	241.2	242.0	241.9	243.1	242.3	240.5	241.0	240.7	240.6	240.2
43.5°	237.6	237.8	238.6	237.7	239.7	238.7	237.4	237.5	237.4	237.3	236.9
44°	234.2	234.4	234.9	234.7	236.5	235.6	234.2	234.3	234.3	234.0	233.4
44.5°	230.2	230.9	231.2	232.1	232.6	231.9	230.4	230.9	230.8	230.6	229.6



TEST NUMBER: A1913422A001

CATALOG NUMBER: N/A

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
45°	226.8	227.2	227.4	226.8	229.0	228.4	227.4	227.6	227.2	227.3	225.8
45.5°	223.5	223.2	223.9	222.8	225.5	225.3	224.1	224.2	223.6	224.0	222.5
46°	220.2	220.0	220.3	219.9	222.2	221.8	220.6	221.1	220.4	220.9	219.5
46.5°	216.6	216.2	216.8	216.8	218.6	218.2	216.7	217.7	216.6	217.0	216.2
47°	212.8	212.5	213.3	213.0	214.9	214.6	212.9	214.0	213.1	213.1	212.8
47.5°	209.2	209.2	209.8	209.1	211.3	211.1	209.2	210.3	209.4	209.5	209.4
48°	205.3	206.0	206.0	205.5	207.6	207.4	205.7	206.4	205.9	205.9	206.1
48.5°	201.4	202.3	202.5	202.7	204.0	203.5	202.2	202.7	202.3	202.0	202.1
49°	197.7	198.2	198.8	198.8	199.9	199.8	198.6	198.9	198.8	198.2	197.9
49.5°	194.2	194.5	195.3	195.2	196.3	195.8	195.0	195.3	195.2	194.3	194.0
50°	190.4	191.0	191.2	191.3	192.5	192.1	191.2	191.8	191.3	190.4	190.4
50.5°	186.4	186.8	187.8	188.1	188.8	188.2	187.4	188.3	186.8	186.2	186.9
51°	182.8	183.4	184.1	183.6	185.0	184.2	183.8	184.4	182.9	182.4	183.2
51.5°	178.9	179.1	180.3	179.7	181.2	180.6	180.1	180.4	179.4	179.0	179.5
52°	175.4	175.6	176.2	176.3	177.4	177.2	176.0	176.5	175.6	175.3	175.7
52.5°	171.7	171.7	172.5	172.5	173.8	173.4	172.0	172.8	171.8	171.5	171.8
53°	167.8	168.1	168.6	168.6	170.0	169.7	168.1	168.6	167.4	167.9	167.7
53.5°	163.8	164.2	164.3	164.2	166.1	166.0	164.2	164.6	163.6	164.1	163.8
54°	159.8	160.1	159.9	160.5	162.4	162.1	160.4	160.6	159.7	160.0	159.4
54.5°	156.1	156.6	156.3	156.5	158.6	158.2	156.7	156.9	156.0	156.0	155.6
55°	152.2	152.7	152.6	152.6	154.6	154.3	153.0	153.0	152.2	152.2	152.2
55.5°	148.4	148.6	148.8	148.9	150.6	149.9	149.2	148.8	148.5	148.6	148.0
56°	144.4	144.7	145.1	145.3	146.4	145.5	145.2	144.8	144.7	144.7	143.9
56.5°	140.5	140.9	141.3	141.6	142.5	141.6	141.6	141.0	140.6	140.5	139.8
57°	136.4	137.1	137.3	137.6	138.2	137.7	137.5	136.8	136.6	136.3	136.0
57.5°	132.5	133.1	133.4	133.0	134.2	133.8	133.5	132.9	132.5	131.8	132.0
58°	128.3	128.9	129.4	129.0	129.9	130.0	129.3	128.9	128.6	127.9	128.0
58.5°	124.2	125.1	125.4	125.1	126.0	125.9	125.3	125.0	124.1	124.0	124.1
59°	119.7	121.3	121.3	121.4	122.1	121.9	121.2	120.9	120.0	120.0	119.9
59.5°	115.1	117.1	117.5	117.4	118.2	117.8	117.0	116.8	115.4	116.0	115.9
60°	110.8	113.0	113.3	113.6	114.1	113.8	113.0	112.9	111.2	112.3	112.0
60.5°	106.4	108.4	109.1	109.8	110.1	109.8	109.2	109.0	107.1	108.0	108.2
61°	101.8	103.9	104.9	105.3	106.1	105.7	105.3	104.8	102.5	103.5	104.3
61.5°	97.2	99.5	100.9	101.3	102.1	101.8	101.4	100.6	98.1	99.1	99.9
62°	92.4	94.9	96.9	97.2	97.9	97.7	97.4	96.5	93.6	95.1	95.7
62.5°	87.8	90.4	92.9	92.8	93.7	93.6	93.4	92.3	89.1	90.9	91.9
63°	83.1	86.2	88.7	89.1	89.7	89.7	89.4	88.2	84.6	86.7	88.1
63.5°	78.4	81.9	84.8	85.1	85.9	86.1	85.7	84.0	80.0	82.3	84.3
64°	73.7	77.5	80.9	81.0	81.9	81.9	81.7	79.9	75.4	78.0	80.5
64.5°	69.0	73.2	77.1	76.9	78.2	78.0	78.0	75.6	71.0	73.6	76.7
65°	64.7	68.8	73.1	73.3	74.3	74.3	74.1	71.4	66.4	69.4	72.8
65.5°	60.0	64.8	69.0	69.0	70.3	70.4	70.4	67.2	61.9	65.0	68.8
66°	55.6	60.5	65.1	65.2	66.6	66.4	66.5	62.9	57.4	60.7	64.9
66.5°	51.4	56.5	61.3	61.6	62.9	62.7	62.7	58.9	53.2	56.6	61.1
67°	47.3	52.6	57.7	57.7	59.3	59.0	59.0	55.2	48.8	52.7	57.3





TEST NUMBER: A1913422A001

CATALOG NUMBER: N/A

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
67.5°	43.1	48.8	54.2	54.0	55.6	55.4	55.5	51.2	44.6	48.9	53.8
68°	39.1	45.0	50.6	50.6	52.2	51.9	51.9	47.5	40.4	45.0	50.1
68.5°	35.2	41.5	47.0	46.9	48.5	48.4	48.3	43.7	36.5	41.2	46.6
69°	31.6	38.0	43.9	43.7	45.0	45.0	44.9	40.2	32.7	37.7	43.4
69.5°	28.0	34.8	40.4	40.3	41.6	41.7	41.7	37.1	29.2	34.3	40.2
70°	24.6	31.4	37.1	37.2	38.4	38.5	38.4	33.9	26.0	31.2	36.9
70.5°	21.6	28.4	33.8	34.0	35.2	35.4	35.3	30.8	23.1	28.3	33.7
71°	18.9	25.6	31.0	31.1	32.2	32.2	32.2	28.0	20.6	25.4	30.9
71.5°	16.9	23.2	28.0	28.2	29.3	29.4	29.4	25.6	18.5	23.1	28.1
72°	15.4	21.0	25.4	25.6	26.6	26.7	26.7	23.2	16.8	21.0	25.4
72.5°	14.4	19.0	22.9	23.0	24.1	24.2	24.2	21.2	15.7	19.1	23.1
73°	13.7	17.3	20.8	21.1	21.8	21.8	21.8	19.2	14.8	17.5	21.1
73.5°	13.0	15.7	18.7	19.0	19.7	19.9	19.8	17.6	14.2	16.0	19.1
74°	12.4	14.3	16.8	17.1	17.8	17.9	17.9	16.1	13.5	14.8	17.3
74.5°	11.7	13.1	15.2	15.5	15.9	16.2	16.3	14.8	12.7	13.7	15.8
75°	11.1	12.1	13.7	14.3	14.3	14.8	14.9	13.7	12.0	12.7	14.6
75.5°	10.4	11.2	12.6	13.2	13.0	13.7	13.7	12.6	11.3	11.9	13.4
76°	9.7	10.5	11.8	12.5	12.3	12.8	12.7	11.7	10.5	11.2	12.6
76.5°	9.0	9.8	11.2	11.9	11.6	12.2	12.1	10.9	9.9	10.4	11.8
77°	8.4	9.2	10.6	11.2	11.0	11.6	11.5	10.4	9.2	9.8	11.4
77.5°	7.8	8.7	10.0	10.8	10.4	10.9	10.9	9.6	8.7	9.2	10.7
78°	7.3	8.0	9.4	10.1	10.0	10.4	10.3	9.2	8.3	8.6	10.2
78.5°	6.8	7.4	8.9	9.6	9.4	9.7	9.7	8.4	7.3	8.2	9.4
79°	6.1	6.8	8.4	9.0	8.8	9.2	9.3	8.2	6.8	7.3	8.8
79.5°	5.6	6.3	7.9	8.5	8.5	8.5	8.6	7.2	6.2	6.7	8.4
80°	5.0	5.8	7.3	7.9	8.0	8.3	8.2	6.6	5.6	6.2	7.7
80.5°	4.6	5.3	6.7	7.4	7.2	7.5	7.4	6.2	5.1	5.4	7.2
81°	4.0	4.8	6.3	6.9	6.7	7.1	7.0	5.5	4.4	5.0	6.5
81.5°	3.5	4.3	5.8	6.3	6.2	6.5	6.3	5.1	4.1	4.4	6.3
82°	3.0	3.8	5.2	5.9	5.7	6.2	6.2	4.4	3.3	4.2	5.4
82.5°	2.5	3.3	4.8	5.4	5.1	5.4	5.4	4.1	3.0	3.3	5.0
83°	2.0	2.8	4.3	4.8	4.7	5.0	5.0	3.3	2.2	2.8	4.5
83.5°	1.5	2.5	4.0	4.4	4.2	4.4	4.4	3.0	2.0	2.2	4.1
84°	1.2	2.1	3.6	3.9	4.2	4.3	4.2	2.4	1.2	2.0	3.6
84.5°	1.0	1.9	3.1	3.4	3.2	3.4	3.4	2.0	0.7	1.7	3.2
85°	0.8	1.6	2.7	2.9	2.8	3.0	3.1	2.0	0.3	1.1	2.8
85.5°	0.8	1.3	2.4	2.5	2.2	2.4	2.6	1.3	0.1	0.9	2.2
86°	0.6	1.1	2.0	2.1	1.9	2.0	2.2	1.1	0.0	0.8	2.0
86.5°	0.5	0.9	1.6	1.7	1.3	1.9	2.0	0.8	0.0	0.3	1.9
87°	0.3	0.4	1.1	1.3	0.9	1.1	1.3	0.8	0.0	0.1	1.1
87.5°	0.2	0.4	1.0	0.9	0.8	0.8	1.0	0.3	0.0	0.0	1.0
88°	0.0	0.3	0.6	0.5	0.1	0.3	0.8	0.0	0.0	0.0	0.3
88.5°	0.0	0.0	0.3	0.2	0.0	0.0	0.2	0.0	0.0	0.0	0.0
89°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
89.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1913422A001

CATALOG NUMBER: N/A

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
91°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
91.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
93°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
93.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
94°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
94.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
96°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
96.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
101°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
101.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
103°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
103.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
104°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
104.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
106°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
106.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
108°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
108.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
109°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
109.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
111°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
111.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
112°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1913422A001

CATALOG NUMBER: N/A

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
113°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
113.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
114°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
114.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
116°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
116.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
118°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
118.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
119°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
119.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
121°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
121.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
123°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
123.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
124°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
124.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
126°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
126.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
128°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
128.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
129°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
129.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
131°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
131.5°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132°	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
133°	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
133.5°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
134°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
134.5°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1913422A001

CATALOG NUMBER: N/A

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
135°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135.5°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
136°	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
136.5°	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
138°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
138.5°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
139°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
139.5°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140.5°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
141°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
141.5°	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142°	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
143°	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
143.5°	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
144°	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.1	0.0	0.0
144.5°	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.1	0.0	0.0
145°	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.1	0.0	0.0
145.5°	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.1	0.0	0.0
146°	0.1	0.1	0.0	0.1	0.1	0.0	0.0	0.0	0.1	0.0	0.0
146.5°	0.1	0.1	0.0	0.1	0.1	0.0	0.0	0.0	0.1	0.0	0.0
147°	0.1	0.1	0.0	0.1	0.1	0.1	0.0	0.1	0.1	0.0	0.0
147.5°	0.1	0.1	0.0	0.1	0.1	0.1	0.0	0.1	0.1	0.0	0.0
148°	0.1	0.1	0.0	0.1	0.1	0.1	0.0	0.1	0.1	0.0	0.0
148.5°	0.1	0.1	0.0	0.1	0.1	0.1	0.0	0.1	0.1	0.0	0.1
149°	0.1	0.1	0.0	0.1	0.1	0.1	0.0	0.2	0.1	0.1	0.1
149.5°	0.1	0.1	0.0	0.1	0.2	0.1	0.0	0.2	0.1	0.1	0.0
150°	0.1	0.1	0.0	0.1	0.1	0.1	0.0	0.1	0.1	0.1	0.1
150.5°	0.1	0.1	0.0	0.1	0.1	0.1	0.0	0.1	0.2	0.1	0.1
151°	0.1	0.1	0.0	0.1	0.2	0.1	0.1	0.1	0.2	0.1	0.1
151.5°	0.1	0.1	0.0	0.1	0.2	0.2	0.1	0.1	0.2	0.2	0.1
152°	0.1	0.1	0.0	0.1	0.1	0.2	0.1	0.1	0.2	0.2	0.1
152.5°	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.1
153°	0.1	0.1	0.0	0.1	0.2	0.2	0.1	0.1	0.2	0.3	0.1
153.5°	0.1	0.1	0.0	0.1	0.3	0.1	0.1	0.1	0.2	0.3	0.2
154°	0.1	0.1	0.0	0.1	0.3	0.3	0.1	0.1	0.3	0.3	0.2
154.5°	0.1	0.1	0.0	0.1	0.3	0.3	0.1	0.1	0.3	0.3	0.1
155°	0.1	0.1	0.0	0.1	0.3	0.2	0.1	0.1	0.3	0.3	0.3
155.5°	0.1	0.1	0.0	0.1	0.3	0.2	0.2	0.1	0.3	0.3	0.3
156°	0.1	0.1	0.0	0.1	0.3	0.2	0.2	0.1	0.3	0.3	0.2
156.5°	0.1	0.1	0.0	0.1	0.3	0.2	0.2	0.1	0.3	0.3	0.2
157°	0.1	0.1	0.0	0.1	0.3	0.2	0.2	0.1	0.3	0.3	0.3



TEST NUMBER: A1913422A001

CATALOG NUMBER: N/A

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
157.5°	0.1	0.1	0.0	0.1	0.3	0.2	0.2	0.1	0.4	0.3	0.2
158°	0.1	0.1	0.0	0.1	0.3	0.2	0.2	0.1	0.4	0.3	0.2
158.5°	0.6	0.1	0.0	0.1	0.3	0.2	0.3	0.1	0.3	0.3	0.3
159°	0.6	0.1	0.0	0.1	0.4	0.2	0.2	0.1	0.5	0.3	0.3
159.5°	0.6	0.1	0.0	0.1	0.3	0.2	0.2	0.1	0.4	0.3	0.3
160°	0.6	0.1	0.0	0.1	0.5	0.2	0.3	0.1	0.5	0.3	0.3
160.5°	0.6	0.1	0.0	0.1	0.4	0.2	0.3	0.1	0.5	0.3	0.4
161°	0.6	0.1	0.0	0.1	0.4	0.2	0.3	0.1	0.5	0.3	0.4
161.5°	0.6	0.1	0.0	0.1	0.4	0.2	0.3	0.1	0.5	0.4	0.4
162°	0.6	0.1	0.0	0.1	0.4	0.2	0.3	0.1	0.5	0.4	0.4
162.5°	0.6	0.1	0.0	0.4	0.4	0.2	0.3	0.1	0.5	0.4	0.4
163°	0.6	0.1	0.0	0.5	0.5	0.2	0.3	0.1	0.5	0.4	0.5
163.5°	0.6	0.1	0.0	0.5	0.5	0.2	0.3	0.1	0.5	0.4	0.4
164°	0.6	0.1	0.0	0.5	0.5	0.2	0.3	0.1	0.5	0.5	0.4
164.5°	0.6	0.1	0.0	0.5	0.5	0.2	0.3	0.1	0.5	0.4	0.4
165°	0.6	0.1	0.0	0.5	0.6	0.2	0.3	0.1	0.6	0.4	0.4
165.5°	0.6	0.1	0.0	0.5	0.6	0.2	0.3	0.1	0.6	0.5	0.4
166°	0.6	0.1	0.0	0.5	0.5	0.2	0.5	0.1	0.6	0.5	0.4
166.5°	0.6	0.1	0.0	0.5	0.5	0.2	0.4	0.1	0.6	0.5	0.4
167°	0.6	0.1	0.1	0.5	0.5	0.2	0.4	0.1	0.6	0.5	0.5
167.5°	0.6	0.1	0.0	0.5	0.5	0.2	0.4	0.1	0.6	0.5	0.5
168°	0.6	0.1	0.0	0.5	0.6	0.2	0.4	0.1	0.6	0.5	0.5
168.5°	0.6	0.1	0.1	0.5	0.6	0.2	0.4	0.1	0.7	0.5	0.5
169°	0.6	0.1	0.1	0.5	0.6	0.2	0.5	0.1	0.7	0.5	0.6
169.5°	0.6	0.1	0.1	0.5	0.6	0.2	0.5	0.1	0.7	0.5	0.7
170°	0.6	0.1	0.1	0.5	0.6	0.2	0.5	0.1	0.7	0.5	0.9
170.5°	0.6	0.1	0.1	0.5	0.6	0.2	0.5	0.1	0.7	0.5	0.1
171°	0.6	0.1	0.1	0.5	0.6	0.2	0.5	0.1	0.7	0.5	0.7
171.5°	0.6	0.1	0.1	0.5	0.6	0.2	0.5	0.1	0.7	0.5	0.7
172°	0.6	0.1	0.1	0.5	0.6	0.2	0.5	0.1	0.7	0.5	0.2
172.5°	0.6	0.1	0.1	0.5	0.6	0.2	0.5	0.1	0.7	0.5	0.2
173°	0.6	0.1	0.1	0.5	0.6	0.2	0.5	0.1	0.7	0.5	0.5
173.5°	0.6	0.1	0.1	0.5	0.6	0.2	0.5	0.1	0.7	0.5	0.5
174°	0.6	0.1	0.1	0.5	0.6	0.2	0.6	0.1	0.7	0.5	0.5
174.5°	0.6	0.1	0.1	0.5	0.6	0.2	0.6	0.1	0.7	0.5	0.6
175°	0.6	0.1	0.1	0.5	0.6	0.2	0.5	0.1	0.7	0.5	0.5
175.5°	0.6	0.1	0.1	0.5	0.6	0.2	0.5	0.1	0.7	0.5	0.5
176°	0.6	0.1	0.1	0.5	0.6	0.2	0.5	0.1	0.7	0.5	0.5
176.5°	0.6	0.1	0.1	0.5	0.6	0.2	0.5	0.1	0.7	0.5	0.5
177°	0.6	0.1	0.1	0.5	0.6	0.2	0.6	0.1	0.7	0.5	0.5
177.5°	0.6	0.1	0.1	0.5	0.6	0.2	0.6	0.1	0.7	0.5	0.5
178°	0.6	0.1	0.1	0.5	0.6	0.2	0.7	0.1	0.2	0.5	0.5
178.5°	0.7	0.1	0.1	0.5	0.6	0.2	0.7	0.1	0.2	0.5	0.5
179°	0.7	0.1	0.1	0.5	0.6	0.2	0.4	0.1	0.3	0.5	0.3
179.5°	0.5	0.1	0.1	0.5	0.6	0.2	0.4	0.1	0.2	0.5	0.1



TEST NUMBER: A1913422A001

CATALOG NUMBER: N/A

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
180°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4



TEST NUMBER: A1913422A001

CATALOG NUMBER: N/A

**CANDELA DISTRIBUTION (continued):**

	247.5°	270°	292.5°	315°	337.5°	360°
0°	376.6	376.6	376.6	376.6	376.6	376.6
0.5°	375.1	375.8	375.5	372.4	375.0	375.6
1°	374.2	374.7	374.2	373.8	375.8	375.9
1.5°	375.0	374.7	373.6	374.4	374.8	374.8
2°	374.2	371.9	372.7	373.8	375.5	373.9
2.5°	371.6	374.3	373.2	372.9	374.4	374.0
3°	373.1	373.2	372.6	373.6	374.8	373.4
3.5°	371.2	372.6	372.6	373.6	375.5	373.1
4°	372.5	371.9	374.2	372.2	373.8	373.5
4.5°	373.7	371.9	373.0	371.6	374.7	372.7
5°	371.3	372.1	372.7	372.2	373.8	373.6
5.5°	371.7	370.6	370.7	371.7	373.8	373.6
6°	374.4	370.1	369.3	371.0	372.3	372.0
6.5°	370.8	372.9	371.4	370.7	371.6	372.0
7°	369.8	369.2	370.4	368.5	370.2	371.9
7.5°	366.5	370.0	369.9	369.3	370.8	372.5
8°	367.9	367.8	371.3	369.9	369.7	371.4
8.5°	369.9	369.9	369.5	369.4	370.6	371.9
9°	366.9	368.7	368.1	370.4	370.6	373.0
9.5°	367.8	367.5	368.5	367.2	369.7	371.1
10°	367.9	366.0	368.5	363.8	369.0	369.0
10.5°	365.8	364.2	366.6	365.1	367.6	367.2
11°	367.1	365.5	366.5	365.1	365.9	368.9
11.5°	365.4	364.3	364.2	362.7	366.0	364.7
12°	363.6	363.2	365.5	362.3	365.6	365.4
12.5°	363.9	363.0	363.5	361.7	364.2	364.6
13°	360.9	362.3	362.4	360.1	361.2	362.4
13.5°	360.1	360.9	360.1	358.3	362.0	360.6
14°	359.0	358.8	359.8	357.4	360.9	361.8
14.5°	358.0	359.3	359.2	355.1	359.0	361.0
15°	357.2	358.4	358.3	355.6	360.0	360.9
15.5°	356.3	356.7	356.1	354.6	359.8	359.2
16°	356.2	354.1	355.8	353.0	357.6	355.0
16.5°	353.9	353.4	354.2	353.5	355.6	354.2
17°	351.0	351.8	351.7	353.1	356.6	356.2
17.5°	352.3	351.2	350.1	351.0	355.2	355.0
18°	350.7	351.0	346.9	351.1	353.0	353.9
18.5°	348.7	348.7	345.6	348.7	351.4	351.9
19°	349.2	345.4	345.8	346.8	350.6	349.8
19.5°	343.6	345.2	345.2	346.2	348.3	347.9
20°	343.0	343.2	347.0	344.9	347.1	347.2
20.5°	343.7	342.5	344.0	343.8	344.3	345.5
21°	343.3	342.1	344.0	341.5	341.6	343.2
21.5°	341.1	340.1	339.7	339.7	341.6	341.4
22°	343.1	338.5	337.3	338.3	341.8	340.5



TEST NUMBER: A1913422A001

CATALOG NUMBER: N/A

**CANDELA DISTRIBUTION (continued):**

	247.5°	270°	292.5°	315°	337.5°	360°
22.5°	335.0	336.2	337.8	337.6	340.0	340.2
23°	335.3	334.5	336.4	335.2	339.1	338.6
23.5°	333.3	332.9	334.4	333.4	336.2	336.0
24°	331.7	331.2	332.7	333.1	335.3	334.6
24.5°	329.8	330.0	329.9	329.9	333.5	332.9
25°	327.9	329.4	328.5	329.3	330.8	331.8
25.5°	326.6	326.9	327.9	327.3	330.8	330.4
26°	324.7	324.5	326.7	324.7	327.8	328.1
26.5°	323.0	323.1	325.0	322.6	325.0	325.6
27°	321.1	321.3	322.2	322.0	323.0	324.3
27.5°	318.9	318.5	319.5	320.6	320.8	322.0
28°	317.6	316.7	317.3	318.9	319.9	320.0
28.5°	316.0	314.2	316.1	316.6	318.1	318.0
29°	313.0	312.9	313.9	314.2	315.3	316.5
29.5°	311.5	311.9	312.0	312.7	313.6	314.8
30°	309.1	309.6	309.8	309.8	311.7	312.8
30.5°	307.5	307.2	307.8	307.9	309.6	311.0
31°	304.5	304.6	305.9	305.4	307.9	308.2
31.5°	302.2	303.2	304.0	303.9	305.9	305.4
32°	300.2	301.8	301.8	301.3	304.1	303.0
32.5°	298.5	299.3	299.6	298.9	302.0	301.1
33°	296.5	297.0	297.6	297.5	299.3	299.0
33.5°	294.3	294.9	294.1	294.5	296.8	296.9
34°	292.0	291.4	291.8	292.4	294.3	295.7
34.5°	289.7	288.9	289.9	289.7	292.0	292.2
35°	287.1	286.5	287.4	287.2	289.7	289.8
35.5°	284.3	284.7	284.9	284.9	287.5	287.3
36°	281.9	281.9	281.8	282.6	284.6	285.3
36.5°	279.6	278.8	278.6	279.8	281.9	282.0
37°	276.7	275.5	276.0	277.4	278.9	279.4
37.5°	274.1	273.1	273.5	274.8	275.1	276.5
38°	271.4	270.3	270.6	272.0	272.7	274.0
38.5°	269.2	267.7	267.8	268.6	270.0	271.7
39°	266.3	264.3	264.5	265.1	267.3	268.2
39.5°	262.7	261.2	261.9	262.4	264.5	264.1
40°	259.5	258.2	258.7	259.3	261.6	261.8
40.5°	256.4	255.0	255.7	256.1	258.4	258.6
41°	253.8	251.8	252.1	252.9	255.6	255.1
41.5°	250.8	248.4	249.0	249.4	251.6	251.6
42°	247.4	245.6	245.9	245.6	247.9	248.1
42.5°	243.8	242.4	242.7	242.9	244.8	245.1
43°	240.4	238.9	239.0	239.2	241.3	241.3
43.5°	237.1	235.4	235.5	235.7	237.2	237.6
44°	233.9	232.3	232.2	232.0	234.1	234.2
44.5°	230.5	229.2	229.2	229.1	230.5	230.2





TEST NUMBER: A1913422A001

CATALOG NUMBER: N/A

**CANDELA DISTRIBUTION (continued):**

	247.5°	270°	292.5°	315°	337.5°	360°
45°	227.1	225.9	225.8	225.7	227.3	226.8
45.5°	223.7	222.9	222.3	222.2	223.4	223.5
46°	220.4	219.1	219.1	218.6	220.1	220.2
46.5°	216.8	215.4	215.4	215.2	216.0	216.6
47°	213.3	211.4	211.4	211.9	212.4	212.8
47.5°	209.5	207.8	208.0	208.3	208.6	209.2
48°	205.8	204.5	204.4	204.6	204.7	205.3
48.5°	202.0	200.9	200.8	200.7	200.7	201.4
49°	198.2	197.3	197.3	197.3	197.0	197.7
49.5°	194.3	193.5	193.7	193.1	193.5	194.2
50°	190.5	190.1	189.8	189.2	189.5	190.4
50.5°	186.6	186.5	186.0	185.5	185.9	186.4
51°	182.8	182.5	182.2	182.0	182.3	182.8
51.5°	178.9	178.9	178.8	178.0	178.8	178.9
52°	175.0	175.3	174.9	174.1	175.4	175.4
52.5°	171.2	171.5	171.0	170.4	171.6	171.7
53°	167.2	167.2	167.3	166.7	167.6	167.8
53.5°	163.3	162.5	163.4	163.1	163.8	163.8
54°	159.4	159.5	159.8	159.3	159.8	159.8
54.5°	155.9	155.2	155.7	155.5	156.0	156.1
55°	151.9	151.6	151.7	151.5	152.1	152.2
55.5°	148.0	147.6	147.8	147.5	148.3	148.4
56°	143.9	143.6	144.0	143.9	144.2	144.4
56.5°	139.8	139.5	140.1	139.9	140.2	140.5
57°	135.7	135.2	136.0	135.8	136.2	136.4
57.5°	131.9	131.2	131.9	131.5	132.4	132.5
58°	128.0	127.4	127.5	127.4	128.7	128.3
58.5°	124.1	123.5	123.5	123.8	124.9	124.2
59°	120.1	119.5	119.6	119.5	120.8	119.7
59.5°	116.1	115.1	115.5	115.4	116.6	115.1
60°	112.2	111.1	111.3	111.2	112.4	110.8
60.5°	108.1	107.0	107.3	107.2	108.1	106.4
61°	104.1	103.1	103.2	103.2	103.6	101.8
61.5°	100.2	99.0	99.1	99.1	99.3	97.2
62°	96.1	94.8	95.0	95.3	94.8	92.4
62.5°	92.2	90.7	90.8	91.1	90.4	87.8
63°	88.2	86.6	86.8	87.4	86.1	83.1
63.5°	84.1	82.5	82.8	83.4	81.7	78.4
64°	80.1	78.6	78.9	79.2	77.4	73.7
64.5°	76.2	74.8	75.0	75.5	73.0	69.0
65°	72.4	70.7	71.3	71.5	68.6	64.7
65.5°	68.5	67.0	67.4	67.6	64.4	60.0
66°	64.7	63.2	63.6	63.8	60.4	55.6
66.5°	60.8	59.5	59.8	60.1	56.5	51.4
67°	57.2	55.8	56.3	56.4	52.6	47.3



TEST NUMBER: A1913422A001

CATALOG NUMBER: N/A

**CANDELA DISTRIBUTION (continued):**

	247.5°	270°	292.5°	315°	337.5°	360°
67.5°	53.6	52.2	52.8	53.0	48.8	43.1
68°	49.8	48.7	49.2	49.5	45.3	39.1
68.5°	46.5	45.2	45.8	46.0	41.4	35.2
69°	43.0	41.7	42.4	42.6	38.0	31.6
69.5°	39.9	38.5	39.0	39.3	34.6	28.0
70°	36.8	35.3	35.8	36.1	31.6	24.6
70.5°	33.8	32.2	32.8	32.9	28.4	21.6
71°	30.8	29.4	29.8	30.0	25.6	18.9
71.5°	28.1	26.7	27.0	27.2	23.1	16.9
72°	25.6	24.2	24.4	24.5	21.0	15.4
72.5°	23.2	21.9	22.1	22.2	19.0	14.4
73°	21.0	19.6	20.2	20.0	17.2	13.7
73.5°	19.0	17.6	18.2	18.0	15.6	13.0
74°	17.3	16.0	16.6	16.2	14.2	12.4
74.5°	15.8	14.6	15.1	14.6	13.0	11.7
75°	14.6	13.8	14.0	13.4	12.0	11.1
75.5°	13.6	13.2	13.0	12.4	11.0	10.4
76°	12.8	12.5	12.5	11.7	10.4	9.7
76.5°	12.1	12.0	11.8	11.2	9.8	9.0
77°	11.6	11.3	11.2	10.6	9.1	8.4
77.5°	11.0	10.7	10.6	10.0	8.5	7.8
78°	10.4	10.2	10.1	9.4	7.9	7.3
78.5°	9.7	9.6	9.5	8.9	7.4	6.8
79°	9.3	9.0	8.9	8.4	6.8	6.1
79.5°	8.6	8.4	8.4	7.8	6.3	5.6
80°	8.3	7.9	7.8	7.2	5.7	5.0
80.5°	7.6	7.3	7.3	6.8	5.1	4.6
81°	7.1	6.8	6.8	6.2	4.7	4.0
81.5°	6.4	6.2	6.2	5.6	4.1	3.5
82°	6.1	5.8	5.6	5.2	3.7	3.0
82.5°	5.3	5.2	5.2	4.7	3.2	2.5
83°	4.9	4.7	4.7	4.3	2.7	2.0
83.5°	4.2	4.2	4.1	3.8	2.5	1.5
84°	4.2	3.7	3.6	3.4	2.1	1.2
84.5°	3.2	3.2	3.1	3.1	1.8	1.0
85°	2.8	2.7	2.7	2.7	1.6	0.8
85.5°	2.3	2.3	2.2	2.3	1.3	0.8
86°	2.0	1.8	1.9	1.8	0.9	0.6
86.5°	1.5	1.5	1.5	1.5	1.1	0.5
87°	1.0	1.1	1.1	1.1	0.7	0.3
87.5°	0.8	0.7	0.8	0.8	0.5	0.2
88°	0.2	0.4	0.3	0.5	0.3	0.0
88.5°	0.0	0.2	0.1	0.1	0.1	0.0
89°	0.0	0.0	0.0	0.0	0.0	0.0
89.5°	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1913422A001

CATALOG NUMBER: N/A

**CANDELA DISTRIBUTION (continued):**

	247.5°	270°	292.5°	315°	337.5°	360°
90°	0.0	0.0	0.0	0.0	0.0	0.0
90.5°	0.0	0.0	0.0	0.0	0.0	0.0
91°	0.0	0.0	0.0	0.0	0.0	0.0
91.5°	0.0	0.0	0.0	0.0	0.0	0.0
92°	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0
93°	0.0	0.0	0.0	0.0	0.0	0.0
93.5°	0.0	0.0	0.0	0.0	0.0	0.0
94°	0.0	0.0	0.0	0.0	0.0	0.0
94.5°	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0
95.5°	0.0	0.0	0.0	0.0	0.0	0.0
96°	0.0	0.0	0.0	0.0	0.0	0.0
96.5°	0.0	0.0	0.0	0.0	0.0	0.0
97°	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0
98°	0.0	0.0	0.0	0.0	0.0	0.0
98.5°	0.0	0.0	0.0	0.0	0.0	0.0
99°	0.0	0.0	0.0	0.0	0.0	0.0
99.5°	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0
100.5°	0.0	0.0	0.0	0.0	0.0	0.0
101°	0.0	0.0	0.0	0.0	0.0	0.0
101.5°	0.0	0.0	0.0	0.0	0.0	0.0
102°	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0
103°	0.0	0.0	0.0	0.0	0.0	0.0
103.5°	0.0	0.0	0.0	0.0	0.0	0.0
104°	0.0	0.0	0.0	0.0	0.0	0.0
104.5°	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0
105.5°	0.0	0.0	0.0	0.0	0.0	0.0
106°	0.0	0.0	0.0	0.0	0.0	0.0
106.5°	0.0	0.0	0.0	0.0	0.0	0.0
107°	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0
108°	0.0	0.0	0.0	0.0	0.0	0.0
108.5°	0.0	0.0	0.0	0.0	0.0	0.0
109°	0.0	0.0	0.0	0.0	0.0	0.0
109.5°	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0
110.5°	0.0	0.0	0.0	0.0	0.0	0.0
111°	0.0	0.0	0.0	0.0	0.0	0.0
111.5°	0.0	0.0	0.0	0.0	0.0	0.0
112°	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1913422A001

CATALOG NUMBER: N/A

**CANDELA DISTRIBUTION (continued):**

	247.5°	270°	292.5°	315°	337.5°	360°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0
113°	0.0	0.0	0.0	0.0	0.0	0.0
113.5°	0.0	0.0	0.0	0.0	0.0	0.0
114°	0.0	0.0	0.0	0.0	0.0	0.0
114.5°	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0
115.5°	0.0	0.0	0.0	0.0	0.0	0.0
116°	0.0	0.0	0.0	0.0	0.0	0.0
116.5°	0.0	0.0	0.0	0.0	0.0	0.0
117°	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0
118°	0.0	0.0	0.0	0.0	0.0	0.0
118.5°	0.0	0.0	0.0	0.0	0.0	0.0
119°	0.0	0.0	0.0	0.0	0.0	0.0
119.5°	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0
120.5°	0.0	0.0	0.0	0.0	0.0	0.0
121°	0.0	0.0	0.0	0.0	0.0	0.0
121.5°	0.0	0.0	0.0	0.0	0.0	0.0
122°	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0
123°	0.0	0.0	0.0	0.0	0.0	0.0
123.5°	0.0	0.0	0.0	0.0	0.0	0.0
124°	0.0	0.0	0.0	0.0	0.0	0.0
124.5°	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0
125.5°	0.0	0.0	0.0	0.0	0.0	0.0
126°	0.0	0.0	0.0	0.0	0.0	0.0
126.5°	0.0	0.0	0.0	0.0	0.0	0.0
127°	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.1	0.0	0.0	0.0	0.0
128°	0.0	0.1	0.0	0.0	0.0	0.0
128.5°	0.0	0.1	0.0	0.0	0.0	0.0
129°	0.0	0.1	0.0	0.0	0.0	0.0
129.5°	0.0	0.1	0.0	0.0	0.0	0.0
130°	0.0	0.1	0.0	0.0	0.0	0.0
130.5°	0.0	0.1	0.0	0.0	0.0	0.0
131°	0.0	0.2	0.0	0.0	0.0	0.0
131.5°	0.0	0.1	0.0	0.0	0.0	0.1
132°	0.0	0.2	0.0	0.0	0.0	0.0
132.5°	0.0	0.2	0.0	0.0	0.0	0.0
133°	0.0	0.2	0.0	0.0	0.0	0.0
133.5°	0.0	0.2	0.0	0.0	0.1	0.1
134°	0.0	0.3	0.0	0.0	0.1	0.1
134.5°	0.0	0.3	0.0	0.0	0.1	0.1



TEST NUMBER: A1913422A001

CATALOG NUMBER: N/A

**CANDELA DISTRIBUTION (continued):**

	247.5°	270°	292.5°	315°	337.5°	360°
135°	0.0	0.3	0.1	0.1	0.2	0.1
135.5°	0.0	0.3	0.1	0.1	0.2	0.1
136°	0.0	0.2	0.1	0.1	0.2	0.1
136.5°	0.0	0.2	0.1	0.1	0.2	0.1
137°	0.0	0.2	0.1	0.1	0.2	0.1
137.5°	0.0	0.2	0.1	0.1	0.2	0.1
138°	0.0	0.2	0.1	0.1	0.2	0.1
138.5°	0.0	0.2	0.1	0.1	0.2	0.1
139°	0.0	0.2	0.1	0.1	0.2	0.1
139.5°	0.0	0.2	0.1	0.2	0.2	0.1
140°	0.0	0.2	0.1	0.2	0.2	0.1
140.5°	0.0	0.2	0.1	0.1	0.2	0.1
141°	0.0	0.2	0.1	0.1	0.2	0.1
141.5°	0.0	0.2	0.1	0.1	0.2	0.1
142°	0.0	0.2	0.1	0.1	0.2	0.1
142.5°	0.0	0.2	0.1	0.1	0.2	0.1
143°	0.0	0.2	0.1	0.1	0.2	0.1
143.5°	0.0	0.2	0.1	0.1	0.2	0.1
144°	0.0	0.2	0.1	0.1	0.2	0.1
144.5°	0.0	0.2	0.1	0.1	0.2	0.1
145°	0.0	0.2	0.1	0.1	0.2	0.1
145.5°	0.0	0.2	0.1	0.1	0.2	0.1
146°	0.0	0.2	0.1	0.1	0.2	0.1
146.5°	0.0	0.2	0.1	0.1	0.2	0.1
147°	0.0	0.2	0.1	0.1	0.2	0.1
147.5°	0.0	0.2	0.1	0.1	0.2	0.1
148°	0.1	0.2	0.1	0.1	0.2	0.1
148.5°	0.1	0.2	0.1	0.1	0.2	0.1
149°	0.0	0.2	0.1	0.1	0.2	0.1
149.5°	0.0	0.2	0.1	0.1	0.2	0.1
150°	0.1	0.2	0.1	0.1	0.2	0.1
150.5°	0.1	0.2	0.1	0.1	0.2	0.1
151°	0.1	0.2	0.1	0.1	0.2	0.1
151.5°	0.1	0.2	0.1	0.1	0.2	0.1
152°	0.1	0.2	0.1	0.1	0.2	0.1
152.5°	0.1	0.2	0.1	0.1	0.2	0.1
153°	0.1	0.2	0.1	0.1	0.2	0.1
153.5°	0.1	0.2	0.1	0.1	0.2	0.1
154°	0.1	0.2	0.1	0.1	0.2	0.1
154.5°	0.1	0.2	0.1	0.1	0.2	0.1
155°	0.1	0.2	0.1	0.1	0.2	0.1
155.5°	0.1	0.2	0.1	0.1	0.2	0.1
156°	0.1	0.2	0.1	0.1	0.2	0.1
156.5°	0.1	0.2	0.1	0.1	0.2	0.1
157°	0.1	0.2	0.1	0.1	0.2	0.1



TEST NUMBER: A1913422A001

CATALOG NUMBER: N/A

**CANDELA DISTRIBUTION (continued):**

	247.5°	270°	292.5°	315°	337.5°	360°
157.5°	0.1	0.2	0.1	0.1	0.2	0.1
158°	0.1	0.2	0.1	0.1	0.2	0.1
158.5°	0.1	0.2	0.1	0.1	0.2	0.6
159°	0.1	0.2	0.1	0.1	0.2	0.6
159.5°	0.1	0.2	0.1	0.1	0.2	0.6
160°	0.1	0.2	0.1	0.1	0.2	0.6
160.5°	0.1	0.2	0.2	0.1	0.2	0.6
161°	0.1	0.2	0.3	0.1	0.2	0.6
161.5°	0.1	0.2	0.2	0.1	0.2	0.6
162°	0.1	0.2	0.2	0.1	0.2	0.6
162.5°	0.1	0.2	0.1	0.1	0.2	0.6
163°	0.1	0.2	0.5	0.1	0.2	0.6
163.5°	0.1	0.2	0.4	0.1	0.2	0.6
164°	0.1	0.2	0.4	0.1	0.2	0.6
164.5°	0.1	0.2	0.3	0.1	0.2	0.6
165°	0.1	0.2	0.3	0.1	0.2	0.6
165.5°	0.1	0.2	0.3	0.1	0.2	0.6
166°	0.1	0.2	0.3	0.1	0.2	0.6
166.5°	0.1	0.2	0.3	0.1	0.2	0.6
167°	0.1	0.2	0.3	0.1	0.2	0.6
167.5°	0.1	0.2	0.3	0.1	0.2	0.6
168°	0.1	0.2	0.3	0.1	0.2	0.6
168.5°	0.1	0.2	0.3	0.1	0.2	0.6
169°	0.1	0.2	0.3	0.1	0.2	0.6
169.5°	0.1	0.2	0.3	0.1	0.2	0.6
170°	0.1	0.2	0.3	0.1	0.2	0.6
170.5°	0.1	0.2	0.3	0.1	0.2	0.6
171°	0.1	0.2	0.3	0.1	0.2	0.6
171.5°	0.1	0.2	0.3	0.1	0.2	0.6
172°	0.1	0.2	0.3	0.1	0.2	0.6
172.5°	0.1	0.2	0.3	0.1	0.2	0.6
173°	0.1	0.2	0.3	0.1	0.2	0.6
173.5°	0.1	0.2	0.3	0.1	0.2	0.6
174°	0.1	0.2	0.3	0.1	0.2	0.6
174.5°	0.1	0.2	0.3	0.1	0.2	0.6
175°	0.1	0.2	0.3	0.1	0.2	0.6
175.5°	0.1	0.2	0.3	0.1	0.2	0.6
176°	0.1	0.2	0.3	0.1	0.2	0.6
176.5°	0.1	0.2	0.3	0.1	0.2	0.6
177°	0.1	0.2	0.3	0.1	0.2	0.6
177.5°	0.1	0.2	0.3	0.1	0.2	0.6
178°	0.1	0.2	0.3	0.1	0.2	0.6
178.5°	0.1	0.2	0.3	0.1	0.2	0.7
179°	0.1	0.2	0.3	0.1	0.2	0.7
179.5°	0.1	0.2	0.3	0.1	0.2	0.5



TEST NUMBER: A1913422A001

CATALOG NUMBER: N/A

**CANDELA DISTRIBUTION (continued):**

	247.5°	270°	292.5°	315°	337.5°	360°
180°	0.4	0.4	0.4	0.4	0.4	0.4

(END OF REPORT)