

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P886898

Luminaire Tested: ML412LSFL95FS1E-TIR4D40FL-TL4RDMW-1020LM-4000K

Issue Date: 7/9/2024

Test Information

Test Method: LM-79-2019
Report Number: P886898
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2402-314-39)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/9/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML412LSFL95FS1E-TIR4D40FL-TL4RDMW-1020LM-4000K
Description: 4IN ROUND ML FLEX, SELECTABLE CCT, WITH 40D TIR, MATTE WHITE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 95CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1320.5 lumens
Efficiency: N/A
Efficacy: 75.0 lumens/watt
Spacing Criteria (0/90/45): 0.67 / 0.67 / 0.64
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 17.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P886898
CATALOG NUMBER: ML412LSFL95FS1E-TIR4D40FL-TL4RDMW-1020LM-4000K

Luminous Intensity Polar Plot





TEST NUMBER: P886898

CATALOG NUMBER: ML412LSFL95FS1E-TIR4D40FL-TL4RDMW-1020LM-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	99	98	97	95	95	95	92	90																	
	1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	92	90	88	86	86	86	83	82																	
	2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	93	92	90	90	90	88	86	84	82	82	82	80	78																	
	3	105	100	96	92	104	99	95	92	96	93	90	94	91	89	92	89	88	86	86	86	83	82	80	78	78	76	75	75																	
	4	101	95	90	87	100	94	90	86	92	88	85	90	87	84	88	86	83	82	82	82	80	78	76	75	75	75	75	75																	
	5	97	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	78	78	78	76	75	73	72	72	72	72	72																	
	6	94	87	82	78	93	86	81	78	84	80	77	83	80	77	82	79	76	75	75	75	76	76	76	76	76	76	76	76																	
	7	90	83	78	74	89	82	78	74	81	77	74	80	76	73	79	76	73	72	72	72	76	76	76	76	76	76	76	76																	
	8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69	76	76	76	76	76	76	76	76																	
	9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66	66	66	76	76	76	76	76	76	76	76																	
	10	81	73	69	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64	64	64	76	76	76	76	76	76	76	76																	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	357727
5°	347616
10°	313109
15°	266107
20°	202458
25°	114621
30°	46275
35°	9260
40°	3349
45°	2425
50°	2322
55°	2430
60°	2566
65°	2539
70°	2488
75°	2478
80°	2486
85°	2406

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 2594 cd/sqm



TEST NUMBER: P886898

CATALOG NUMBER: ML412LSFL95FS1E-TIR4D40FL-TL4RDMW-1020LM-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	258.2	19.6
10°-20°	570.9	43.2
20°-30°	391.5	29.7
30°-40°	62.3	4.7
40°-50°	11.3	0.9
50°-60°	10.3	0.8
60°-70°	8.6	0.6
70°-80°	5.5	0.4
80°-90°	1.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1220.6	92.4
0°-40°	1282.9	97.2
0°-60°	1304.5	98.8
0°-90°	1320.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1320.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2900	
5°	2808	258
15°	2084	571
25°	842	392
35°	62	62
45°	14	11
55°	11	10
65°	9	9
75°	5	5
85°	2	2
90°	0	



TEST NUMBER: P886898

CATALOG NUMBER: ML412LSFL95FS1E-TIR4D40FL-TL4RDMW-1020LM-4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2900.2
2.5°	2891.5
5°	2807.5
7.5°	2676.6
10°	2499.9
12.5°	2300.6
15°	2083.9
17.5°	1842.2
20°	1542.4
22.5°	1188.8
25°	842.2
27.5°	563.2
30°	324.9
32.5°	149.9
35°	61.5
37.5°	33.8
40°	20.8
42.5°	15.6
45°	13.9
47.5°	13.0
50°	12.1
52.5°	12.1
55°	11.3
57.5°	11.3
60°	10.4
62.5°	9.5
65°	8.7
67.5°	7.8
70°	6.9
72.5°	6.1
75°	5.2
77.5°	4.3
80°	3.5
82.5°	2.6
85°	1.7
87.5°	0.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)