

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P886796

Luminaire Tested: ML310LSFLD2W1E-TIR4D40FL-TL3RDMB-600LM-2700K

Issue Date: 7/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P886796
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2402-314-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML310LSFLD2W1E-TIR4D40FL-TL3RDMB-600LM-2700K
Description: 3IN ROUND ML FLEX, SELECTABLE CCT, WITH 40D TIR, MATTE BLACK TRIM
Light Source: (1) D2W LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 725.5 lumens
Efficiency: N/A
Efficacy: 76.4 lumens/watt
Spacing Criteria (0/90/45): 0.67 / 0.67 / 0.62
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct


Input Watts (W): 9.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P886796

CATALOG NUMBER: ML310LSFLD2W1E-TIR4D40FL-TL3RDDB-600LM-2700K

Luminous Intensity Polar Plot





TEST NUMBER: P886796

CATALOG NUMBER: ML310LSFLD2W1E-TIR4D40FL-TL3RDMB-600LM-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96	96	96	96
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92	92	92	92
3	106	101	97	94	105	100	96	93	97	94	92	95	93	91	93	91	89	88	88	88	88
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84	84	84	84
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81	81	81	81
6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77	77	77	77
7	92	85	80	77	91	84	80	77	83	79	76	82	78	76	81	78	76	74	74	74	74
8	89	81	77	74	88	81	77	73	80	76	73	79	75	73	78	75	73	72	72	72	72
9	86	78	74	71	85	78	74	71	77	73	70	76	73	70	76	72	70	69	69	69	69
10	83	75	71	68	82	75	71	68	74	70	68	74	70	67	73	70	67	66	66	66	66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	369313
5°	359057
10°	328295
15°	280637
20°	204511
25°	110377
30°	37499
35°	7094
40°	1975
45°	403
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 403 cd/sqm



TEST NUMBER: P886796

CATALOG NUMBER: ML310LSFLD2W1E-TIR4D40FL-TL3RDMB-600LM-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.7	20.8
10°-20°	335.3	46.2
20°-30°	211.4	29.1
30°-40°	26.8	3.7
40°-50°	1.5	0.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	697.3	96.1
0°-40°	724.1	99.8
0°-60°	725.5	100.0
0°-90°	725.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	725.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1684	
5°	1631	151
15°	1236	335
25°	456	211
35°	26	27
45°	1	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P886796

CATALOG NUMBER: ML310LSFLD2W1E-TIR4D40FL-TL3RDMB-600LM-2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1684.2
2.5°	1675.3
5°	1631.2
7.5°	1562.6
10°	1474.4
12.5°	1362.8
15°	1236.2
17.5°	1076.2
20°	876.4
22.5°	656.5
25°	456.2
27.5°	287.3
30°	148.1
32.5°	62.4
35°	26.5
37.5°	13.9
40°	6.9
42.5°	2.5
45°	1.3
47.5°	0.6
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)